



* Representative image

Connector, Parallel Groove

by ANDERSON
Catalog ID: XP050050

Four Bolt Bronze Cross Parallel Groove Connector

- Center spacer has 2 grooves for parallel and perpendicular tap connections.

Product Details

General

Bolt Head Type	Hex
Bolt Installation Torque (Recommended)	0 ft-lbs
Cover Available	No
Inhibitor Loaded	No
Material	Bronze
Material - Body	Bronze Alloy
Material - Body Halves	Bronze Alloy
Material - Bolt	Silicon Bronze
Material - Bottom Member	Bronze Alloy
Material - Hardware	Silicon Bronze
Material - Spacer	Copper Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Four Bolt
UPC	096359353812

Dimensions

Bolt Diameter	0.380 in
Diameter - Bolt	0.38 in
Weight	1.372 lb

Conductor Related

Conductor Diameter (Tap) - Maximum	0.813 in
Conductor Diameter (Tap) - Minimum	0.46 in
Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.46 in
Conductor Diameter Range	0.46 - 0.813

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com