

# Yoke Plate, Crescent

by ANDERSON  
Catalog ID: YPC4024534

Yoke Plate, 42 deg. Angle Single String, Ductile Iron, UTS 40,000 lb



**Oh No!**  
IMAGE COMING SOON

## Product Details

### General

Material	Ductile Iron
Number of Bolt Holes	0
Series	YPC Series
Strength Rating - Ultimate	40000 lb
Strength Rating - Ultimate Body	0 lb
Type	Suspension Angle Yokes
UPC	096359344773

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	1.25 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	7.065 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	6.860 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

**For further technical assistance, please contact us**

**Domestic Customer Service**

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscshubbell.com](mailto:hpscshubbell.com)

**International Customer Service**

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)