

Yoke Plate, Crescent

by ANDERSON
Catalog ID: YPC509378

Yoke Plate, 15-75 deg. Angle Single String, Steel, UTS 50,000 lb



Oh No!
IMAGE COMING SOON

Product Details

General

Material	Steel
Number of Bolt Holes	0
Series	YPC Series
Strength Rating - Ultimate	50000 lb
Strength Rating - Ultimate Body	0 lb
Type	Suspension Angle Yokes
UPC	096359344780

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Insulator Attachment Holes	1.25 in
Diameter - Pin	0 in
Insulator / Conductor Hole Spacing	18 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Length - Coupling	12.44 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Thickness	0.75 in
Weight	30.380 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Diameter - Conductor Attachment Holes

1.25 in

Logistics

Pallet Quantity

72 EA

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com