

TRA4– Period Pole Mount Arm

TYPE



TRA4

1. ARM

2. COLOR

1. ARM

- TRA4 Single arm.
- TRA4-2 Twin arm.

2. COLOR


- BLS** Black Gloss Smooth
- BLT** Black Matte Textured
- DBS** Dark Bronze Gloss Smooth
- DBT** Dark Bronze Matte Textured
- GTT** Graphite Matte Textured
- LGS** Light Grey Gloss Smooth
- LGT** Light Grey Matte Textured
- PSS** Platinum Silver Smooth
- VGT** Verde Green Textured
- WHS** White Gloss Smooth
- WHT** White Matte Textured

Color Option

- CC*** Custom Color


** Consult factory for custom color, marine and corrosive finish options*

DIMENSIONS



TRA4-2
EPA: 11125
WT: 19 LBS

TRA4-2 (4" pole)



TRA4
EPA: 08235
WT: 19 LBS

TRA4 (4" pole)

SPECIFICATIONS

The arm shall be one piece cast aluminum construction. The arm shall be prewired with a quick connector for easy installation.

The arm shall have a cast aluminum fitter welded to the top of the arm(s) for attaching the fixture. The fixture shall be mounted with three stainless steel bolts through the top of the arm fitter into the fixture. The attachment point shall have a silicone pad for sealing the fixture to arm connection.

The arm shall bolt to a 4"/100mm diameter pole.

JOB _____
 TYPE _____
 NOTES _____

