

Type:
Job:
Fixture Catalog number:

Fixture and Finish

Mounting Options:

Ordered Separately from Fixture
See pages 2-4

Approvals:

Date:
Page: 1 of 4

Specifications

Hood: Die-cast aluminum.

Husk: Die-cast aluminum.

Globe: (EL121) Diffused-coated glass, threaded to husk, with neoprene gasket.


Stem: 1/2" schedule 40 aluminum pipe with 1/2" NPT and solid brass locknut for mounting.

Socket: Porcelain medium base.

Wiring: No. 18AWM rated 105°C.

Finish: Super TGIC thermoset polyester powder coat paint, 2.5 mil nominal thickness, applied over a titanated zirconium conversion coating; 2500 hour salt spray test endurance rating. Standard colors are Black (**BL**), Dark Bronze (**DB**), and Verde Green (**GR**).

Certification: UL Listed to U.S. and Canadian safety standards for wet locations.



ORDERING INFORMATION

Fixture	Finish
<input type="checkbox"/> EL121BL	Black
<input type="checkbox"/> EL121DB	Dark Bronze
<input type="checkbox"/> EL121GR	Verde Green

Wattage / Lamp

75W
A-19
Incandescent



KIM LIGHTING RESERVES THE RIGHT TO CHANGE SPECIFICATIONS WITHOUT NOTICE.