

**Type:**  
**Job:**  
**Ordering Example:**

**1A / RA173 / 150PMH277 / LG-P / HA01S-TM1**

Mtg    Fixture    Elec Module    Finish    Option

**Ordering Information**

Always refer to the specific luminaire catalog, and the ordering information page within that catalog. Place the optional Heritage Arm catalog number as an "Option" following the Fixture catalog numbers.


**Approvals:**

**Date:**  
**Page: 1 of 2**

**Specifications**


**HA01L**

**Large Arm**  
 for Kim RA25, AE21,  
 and BE21 and LET26  
 fixtures only.



**HA01S**

**Small Arm**  
 for Kim RA17, AE17,  
 and BE17, and  
 LET19 fixtures only.



**Arm:** One-piece, extruded aluminum, pole top mounted crook arm with cast hub and cover. Crook Arm slip fits into, and is secured to an internal extruded pole adaptor with stainless steel allen-head cap bolts. Stainless steel bolts secure cover to internal extruded pole adaptor. Arm-to-luminaire attachment is by concealed stainless steel bolts, projecting into the crook arm to secure the mounting. Small arm utilizes 3/8" studs and large arm utilizes 1/2" studs.

**Finish:** Premium Super TGIC thermoset polyester powder coating, 2.5 mil nominal thickness, applied over a titanated zirconium conversion coating. Arm color is always provided to match the selected pole and luminaire color.

**Optional Finial not available.**

**Optional Wall Mount not available.**

**Optional Tenon Mount (See page 2)**

**NOTES:**

- 1) Refer to page **75** of Arms and Poles Selection Guide for wind map and application information.
- 2) Refer to pages **78** and **79** of Arms and Poles Selection Guide for luminaire Optical Centerline Matrix.
- 3) A regularly scheduled maintenance program must be established to insure paint coating is intact, corrosion or structural damage has not occurred, and all mounting rods, nuts and bolts are tight. Failure to do so could lead to damage or serious personal injury.

Type:

Job:

Page: 2 of 2

## Standard Features


ERA® Arm	Arm/Fixture	Mounting Configuration
HA01		Plan View: ●-
		Cat. No.: <b>1A</b>
	<b>Large</b>	EPA:
	HA01L - RA25	1.8
	HA01L - AE21/BE21	1.7
	HA01L - LET26	1.9
	<b>Small</b>	
HA01S - RA17	1.1	
HA01S - AE17/BE17	1.0	
HA01S - LET19	1.3	

## Optional Feature

### Tenon Mount (Poles by others)


**NOTE:** All small arm assemblies require a steel 2" pipe tenon (2<sup>3</sup>/<sub>8</sub>" O.D.) x 4" long.

All large arm assemblies require a steel 2<sup>1</sup>/<sub>2</sub>" pipe tenon (2<sup>7</sup>/<sub>8</sub>" O.D.) x 4" long.



### Post Top Crook - Small

Cat. No.	Mounting
HA01S-TM1	1A



### Post Top Crook - Large

Cat. No.	Mounting
HA01L-TM1	1A