

JOB \_\_\_\_\_ TYPE \_\_\_\_\_  
NOTES \_\_\_\_\_ APPROVALS \_\_\_\_\_

**FEATURES**

- Unique swivel mount provides superior aiming without loosening over time
- Available in 3500K and 5100K standard CCT



**Certifications**



**SPECIFICATIONS**



Approx. Weight = 3.16 lbs.



**ORDERING CODE**

KLV217			
<b>Fixture<sup>1</sup></b>	<b>Electrical Module</b>		<b>Fixture Finish</b>
	Source	Color Temperature	Aluminum
	3L 3 LEDs	3K 3500K 5K 5100K	BL Black DB Dark Bronze GR Verde Green

<b>Fixture Options</b>	<b>Transformer Options</b>	<b>Mounting Options</b>
<u>Barn Doors</u> <b>BD215BL</b> Black <b>BD215DB</b> Dark Bronze <b>BD215GR</b> Verde Green <u>Fixed Hood</u> <b>FH215BL</b> Black <b>FH215DB</b> Dark Bronze <b>FH215GR</b> Verde Green	Refer to 112V Above-Grade/In-Grade Transformers spec sheet <a href="http://www.kimlighting.com/products/transformers">http://www.kimlighting.com/products/transformers</a>	Refer to 120 Volt Mounting Options Spec Sheet <a href="http://cdn.kimlighting.com/content/products/specs/specs_files/kl_120vmounting_spec.pdf">http://cdn.kimlighting.com/content/products/specs/specs_files/kl_120vmounting_spec.pdf</a> for individual mounting options.

<sup>1</sup> U.S. PATENT D298,656

Kim Lighting reserves the right to change specifications without notice.

**SPECIFICATIONS**

**Housing and Lens Frame:**

- Die-cast low copper alloy (<0.6% Cu) aluminum.

**Swivel:**

- Die-cast aluminum with locking teeth and 1/2" solid brass NPT mount. Provides horizontal rotation independent of the threaded mount. Swivel locked by 1/4-20 stainless set screw. Clear anodized prior to powder coating for added corrosion resistance.

**Gasketing:**

- Silicone gaskets throughout.

**Fasteners:**

- Stainless steel.

**Wiring:**

- 6' No. 18-2 12 Volt cable with fork connectors.

**Optical System:**

- A total of 3 LED emitters configured in a rectangular array comprised together as a module. Available in 3500K and 5100K.

**Driver:**

- Constant current 3.8W electronic driver. Available in 12V input. -40°F. starting temperature. All drivers are Underwriters Laboratories recognized.

**Finish:**

- Each luminaire receives a fade and abrasion resistant, electrostatically applied, thermally cured, triglycidal isocyanurate (TGIC) polyester powdercoat finish. Standard colors include (BL) Black, (DB) Dark Bronze, (GR) Verde Green.

**Certifications and Listings:**

- UL Listed to U.S. and Canadian safety standards for wet locations.

**WARRANTY:**


- For full warranty see <http://www.hubbellighting.com/resources/warranty>

**OPTIONS**

**Barn Doors**

**BD215**


Extruded aluminum, fully adjustable. Provides beam and glare control. Available in Black, Dark Bronze or Verde Green finish.



**Fixed Hood**

**FH215**

Formed .062" thick aluminum. Provides glare control. Available in Black, Dark Bronze or Verde Green finish.



Kim Lighting reserves the right to change specifications without notice.