



Remodel Construction

RMNICS

Line Voltage
Shallow Housing Incandescent
Downlight
IC/Non-IC Rated
120V

APPLICATIONS:

Designed for quick and easy installation into existing ceiling surfaces where insulation is present. With a housing height of just 5 1/2", the RMNICS is a good solution for applications where there is limited ceiling joist depth, such as outdoor soffits, overhangs, and foyers.

REFLECTOR:

Trims feature a rigid flat spring retention method which has a positive upward spring action to ensure a snug fit to the ceiling plane, eliminating unwanted light leak and sagging over time. Trims come standard with a painted white trim ring.

LAMP/SOCKET:

Porcelain socket with brass or copper screw shell. Socket snaps into trim carrier to place lamp in proper position ensuring consistent appearance and performance. Thermal protector prevents fixture from overheating when improperly installed or over-lamped. Refer to trim for specific lamp information. Lamps furnished by others.

INSTALLATION:

Adjustable slide bars lock unit securely to ceiling.

HOUSING:

Galvanized steel shallow housing construction with overspray protection for 2 X 6 construction. Housing adjusts from 1/2" to 1" thick ceilings. Notched mounting frame for easy alignment. Housing includes 1/2" knock outs, thermal protector, and a grounding pigtail. Rated for 4 #12 90° conductors (2 in/2 out). Rated for 60° supply wires in end-of-run applications.

LABELS:

IC/Non-IC rated. UL, CUL listed for damp location and through wiring. Thermally protected.

DATE: _____ TYPE: _____

FIRM NAME: _____

PROJECT: _____

LiteBox® **6"**


Aperture: Nominal 6"

Ceiling Cutout: 6 5/8"

Maximum Ceiling Thickness: 1"

For conversion to millimeters,
multiply inches by 25.4

Not to Scale



CATALOG NUMBER:

EXAMPLE: RMNICS-TO65

Order housing, reflector, and accessories separately

HOUSING

RMNICS

TRIMS

ADJUSTABLE
 TA61

BAFFLE
 TB63
 TBW63

LENSED
 TL68
OPEN
 TO65

ACCESSORIES

LB6LEDA SERIES
800 & 1000 lumen
LED Modules with
dimming to 15%,
120V See spec
sheets for details



A Division of Hubbell Lighting, Inc.

In a continuing effort to offer the best product possible we reserve the right to change, without notice, specifications or materials that in our opinion will not alter the function of the product.
Web: www.prescolite.com • Tech Support: (888) 777-4832

LB-INC-015

LED



LB6LEDA Series

White LED module 800 & 1000 lumens,
See spec sheets for details.

Adjustable



TA61

White eyeball.
Max. 75W PAR-30, 65W BR-30
Adj. 358°H x 30°V

Baffle



TB63

Black stepped baffle.
Max. 75W PAR-30, 65W BR-30



TBW63

White stepped baffle.
Max. 75W PAR-30, 65W BR-30

Lensed



TL68

Flush white albalite glass shower lens.
Metal flange. Wet location approved.
Max. Non-IC Application Only:
60W A-19

Open



TO65

White open trim.
Max. 75W PAR-30, 65W BR-30

Refer to www.prescolite.com for photometrics.