




LZR Series

Architectural/commercial high-performance remote lighting fixtures.

FEATURES

LZR Remote heads are constructed of impact-resistant thermoplastic. Mounts to standard electrical boxes using universal mounting plate provided. Fixture housing mounts to back-plate with a choice of lamp orientation. Housing secured to back plate with locking screws. Pigtail leads are provided for lamp connections. Available in white or black finish. Lamp Choices: 5 watt halogen, 10 watt halogen, or 3 watt LED for greater spacing. Halogen lamps have integral clear glass protective lens.

DIMENSIONS




Dimensions
 Single: 4 3/4" (12 cm) wide x 4 3/4" (12 cm) long x 3 1/2" (8.9 cm) high
 Tandem: 4 3/4" (12 cm) wide x 9 1/2" (24 cm) long x 3 1/2" (8.9 cm) high

Catalog Number	
Comments	Type



APPLICATION DATA



Meets Life Safety Code minimum illuminance of 0.1 fc and average illuminance of 1.0 fc. Assumes open space with no obstructions, mounting height of 7.5', ceiling height of 9' and reflectances of 80/50/20. Photometry files available on the Dual-Lite web site (www.dual-lite.com).

ORDERING GUIDE

LZR

Model	Heads	Housing Finish	Volts	Watts
LZR	S Single D Double	W White B Black	06 6VDC 12 12VDC	05 5 watt Halogen 10 10 watt Halogen 03L 3 watt LED

Dual-Lite • www.dual-lite.com

A Hubbell Lighting, Inc. brand with representatives' offices in principal cities throughout North America.

Copyright © Hubbell Lighting Inc., All Rights Reserved • Specifications subject to change without notice. • Printed in U.S.A.



Hubbell Lighting, Inc.

0601555 B 9/12

U.S. Patent Nos. D400,991, D426,334, D441,475; 6,045,242