

PGR *PGR High Performance LED Remote*

FEATURES

The PGR offers LED performance in a remote fixture. Architectural style for indoor or outdoor application. The unit is illuminated by 4 high power LED's arranged so that in the event of 1 or 2 LED failures the unit will continue to operate. The PGN accepts DC voltage which must be supplied from an external 6-12V DC emergency lighting unit. Housing and mounting plate are constructed of 1/8" die-cast aluminum and sealed with a 1/8" closed-cell silicone gasket. Housing finish is powder coated electro-deposition paint available in four colors: dark bronze, white, platinum silver and black. Remote can be wall-mounted by use of a universal molded-in template. Wired from the j-box through the back or through a conduit entry at the top.

Input Power Requirements

12 watts at 6vDC, 13 watts at 12vDC

Specific LED information

Lamp Color: neutral White, 4000K
 Color Rendering Index(CRI): 75
 Total Lamp Output: 445 Lumens min. Initial
 LED Lamplife: 48,000 hrs. at 70% of Initial
 U.S. Patent No. D627,916



White



Black

Ordering Information

PGR

Series

W

Finish

- W** White
- Z** Dark Bronze
- P** Platinum Silver
- B** Black

LZ Series *Matching Remote Lighting Heads*

FEATURES

Architectural/commercial design. High performance MR-16 halogen lamps standard. Mounts to standard electrical boxes using universal mounting plate provided. Fixture housing mounts to back plate in a choice of four mounting positions. Housings secured using locking screws provided.



Ordering Information

LZR

Series

S

Heads

- S** Single
- D** Double

W

Finish

- W** White
- B** Black

06

Volts

- 06** 6VDC
- 12** 12VDC

03L

Watts

- 05** 5 watt halogen
- 10** 10 watt Halogen
- 03L** 3 watt LED

OMS Series

Outdoor Remote Lighting Heads

FEATURES

Outdoor aluminum spot with sealed lamp and swivel assembly. Furnished with round gasketed aluminum mounting plate. Mounts to 3½" octagonal boxes.



Ordering Information

OMS	S	W	0620
Series	Heads	Finish	Lamp
	S Single D Double	W White B Black	0605 6 volt, 5.4 watts Incandescent ¹ 0607 6 volt, 7.2 watts Incandescent ¹ 0608 6 volt, 8 watts Halogen 0612 6 volt, 12 watts Halogen 0618 6 volt, 18 watts Incandescent 0620 6 volt, 20 watts Halogen 0625 6 volt, 25 watts Incandescent ¹ 1207 12 volt, 7.2 watts Incandescent ¹ 1208 12 volt, 8 watts Halogen 1212 12 volt, 12 watts Halogen 1218 12 volt, 18 watts Incandescent 1225 12 volt, 25 watts Incandescent 1235 12 volt, 35 watts Incandescent 1250 12 volt, 50 watts Incandescent

¹Sealed Beam Type Lamp