



TRIANGLE PENDANT

Security Lighting's Triangle Pendant offers a dramatic impact in all of today's contemporary decors.

These shades are uniquely engineered to suit all high traffic areas in demanding restaurant environments and include a durable fabric look material which can be cleaned. With white interior color, shades are translucent and provide the added benefit of glowing effect.


Socket Assemblies provided with 8 feet of wire and 6 LED lamps are Omni Directional GU24 base, 90 CRI for high color rendering ability. Both stems consist of canopy, (1) 30" and (2) 12" rigid rod segments. With the addition of optional supplemental stem length mounting kit, pendant can be mounted at varying heights.

Pendants are available in custom sizes, shapes, colors, prints and are offered with a range of LED lamp options in various lumen packages. Please consult the factory for more information.



Certifications/Listings

Dimensions



Ordering Information Ordering Example: LCT-P-XX-608LED-BS-X

L	CT	P	608LED	BS		
Size	Shape	Series	Shade Color	Source	Mounting Mechanism	Options
L Large ¹	CT Custom Triangle	P Pendant	608LED	(6) 8 watt GU24 Base LED lamp ²	BS Brushed Steel Rigid Stem/Canopy ⁵	SA05012900 Supplemental stem light adjustment kit (3) 3" stems with connectors 94862413 Additional stem kit (1) 30" stem, (2) 12" stems with canopy SA05008300-20FT Large Triangle additional 12 feet of wire ³
		OO White Exterior, White Interior YL White Exterior, Yellow Interior YO Yellow Exterior, White Interior CG Cool Grey Exterior, White Interior WB Warm Brown Exterior, White Interior RD Red Exterior, White Interior GN Green Exterior, White Interior OR Orange Exterior, White Interior BL Blue Exterior, White Interior				

¹ Includes lens

² Stem consists of Canopy, (1) 30" and (2) 12" rigid rod segments for total of 54"


³ For maximum wire length of 20 feet

TRIANGLE PENDANT

Decorative Shade Colors



00 White Exterior, White Interior



YL White Exterior, Yellow Interior



Y0 Yellow Exterior, White Interior




CG Cool Grey Exterior, White Interior




WB Warm Brown Exterior, White Interior




GN Green Exterior, White Interior



RD Red Exterior, White Interior



OR Orange Exterior, White Interior




BL Blue Exterior, White Interior




PENDANT COLOR OPTIONS


Custom Shapes and Colors Available
Contact Factory for More Information



White Moire 3277




Apple 3221



Beige Northfield 3255




Black Trilam 3219




Bleached Burlap 3271



Blue Sunkiss 3235



Blue Moire 3296



Blue Serpentine 3292



Brown Trilam 3240




Camelot Copper 3225



Camelot Tussah 3267



Croissant Silkglow 3253



Dark Wood 3244



Grey Trilam 3238



Kinwashi 3275



Kona Navy 3233



Kona Ocean 3231




Kraft 3250




Light Wood 3252



Winter White 3281



Medium Wood 3246



Metallic Vine 3288



Mystique Black 3217



Mystique Burgundy 3227




Natural Burlap On Dulk 3257




Natural Cork 3248




Natural Franklin 3265



Orange Serpentine 3294



Potpourri 3273



Purple Moire 3212



Roja Red 3228



Silkara Burlap 3261



Slate 3242




Tangelo 3223



Tan Trilam 3269




Thai Banana 3263




Vellum 3259



White-N-Silver 3287




White Serpentine 3214



White Grid 3290



White Brighton 3279



Web: www.securitylighting.com

2100 Golf Road, Suite 460, Rolling Meadows, IL 60008-4704

Phone: 1-800-LIGHT IT, 1-800-544-4848, Fax: 847-279-0642

Copyright ©2016 Security Lighting, a division of Hubbell Lighting, Inc.

All Rights Reserved. • Specifications subject to change without notice. • Printed in U.S.A. • SL0040 06/19

