



Primary Volts	%	Connect Leads to Tap No.
242	105	1
236	102.5	2
230	100	3
224	97.5	4
219	95	5
Secondary Volts		
230		X1, X2, X3
133 1 phase		X1 & X0 X2 & X0 X3 & X0

ACME ELECTRIC

Type No.

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
145	DTFA-0145-4S	230Δ	230Y/13	WS-A-	980 Lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Impedance		4.90 %	Windings	AL	Typical Efficiency	98.22%
Insulation	220°C	Standards:		UL/CSA			No Load Losses	544W
Sound Level	50 dB						Full Load Losses	2,781W

						A	PRINTS TO	CONTROL 7	A
--	--	--	--	--	--	---	-----------	-----------	---