



Primary Volts	%	Connect Leads to Tap No.
242	105	1
236	102.5	2
230	100	3
224	97.5	4
219	95	5
Secondary Volts		
230		X1, X2, X3
133 1 phase		X1 & X0 X2 & X0 X3 & X0

ACME  ELECTRIC

Type No.

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
220	<b>DTFA-0220-4S</b>	230Δ	230Y/13	WS-A-	1120 lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Regulation @ 100%		2.795 %	Impedance		6.22 %	Typical Efficiency	98.53%
Insulation	220°C	Standards :		UL/CSA				No Load Losses	617W
Sound Level	55 dB							Full Load Losses	6,424W

A PRINTS TO CONTROL 7 A