



Revisions



Primary Volts	%	Connect Leads to Tap No.
483	105	1
472	102.5	2
460	100	3
449	97.5	4
437	95	5
Secondary Volts		
230		X1, X2, X3
133		X1 & X0 X2 & X0 X3 & X0
1 phase		



KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
118	DTGA-0118-4S	460Δ	230Y/133	WS A-3	765 Lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C
Insulation	220°C
Sound Level	50 dB

Impedance	5.7%
-----------	------

Windings	AL
----------	----

Typical Efficiency	
No Load Losses	
Full Load Losses	

Type No.

						A	PRINTS TO	CONTROL 7	A
--	--	--	--	--	--	----------	-----------	------------------	----------