



Primary Volts	%	Connect Leads to Tap No.
483	105	1
472	102.5	2
460	100	3
449	97.5	4
437	95	5
Secondary Volts		
230		X1, X2, X3
133 1 phase		X1 & X0 X2 & X0 X3 & X0

NOTE:
PRIMARY AND SECONDARY BUS AREA
IN FRONT OF CASE.



KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
220	DTGA-0220-4S	460Δ	230Y/13	WS-A-	1120 lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Regulation @ 35% FL		Windings:	AL	Typical Efficiency	
Insulation	220°C	Standards :	UL/CSA	Impedance:	5.70 %	No Load Losses	
Sound Level	55 dB					Full Load Losses	

Type No.

						A	PRINTS TO	CONTROL 7	A
--	--	--	--	--	--	---	-----------	-----------	---