



Revisions



Primary Volts	%	Connect Leads to Tap No.
483	105	1
472	102.5	2
460	100	3
449	97.5	4
437	95	5

Secondary Volts		Connect Leads to Tap No.
460		X1, X2, X3
266		X1 & X0
1 phase		X2 & X0
		X3 & X0



Type No.

DRAWN:

DATE: August 27, 2015

CASE

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
440	DTGB-0440-4S	460Δ	460Y/266	WS-A-7	2295 Lbs	3φ	60 Hz

Winding Rise:	150°C
Insulation:	220°C
Sound Level:	60db

TYPICAL PERFORMANCE DATA

Regulation @ 100% PF:	2.29%
Standards:	UL/CSA

Windings:	AL
Impedance:	6.88%

Typical Efficiency:	97.68%
No Load Losses:	1,288 W
Full Load Losses:	10,472 W

Control
7 A