



Type No.

KVA	CATALOG NUMBER	VOLTAGE		WIRING DIAGRAM	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
93	DTGB-093-4S	460	460Y/26	1	685 Lbs	3	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C
Insulation	220°C
Sound Level	50 dB

Impedance	3.399 %
-----------	---------

Windings	AL
----------	----

Typical Efficiency	98.02%
No Load Losses	490W
Full Load Losses	2,335W

A PRINTS TO CONTROL 7 A