


NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS



Primary Volts	%	Connect Leads to Tap No.
604	105	1
589	102.5	2
575	100	3
561	97.5	4
546	95	5
Secondary Volts		
230		X1, X2, X3
133		X1 & X0
1 phase		X2 & X0
		X3 & X0

ACME ELECTRIC

Type No.

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
145	DTHA-0145-4S	575Δ	230Y/13	WS-A-	990 Lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Impedance	5.12 %	Windings	AL	Typical Efficiency	
Insulation	220°C	Standards :	UL/CSA			No Load Losses	
Sound Level	50 dB					Full Load Losses	

A PRINTS TO CONTROL 7 A