


NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS



Primary Volts	%	Connect Leads to Tap No.
604	105	1
589	102.5	2
575	100	3
561	97.5	4
546	95	5
Secondary Volts		
460		X1, X2, X3
266 1 phase		X1 & X0 X2 & X0 X3 & X0

ACME ELECTRIC

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
145	DTHB-0145-4S	575Δ	460Y/26	WS-A-	990 Lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Impedance	5.7%	Windings	AL	Typical Efficiency	98.48%
Insulation	220°C	Standards	UL/CSA			No Load Losses	506W
Sound Level	50 dB					Full Load Losses	3,560W

Type No.

					A	PRINTS TO	CONTROL 7	A
--	--	--	--	--	---	-----------	-----------	---