


NOTE: PRIMARY AND SECONDARY BUS AREA IN FRONT OF CASE.

KEY: DENOTES CONDUIT AREAS



Primary Volts	%	Connect Leads to Tap No.
604	105	1
589	102.5	2
575	100	3
561	97.5	4
546	95	5
Secondary Volts		
460		X1, X2, X3
266		X1 & X0
1 phase		X2 & X0
		X3 & X0

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
220	DTHB-0220-4S	575Δ	460Y/26	WS-A-	1130 lbs	3φ	60 Hz

TYPICAL PERFORMANCE DATA

Winding Rise	150°C	Regulation @ 100%		Impedance:	5.91 %	Typical Efficiency	
Insulation	220°C	Standards :	UL/CSA			No Load Losses	
Sound Level	55 dB					Full Load Losses	



Type No.

					A	PRINTS TO	CONTROL 7	A
--	--	--	--	--	----------	-----------	------------------	----------