



# Revisions



Primary Volts	%	Connect Leads to Tap No.
604	105	1
589	102.5	2
575	100	3
561	97.5	4
546	95	5

Secondary Volts		Connect Leads to Tap No.
460		X1, X2, X3
266		X1 & X0
1 phase		X2 & X0
		X3 & X0



Type No.

DRAWN:

DATE: August 27, 2015

CASE

KVA	CATALOG NUMBER	VOLTAGE		WEATHER SHIELD	WEIGHT	PHASE	FREQ.
		HIGH	LOW				
440	DTHB-0440-4S	575Δ	460Y/266	WS-A-7	2580 Lbs	3φ	60 Hz

Winding Rise:	150°C
Insulation:	220°C
Sound Level:	60db

## TYPICAL PERFORMANCE DATA

Regulation @ 100% PF:	2.58%
Standards:	UL/CSA

Windings:	AL
Impedance:	7.29%

Typical Effic @35%:	98.57%
No Load Losses:	1,288 W
Full Load	11,635

Control  
7

A