

YAEBAF1CPTN

by Burndy
Catalog ID: YAEBAF1CPTN

Cu T Type Battery Post Connector Terminal, #1 AWG, 2.36" L, 1.89" W,
Pink



Product Details

General

Application	Power Connector
Color Code	Pink
Connector Type	Terminal
Die Index	11
Installation Torque Recommended in-lb	72 LBS/in
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810566268
UPC 12 Digit	7818105662688

Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-9/32

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	10

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)