



YAEBAF25NTNOEM

by Burndy
Catalog ID: YAEBAF25NTNOEM

Cu T-Type Battery Post Connector Terminal, 1/0 AWG, Pink, 12 Index, 1-9/32 IN Strip Length, Polarity N

Product Details

General

Application	Power Connector
Connector Type	Terminal
Installation Torque Recommended in-lb	72 LBS/in
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810547502
UPC 12 Digit	7818105475022

Dimensions

Dimension - Inside Diameter inch	0.46 in
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.38 in
Dimension - Outside Diameter inch	0.63 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

Standards - RoHS Compliant	Yes
UL Listed	No

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)