

# YAEBAS1CNTNOEM

by Burndy  
Catalog ID: YAEBAS1CNTNOEM

Cu Battery Post Connector Terminal, #1 AWG, Green, 11 Index, 1-3/32 IN Strip Length, Polarity N



## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Installation Torque Recommended in-lb	72 LBS/in
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810547540
UPC 12 Digit	7818105475400

### Dimensions

Dimension - Inside Diameter inch	0.340 in
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.21 in
Dimension - Outside Diameter inch	0.55 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	1
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

Standards - RoHS Compliant	Yes
UL Listed	No

## Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)