



YAEBAS26PTN

by Burndy
Catalog ID: YAEBAS26PTN

Battery Post HYDENT Cu Terminals, 2/0 AWG, 2.36" L, 1.02" W, Orange,
Wire Strip Length - 1-3/32" L

Product Details

General

Application	Power Connector
Color Code	Orange
Connector Type	Terminal
Die Index	13
Installation Torque Recommended in-lb	72 LBS/in
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	HYDENT™
Type	OEM Terminals
UPC	781810562628
UPC 12 Digit	7818105626288

Dimensions

Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.36 in
Dimension - Strip Length inch	1-3/32 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
-----------------	--------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)