

YAES14N7

by Burndy
Catalog ID: YAES14N7

Prop 65 Notice

Nylon Insulated Cu Ring Tongue Terminal, Wire Range: 16-14 AWG, Stud Size: #4-#6, Tin Plated, Package: Bulk, Strip Length: 7/32 IN



Product Details

General

Color Code	Blue
Connector Type	Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Military Specification	MS25036
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	INSULUG™
UPC	781810804766
UPC 12 Digit	7818108047666

Dimensions

Dimension - G inch	0.15 in
Dimension - Length Overall inch	0.91 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Width inch	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	16 AWG;14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL486 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)