

# YAV14T34FBOX

by Burndy  
Catalog ID: YAV14T34FBOX

Prop 65 Notice

Seamless Uninsulated Fork Tongue Terminal, #20-14 AWG, #8-10 Stud, .82 in L.

Features: The Type YAV-T-F HYLUG Is A Seamless Heavy Duty Uninsulated Compression Fork tongue Terminal Manufactured From Electro -Lytic Copper For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, The Seamless Design Produces A Double Thick Tongue And The Seamless Barrel Provides A Strong Highly Reliable Connection, All The Benefits Of The Type YAV Apply For The Same Wire Sizes, Fork Tongue: Allows Installation Of Compression Terminal Under Screw Head Without Complete Removal Of The Screw, Wire Shroud: No, Package: Box, Installation Tool: Non-Ratchet: Y10D, Y1022 Tool, Ratchet: MR8-G98, MR8-9Q, Y8MRB-1, MR20 Tool, Conductor Type: Commercial/Military Stranded Copper, Wire Strip Length: 9/32 IN, Finish: Electro-Tin Plated, Tongue Angle: Straight



## Product Details

### General

Application	For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors
Connector Type	Terminal - Fork
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Fork Tongue
UPC	781810534052
UPC 12 Digit	7818105340522

### Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.27 in
Dimension - D inch	0.48 in
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.82 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Pad Width inch	0.37 in

Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8;#9;#10
Dimension - Z inch	0.26 in

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 20;AN 18;AN 16;AN 14
Conductor - Copper Str Aircraft Size Range	AN 20-AN 14
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)