

YAV16M4

by Burndy
Catalog ID: YAV16M4

Compression terminal HYLUG™ Copper tubing; 1 Hole; 16 mm²; M4 Stud;
Tin Plating



Product Details

General

Die Index	7
Material	Copper
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637494
UPC 12 Digit	7818106374944

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Hole Size inch	0.18 in
Dimension - Hole Size mm	4.6 mm
Dimension - L Length Overall mm	31.5 mm
Dimension - Length Overall inch	0.09 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	0.51 in
Dimension - Z inch	0.29 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)