

YAV4CL2TC38FX45

by Burndy
Catalog ID: YAV4CL2TC38FX45

Prop 65 Notice

Cu Comp Terminal, 2 Holes W/InspWindow, #4 Weld 5(91/#24)-4 (105/#24)DLO Flex, #4 AWG Code, 40&50 Navy, 3/8" Stud, 1.00" Spacing, 45 Deg Bent, Standard Brll



Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	8
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin-Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810037096
UPC 12 Digit	7818100370966

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Height inch	0.87 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	67 mm
Dimension - Length Overall inch	2.64 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	9/16
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	5 (91/#24) DLO;4 (105/#24) DLO
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy;50 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - CopperWeld Str Size	4 A AWG;4 D AWG;4 N AWG;4 P AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)