



YAV4CL4B

by Burndy
Catalog ID: YAV4CL4B

Cu Tube Compression Ring Tongue Terminal, 1 Hole W/InspWindow,
#5(91/#24) - #3(125/#24)DLO, 5/16" Stud, Uninsulated, Belled End

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	yes
Plating Type	Tin-Plated
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810429136
UPC 12 Digit	7818104291366

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	1.34 in
Dimension - Pad Width inch	0.62 in
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	5 (91/#24) DLO;4 (105/#24) DLO;3 (125/#24) DLO
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)