



YAV4CL5BOX

by Burndy
Catalog ID: YAV4CL5BOX

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Hole, AN-4 Flex, 1/2" Stud, Short Barrel, Tin Plated

Product Details

General

Connector Type	Terminal
Die Index	40
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> DLP Copper Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810539453

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	0.28 in
Dimension - Length Overall inch	1.68 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.73 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Solid Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)