



YAV6CL4BOX

by Burndy
Catalog ID: YAV6CL4BOX

Pure Electrolytic Copper Ring Tongue Copper, 5, 6 AWG, 5/16 IN Stud, Electro-Tin Plated.

Features: HYLUG Type YAV Is A Seamless, Heavy Duty Uninsulated Compression Terminal Manufactured From Electrolytic Copper And Is For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, The Seamless Tubing Produces A Double Thick Tongue And Seamless Barrel Design Provides A Strong Connector For Demanding Applications Requiring High Reliability, Applications Include Aircraft, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance, The YAV HYLUG Terminals Meet The Requirements Of SAE-AS7928 And Are Listed Per AS20659 For Use With Copper Aircraft Cable Per MIL-W-5086, The Benefits Of YAV-L Connectors Are The Same As YAV Connectors For Stranded Conductors, Wire Shroud: No, Ms20659 Dash Number: -131, Installation Tool: HYTOOL: Non-Ratchet: MY28, MY29-11 Tool, Ratchet: MR4C Tool, Finish: Electro-Tin Plated, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: Y29B, Y29NC Tool, DV6L Die Nest, Y29PL Die Indentor, (1) Crimp, Y35, Y39, Y750 Tool, UV6L Die Nest, Y34PLA Die Indentor, (1) Crimp, Package: Box, Conductor Type: Commercial/Military Stranded Copper, Die Index: 39, Wire Strip Length: 1/2 IN, Tongue Angle: Straight

Product Details

General

Application	For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance
Connector Type	Terminal - Ring
Die Index	39
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> DLP Copper Tin Plating
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810539101
UPC 12 Digit	7818105391011

Dimensions

Dimension - B Length fraction	1/2 in
-------------------------------	--------

Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.69 in
Dimension - Hole Size inch	0.38 in
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	1.43 in
Dimension - N inch	0.3 in
Dimension - Outside Diameter inch	0.30 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	1/2 in
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Flex G Size	6
Conductor - Copper Flex H Size	6
Conductor - Copper Flex I Size	6
Conductor - Copper Flex K Size	6
Conductor - Copper Flex M Size	6
Conductor - Copper Solid Size	6
Conductor - Copper Solid Size Range	6
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Aircraft Size Range	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL467 • Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)