



## YAV8CRS3

by Burndy  
Catalog ID: YAV8CRS3

Copper Compression Right Angled Lug, Heavy Duty, 1 Hole W/ Inspection Hole, AN-8 Flex, 3/8" Stud, Short Barrel, Tin Plated

### Product Details

#### General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810082188

#### Dimensions

Dimension - B Length fraction	4/9 in
Dimension - B Length inch	0.44 in
Dimension - G inch	0.84 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Pad Width inch	0.56 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.34 in

#### Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1000
-----------------------	------

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)