

HUBBELL® Delivery Systems



Innovative Product Solutions
for Delivering
Power, Data and Audio Video



HUBBELL®

Delivery Systems

Businesses today require a more intelligent and connected way of communicating than ever before. To support their ever-changing, ever-expanding requirements, Hubbell Delivery Systems products bring power, data, and audio/video solutions to wherever they're needed within a building. You've never had so many customized options for getting power, data, and AV from point A to point B: in or above the floor, through the floor, ceiling to floor, along the wall, or in the wall or ceiling. Hubbell product solutions revolutionize the way power, data, and AV are delivered.



In the Floor/Above the Floor



From conference rooms, classrooms, and open offices to stages, security gates, and museum exhibits,

Hubbell's flush and recessed floor boxes accommodate the industry's broadest range of power, data, and AV applications in a single location: in or above the floor. Whatever your floor type, these solutions provide consistent aesthetics and unobtrusive power delivery options.

Through the Floor



In all types of environments – even in raised-floor installations – bringing power, data, and

AV through the floor allows end-users to reconfigure with minimal downtime, and without worrying about power, data, and AV access. Ideal for retrofit applications, poke-through devices allow fire-safe, through-the-floor solutions that don't require leveling.

Ceiling to Floor



Attractive, durable, customizable power poles effectively distribute power, fiber, and data cabling from

the ceiling to the floor. Available in varying lengths and colors, custom options maximize space and allow workstations, retail checkout areas, collaboration areas, digital signage, vending machines, appliances, and kiosks to be pulled away from the wall.

TABLE OF CONTENTS

Floor Boxes

SystemOne Recessed	
with Rectangular Cover	4
with Round Cover	5
SystemOne Flush	6
Flush, Recessed and	
Convention Center	7

Fire-Rated Poke-Throughs

SystemOne	
Recessed	8
Flush	9
Fire-Rated Poke-Throughs	10

Service Poles

Aluminum Service Poles	11
Accessories	11



In and Along the Wall



Wall ducts, non-metallic and metal raceway delivery options feature mounted outlets and

are designed for enclosure of power and data cabling, as well as medical equipment wiring. Installing faster and neater than in-wall systems, Hubbell's along-the-wall delivery solutions make it easy to reconfigure interior spaces as requirements and uses change.

In the Wall or Ceiling



Hubbell's in-wall and in-ceiling power, data, and AV solutions include options ranging from ceilings boxes

and large capacity wall boxes to flat panel TV enclosures. Airports, hospitals, offices, and schools all benefit from connectivity through a single wall or ceiling access point for electronic devices, digital signage, kiosks and displays, and projection systems.

On the Surface



Table top and work surface boxes bring power, AV and charging solutions to the places it's needed most – at the work

surface, where computers, laptops, smartphones, tablets, projectors and other devices are often plugged in or charged. Convenient access to power, data and multimedia applications directly at the work surface area has become a common need in almost every business, educational, healthcare and hospitality environment.

Raceway, WireBasket Tray and Wall/Trench Duct

Metal	12
Non-Metallic	12
Wire Basket Tray	13
Wall Duct	13
Trench Duct	13

In Wall Solutions

Flat Panel TV Enclosure	14
Large Capacity Wall Box	14
Gangable Wall Box	14

In Ceiling Solutions


Wireless Access Box	14
AV Ceiling Enclosure	14

Table Top Boxes

Low Voltage and Pre-Wired	15
-------------------------------------	----

Work Surface Boxes

Flush Mount/Lift Up Style	15
USB Pop-Up Boxes	15



SystemOne Recessed Floor Boxes

SystemOne Recessed Floor Boxes are the newest addition to the Hubbell Delivery Systems family. Available in 2-, 4-, 6- or 10-gang capacities, these boxes are used in concrete, wood or raised access floors and can accommodate conduits from 1/2" up to 2". With traditional rectangular covers or plated round covers, SystemOne Recessed covers offer a common look in a multitude of architectural designs. Whether used in an atrium, lobby, conference room or server room, the new boxes and covers meet the demands of any project, anywhere.

The **Hubbell SystemOne Recessed Floor Box** line offers a common look regardless of capacity or installation. This simple concept ensures a consistent look throughout a building with rectangular or round covers. Round covers lend themselves to multi-story buildings, also using Fire-Rated Poke-Through devices. All SystemOne covers are ADA and UL514A compliant. The doors open to 180° for maximum access. Cables and plugs are protected by recessed connections.

Rectangular Covers

Concrete Floors



Floor Boxes - SystemOne for Concrete Floors with Rectangular Covers

Box Type	2-Gang		4-Gang		6-Gang	10-Gang
	3" Min. Pour Depth	2 1/2" Min. Pour Depth	3" Min. Pour Depth	2 1/2" Min. Pour Depth	3" Min. Pour Depth	5 1/2" Min. Pour Depth
Standard	CFB2G30	CFB2G25	CFB4G30	CFB4G25	CFB6G30	CFB10G55
On-grade	CFB2G30CR	CFB2G25CR	CFB4G30CR	CFB4G25CR	CFB6G30CR	CFB10G55CR



Rectangular Covers

Surface Style covers are for use with carpet, tile, VCT and other engineered floors

Flush Style covers are for use with tile, finished concrete and Terrazzo floors

Style	For use with 2-Gang and 4-Gang Boxes			For use with 6-Gang and 10-Gang Boxes	
	Flat Surface	With Insert	Furniture Feed (2-Gang Only)	Flush Surface	With Insert
Surface	24GCCVRxx	24GCCVRxxC	2GCFFCVRxx	610GCCVRxx	610GCCVRxxC
Flush	24GTCVRxx	24GTCVRxxC	2GTFFCVRxx	610GTCVRxx	610GTCVRxxC

For cover powder coat finish replace xx with: **ALU** (Aluminum), **BK** (Black), **BRS** (Brass), **BRZ** (Bronze) or **NK** (Nickel)

Raised Access Floors



Floor Boxes - SystemOne for Raised Access Floors

Box Type	2-Gang		4-Gang		10-Gang
	5" Box Depth	2 1/2" Box Depth	5" Box Depth	2 1/2" Box Depth	5 1/2" Box Depth
Standard*	AFB2G50	AFB2G25	AFB4G50	AFB4G25	AFB10G55

* Add Suffix CHI for use in the City of Chicago.

Rectangular Covers

Available in five powder coat finishes, these covers are for use with raised access tiles and wood floors. See Hubbell's online catalog for ordering information.

SystemOne Recessed Floor Boxes

Features

- Cables and connections are protected by recessed functionality
- Open architecture sub-plate design
- Common door layout regardless of flange for harmonized look
- Meets UL 514A scrub water requirements with ScrubShield® technology
- Easy selection with common look for all floor types
- Surface flange available for carpeted floors with 0.15 in. rise meets ADA requirements
- Hideaway egress doors fold under cover while in use
- 180° opening of main door
- 2, 4 and 6-Gang deep series floor boxes accept a 2 inch conduits with the use of CFBHUB2 adapter
- 10-Gang floor box features a 2 inch knockout



Round Covers

Concrete Floors



Floor Boxes - SystemOne for Concrete Floors with Round Covers

	2-Gang	2-Gang Deep	4-Gang	4-Gang Deep	6-Gang Deep	10-Gang
Box Type	3¾" Min. Pour Depth	3¾" Min. Pour Depth	3¾" Min. Pour Depth	3¾" Min. Pour Depth	3¾" Min. Pour Depth	6¼" Min. Pour Depth
Standard	CFB2G30R	CFB2G25R	CFB4G30R	CFB4G25R	CFB6G30R	CFB10G55R
On-grade	CFB2G30RCR	CFB2G25RCR	CFB4G30RCR	CFB4G25RCR	CFB6G30RCR	CFB10G55RCR



Round Covers

Round covers are suitable for use with all floor types

	for use with 2-Gang		for use with and 4-Gang Boxes 6-Gang and 10-Gang Boxes
Style	Flush Surface	Furniture Feed	Flush Surface
Round	CFBS1R6CVRxxx	CFBS1R6FFCVRxxx	CFBS1R8CVRxxx

For cover finishes replace xxx with: **ALU** (Brushed Aluminum) **BLK** (Black Powder Coat), **BRS** (Brass Plated), **BRZ** (Bronze Plated) or **NK** (Nickel Plated)

Raised Access Floors



Floor Boxes - SystemOne for Raised Access Floors

4-Gang Box Only	4-Gang Box with 8 in. Round Cover
6¼" Box Depth	Cover
RAFB4BASE	RAFB4xxx

For cover finishes replace xxx with: **ALU** (Brushed Aluminum) **BLK** (Black Powder Coat), **BRS** (Brass Plated), **BRZ** (Bronze Plated) or **NK** (Nickel Plated)

Hubbell Connexion 2.0 Zone Distribution System

The Hubbell CONNEXION 2.0 Zone Distribution System is a factory assembled, flexible, modular system that delivers power in raised floor installations.

The SystemOne Line of Raised Access Floor Boxes works with the Hubbell Connexion Zone Distribution System.






SystemOne Flush Floor Boxes

Featuring unique cover and sub-plate designs, the **Hubbell SystemOne Flush Floor Box** offering provides industry leading flexibility while accommodating an extensive range of applications. These floor boxes are constructed to give customers the ability to create personal solutions for their most demanding, power, data and audio/video requirements.

Features

- Easily installed, aesthetic and configurable floor box solution, for open floor plan spaces for Multi-service, multimedia and 4x4 applications (4x4 applications have (4) power outlets and (4) data openings)
- The Hubbell SystemOne Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar and are available in black, gray, brass, aluminum and ivory powder coat finishes
- Subplates accommodate various power and data configurations



Floor Boxes









Description	Cast Iron	Steel	Steel AV	Non-Metallic
Fully Adjustable, concrete cover, closure plugs and non-metallic low voltage divider is also included.	S1CFB	S1SFB	S1SFBAB	S1PFB



Covers

Description	Finish	Aluminum	Brass	Black	Gray	Ivory
Cast aluminum	Carpet	S1CFCAL	S1CFCBRS	S1CFCBL	S1CFCGY	S1CFCI
Covers with Durable Tile		S1TFCAL	S1TFCBRS	S1TFCBL	S1TFCGY	S1TFCI
powder coat finish						

Subplates

Description		Description		Description	
Style Line® Decorator/GFCI for power and/or datacom applications	 S1SP	Duplex/Duplex for power and/or datacom applications	 S1SPDU	Duplex/Style Line® Decorator for power and/or datacom applications	 S1SPDUSL
(4) 20A and (4) keystone openings. Power can be wired as single or two circuit and isolated ground.	 S1SP4X4	Single Receptacle Opening for 20A-30A Twist-Lock® recep. (1.56" OD) and (2) Keystone openings	 S1SPTL	Hubbell AV + Power (1) 20A, 125V receptacle and 3 unit recessed iSTATION opening for Data	 S1SP3IM
Carpet Furniture Feed Cover/Flange* (1) ¾" and (1) 1½" NPT access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.	 S1SPFFxx*	Tile Furniture Feed Cover/Flange* (1) ¾" and (1) 1½" NPT access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	 S1SPFTxx*		

*Note: Furniture Feed available in the following finishes. Replace xx with desired finish. Aluminum (AL), Brass (BRS), Black (BL), Gray (GY) or Ivory (I). For full offering of SystemOne sub-plates and accessories, please visit our online catalog at hubbell-wiring.com.



Flush Floor Boxes Ballroom and Convention Center

Hubbell offers a wide variety of traditional solutions including single and multi-gang **Cast Iron, Stamped Steel and Non-Metallic Floor Boxes** in both round and rectangular designs. These boxes can be finished with either brass or aluminum covers and flanges to match any office décor. All Hubbell floor box assemblies exceed UL scrub water exclusion requirements

Features

- PVC, Stamped Steel, or Cast iron versions available
- UL 514A & ADA compliant
- Brass and Aluminum finishes



Flush Round



Round Boxes



Rectangular Boxes



Round Covers




Rectangular Covers

Non-Metallic	Cast Iron		Gang	Cast Iron	Stamped Steel	Description	Cat No.		Description	Type	Cat No.
Non-Metallic	PFB1	Deep Box	1	B2436	B2431	Brass Duplex Flap	S3925	Brass	Duplex Flap		S3825
Cast Iron	B2537	with Brass Collar	2	B4233	B2432	Single Single Rec.	S2925	One Required	Single Rect.		S2825
Stamped Steel	B2529		3	B4333	B2433	Service Combination	S2525	Per Gang	Style Line®		S3826
									Blank		S3813

Also available in Aluminum.

Recessed 7 and 11-Gang Concrete Floor Boxes



Boxes and Covers

Description	Min. Depth of Pour	7-Gang	11-Gang
Boxes	4.08" (103.5)	CFB7G4	CFB11G4
	6.08" (154.3)	CFB7G6	CFB11G6
Flange and cover	Carpet	CFB7CVRxxx	CFB11CVRxxx
	Tile	CFB7Txxx	CFB11Txxx

xxx = finish. Aluminum (ALU) or Brass (BRS)

Recessed Ballroom Series Floor Boxes



Boxes and Covers

Description	Min. Depth of Pour	Carpet Application	Tile Application
Boxes	4.95" (127.0)	CFB8FC1	—
	7.15" (182.0)	—	CFB8FC2
Cover	Flush (2 egress doors)	CFB8CVRxxx1	CFB8CVRxxx2
	Blank	CFB8JBC1	CFB8JBC2

xxx = finish. Aluminum (ALU) or Brass (BRS)

Metallic Convention Center Utility Boxes*



Steel Convention Center Utility Box

Description	Cover for Power and Data/Communications	Cover for Power, Data/Communications and Air/Water Box	Cover for Air/Water Only
Painted Galvanized Steel Box	HBLSCCUBPD	HBLSCCUBPDW	HBLSCCUBW
Stainless Steel Box	HBLSCCUBPDSS	HBLSCCUBPDWSS	HBLSCCUBWSS

*All boxes provided with temporary galvanized steel concrete covers.

**Contact Hubbell for available configurations of power and data panels.



Power and Data Panels**

Custom manufactured and pre-wired to your project specifications. Panel options include 60A pin and sleeve, 20A and 30A Twist-Lock®, 20A GFCI, isolated ground or industrial straight blade devices.



SystemOne Recessed Fire-Rated Poke-Throughs

Hubbell's **SystemOne Recessed 4, 6 and 8-inch Fire-Rated Poke-Throughs** (FRPT) enhance functionality providing increased power, data and audio visual capacity. Safety is improved with recessed connectivity, a low .125 inch profile flange, and egress doors that hinge inwards. Building value is enhanced with plated finishes to match and blend with modern building décor.

Features

- Recessed connections
- Flush, durable, low profile covers are available in brushed brass plated, satin nickel plated, antique bronze plated, brushed aluminum and black powder coat
- Variety of subplates to accommodate various power and data configurations

4-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Power includes: pre-wired quad receptacles, (2) ½ in. EMT and (1) ¾ in. EMT	Brushed Aluminum	S1R4PTQUADALU	Satin Nickel Plated	S1R4PTQUADNKL
	Brushed Brass Plated	S1R4PTQUADBRS	Black Powder Coat	S1R4PTQUADBLK
	Antique Bronze Plated	S1R4PTQUADBRZ	Gray Powder Coat	S1R4PTQUADGRY
Recessed Connectivity	Brushed Aluminum	S1R4PTALU	Satin Nickel Plated	S1R4PTNKL
	Brushed Brass Plated	S1R4PTBRS	Black Powder Coat	S1R4PTBLK
	Antique Bronze Plated	S1R4PTBRZ	Gray Powder Coat	S1R4PTGRY

6-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Data/AV includes: (2) pre-wired 20A receptacles with 18 in. leads plus (2) decorator openings including 2 in. EMT and ¾ in. EMT, (1) flange and cover assembly	Brushed Aluminum	S1R6PTWZALU	Satin Nickel Plated	S1R6PTWZNKL
	Brushed Brass Plated	S1R6PTWZBRS	Black Powder Coat	S1R6PTWZBLK
	Antique Bronze Plated	S1R6PTWZBRZ		
FRPT for Furniture Feed Applications (1) 2 in. EMT, (1) ¾ in. EMT, (1) flange and cover assembly	Brushed Aluminum	S1R6PTFFALU	Satin Nickel Plated	S1R4PTNKL
	Brushed Brass Plated	S1R6PTFFBRS	Black Powder Coat	S1R4PTBLK
	Antique Bronze Plated	S1R6PTFFBRZ		
Through floor fitting including 2 in. EMT and ¾ in. EMT	—	S1R6PTFIT		

8-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Data/AV includes: (4) pre-wired 20A receptacles with 18 in. leads plus (3) gangs with 2 in. EMT for data and AV, (1) flange and cover assembly	Brushed Aluminum	S1R8PTZZ3ALU	Satin Nickel Plated	S1R8PTZZ3NKL
	Brushed Brass Plated	S1R8PTZZ3BRS	Black Powder Coat	S1R8PTZZ3BLK
	Antique Bronze Plated	S1R8PTZZ3BRZ		
For Power includes: (4) pre-wired 20A receptacles with 18 in. leads plus 2-gangs with 2 in. EMT and 1 in. EMT (1) flange and cover assembly	Brushed Aluminum	S1R8PTZZ2ALU	Satin Nickel Plated	S1R8PTZZ2NKL
	Brushed Brass Plated	S1R8PTZZ2BRS	Black Powder Coat	S1R8PTZZ2BLK
	Antique Bronze Plated	S1R8PTZZ2BRZ		
Through floor fitting including 2 in. EMT for data and AV	—	S1R8PTFIT3		

Hubbell SystemOne Universal Covers



Brushed Aluminum



Brushed Brass Plated



Antique Bronze Plated



Satin Nickel Plated



Black Powder Coat





SystemOne Floor Flush Fire-Rated Poke-Throughs

Hubbell's offering of **SystemOne Flush Fire-Rated Poke-Throughs** provide installers with a broad range of options to support a wide array of connections. From multi-service and multimedia to 4X4 and furniture feed applications, Hubbell SystemOne Flush Fire-Rated Poke-Through products provide users the flexibility to create personal solutions for their most demanding applications.

Features

- Easily installed, aesthetic and configurable floor box solution, for open floor plan spaces for Multi-service, multimedia and 4x4 applications
- The Hubbell SystemOne Universal Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar and are available in black, gray, brass, aluminum and ivory powder coat finishes
- Subplates accommodate various power and data configurations
- 4-Inch core holes




Fire-Rated Poke-Throughs









Description	Finish	(4) 20A; (4) keystone	Dual Style Line	Modular AV	Furniture Feed
Factory Assembled units include through floor fitting, cover and sub-plate.	Aluminum	S1PT4X4AL	S1PTAL	S1PT3IMAL	S1PTFFAL
	Brass	S1PT4X4BRS	S1PTBRS	S1PT3IMBRS	S1PTFFBRS
	Black	S1PT4X4BL	S1PTBL	S1PT3IMBL	S1PTFFBL
	Gray	S1PT4X4GY	S1PTGY	S1PT3IMGY	S1PTFFGY
Through Floor Fittings	—	S1PT4X4FIT	S1PTFIT	S1PTAVFIT	—

Covers

Description	Finish	Aluminum	Brass	Black	Gray	Ivory
Cast aluminum Covers with durable powder coat finish	Carpet	S1CFCAL	S1CFCBRS	S1CFCBL	S1CFCGY	S1CFCI
	Tile	S1TFCAL	S1TFCBRS	S1TFCBL	S1TFCGY	S1TFCI



Subplates

Description		Description		Description	
Style Line® Decorator/GFCI for power and/or datacom applications	 S1SP	Duplex/Duplex for power and/or datacom applications	 S1SPDU	Duplex/Style Line® Decorator for power and/or datacom applications	 S1SPDUSL
(4) 20A and (4) keystone openings. Power can be wired as single or two circuit and isolated ground.	 S1SP4X4	Single Receptacle Opening for 20A-30A Twist-Lock® recep. (1.56 in. OD) and (2) Keystone openings	 S1SPTL	Hubbell AV + Power (1) 20A, 125V receptacle and 3 unit recessed iSTATION opening for Data	 S1SP3IM
Carpet Furniture Feed Cover/Flange* (1) ¾ in. and (1) 1½ in. NPT access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.	 S1SPFFxx*	Tile Furniture Feed Cover/Flange* (1) ¾ in. and (1) 1½ in. NPT access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	 S1SPFTxx*		

*Note: Furniture Feed available in the following finishes. Replace xx with desired finish. Aluminum (AL), Brass (BRS), Black (BL), Gray (GY) or Ivory (I). For full offering of SystemOne sub-plates and accessories, please visit our online catalog at hubbell-wiring.com.





Fire-Rated Poke-Throughs with 2 or 3 Inch Core

Hubbell offers a variety of single and multi-service **Flush Fire-Rated Poke-Through** products. It incorporates a Hubbell Style Line®, 20 amp, duplex receptacle and two Hubbell Category 5e data jacks. The jacks mount flush to the cover for an unobtrusive appearance. Flush and pedestal style **Furniture Feed Fire-Rated Poke-Throughs** deliver power and voice/data cabling to feed furniture systems.

Features

- Available Flush and Pedestal Versions in metal and non-metallic covers
- UL514A scrub water compliant
- 2 or 3 Inch core holes

2X2 Poke-Through One-Piece Units (PT2X2FIT)

Description	Finish	Non-metallic Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A Style Line® decorator receptacle and (2) Category 5e data jacks	Black	PT2X2BL	PT2X2IGBL
	Gray	PT2X2GY	PT2X2IGGY



Finish	Metal Cover	
	Standard Receptacle	Isolated Ground
Black/Brass Brass Finish/ Brass	PT2X2BRS3	PT2X2IGBRS3
	PT2X2BRS	PT2X2IGBRS



Flush Duplex FRPT, One-Piece Units

Description	Finish	Non-metallic Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A duplex receptacle; flip lid cover with (2) ½ in. diameter low voltage feed-through holes	Black	PT7FSDBLA	—
	Brown	PT7FSDBRA	—
	Gray	PT7FSDGYA	PT7IGFSDGYA
	Ivory	PT7FSDIA	PT7IGFSDIA



Finish	Metal Cover	
	Standard Receptacle	Isolated Ground
All Brass Black/Brass	PT7FSDBRS2A	PT7IGFSDBRSA
	PT7FSDBRS3A	—



Flush Furniture Feed FRPT, One-Piece Units

Description	Finish	Three Service
Aluminum cover with (2) ½ in. threaded hubs for low voltage and (1) ¼ in. threaded hub for power	Black	PT73FFSDBK
	Gray	PT73FFSDGY
	Ivory	PT73FFSDI



Finish	Color	Single Service
Aluminum cover with (1) KO to accept a ¼ in. connector	Gray	PT7FFSDGY
	Ivory	PT7FFSDI



Painted Pedestal FRPT

Description	Finish	
Large Capacity Multi-Service Pedestal Through-Floor Fitting with (1) 1 ¼ in. EMT stem for low voltage and (1) ½ in. EMT stem for power applications.	Black	PT7XC
	Gray	
	Ivory	



Description	Color	4-Gang	6-Gang
Pedestal Service Fittings (Order 1 plate per gang)	Gray	FR480BKA	FR680BKA
	Ivory	FR480GYA	FR680GYA





Aluminum Service Poles

Hubbell offers a line of attractive and durable **Aluminum Service Poles** which distribute power and telecommunications wiring from above the ceiling to workstations below.

They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices. Poles with three service capability have a divider to separate power and low voltage wiring.

Features

- Available in gray, ivory, black, white and office white painted and clear anodized aluminum
- Style Line® decorator duplex receptacles and two Style Line® knockouts for communications
- Includes ceiling trim mounting plate and scuff boot



Three Service Aluminum Service Poles

Description	Height Feet (m)	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)
(2) 20A 125V Style Line® duplex receptacles; one circuit	Black	HBLPP10BK	HBLPP12BK	HBLPP15BK
	Gray	HBLPP10A	HBLPP12A	HBLPP15A
	Ivory	HBLPP10AI	HBLPP12AI	HBLPP15AI
	Office White	HBLPP10OW	HBLPP12OW	HBLPP15OW
	White	HBLPP10W	HBLPP12W	HBLPP15W
	Clear Anodized Aluminum	HBLPP10AAL	HBLPP12AAL	HBLPP15AAL
(1) Orange isolated ground 20A 125V Style Line® duplex receptacle; (1) 20A 125V Style Line® duplex receptacle; two circuits	Black	HBLPP10IGBK	—	—
	Gray	HBLPP10IGA	—	—
	Ivory	HBLPP10IGAI	—	—
	Office White	HBLPP10IGOW	—	—
	White	HBLPP10IGW	—	—
	Clear Anodized Aluminum	HBLPP10IGAL	—	—
(2) Orange isolated ground 20A 125V Style Line® duplex receptacles; (1) isolated ground surge suppression 20A 125V duplex receptacle; one circuit	Black	HBLPP10SBK	—	—
	Gray	HBLPP10SA	—	—
	Ivory	HBLPP10SAI	—	—
	Office White	HBLPP10SOW	—	—
	White	HBLPP10SW	—	—
	Clear Anodized Aluminum	HBLPP10SAL	—	—
(1) 20A 125V GFCI Self Test duplex receptacle with (2) ground fault protected 20A 125V Style Line® duplex receptacles; one circuit.	Black	HBLPP10GFBK	HBLPP12GFBK	HBLPP15GFBK
	Gray	HBLPP10GF	HBLPP12GF	HBLPP15GF
	Ivory	HBLPP10GFI	HBLPP12GFI	HBLPP15GFI
	Office White	HBLPP10GFW	HBLPP12GFW	HBLPP15GFW
	White	HBLPP10GFW	HBLPP12GFW	HBLPP15GFW
	Clear Anodized Aluminum	HBLPP10GFAL	HBLPP12GFAL	HBLPP15GFAL
Blank pole; divider; (4) Style Line® device knockouts	Black	HBLPPOBK	HBLPPO12BK	HBLPPO15BK
	Gray	HBLPPOA	HBLPPO12A	HBLPPO15A
	Ivory	HBLPPOAI	HBLPPO12AI	HBLPPO15AI
	Office White	HBLPPOOW	HBLPPO12OW	HBLPPO15OW
	White	HBLPPOW	HBLPPO12W	HBLPPO15W
	Clear Anodized Aluminum	HBLPPOAAL	HBLPPO12AAL	HBLPPO15AAL



Accessories

Description

Adjustable T-bar assembly for mounting poles in the middle of ceiling tile.

ATB

Replacement service pole trim kit (office white).

PPTRIM1





Metal and Non-Metallic Raceway

Hubbell's complete line of **Metal** and **Non-Metallic Raceway** is optimal for delivering power and technology to the point of use in laboratories, classrooms, offices and more while offering maximum flexibility for changing needs. Raceway offers the ability to provide standard convenience receptacles and datacomm connections, as well as serve the power requirements of larger equipment. Receptacles or datacomm ports can also be easily added where needed.

Features

- Metal and Non-Metallic Raceways are available in a single and multi-channel as well as PlugTrak and Portable PlugTrak
- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation
- Aluminum Raceway resists oxidation, corrosion and fading and are available in single, dual and three channel with a wide selection of fittings and boxes

Single Channel Metal Raceway



Raceway

Description	Color	HBL500	HBL700	HBL750	HBL4750	Single Channel Base	5 ft. Cover	7.5 In. Precut Cover*
Base and Cover	Ivory	HBL5005IV	—	HBL7505IV	Ivory	HBL4750B10IV	HBL4750CIV	HBL4750C075IV
	Ivory	HBL50010IV	HBL700IV	HBL75010IV	Gray	HBL4750B10GY	HBL4750CGY	HBL4750C075GY
	White	HBL50010W	HBL700W	HBL75010W				
		A: .53" (13.46) B: .76" (19.30)	A: .67" (16.90) B: .76" (19.30)	A: .85" (21.59) B: .76" (19.30)			A: 4.75" (120.65) B: 1.75" (44.45)	*Available in pre-cut lengths of 7.5 in. to 31.5 in.



Boxes (HBL500, HBL700 and HBL750 Series)

Color	Low Profile Switch/Recept.	Alarm Device Box	Round Extension Box	Outlet Box
Ivory	HBL5748SIVA	HBL5752IVA	HBL5737IVA	HBL5733IVA
White	HBL5748SWA	—	HBL5737WA	—
Red	—	HBL5752RA	—	—

2-Gang Cover Plates (HBL4750 Series)

Color	(2) Duplex	(1) Duplex, (1) Style Line®	(1) Style Line®, (1) Blank	(1) Single Round (1) Blank
Ivory	HBL4747BBIV	HBL4747BRIV	HBL4747RXIV	HBL4747AXIV
Gray	HBL4747BBGY	HBL4747BRGY	HBL4747RXGY	HBL4747AXGY

Non-Metallic Raceway



Raceway (Office White)

Single Channel PP1			Two Channel PB2		
Length	Base	Cover	Length	Base	Cover
5 ft.	PP1BC5		5 ft.	PB2B5	PB2C5
7 ft.	PP1BC7		10 ft.	PB2B10	PB2C10
		A: 0.77" (19.56) B: 0.84" (21.34)			A: .85" (21.59) B: .76" (19.30)

Aluminum Raceway



Raceway (Anodized Aluminum)

Channel	Base 10ft. Lengths	Cover 5ft. Lengths	Duplex Receptacle	Rectangular Style Line®
Single	HBLALU3800B10	HBLALUC5	HBLALUDR	HBLALUG
Two	HBLALU4800B10	HBLALUC5		
		A: 2.25" (57.15) B: 3.00" (76.20)		
		A: 2.25" (57.15) B: 6.00" (152.40)		
			HBLALUF	HBLALUBL



Wire Basket Tray and Duct Systems

Hubbell Wire Basket Systems are designed to meet specific requirements. Pre-galvanized wire baskets are ideal for commercial and controlled interior environments while the stainless steel baskets are best suited for highly corrosive industrial applications such as food processing and marine.

Hubbell Trench and Wall Duct Systems are large capacity in-floor and in-wall management systems that enclose the wiring to X-Ray or MRI equipment. Ideal for retail facilities, open office workstations, fitness centers, casinos, medical facilities and libraries, the **Hubbell Under Floor Duct System** is an in-slab wire management product for delivering power, voice and data services. This system is uniquely designed with multiple compartments, allowing unlimited design options and cost savings in labor and materials from other single-compartment systems.

Features

- Wire basket pre-galvanized finish is environmentally friendly
- High capacity design supports large wiring for single and multiple service requirements while open top design allows wire to be easily laid in duct.



Wire Basket Trays



Flattened

.03125 sq. inch
"Flat" Wire Design

Flat Style Wire Basket Trays

Width x Length Inches (mm)	Pre-Galvanized	2" (51mm) Deep Black	Pre-Galvanized	6" (152mm) Deep Black
4" (102) x 118" (3000)	HBT0204S	HBT0204SBK	HBT0604S	HBT0604SBK
6" (152) x 118" (3000)	HBT0206S	HBT0206SBK	HBT0606S	HBT0606SBK
8" (203) x 118" (3000)	HBT0208S	HBT0208SBK	HBT0608S	HBT0608SBK
12" (305) x 118" (3000)	HBT0212S	HBT0212SBK	HBT0612S	HBT0612SBK
16" (406) x 118" (3000)	HBT0216S	HBT0216SBK	HBT0616S	HBT0616SBK
18" (457) x 118" (3000)	HBT0218S	HBT0218SBK	HBT0618S	HBT0618SBK
20" (508) x 118" (3000)	HBT0220S	HBT0220SBK	HBT0620S	HBT0620SBK

Wall and Trench Duct



Wall Duct Products

Hubbell's Wall Duct System is a large capacity in-wall management system that encloses the wiring to X-Ray machines or MRI equipment. The HBL Wall Duct System is available in steel or aluminum or versions and may be surfaced or flush mounted. Vertical runs along the wall are typically flush mounted while ceiling applications are typically surfaced mounted.

Trench Duct Products

The Hubbell Trench system is an in-floor wire management system for high capacity wiring needs that require multiple circuit separation. Trench duct is commonly used as a feeder system for medical wall duct when installing radiology equipment such as X-Ray and MRI machines. The HBL Trench Duct series is available in single, double, three and four compartment types providing a method of separating multiple services.

Under Floor Duct Products

The Hubbell Underfloor Duct system is an in-slab wire management product for delivering power, voice and data services for applications that include retail facilities, open office workstations, fitness centers, casinos, medical facilities and libraries. Eight duct profiles are available to accommodate numerous in-slab wire management for power and communications.



Ceiling Enclosures and Wall Enclosures and Boxes

AV Wall Boxes deliver high-density connectivity and power in the wall while the **Ceiling Enclosures** are designed to work with active AV devices to integrate AV distribution, data connections and power in one location, providing a direct connection to a projector or a display device. The **Hubbell Gangable AV Wall Boxes** are designed to be installed independently or ganged together to receive any number of devices, allowing them to accept any standard wallplate

Features

- The Hubbell Gangable AV Wall Boxes are the ideal solution for in wall applications requiring AV, data and power
- The FPTV Box allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords
- The AV Ceiling Box is a flush mounted white enclosure providing a consistent look when mounted in the ceiling

In the Wall Solutions



AV In-Wall Enclosure (FPTV)

Enclosure	Cover	Power Kits	
		Standard	Surge
2-Gang	NSAV62M	NSAV6C	NSOKP
4-Gang	NSAV124M	NSAV12C	NSOKPS



Large Capacity Wall Box with 2 Inch KOs

Description	Wall Box	Mud Rings (Height)				Low Voltage Partition
		1/2"	5/8"	3/4"	1"	
2-Gang 66.7 in. ³ capacity	HBL260	–	HBL818	HBL840	HBL819	HBL981
3-Gang 113.3 in. ³ capacity	HBL263	HBL792	HBL793	HBL794	–	HBL981



Wall Box

	Office White	Black
8"x11"x13"	WBW10W	WBW1BK



Two and Three Gang Gangable AV Wall Box with 2 Inch KOs

	Catalog Number	Low Voltage Partition
2-Gang 54 in. ³ capacity	HBL985	HBL989
3-Gang 79 in. ³ capacity	HBL986	

HBL985 and HBL986
with **HBL989**
Low Voltage Partition

In the Ceiling Solutions



Wireless Access Point Ceiling Box

Description	Universal WAP	Cisco® Aironet®
		1200 series
	WBC1	WBC12



AV Ceiling Enclosure

Description	Catalog Number
Flush mounted to ceiling 24"x12"x8" white enclosure (2) 20A Duplex and 2-gang back box	AVCE1H



Work Surface Connectivity Boxes and Table Top Boxes

This family of furniture and **Work Surface Connectivity Boxes** installs into conference tables and workstations to bring power, voice, data, and multimedia directly to the point of use. In addition, they offer an aesthetic design with improved cable management. Now, users can plug in laptops, projectors and other equipment at the desktop level — no more crawling under the table or moving obstacles to get to the electrical outlet and network connectivity.

Features

- Boxes are designed for easy installation and are available pre-wired or empty for field wiring.
- Convenient and attractive method for work surface power and data connections, these boxes are available in several finishes to match any decor.



Table Top Boxes



Low Voltage Only

Description	Finish	Blank Opening	XLR Microphone Jack
For 2 inch diameter hole configurations.	Black Anod. Alum.	TTBKSBK	TTBXLRBK
	Clear Anod. Alum.	TTBKSAAL	TTBXLRAL
	Solid Brass	TTBKSBR	TTBXLRRB

Pre-Wired Dual-Service

Description	Finish	(1) 15-pin and (1) 15A Outlet	(2) 15A Outlets
For 3.5" diameter hole configurations, 9 ft. power supply cord.	Black Anod. Alum.	TTBDS1BK	TTBDS2BK
	Clear Anod. Alum.	TTBDS1AL	TTBDS2AL
	Solid Brass	TTBDS1BR	TTBDS2BR

Furniture and Work Surface Connectivity Boxes



Flush Mount Boxes

	Square Flush Mount Box with Cover		Rectangular Flush Mount with Cover		Recessed Mount
Gang	Black Finish	Stainless Steel	Black Finish	Stainless Steel	Black Finish
2-Gang	HBLSHA2	HBLSHA2BSS	HBLPHA2	HBLPHA2BSS	HBLMIR2
4-Gang	—	—	HBLPHA4	HBLPHA4BSS	HBLMIR4

Surface and Under Desk Mount

	Surface Mount	Under the Desk Mount
Gang	Black Finish	Black Finish
2-Gang	HBLCON2	HBLMAR2
3-Gang	HBLCON3	HBLMAR3

Pre-Wired Work Surface Boxes



2x2 USB Work Surface Box

Finish	Catalog Number
Brushed Aluminum	WSBUSB2X2ALU
Black Powder Coat	WSBUSB2X2BLK

Lift-Up Style

Finish	Catalog Number
Black Finish	WSBC21UBK
Silver	WSBC21USV

HUBBELL®

Delivery Systems



Delivery eTour

This interactive, virtual tour of a city takes visitors through various commercial settings. As users navigate their way through the virtual city, the eTour demonstrates where and how Hubbell Delivery Systems products can be deployed in the floor, through the floor, on the wall, on the surface and from floor to ceiling and demonstrates solutions in these spaces.

Visit www.hubbell-wiring.com to take the tour.



Car
Dealership



Show Room




Product Page



Available Literature

Hubbell offers an extensive literature library for product support. Downloadable PDFs are available on line.



Hubbell Wiring
Device-Kellems Catalog



Hubbell Premise Wiring
Catalog



SystemOne Recessed
Floor Boxes



SystemOne Recessed
Fire-Rated Poke-Throughs

HUBBELL®
Wiring Systems

www.hubbell-wiring.com
www.hubbell-premise.com



Hubbell Wiring Device-Kellems
Hubbell Incorporated (Delaware)
40 Waterview Drive, Shelton, CT 06484
Phone (800) 288-6000 • FAX (800) 255-1031

Hubbell Premise Wiring
Hubbell Incorporated (Delaware)
23 Clara Drive • Mystic, CT 06355
Phone (800) 626-0005 • FAX (860) 535-8328

Printed in U.S.A. Specifications subject to change without notice. © Registered trademark of Hubbell Incorporated.

WLBVM009 8/15



Innovative Products Solutions
for Delivering
Power, Data and Audio Video