

Residential Product Guide



Table of Contents

Hubbell tradeSELECT® and netSELECT®

Select the best when it comes to electrical devices and voice/data products. Choose Hubbell for the superior performance, innovation and style your home deserves.

Energy Savings Like Never Before

Energy efficiency isn't just good for the environment – it's good for homeowners, too. Occupancy sensors and timers offer real energy savings so you can enjoy significant long-term, ongoing reductions in electric bills. Hubbell offers a range of options for controlling residential energy use. Sensors turn lights on when you need them, and automatically turn them off when you leave the room. Digital timers provide economic lighting and fan control with just the touch of a finger. LED-compatible dimmers allow you to control lighting levels, offering just the right atmosphere with comfort and convenience.

RDVCL153PW

DT5030W







WS2000W



Products for Your Home

Safety with Styling

When you think safety, think Hubbell. Our range of products makes a difference. GFCI and AFCI receptacles provide the best in people and fire protection, minimizing worry about shocks and electrical fires. Tamper-resistant receptacles reduce the risk of injury by preventing foreign objects from making electrical contact. New nightlight switches and receptacles provide a guiding light, with energy efficiency. But putting safety first doesn't mean that aesthetics should be ignored. To align with residential décor, Hubbell wiring devices are offered in a full range of designs that blend beautifully with furnishings and finishes.





Technology and the Interconnected World

To accommodate advanced electronic devices, homes need to be wired for the ever-changing pace of technology. Not only should wiring systems complement aesthetics, but they should also be efficient, reliable, and safe in order to support computers, televisions, and security systems. From network enclosures to USB charging outlets, Hubbell has a broad line of products that are specifically designed to support the connectivity and power needs of homeowners.





Enhanced Home Products



Decorator Night Lights

Night light switches and receptacles help light the way. Put light where safety is a concern for seniors and children: in the bedroom, along the hallway, and in the bathroom.





Countertop Pop Up Receptacles

Because spills happen. These pop up receptacles fit perfectly into the kitchen island. Pop-up receptacles provide power and are designed for use in compliance with NEC 406.5. UL tested and water resistant to a half gallon spill.





Occupancy Sensors


Saving energy has never been so easy. Have the lights turn on automatically when you are there and turn off when you're not. Excellent for the laundry, bathroom and walkthrough areas, basements and attics. Available in automatic and vacancy options, with time adjustments.



HUBBELL

netSelect[®] Structured Wiring

Use structured wiring cabinets and modules to locate and terminate all of your service provider and data connections. This network solution secures your voice/data and entertainment systems in one location. A modular approach makes it easy to upgrade, and keep pace with evolving technologies.



Conveniently charge portable electronics with combination USB chargers and power outlets. Perfect for the home office, these receptacles have standard electrical power along with high power 5 Amp USB ports for the maximum in charging capacity. Surge devices manage power quality and help protect electronics. Receptacles give you point of use protection, while panel protection is specifically designed to catch incoming power spikes from outside the home.





Residential floor box receptacles offer a solution to bring power where you need it. In large rooms, access to power may be needed in the center for lighting, entertainment systems, and everyday portable power for laptops and tablets. Floor boxes are the answer. Available in multiple finishes in metal and plastic to blend in to any design.

GFCI

GFCIs are people protection, eliminating power when there is a non-typical path to ground. Anywhere there is water, GFCI protection is recommended. Add a level of safety where people, power and water meet.

Flat Panel TV

Flat panel television enclosures deliver high-density connectivity for power in the wall. Allows for flat panel displays to sit flush against the wall with no dangling cords. Compatible with a wide variety of TV mounts, the entire system enables high-density cables to fit in the smallest footprint possible.




Standard and Decorator Switches

Decorator switches provide a sleek and appealing look. They are the perfect finishing touch to complement any interior. Easy to use, simply press the rocker. Night light switches help light the way. Increase security and safety to see where you are going.



Note: *Light glows through the top portion of the rocker when switch is in the OFF position. Does not require a neutral wire. **Light glows through the top portion of the rocker when switch is in the OFF position. Requires a neutral wire.




Description	Three (3)	Two (2)	Single Pole	Single Pole Switch,	Two (2)	Three Way Switch,
	Single Pole	Single Pole	and Three Way	Tamper-Resistant,	Three Way	Tamper-Resistant,
	Switches	Switches	Switch	Receptacle	Switches	Receptacle
Termination	Self-Grounding,	Self-Grounding,	Self-Grounding,	Self-Grounding,	Self-Grounding,	Self-Grounding,
	Side Wire	Side Wire	Side Wire	Side Wire	Side Wire	Side Wire
Rating	15A	15A	15A	15A 120V (switch)	15A	15A 120V (switch)
	120-277V AC	120-277V AC	120-277V AC	15A 125V (recept.)	120-277V AC	15A 125V (recept.)
Black	–	RCD101BK	RCD103BK	RCD108BKTR	RCD303BK	RCD308BKTR
Ivory	RCD111I	RCD101I	RCD103I	RCD108ITR	RCD303I	RCD308ITR
Light Almond	RCD111LA	RCD101LA	RCD103LA	RCD108LATR	RCD303LA	RCD308LATR
White	RCD111W	RCD101W	RCD103W	RCD108WTR	RCD303W	RCD308WTR



Toggle Switches

Description	Single Pole	Three Way	Four Way
Termination	Grounding,	Grounding,	Self-Grounding,
	Push and Side Wire	Push and Side Wire	Side Wire
Rating	15A 120V AC	15A 120V AC	15A 120V AC
Brown	RS115	RS315	RS415
Ivory	RS115I	RS315I	RS415I
Light Almond	RS115LA	RS315LA	RS415LA
White	RS115W	RS315W	RS415W



Description	Two (2)	Single Pole Switch,	Single Pole
	Single Pole	Tamper-Resistant	and Three Way
	Switches	Receptacle	Switch
Termination	Self-Grounding,	Self-Grounding,	Self-Grounding,
	Side Wire	Side Wire	Side Wire
Rating	15A 120V AC	15A 120V (switch) 15A 125V (recept.)	15A 120V AC
Brown	RC101	RC108TR	RC103
Ivory	RC101I	RC108ITR	RC103I
Light Almond	RC101LA	RC108LATR	RC103LA
White	RC101W	RC108WTR	RC103W

Note: *Neutral required for pilot light.



Sensors, Dimmers and Timers

Saving energy has never been so easy Sensors control the lights automatically. Occupancy sensors are designed to turn on when you are there, and off when you're not. All are adjustable for delayed off. Vacancy sensors are turned on like an ordinary switch, but automatically turn lights off.





Passive Infrared Occupancy S	ensors	CONTRACTOR OF			State of
Description	Color	Standard	Description	Color	Standard
Auto-ON/auto-OFF operation; 120/277V AC; 3-way capable	,	WS2000I WS2000LA WS2000W	Auto-ON/auto-OFF; two circuits; 120V AC only	lvory Light Almond White	WS1020I WS1020LA WS1020W
Auto-ON/auto-OFF operation; 120V AC only	,	WS1000I WS1000LA WS1000W	Manual-ON/auto-OFF; two circuits; 120V AC only	lvory Light Almond White	WS1021I WS1021LA WS1021W
Manual-ON/auto-OFF operation; 120V AC only	lvory White	WS1001I WS1001W			

Dimmers manage the precise amount of light, so you use exactly what you need. Developed for all types of home lamp loads: incandescent, compact fluorescent or LED. One dimmer does it all.





	mene	
Description	Rocker Dimmer	Toggle Dimmer
Rating	Inc/Halo 600W, CFL/LED 150W, 120V AC, 60Hz	Inc/Halo 600W, CFL/LED 150W, 120V AC, 60Hz
Termination	Single Pole/Three Way	Single Pole/Three Way
lvory Light Almond White	RDVCL153PI RDVCL153PLA RDVCL153PW	RAYCL153PI RAYCL153PLA RAYCL153PW



Count Down Timer Wall Switch

CFL/LED Dimmers

Description	Color	Catalog Number
30 Minutes: OFF, 5, 10, 20, 30	lvory Light Almond White	DT5030I DT5030LA DT5030W
60 Minutes: OFF, 15, 30, 45, 60	lvory Light Almond White	DT5060I DT5060LA DT5060W
12 Hours: OFF, 2, 4, 8, 12	lvory Light Almond White	DT5012I DT5012LA DT5012W

Note: Neutral required.

3 Speed Fan Speed Co	ntrols		
Description	Rocker Slide Adjustment	Toggle 3-Speed	
Rating	1.5A 120V AC	1.5A 120V AC	
Termination	Single Pole/Three Way	Single Pole/Three Way	
lvory Light Almond White	RDVFSQFI RDVFSQFLA RDVFSQFW	RAYFSQFI RAYFSQFLA RAYFSQFW	



Digital Timer Wall Switch

-			
960W @ 120V AC and 1200W @ 277V AC; 1/6hp			
Description	Color	Catalog Number	
Dip switch enabled preset intervals. User adjustable 1 min up to 4 hours,	White	DT2000W	
3-way capable. Includes an ON/OFF			
momentary push button switch feature.			

Note: Neutral required.

 $\overline{7}$

HUBBELL

Tamper-Resistant Receptacles

Put power where you need it, in style with Decorator receptacles. The same quality and performance as standard devices, but with a contemporary style. Tamper resistant devices prevent accidental insertion of a signal item, like pins and keys to help keep children safe. The Tamper Resistant mechanism is cam action for smooth insertion of plugs, like it is not even there.

Decorator Duplex Recepta 2 Pole, 3 Wire	cles,		
Description	Weather and Tamper-Resistant	Tamper-Resistant	Nightlight Receptacle
Termination	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire	Nightlight 0.5 Lumen Back and Side Wire
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R
Black Brown Gray Ivory Light Almond White	RRD15SBKWRTR RRD15SWRTR RRD15SGYWRTR RRD15SIWRTR RRD15SLAWRTR RRD15SWWRTR	RRD15SBKTR RRD15STR RRD15SGYTR RRD15SITR RRD15SLATR RRD15SWTR	– – DR15NLIV DR15NLLA DR15NLWH

		ALL D	No.
Decorator Single Recept 2 Pole, 3 Wire	1 m 1 m	11-	
Description	Tamper-Resistant	Tamper-Resistant	Standard
Termination	Self-Grounding,	Self-Grounding,	Self-Grounding,
	Side Wire	Side Wire	Side Wire
Rating	20A 125V	20A 125V	20A 250V
	NEMA 5-15R	NEMA 5-20R	NEMA 6-20R
Black	RRD151BKTR	RRD201BKTR	RRD205BK
Brown	RRD151TR	RRD201TR	RRD205
Grav	RRD151GYTR	RRD201GYTR	RRD205GY

8.6.0

RRD201ITR

RRD201LATR

RRD201WTR

CENE)

RRD205I

RRD205LA

RRD205W

8.5.0

RRD151ITR

RRD151LATR

RRD151WTR

The XClamp eliminates the need to loop the wire. Best solution for either 15 or 20 Amp branch circuits.

	p
	-
11	14
	1
1.1	D
9	5

XClamp Duplex Receptacles

Description	Color	Catalog Number
Tamper-Resistant, 15A 125V,	lvory	RR15SITRX
2 Pole, 3 Wire Grounding,	Light Almond	RR15SLATRX
20A Circuit Rated	White	RR15SWTRX



Duplex Recept 2 Pole, 3 Wire	Sector Manager 1		Single Receptacles, 2 Pole, 3 Wire				
Description	Weather and Tamper-Resistant	Tamper-Resistant	Description	Weather and Tamper-Resistant	Tamper-Resistant	Weather and Tamper-Resistant	Tamper-Resistant
Termination	Self-Grounding, Push and Side Wire	Self-Grounding, Push and Side Wire	Termination	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire	Self-Grounding, Side Wire
Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	Rating	15A 125V NEMA 5-15R	15A 125V NEMA 5-15R	20A 125V NEMA 5-20R	20A 125V NEMA 5-20R
Brown Gray Ivory Light Almond White	RR15SWRTR RR15SGYWRTR RR15SIWRTR RR15SLAWRTR RR15SWWRTR	RR15STR — RR15SITR RR15SLATR RR15SWTR	Brown Gray Ivory Light Almond White	RR151WRTR RR151GYWRTR RR151IWRTR RR151LAWRTR RR151WWRTR	RR151TR RR151GYTR RR151ITR RR151LATR RR151WTR	RR201WRTR RR201GYWRTR RR201IWRTR RR201LAWRTR RR201WWRTR	RR201TR RR201GYTR RR201ITR RR201LATR RR201WTR

lvory

White

Light Almond

Power Outlets and Specialty Receptacles

More power, better performance for appliances and heavy duty connections.





Range and Dryer Power Receptacles

	Description	Color	Cat. Number	Description	Color	Cat. Number
30A 125/250V NEMA 14-30R UL/CSA	Flush Mount for 1- or 2-Gang Box; 30A 125/250V 3 Pole, 4 Wire with Ground	Black White	RR430F RR430FW	Surface Mount; 30A 125/250V 3 Pole, 4 Wire with Ground	Black	RR430
50A 125/250V NEMA 14-50R UL/CSA	Flush Mount for 1- or 2-Gang Box; 50A 125/250V 3 Pole, 4 Wire with Ground	Black White	RR450F RR450FW	Surface Mount; 50A 125/250V 3 Pole, 4 Wire with Ground	Black	RR450

Recessed receptacles allow you to mount TVs flush or push furniture up against the wall without having to worry about the plug getting damaged or dislodged.





Recessed Receptacles

	Description	Color	Cat. Number	Description	Color	Cat. Number
ŪG	Recessed Duplex Receptacle,	,	RR1510I	Recessed Duplex Receptacle,	,	RR1510I
([[]w)	Tamper-Resistant,	Light Almond	RR1510LA	Tamper-Resistant,	Light Almond	RR1510LA
15A 125V NEMA 5-15R UL/CSA	2 pole, 3 wire, grounding, side wire terminations	White	RR1510W	2 pole, 3 wire, grounding, side wire terminations	White	RR1510W

JLOAD is the most compact combination "power/Audio/Video device" available, in the smallest footprint.





JLOAD[®] Multimedia Products

_						
	Description	Color	Cat. Number	Description	Material	Cat. Number
15A 125V NEMA 5-15R UL/CSA	JLOAD [®] Multimedia Outlet, Provides power, Cat. 5e and coaxial in a single gang box. Requires RJ600 Box. Includes	Black Ivory Light Almond White	RJ650BKTR RJ650ITR RJ650LATR RJ650WTR	JLOAD [®] Multimedia Box, 3" deep with seven ½-inch		
20A 125V NEMA 5-20R UL/CSA	decorator frame, one Cat. 5e, one F-connector and one power receptacle 125V with voltage dividers.*	Black Ivory Light Almond White	RJ620BKTR RJ620ITR RJ620LATR RJ620WTR	knockouts, non-metallic sheathed cable clamps on each side. Screw in mounting to stud		RJ600

Note: *Dividers provided for use with the RJ600, RF515 series and RU200 series boxes. RF408 required for use with the RF400 series floor boxes.

GFCI/AFCI Receptacles

Safety plus more. Tamper resistant and self-testing for the utmost in protection. GFCIs are people protection, eliminating power when there is an unintended path to ground, like when a person touches power. Required in most areas of the home where water may be present.





GFCI Receptacles

OLCI KEL	epiucies			Profile and	
Rating	Color	Standard	Night Light Two LED Night Lights	Combination Switch 15A 120V Switch	Weather and Tamper-Resistant
UG	Black	GFTRST15BK	GFTRST15BKNL	_	GFTWRST15BK
(🛛 🗍 w)	Brown	GFTRST15	GFTRST15NL	_	GFTWRST15
\smile	lvory	GFTRST15I	GFTRST15INL	GFSPST15I	GFTWRST15I
15A 125V NEMA 5-15R	Light Almond	GFTRST15LA	GFTRST15LANL	GFSPST15LA	GFTWRST15LA
UL CSA 0.5 HP	White	GFTRST15W	GFTRST15WNL	GFSPST15W	GFTWRST15W
UG	Black	GFTRST20BK	GFTRST20BKNL	_	GFTWRST20BK
([] þw)	Brown	GFTRST20	GFTRST20NL	-	GFTWRST20
\smile	lvory	GFTRST20I	GFTRST20INL	_	GFTWRST20I
20A 125V NEMA 5-20R	Light Almond	GFTRST20LA	GFTRST20LANL	_	GFTWRST20LA
UL CSA 1 HP	White	GFTRST20W	GFTRST20WNL	-	GFTWRST20W

AFCIs help protect against fire, eliminating power when it senses an arching, occurring when there is a damaged wire or cord set inserted into the outlet. Easily added to most living areas and bedrooms in the home for added protection.





Dual Function

AFCI/GFC	l Receptacles	808			80.8
Rating	Color	Standard	Rating	Color	Standard
15A 125V NEMA 5-15R UL CSA 0.5 HP	Black Brown Ivory Light Almond White	AFGF15TRBK AFGF15TR AFGF15TRI AFGF15TRLA AFGF15TRW	20A 125V NEMA 5-20R UL CSA 1 HP	Black Brown Ivory Light Almond White	AFGF20TRBK AFGF20TR AFGF20TRI AFGF20TRLA AFGF20TRW

Required by the NEC in specific rooms in the home, these are great for new construction as well a renovation to add more safety and protection.

Arc Fault AFCI Rece	eptacles				
Rating	Color	Standard	Rating	Color	Standard
15A 125V NEMA 5-15R UL CSA 0.5 HP	Black Brown Ivory Light Almond White	AFR15TRBK AFR15TR AFR15TRI AFR15TRLA AFR15TRW	20A 125V NEMA 5-20R UL CSA 1 HP	Black Brown Ivory Light Almond White	AFR20TRBK AFR20TR AFR20TRI AFR20TRLA AFR20TRW

USB Charging Receptacles

USBs give you more ways to charge your portable electronics. High power output - 5 Amps, the USB ports are capable of charging two devices simultaneously.



USB Charger Type-C		LINCERS .	LINE OF C
Description	Color	15A 125V	20A 125V
USB Charger Outlet:	Black	USB15C5BK	USB20C5BK
two Type-C port	Brown	USB15C5	USB20C5
configurations,	lvory	USB15C5I	USB20C5I
high power 5 Amp, 5 Volt	Light Almond	USB15C5LA	USB20C5LA
DC output, USB ports	White	USB15C5W	USB20C5W
rated 10,000 cycles			



USB Charger Combination	Type A&C	LOCATO -	COLORG
Description	Color	15A 125V	20A 125V
USB Charger Outlet: one Type A and one Type-C port configuration, high power 5 Amp, 5 Volt DC output, USB ports rated 10,000 cycles	Black Brown Ivory Light Almond White	USB15AC5BK USB15AC5 USB15AC5I USB15AC5IA USB15AC5LA USB15AC5W	USB20AC5BK USB20AC5 USB20AC5I USB20AC5LA USB20AC5W





Specialty USB Receptacles


....

sponally ore notoplation					
Description	Color	Catalog Number	Description	Color	Catalog Number
Switch Combo Outlet, two USB Type A ports, 2.1 Amp, 5 Volt DC, Style Line® decorator	Black Brown Ivory Light Almond White	USB102BK USB102 USB102I USB102LA USB102W	USB Charger 4 Port Outlet, four USB Type A ports, 5 Amp, 5 Volt DC, Style Line® decorator	Black Brown Ivory Light Almond White	USB4BK USB4 USB4I USB4LA USB4W

Compatible with USB1.1/2.0/3.0 devices in accordance with the battery charging spec for all phones and tablets.

Surge Protective Devices

Surge devices manage power quality and help protect electronics. Receptacles give you point of use protection, while panel protection is specifically designed to catch incoming power variations from outside the home.



Circuit Guard® Duplex Receptacl	es		
Specification Grade	; 240 Joules, 15kA Peal	k Current	
Description	Surge protection receptacle with light	Surge with light and alarm	Isolated ground, surge with light and alarm
lvory White	HBL5260ISA HBL5260WSA	HBL5262ISA HBL5262WSA	IG5262ISA IG5262WSA

Power Delivery Systems

Power where you need it, when you want it. Residential floor box receptacles offer an economical solution to bring power where you need it. Available in configurations for either slab on grade or wood subflooring, they come in multiple finishes to blend in.



Floor Boxes for Structural Wood Floors Mounts to Subfloor or Joists		6				Lan (A)
Description	Finish	Catalog No.	Finish	Catalog No.	Finish	Catalog No.
Decorator duplex floor box kit;	Solid Brass	RF515BR	Black Paint	RF515BK	Chrome Plated	RF515CH
steel box, flange and door assembly	Stainless Paint	RF515SS	Chestnut Brown Paint	RF515BN	Copper Plated	RF515CU
15A 125V receptacle	Almond Paint	RF515AL	Brass Plated	RF515BP	Nickel Plated	RF515NI
15A 125V receptacle	Almond Paint	RF515AL	Brass Plated	RF515BP	Nickel Plated	



Description	Rating	Finish	Catalog Number	Finish	Catalog Number
Flange and Hinged Door Cover Assembly. Includes tamper-resistant duplex receptacle	15A 125V NEMA 5-15R	Brushed Aluminum Brushed Brass Plated Solid Brass	RF406ALU RF406BP RF406BR	Almond Nylon Black Nylon Brown Nylon Gray Nylon	RF406AL RF406BK RF406BN RF406GY
PVC Floor Box Includes round box Max 6-inch (4% in	. diameter x 6.0 in.	Gray	RF400		

deep), four reducers, closure plugs, and concrete cover with locator flag.



SystemOne Fully Adjustable 4 inch **Recessed Floor Box for Concrete Floors**

Floor Boyos for Concrete Floors

Description Non-Metallic floor box; requires adjustable mounting cup, sold separately.

Adjustable Mounting Cup

Description

CFBS1R4PFB

Catalog Number



required for CFBS1R4 Series

Adjustable mounting cup for 4 inch floor boxes; floor boxes purchased independently from cup



SystemOne 4 inch Recessed Floor Box for Wood Floors	
Description	Catalog Number
Floor Box	AFBS1R4BASE

Architectural Covers				
Description	Finish	Catalog Number		
eerer ier dee mar	Brushed Aluminum Black Powder Coat	AFBS1R4CVRALU AFBS1R4CVRBLK		
	Brushed Aluminum Black Powder Coat	CFBS1R4CVRALU CFBS1R4CVRBLK		

Note: Other finishes available. See full line catalog for details.

Device Mounting Plates

For use with CFBS1R4 and AFBS1R4 Series floor boxes

(1) decorator opening and (2) jack openings

Sub-plate with



(4) single 20A receptacles S1R4SPQUAD





www.hubbell.com

Because spills happen. Pop-up receptacles provide a power source ideal for kitchen and bath counter tops. *UL listed 498 Section 146, for use in compliance with NEC 406.5. UL tested and water resistant to a half gallon spill.*



Counterton Recentacies



connerrop veceptacies				
Description	Finish	Color/Material	Surface Mount	Flush Mount
15A 125V Tamper-Resistant Pop-Up Kitchen Counter Receptacle, Rated for 20A circuits Cover: machined aluminum, Wiring chamber accepts 1/2" MC or non-metallic sheath cable	Powder Coated	Black White	RCT200BK RCT200W	RCT201BK RCT201W
	Brushed	Aluminum Brass Nickel	RCT200ALU RCT200BR RCT200NI	RCT201ALU RCT201BR RCT201NI
	Polished	Chrome	RCT200CH	RCT201CH
	Matte	Bronze	RCT200BZE	RCT201BZE



Desktop combination power and charging helps manage the home office. Ideal for work surfaces like desktops where computers and mobile electronics are used. The unit is supplied with a 5 foot cord and plug allowing it to be easily installed. Listed to UL962A for furniture power.

2X2 USB Work Surface Pop-Up Box

Description	Finish	Catalog Number	5 15.2.0
Equipped with a tamper-resistant duplex receptacle and two Type A USB charging ports; 15A 125 volt; 5" x 5" x 3.55" Max. surface thickness: 1.125"	Brushed Aluminum Black Powder Coat	WSBUSB2X2ALU WSBUSB2X2BLK	

Sometimes the best place for an outlet is to hide it under a cabinet or shelf. These outlet boxes comply for kitchen placement above or below the counter surface. Accommodates GFCIs and decorator receptacles.




Note: *Steel box with nylon cover.

Structured Wiring

The network solution that satisfies the need for dependable and flexible management of your voice/data and entertainment multimedia systems. This modular system makes it easy to upgrade, and keep pace with evolving technologies. Cabinets mount surface or recessed, between 16" studs. All are powder coated painted with 14 gauge steel for maximum impact resistance. Hinged cover can be mounted to swing from either side. Provisions to mount optional power outlets and lock kits.

Today's Communications Entail a Lot More Than Just Talking. netSELECT® Keeps You Connected—Internet, Voice, Data and Entertainment



Note: *Door covers rough-in, no trim ring provided.

HUBBELL

Network Modules

Modular components enable your design to match your performance requirements. Modules snap horizontally or vertically into the enclosures for optimum space management.



Catalog Number

NSOTVDM6

Combination Module

Description

6-port telephone panel, 6-port coaxial splitter, and 6-port Category 5e panel; Provides voice, video, and data distribution in a space efficient package; perfect for use with NSOBOX10 and NS790xx plates to quickly establish a comprehensive home network.





Description

Catalog Number 8-port phone outlets to manage up to (4) incoming lines for voice or accessory applications in a protected PCB module; RJ31X interface jack included for security

NSOPTM8

Data Module

Description

Category 5e data module, 8-port supports Gigabit Ethernet for up to (8) Category 5e data lines with front 110 punch-down terminations in a protected PCB module



NSODM8

Catalog Number

6-Way Coaxial Splitter Module Description



1GHz, basic unit with one incoming line and six outgoing

system connection; RJ45 jack interfaces with

optional NSOETM8 telephone expansion module for additional extensions.





Fixed Video Amplifier Module

Description

Provides 10dB video signal amplification for incoming cable feeds; Recommended for use when more than four outputs are installed; Provides 10dB forward path gain and supports current digital cable systems; Includes RG-59 cable jumper to connect amplifier to passive video splitter; 120 Volt rated

Catalog Number NSOVAMP

(i.e. switches, routers) or other devices onto a modular platform; can be custom drilled or used with two included self-adhesive VELCRO® strips

Blank Module Plate

Description



Catalog Number Allows mounting of active components NSOBM

Catalog Number

Multi-Provider Patchable Telecom Module

Description

NSOMTM12 12-port telephone module distributes 4 incoming lines out to 12 locations through RJ-45 jacks; allows data lines to be converted to voice with the move of a patch cord; RJ31X interface jack is included for security system connection

Entertainment Systems

Flat panel television enclosures deliver high-density connectivity for power in the wall. Allows for flat panel displays to sit flush against the wall with no dangling cords. Compatible with a wide variety of TV mounts, the entire system enables high density cables to fit in the smallest footprint possible.



FPTV Connection Enclosures

Description	Color	Catalog Number
2-gang in-wall enclosure 8.16"x7.92"x3.37"	White	NSAV62M
4-gang in-wall enclosure 14.80"x7.92"x3.37"	White	NSAV124M
New work stud brackets		NSAV6NW

Accessories		-	
Description	Surge protected power kit	1-port HDMI frame	2-port HDMI frame
Color	Blue	White	White
	NSOKPS	NS801W	NS802W
	N.		

snap fit snap fit snap fit snap fit jack Color White White White	White
snap fit snap fit snap fit jack	
Description HDMI F-connector Cat 5e	Cat 6 snap fit jack



Description	Color	1-Gang	2-Gang with Feed-Through	
15A 125V	lvory	RR1510I	RR1512I	RR1514I
Duplex	Lt Almond	RR1510LA	RR1512LA	RR1514LA
Receptacle	White	RR1510W	RR1512W	RR1514W

Two Gang AV Wallboxes	-
Description	Catalog Number

•	
2-Gang box, metal 2" KO,	HBL985
54 in ³ capacity; 4.21" x 4.06' x 4.00"	
Low Voltage AV Wallbox Partitions;	HBL989
Solid divider; Use with HBL985	

Wallbox		Ì
Description	Color	Catalog Number
2-Gang, nail-on box, thermoplastic	Blue	RR1500

HDMI Patch Cords, #24 AWG

Tamper-Resistant

Recessed Receptacles

	Statement of the local division in which the local division in the	-	
Length	HDMI Device Patch Cords	Length	Horizontal Cords (Connector to Connector)
3 ft. 6 ft.	HDPC03BK HDPC06BK		
			HDH20BK HDH25BK
		30 ft.	HDH30BK

Note: Black and Non-Plenum only.

NSC P	atch Cords	5	
Color	Length	Category 5e	Category 6
	1 ft.	NSC5EB01	NSC6B01
	3 ft.	NSC5EB03	NSC6B03
Blue	5 ft.	NSC5EB05	NSC6B05
Diue	7 ft.	NSC5EB07	NSC6B07
	10 ft.	NSC5EB10	NSC6B10
	15 ft.	NSC5EB15	NSC6B15

Note: Other colors available. See full line catalog for details.



Voice/Data Connections

Allows for the custom creation of multimedia outlets and workstations while maintaining a decorative look. Multimedia face plates offer a perfect match to electrical wallplates for a consistent finished look.



Description	Decorator Frame, One RJ11 Jack, 6-Position, 4-Conductor	Duplex RJ11 Jacks, 6-Position,	Decorator Frame, Single F-Type Coupler Bulkhead, Female to Female	Decorator Frame, Duplex F-Type Coupler Bulkhead, Female to Female	Decorator Frame, One Cat. 5e One F-Type Coupler Bulkhead, Female to Female
Termination	Screw Terminations	Screw Terminations	Screw Terminations	Screw Terminations	110 Punch-Down
Color					
lvory Light Almond White	NS770I NS770LA NS770W	NS772LA	NS780I NS780LA NS780W	NS782I NS782LA NS782W	NS785I NS785LA NS785W
Molded-In Plates for Voice and CATV/Satellite	· · ·		с () ()		- # -
Description	One F-Type One RJ11 Jack, 6-Position, 6-Conductor	One F-Type One RJ11 Jack, 6-Position, 4-Conducto	One F-Type Coupler Bulkhead, or Female to Female	Duplex F-Type Coupler Bulkhead Female to Female	
Color	Standard	Standard	Standard Mid	I-Size Standard	Standard Mid-Size
lvory Light Almond White	NS748I NS748LA NS748W	NS747I NS747LA NS747W	NS750LA NS	751I NS752I 751LA NS752LA 751W NS752W	NS730I NS735I NS730LA NS735LA NS730W NS735W
1-Gang Multimodia Wallal			•		
Multimedia Wallplo					
Color Ivory Light Almond White	1-Port NSP11I NSP11LA NSP11W	2-Port NSP12I NSP12LA NSP12W	3-Port NSP13I NSP13LA NSP13W	4-Port NSP14I NSP14LA NSP14W	6-Port NSP16I NSP16LA NSP16W

Unloaded Decorator Frames			Ē				
Color	1-Gang,	1-Gang,	1-Gang,	1-Gang,	1-Gang,	1-Gang, Adapter	1-Gang,
	1-Port	2-Port	3-Port	4-Port	6-Port	.406" Dia. Hole*	Adapter Blank**
Black	NS611BK	NS612BK	NS613BK	NS614BK	NS616BK	_	NS620BK
Ivory	NS611I	NS612I	NS613I	NS614I	NS616I	NS621I	NS620I
Light Almond	NS611LA	NS612LA	NS613LA	NS614LA	NS616LA	_	NS620LA
White	NS611W	NS612W	NS613W	NS614W	NS616W	NS621W	NS620W

Note: *For use with rotary dimmers or to pull through AV or telephone cable. **To fill an extra decorator opening or to create customized openings.

For a complete listing of Hubbell Wiring and Premise products, please see our full line catalogs.

Wallplates

Snap-on wallplates offer a clean, elegant look that can be installed in seconds. Thermoplastic plates are virtually unbreakable, an eighth inch larger than standard to hide rough box openings for improved aesthetics. Greater strength, impact and chemical resistance with excellent cleanability.

Snap-On Wallplates

Description	Color	1-Gang	2-Gang	3-Gang	4-Gang
Decorator	lvory	NPS26I	NPS262I	NPS263I	NPS264I
	Light Almond	NPS26LA	NPS262LA	NPS263LA	NPS264LA
	White	NPS26W	NPS262W	NPS263W	NPS264W
Toggle	lvory	NPS1I	NPS2I	NPS3I	-
	Light Almond	NPS1LA	NPS2LA	NPS3LA	-
	White	NPS1W	NPS2W	NPS3W	-



	1. Town Provider	* * * *
J		
	 a a a	a state of the sta

Decorator W	allplates				N N N
Description	Color	1-Gang	2-Gang	3-Gang	4-Gang
Nylon Standard	Black Brown Ivory Light Almond White	NP26BK NP26 NP26I NP26LA NP26W	NP262BK NP262 NP262I NP262LA NP262LA NP262W	NP263BK NP263 NP263I NP263LA NP263LA NP263W	NP264BK NP264 NP264I NP264LA NP264LA NP264W
Nylon Mid-size	Black Brown Ivory Light Almond White	NPJ26BK NPJ26 NPJ26I NPJ26LA NPJ26W	NPJ262BK NPJ262 NPJ262I NPJ262LA NPJ262LA NPJ262W	NPJ263BK NPJ263 NPJ263I NPJ263LA NPJ263LA NPJ263W	NPJ264BK NPJ264 NPJ264I NPJ264LA NPJ264LA NPJ264W

Note: 5-gang (NP265 series) and 6-gang (NP266 series) available.



Nvlon Black NPJ1BK NPJ2BK **NPJ3BK** NPJ4BK NPJ1 NPJ3 NPJ2 NPJ4 Mid-size Brown NPJ2I lvory NPJ1I NPJ3I NPJ4I Light Almond NPJ1LA NPJ2LA NPJ3LA NPJ4LA NPJ4W NPJ2W NPJ3W White NPJ1W

Note: 5-gang (NP5 series) and 6-gang (NP6 series) available.

All nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.



Description

Standard

Nylon

2-Gang Combination	1 Wallplates	18	81	
Description	Color	1-Toggle, 1-Duplex	1-Duplex, 1-Decorator	1-Toggle, 1-Decorator
Nylon Standard	Black Brown Ivory Light Almond White	NP18BK NP18 NP18I NP18LA NP18W	NP826BK NP826 NP826I NP826LA NP826W	NP126BK NP126 NP126I NP126LA NP126W
Nylon Mid-Size	Black Brown Ivory Light Almond White	NPJ18BK NPJ18 NPJ18I NPJ18LA NPJ18W	NPJ826BK NPJ826 NPJ826I NPJ826LA NPJ826W	NPJ126BK NPJ126 NPJ126I NPJ126LA NPJ126W

C. T

.

Duplex Receptacle	Wallplates	8	::
Description	Color	1-Gang, 1-Duplex	2-Gang, 2-Duplex
Nylon Standard	Black Brown Ivory Light Almond White	NP8BK NP8 NP8I NP8LA NP8W	NP82BK NP82 NP82I NP82LA NP82W
Nylon Mid-Size	Black Brown Ivory Light Almond White	NPJ8BK NPJ8 NPJ8I NPJ8LA NPJ8W	NPJ82BK NPJ82 NPJ82I NPJ82LA NPJ82W



3-Gang Combinatio	n Wallplates	115	
Description	Color	2-Toggle, 1-Duplex	2-Toggle, 1-Decorator
Nylon Standard	Black Brown Ivory Light Almond White	– NP28 NP28I NP28LA NP28W	NP226BK NP226 NP226I NP226LA NP226W
Nylon Mid-Size	Black Brown Ivory Light Almond White	– NPJ28 NPJ28I NPJ28LA NPJ28W	NPJ226BK NPJ226 NPJ226I NPJ226LA NPJ226W

Single Receptacle Wallplates		- Care	
Description	Color	1-Gang, 1-Single 2.16 in. Dia. Hole	2-Gang, 1-Single 2.16 in. Dia. Hole
Nylon Standard	Black Brown Ivory White	NP724BK NP724 NP724I NP724W	NP703BK NP703 NP703I NP703W
Nylon Mid-Size	Black Brown Ivory White	NPJ724BK NPJ724 NPJ724I NPJ724W	NPJ703BK NPJ703 NPJ703I NPJ703W

Metal Wallplates are also available. See our full line catalog for details.



Single 15/20A Straight Blade or 15A Twist-Lock® Receptacle Wallplates

Description	Color	1-Gang, 1-Single 1.40 in. Dia. Hole
Nylon Standard	Black Brown Ivory Light Almond White	NP7BK NP7 NP7I NP7LA NP7W
Nylon Mid-Size	Black Brown Ivory Light Almond White	NPJ7BK NPJ7 NPJ7I NPJ7LA NPJ7W

Weather Resistant Covers

NEMA 3R rated Extra Duty non-metallic while-in-use covers offer weather protection for outlets when they are in use. High impact polycarbonate construction provides maximum durability and longevity.

EXTRA DUTY® Non-Metallic While-In-Use Covers

Description	Dimensions Height x Width x Depth	EXTRA DUTY®
Standard size 1-gang box with clear tinted cover, for horizontal or vertical mounting; 16-in-1 configurations	5.90" X 4.18" X 2.75"	RW58300
Extra deep 1-gang box with clear tinted cover, for horizontal or vertical mounting; 16-in-1 configurations	5.92" X 4.20" X 4.75"	RW58350
Standard size 2-gang box, clear tinted cover, for horizontal or vertical mounting; 55-in-1 configurations	5.54" X 5.43" X 2.75"	RW58750



HUBBELL

a Device-Ke

Electric Vehicle Charging Station

The HBLEV30B Electric Vehicle Charging Station enables fast level 2 charging of any SAE J1772 compatible electric vehicle. This new EV charger delivers power and offers a more compact, easy to use and easy to install solution to electric vehicle charging.

Compatible with all Electric Vehicle Supply Equipment (EVSE) Codes, Standards and Recommended Practices, including SAE J1772, NEC 625, UL 2231 and UL 2594.

Level 2 Electrical Vehicle Charging Station

Description	Catalog Number
EV Charging Station; 30A 208-240V AC, 7.2 kW output, wall mount; 20 ft. charging cable, plug-in installation	HBLEV30B
EV Charging Station; 30A 208-240V AC, 7.2 kW output, wall mount 20 ft. charging cable, hardwire installation	HBLEV30BHW

- Water-resistant enclosure is rated UL Type 3R/S for indoor and outdoor use
- Time delay feature to delay charge times for more economical charging rates
- "Auto-reset" feature enables charging to restart following a minor fault, thereby reducing the chance of having an undercharged battery







Hubbell Wiring Device-Kellems Hubbell Incorporated (Delaware) 40 Waterview Drive, Shelton, CT 06484 Phone (800) 288-6000 • FAX (800) 255-1031

www.hubbell.com

Hubbell Premise Wiring Hubbell Incorporated (Delaware) 23 Clara Drive, Suite 103, Mystic, CT 06355 Phone (800) 626-0005 • FAX (860) 535-8328

