



# HUBBELL® Delivery Systems



Innovative Product Solutions  
for Delivering  
Power, Data and Audio Video





## Delivery Systems

Businesses today require a more intelligent and connected way of communicating than ever before. To support their ever-changing, ever-expanding requirements, Hubbell Delivery Systems products bring power, data, and audio/video solutions to wherever they're needed within a building. You've never had so many customized options for getting power, data, and AV from point A to point B: in or above the floor, through the floor, ceiling to floor, along the wall, or in the wall or ceiling. Hubbell product solutions revolutionize the way power, data, and AV are delivered.



### In the Floor/Above the Floor



From conference rooms, classrooms, and open offices to stages, security gates, and museum exhibits,

Hubbell's flush and recessed floor boxes accommodate the industry's broadest range of power, data, and AV applications in a single location: in or above the floor. Whatever your floor type, these solutions provide consistent aesthetics and unobtrusive power delivery options.

### Through the Floor



In all types of environments – even in raised-floor installations – bringing power, data, and

AV through the floor allows end-users to reconfigure with minimal downtime, and without worrying about power, data, and AV access. Ideal for retrofit applications, poke-through devices allow fire-safe, through-the-floor solutions that don't require leveling.

### Ceiling to Floor



Attractive, durable, customizable power poles effectively distribute power, fiber, and data cabling from

the ceiling to the floor. Available in varying lengths and colors, custom options maximize space and allow workstations, retail checkout areas, collaboration areas, digital signage, vending machines, appliances, and kiosks to be pulled away from the wall.

### TABLE OF CONTENTS

#### Floor Boxes

SystemOne Recessed	
with Rectangular Cover . . . . .	4
with Round Cover . . . . .	5
SystemOne Flush . . . . .	6
Flush, Recessed and	
Convention Center . . . . .	7

#### Fire-Rated Poke-Throughs

SystemOne	
Recessed . . . . .	8
Flush . . . . .	9
Fire-Rated Poke-Throughs . . . . .	10

#### Service Poles

Aluminum Service Poles . . . . .	11
Accessories . . . . .	11





### In and Along the Wall



Wall ducts, non-metallic and metal raceway delivery options feature mounted outlets and

are designed for enclosure of power and data cabling, as well as medical equipment wiring. Installing faster and neater than in-wall systems, Hubbell's along-the-wall delivery solutions make it easy to reconfigure interior spaces as requirements and uses change.

### In the Wall or Ceiling



Hubbell's in-wall and in-ceiling power, data, and AV solutions include options ranging from ceilings boxes

and large capacity wall boxes to flat panel TV enclosures. Airports, hospitals, offices, and schools all benefit from connectivity through a single wall or ceiling access point for electronic devices, digital signage, kiosks and displays, and projection systems.

### On the Surface



Table top and work surface boxes bring power, AV and charging solutions to the places it's needed most – at the work

surface, where computers, laptops, smartphones, tablets, projectors and other devices are often plugged in or charged. Convenient access to power, data and multimedia applications directly at the work surface area has become a common need in almost every business, educational, healthcare and hospitality environment.

#### Raceway, WireBasket Tray and Wall/Trench Duct

Metal . . . . .	12
Non-Metallic . . . . .	12
Wire Basket Tray . . . . .	13
Wall Duct . . . . .	13
Trench Duct . . . . .	13

#### In Wall Solutions

Flat Panel TV Enclosure . . . . .	14
Large Capacity Wall Box . . . . .	14
Gangable Wall Box . . . . .	14

#### In Ceiling Solutions

Wireless Access Box . . . . .	14
AV Ceiling Enclosure . . . . .	14

#### Table Top Boxes


Low Voltage and Pre-Wired . . . . .	15
-------------------------------------	----

#### Work Surface Boxes

Flush Mount/Lift Up Style . . . . .	15
USB Pop-Up Boxes . . . . .	15



## SystemOne Recessed Floor Boxes



SystemOne Recessed Floor Boxes are the newest addition to the Hubbell Delivery Systems family. Available in 2-, 4-, 6- or 10-gang capacities, these boxes are used in concrete, wood or raised access floors and can accommodate conduits from 1/2" up to 2". With traditional rectangular covers or plated round covers, SystemOne Recessed covers offer a common look in a multitude of architectural designs. Whether used in an atrium, lobby, conference room or server room, the new boxes and covers meet the demands of any project, anywhere.

The **Hubbell SystemOne Recessed Floor Box** line offers a common look regardless of capacity or installation. This simple concept ensures a consistent look throughout a building with rectangular or round covers. Round covers lend themselves to multi-story buildings, also using Fire-Rated Poke-Through devices. All SystemOne covers are ADA and UL514A compliant. The doors open to 180° for maximum access. Cables and plugs are protected by recessed connections.

## Rectangular Covers

### Concrete Floors



#### Floor Boxes - SystemOne for Concrete Floors with Rectangular Covers

Box Type	2-Gang		4-Gang		6-Gang	10-Gang
	3" Min. Pour Depth	2 1/2" Min. Pour Depth	3" Min. Pour Depth	2 1/2" Min. Pour Depth	3" Min. Pour Depth	5 1/2" Min. Pour Depth
Standard	<b>CFB2G30</b>	<b>CFB2G25</b>	<b>CFB4G30</b>	<b>CFB4G25</b>	<b>CFB6G30</b>	<b>CFB10G55</b>
On-grade	<b>CFB2G30CR</b>	<b>CFB2G25CR</b>	<b>CFB4G30CR</b>	<b>CFB4G25CR</b>	<b>CFB6G30CR</b>	<b>CFB10G55CR</b>



### Rectangular Covers

Surface Style covers are for use with carpet, tile, VCT and other engineered floors

Flush Style covers are for use with tile, finished concrete and Terrazzo floors

Style	For use with 2-Gang and 4-Gang Boxes			For use with 6-Gang and 10-Gang Boxes	
	Flat Surface	With Insert	Furniture Feed (2-Gang Only)	Flush Surface	With Insert
Surface	<b>24GCCVRxx</b>	<b>24GCCVRxxC</b>	<b>2GCFFCVRxx</b>	<b>610GCCVRxx</b>	<b>610GCCVRxxC</b>
Flush	<b>24GTCVRxx</b>	<b>24GTCVRxxC</b>	<b>2GTFFCVRxx</b>	<b>610GTCVRxx</b>	<b>610GTCVRxxC</b>

For cover powder coat finish replace xx with: **ALU** (Aluminum), **BK** (Black), **BRS** (Brass), **BRZ** (Bronze) or **NK** (Nickel)

## Raised Access Floors



#### Floor Boxes - SystemOne for Raised Access Floors

Box Type	2-Gang		4-Gang		10-Gang
	5" Box Depth	2 1/2" Box Depth	5" Box Depth	2 1/2" Box Depth	5 1/2" Box Depth
Standard*	<b>AFB2G50</b>	<b>AFB2G25</b>	<b>AFB4G50</b>	<b>AFB4G25</b>	<b>AFB10G55</b>

\* Add Suffix CHI for use in the City of Chicago.

### Rectangular Covers

Available in five powder coat finishes, these covers are for use with raised access tiles and wood floors. See Hubbell's online catalog for ordering information.

# SystemOne Recessed Floor Boxes

## Features

- Cables and connections are protected by recessed functionality
- Open architecture sub-plate design
- Common door layout regardless of flange for harmonized look
- Meets UL 514A scrub water requirements with ScrubShield® technology
- Easy selection with common look for all floor types
- Surface flange available for carpeted floors with 0.15 in. rise meets ADA requirements
- Hideaway egress doors fold under cover while in use
- 180° opening of main door
- 2, 4 and 6-Gang deep series floor boxes accept a 2 inch conduits with the use of CFBHUB2 adapter
- 10-Gang floor box features a 2 inch knockout



## Round Covers

### Concrete Floors



#### Floor Boxes - SystemOne for Concrete Floors with Round Covers

Box Type	2-Gang		4-Gang		6-Gang Deep	10-Gang
	3¾" Min. Pour Depth	3¼" Min. Pour Depth	3¾" Min. Pour Depth	3¼" Min. Pour Depth	3¾" Min. Pour Depth	6¼" Min. Pour Depth
Standard	<b>CFB2G30R</b>	<b>CFB2G25R</b>	<b>CFB4G30R</b>	<b>CFB4G25R</b>	<b>CFB6G30R</b>	<b>CFB10G55R</b>
On-grade	<b>CFB2G30RCR</b>	<b>CFB2G25RCR</b>	<b>CFB4G30RCR</b>	<b>CFB4G25RCR</b>	<b>CFB6G30RCR</b>	<b>CFB10G55RCR</b>



### Round Covers

Round covers are suitable for use with all floor types

Style	for use with 2-Gang		for use with and 4-Gang Boxes 6-Gang and 10-Gang Boxes
	Flush Surface	Furniture Feed	Flush Surface
Round	<b>CFBS1R6CVRxxx</b>	<b>CFBS1R6FFCVRxxx</b>	<b>CFBS1R8CVRxxx</b>

For cover finishes replace xxx with: **ALU** (Brushed Aluminum) **BLK** (Black Powder Coat), **BRS** (Brass Plated), **BRZ** (Bronze Plated) or **NK** (Nickel Plated)

### Raised Access Floors



#### Floor Boxes - SystemOne for Raised Access Floors

4-Gang Box Only	4-Gang Box with 8 in. Round Cover
6¼" Box Depth	Cover
<b>RAFB4BASE</b>	<b>RAFB4xxx</b>

For cover finishes replace xxx with: **ALU** (Brushed Aluminum) **BLK** (Black Powder Coat), **BRS** (Brass Plated), **BRZ** (Bronze Plated) or **NK** (Nickel Plated)

### Hubbell Connexion 2.0 Zone Distribution System

The Hubbell CONNEXION 2.0 Zone Distribution System is a factory assembled, flexible, modular system that delivers power in raised floor installations.

The SystemOne Line of Raised Access Floor Boxes works with the Hubbell Connexion Zone Distribution System.







## SystemOne Flush Floor Boxes

Featuring unique cover and sub-plate designs, the **Hubbell SystemOne Flush Floor Box** offering provides industry leading flexibility while accommodating an extensive range of applications. These floor boxes are constructed to give customers the ability to create personal solutions for their most demanding, power, data and audio/video requirements.

### Features

- Easily installed, aesthetic and configurable floor box solution, for open floor plan spaces for Multi-service, multimedia and 4x4 applications (4x4 applications have (4) power outlets and (4) data openings)
- The Hubbell SystemOne Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar and are available in black, gray, brass, aluminum and ivory powder coat finishes
- Subplates accommodate various power and data configurations



### Floor Boxes









Description	Cast Iron	Steel	Steel AV	Non-Metallic
Fully Adjustable, concrete cover, closure plugs and non-metallic low voltage divider is also included.	<b>S1CFB</b>	<b>S1SFB</b>	<b>S1SFB AV</b>	<b>S1PFB</b>



### Covers

Description	Finish	Aluminum	Brass	Black	Gray	Ivory
Cast aluminum	Carpet	<b>S1CFCAL</b>	<b>S1CFCBRS</b>	<b>S1CFCBL</b>	<b>S1CFCGY</b>	<b>S1CFCI</b>
Covers with Durable Tile		<b>S1TFCAL</b>	<b>S1TFCBRS</b>	<b>S1TFCBL</b>	<b>S1TFCGY</b>	<b>S1TFCI</b>

### Subplates

Description		Description		Description	
Style Line® Decorator/GFCI for power and/or datacom applications	 <b>S1SP</b>	Duplex/Duplex for power and/or datacom applications	 <b>S1SPDU</b>	Duplex/Style Line® Decorator for power and/or datacom applications	 <b>S1SPDUSL</b>
(4) 20A and (4) keystone openings. Power can be wired as single or two circuit and isolated ground.	 <b>S1SP4X4</b>	Single Receptacle Opening for 20A-30A Twist-Lock® recep. (1.56" OD) and (2) Keystone openings	 <b>S1SPTL</b>	Hubbell AV + Power (1) 20A, 125V receptacle and 3 unit recessed iSTATION opening for Data	 <b>S1SP3IM</b>
Carpet Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" NPT access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.	 <b>S1SPFFxx*</b>	Tile Furniture Feed Cover/Flange* (1) 3/4" and (1) 1 1/2" NPT access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	 <b>S1SPFFTxx*</b>		

\*Note: Furniture Feed available in the following finishes. Replace xx with desired finish. Aluminum (AL), Brass (BRS), Black (BL), Gray (GY) or Ivory (I). For full offering of SystemOne sub-plates and accessories, please visit our online catalog at [hubbell-wiring.com](http://hubbell-wiring.com).



## Flush Floor Boxes Ballroom and Convention Center

Hubbell offers a wide variety of traditional solutions including single and multi-gang **Cast Iron, Stamped Steel and Non-Metallic Floor Boxes** in both round and rectangular designs. These boxes can be finished with either brass or aluminum covers and flanges to match any office décor. All Hubbell floor box assemblies exceed UL scrub water exclusion requirements

### Features

- PVC, Stamped Steel, or Cast iron versions available
- UL 514A & ADA compliant
- Brass and Aluminum finishes




### Flush Round

Round Boxes		Rectangular Boxes			Round Covers			Rectangular Covers		
Non-Metallic	Cast Iron		Gang	Cast Iron	Stamped Steel	Description	Cat No.	Description	Type	Cat No.
Non-Metallic	<b>PFB1</b>	Deep Box	1	<b>B2436</b>	<b>B2431</b>	Brass Duplex Flap	<b>S3925</b>	Brass Duplex Flap		<b>S3825</b>
Cast Iron	<b>B2537</b>	with Brass Collar	2	<b>B4233</b>	<b>B2432</b>	Single Single Rec.	<b>S2925</b>	One Required	Single Rect.	<b>S2825</b>
Stamped Steel	<b>B2529</b>		3	<b>B4333</b>	<b>B2433</b>	Service Combination	<b>S2525</b>	Per Gang	Style Line®	<b>S3826</b>
									Blank	<b>S3813</b>

Also available in Aluminum.

### Recessed 7 and 11-Gang Concrete Floor Boxes



Boxes and Covers		7-Gang	11-Gang
Description	Min. Depth of Pour		
Boxes	4.08" (103.5)	<b>CFB7G4</b>	<b>CFB11G4</b>
	6.08" (154.3)	<b>CFB7G6</b>	<b>CFB11G6</b>
Flange and cover	Carpet Tile	<b>CFB7CVRxxx</b> <b>CFB7Txxx</b>	<b>CFB11CVRxxx</b> <b>CFB11Txxx</b>

xxx = finish. Aluminum (ALU) or Brass (BRS)

### Recessed Ballroom Series Floor Boxes



Boxes and Covers		Carpet Application	Tile Application
Description	Min. Depth of Pour		
Boxes	4.95" (127.0)	<b>CFB8FC1</b>	—
	7.15" (182.0)	—	<b>CFB8FC2</b>
Cover	Flush (2 egress doors) Blank	<b>CFB8CVRxxx1</b> <b>CFB8JBC1</b>	<b>CFB8CVRxxx2</b> <b>CFB8JBC2</b>

xxx = finish. Aluminum (ALU) or Brass (BRS)

### Metallic Convention Center Utility Boxes\*



Steel Convention Center Utility Box	Cover for Power, Data/Communications and Air/Water Box	Cover for Air/Water Only
Description		
Painted Galvanized Steel Box	<b>HBLSCCUBPD</b>	<b>HBLSCCUBW</b>
Stainless Steel Box	<b>HBLSCCUBPDSS</b>	<b>HBLSCCUBWSS</b>

\*All boxes provided with temporary galvanized steel concrete covers.  
\*\*Contact Hubbell for available configurations of power and data panels.

### Power and Data Panels\*\*

Custom manufactured and pre-wired to your project specifications. Panel options include 60A pin and sleeve, 20A and 30A Twist-Lock®, 20A GFCI, isolated ground or industrial straight blade devices.





## SystemOne Recessed Fire-Rated Poke-Throughs

Hubbell's **SystemOne Recessed 4, 6 and 8-inch Fire-Rated Poke-Throughs (FRPT)** enhance functionality providing increased power, data and audio visual capacity. Safety is improved with recessed connectivity, a low .125 inch profile flange, and egress doors that hinge inwards. Building value is enhanced with plated finishes to match and blend with modern building décor.

### Features

- Recessed connections
- Flush, durable, low profile covers are available in brushed brass plated, satin nickel plated, antique bronze plated, brushed aluminum and black powder coat
- Variety of subplates to accommodate various power and data configurations

### 4-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Power includes: pre-wired quad receptacles, (2) ½ in. EMT and (1) ¼ in. EMT	Brushed Aluminum	<b>S1R4PTQUADALU</b>	Satin Nickel Plated	<b>S1R4PTQUADNKL</b>
	Brushed Brass Plated	<b>S1R4PTQUADBRZ</b>	Black Powder Coat	<b>S1R4PTQUADBLK</b>
	Antique Bronze Plated	<b>S1R4PTQUADBRZ</b>	Gray Powder Coat	<b>S1R4PTQUADGRY</b>
Recessed Connectivity	Brushed Aluminum	<b>S1R4PTALU</b>	Satin Nickel Plated	<b>S1R4PTNKL</b>
	Brushed Brass Plated	<b>S1R4PTBRS</b>	Black Powder Coat	<b>S1R4PTBLK</b>
	Antique Bronze Plated	<b>S1R4PTBRZ</b>	Gray Powder Coat	<b>S1R4PTGRY</b>



### 6-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Data/AV includes: (2) pre-wired 20A receptacles with 18 in. leads plus (2) decorator openings including 2 in. EMT and ¼ in. EMT, (1) flange and cover assembly	Brushed Aluminum	<b>S1R6PTWZALU</b>	Satin Nickel Plated	<b>S1R6PTWZNKL</b>
	Brushed Brass Plated	<b>S1R6PTWZBRS</b>	Black Powder Coat	<b>S1R6PTWZBLK</b>
	Antique Bronze Plated	<b>S1R6PTWZBRZ</b>		
FRPT for Furniture Feed Applications (1) 2 in. EMT, (1) ¼ in. EMT, (1) flange and cover assembly	Brushed Aluminum	<b>S1R6PTFFALU</b>	Satin Nickel Plated	<b>S1R4PTNKL</b>
	Brushed Brass Plated	<b>S1R6PTFFBRS</b>	Black Powder Coat	<b>S1R4PTBLK</b>
	Antique Bronze Plated	<b>S1R6PTFFBRZ</b>		
Through floor fitting including 2 in. EMT and ¼ in. EMT	—	<b>S1R6PTFIT</b>		



### 8-Inch Recessed Fire-Rated Poke-Throughs

Description	Finish	Catalog Number	Finish	Catalog Number
For Data/AV includes: (4) pre-wired 20A receptacles with 18 in. leads plus (3) gangs with 2 in. EMT for data and AV, (1) flange and cover assembly	Brushed Aluminum	<b>S1R8PTZZ3ALU</b>	Satin Nickel Plated	<b>S1R8PTZZ3NKL</b>
	Brushed Brass Plated	<b>S1R8PTZZ3BRS</b>	Black Powder Coat	<b>S1R8PTZZ3BLK</b>
	Antique Bronze Plated	<b>S1R8PTZZ3BRZ</b>		
For Power includes: (4) pre-wired 20A receptacles with 18 in. leads plus 2-gangs with 2 in. EMT and 1 in. EMT (1) flange and cover assembly	Brushed Aluminum	<b>S1R8PTZZ2ALU</b>	Satin Nickel Plated	<b>S1R8PTZZ2NKL</b>
	Brushed Brass Plated	<b>S1R8PTZZ2BRS</b>	Black Powder Coat	<b>S1R8PTZZ2BLK</b>
	Antique Bronze Plated	<b>S1R8PTZZ2BRZ</b>		
Through floor fitting including 2 in. EMT for data and AV	—	<b>S1R8PTFIT3</b>		



### Hubbell SystemOne Universal Covers



Brushed Aluminum



Brushed Brass Plated



Antique Bronze Plated



Satin Nickel Plated



Black Powder Coat





## SystemOne Floor Flush Fire-Rated Poke-Throughs

Hubbell's offering of **SystemOne Flush Fire-Rated Poke-Throughs** provide installers with a broad range of options to support a wide array of connections. From multi-service and multimedia to 4X4 and furniture feed applications, Hubbell SystemOne Flush Fire-Rated Poke-Through products provide users the flexibility to create personal solutions for their most demanding applications.

### Features

- Easily installed, aesthetic and configurable floor box solution, for open floor plan spaces for Multi-service, multimedia and 4x4 applications
- The Hubbell SystemOne Universal Cover mounts directly to the floor box riser, eliminating the need for an additional adapter collar and are available in black, gray, brass, aluminum and ivory powder coat finishes
- Subplates accommodate various power and data configurations
- 4-Inch core holes




### Fire-Rated Poke-Throughs









Description	Finish	(4) 20A; (4) keystone	Dual Style Line	Modular AV	Furniture Feed
Factory Assembled units include through floor fitting, cover and sub-plate.	Aluminum	<b>S1PT4X4AL</b>	<b>S1PTAL</b>	<b>S1PT3IMAL</b>	<b>S1PTFFAL</b>
	Brass	<b>S1PT4X4BRS</b>	<b>S1PTBRS</b>	<b>S1PT3IMBRS</b>	<b>S1PTFFBRS</b>
	Black	<b>S1PT4X4BL</b>	<b>S1PTBL</b>	<b>S1PT3IMBL</b>	<b>S1PTFFBL</b>
	Gray	<b>S1PT4X4GY</b>	<b>S1PTGY</b>	<b>S1PT3IMGY</b>	<b>S1PTFFGY</b>
Through Floor Fittings	—	<b>S1PT4X4FIT</b>	<b>S1PTFIT</b>	<b>S1PTAVFIT</b>	—

### Covers

Description	Finish	Aluminum	Brass	Black	Gray	Ivory
Cast aluminum Covers with durable powder coat finish	Carpet	<b>S1CFCAL</b>	<b>S1CFCBRS</b>	<b>S1CFCBL</b>	<b>S1CFCGY</b>	<b>S1CFCI</b>
	Tile	<b>S1TFCAL</b>	<b>S1TFCBRS</b>	<b>S1TFCBL</b>	<b>S1TFCGY</b>	<b>S1TFCI</b>



### Subplates

Description		Description		Description	
Style Line® Decorator/GFCI for power and/or datacom applications	 <b>S1SP</b>	Duplex/Duplex for power and/or datacom applications	 <b>S1SPDU</b>	Duplex/Style Line® Decorator for power and/or datacom applications	 <b>S1SPDUSL</b>
(4) 20A and (4) keystone openings. Power can be wired as single or two circuit and isolated ground.	 <b>S1SP4X4</b>	Single Receptacle Opening for 20A-30A Twist-Lock® recep. (1.56 in. OD) and (2) Keystone openings	 <b>S1SPTL</b>	Hubbell AV + Power (1) 20A, 125V receptacle and 3 unit recessed iSTATION opening for Data	 <b>S1SP3IM</b>
Carpet Furniture Feed Cover/Flange* (1) ¼ in. and (1) 1½ in. NPT access holes for power and/or datacom applications. Universal Cover not required. Includes carpet flange.	 <b>S1SPFFxx*</b>	Tile Furniture Feed Cover/Flange* (1) ¼ in. and (1) 1½ in. NPT access holes for power and/or datacom applications. Universal Cover not required. Includes tile flange.	 <b>S1SPFFxx*</b>		

\*Note: Furniture Feed available in the following finishes. Replace xx with desired finish. Aluminum (AL), Brass (BRS), Black (BL), Gray (GY) or Ivory (I). For full offering of SystemOne sub-plates and accessories, please visit our online catalog at [hubbell-wiring.com](http://hubbell-wiring.com).





## Fire-Rated Poke-Throughs with 2 or 3 Inch Core

Hubbell offers a variety of single and multi-service **Flush Fire-Rated Poke-Through** products. It incorporates a Hubbell Style Line®, 20 amp, duplex receptacle and two Hubbell Category 5e data jacks. The jacks mount flush to the cover for an unobtrusive appearance. Flush and pedestal style **Furniture Feed Fire-Rated Poke-Throughs** deliver power and voice/data cabling to feed furniture systems.

### Features

- Available Flush and Pedestal Versions in metal and non-metallic covers
- UL514A scrub water compliant
- 2 or 3 Inch core holes

### 2X2 Poke-Through One-Piece Units (PT2X2FIT)

Description	Finish	Non-metallic Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A Style Line® decorator receptacle and (2) Category 5e data jacks	Black	<b>PT2X2BL</b>	<b>PT2X2IGBL</b>
	Gray	<b>PT2X2GY</b>	<b>PT2X2IGGY</b>



Description	Finish	Metal Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A Style Line® decorator receptacle and (2) Category 5e data jacks	Black/Brass	<b>PT2X2BRS3</b>	<b>PT2X2IGBRS3</b>
	Brass Finish/Brass	<b>PT2X2BRS</b>	<b>PT2X2IGBRS</b>



### Flush Duplex FRPT, One-Piece Units

Description	Finish	Non-metallic Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A duplex receptacle; flip lid cover with (2) ½ in. diameter low voltage feed-through holes	Black	<b>PT7FSDBLA</b>	—
	Brown	<b>PT7FSDBRA</b>	—
	Gray	<b>PT7FSDGYA</b>	<b>PT7IGFSDGYA</b>
	Ivory	<b>PT7FSDIA</b>	<b>PT7IGFSDIA</b>



Description	Finish	Metal Cover	
		Standard Receptacle	Isolated Ground
Pre-wired 20A duplex receptacle; flip lid cover with (2) ½ in. diameter low voltage feed-through holes	All Brass	<b>PT7FSDBRS2A</b>	<b>PT7IGFSDBRS2A</b>
	Black/Brass	<b>PT7FSDBRS3A</b>	—



### Flush Furniture Feed FRPT, One-Piece Units

Description	Finish	Three Service	
		Standard Receptacle	Isolated Ground
Aluminum cover with (2) ½ in. threaded hubs for low voltage and (1) ¼ in. threaded hub for power	Black	<b>PT73FFSDBK</b>	—
	Gray	<b>PT73FFSDGY</b>	—
	Ivory	<b>PT73FFSDI</b>	—



Description	Finish	Color	Single Service	
			Standard Receptacle	Isolated Ground
Aluminum cover with (1) KO to accept a ¼ in. connector	Black	Gray	<b>PT7FFSDGY</b>	—
	Gray	Ivory	<b>PT7FFSDI</b>	—



### Painted Pedestal FRPT

Description	Finish	Three Service	
		Standard Receptacle	Isolated Ground
Large Capacity Multi-Service Pedestal Through-Floor Fitting with (1) 1¼ in. EMT stem for low voltage and (1) ½ in. EMT stem for power applications.	Black	<b>PT7XC</b>	—



Description	Color	4-Gang		6-Gang	
		Standard Receptacle	Isolated Ground	Standard Receptacle	Isolated Ground
Pedestal Service Fittings (Order 1 plate per gang)	Gray	<b>FR480BKA</b>	—	<b>FR680BKA</b>	—
	Ivory	<b>FR480GYA</b>	—	<b>FR680GYA</b>	—





## Aluminum Service Poles

Hubbell offers a line of attractive and durable **Aluminum Service Poles** which distribute power and telecommunications wiring from above the ceiling to workstations below.

They are offered in lengths of 10' 2", 12' 2", and 15' 2" with a variety of electrical wiring devices. Poles with three service capability have a divider to separate power and low voltage wiring.

### Features

- Available in gray, ivory, black, white and office white painted and clear anodized aluminum
- Style Line® decorator duplex receptacles and two Style Line® knockouts for communications
- Includes ceiling trim mounting plate and scuff boot



### Three Service Aluminum Service Poles

Description	Height Feet (m)	10' 2" (3.10m)	12' 2" (3.71m)	15' 2" (4.62m)	
(2) 20A 125V Style Line® duplex receptacles; one circuit	Black	<b>HBLPP10BK</b>	<b>HBLPP12BK</b>	<b>HBLPP15BK</b>	
	Gray	<b>HBLPP10A</b>	<b>HBLPP12A</b>	<b>HBLPP15A</b>	
	Ivory	<b>HBLPP10AI</b>	<b>HBLPP12AI</b>	<b>HBLPP15AI</b>	
	Office White	<b>HBLPP10OW</b>	<b>HBLPP12OW</b>	<b>HBLPP15OW</b>	
	White	<b>HBLPP10W</b>	<b>HBLPP12W</b>	<b>HBLPP15W</b>	
Clear Anodized Aluminum		<b>HBLPP10AAL</b>	<b>HBLPP12AAL</b>	<b>HBLPP15AAL</b>	
	(1) Orange isolated ground 20A 125V Style Line® duplex receptacle; (1) 20A 125V Style Line® duplex receptacle; two circuits	Black	<b>HBLPP10IGBK</b>	—	—
		Gray	<b>HBLPP10IGA</b>	—	—
		Ivory	<b>HBLPP10IGAI</b>	—	—
		Office White	<b>HBLPP10IGOW</b>	—	—
White		<b>HBLPP10IGW</b>	—	—	
Clear Anodized Aluminum	<b>HBLPP10IGAL</b>	—	—		
(2) Orange isolated ground 20A 125V Style Line® duplex receptacles; (1) isolated ground surge suppression 20A 125V duplex receptacle; one circuit	Black	<b>HBLPP10SBK</b>	—	—	
	Gray	<b>HBLPP10SA</b>	—	—	
	Ivory	<b>HBLPP10SAI</b>	—	—	
	Office White	<b>HBLPP10SOW</b>	—	—	
	White	<b>HBLPP10SW</b>	—	—	
Clear Anodized Aluminum	<b>HBLPP10SAL</b>	—	—		
(1) 20A 125V GFCI Self Test duplex receptacle with (2) ground fault protected 20A 125V Style Line® duplex receptacles; one circuit.	Black	<b>HBLPP10GFBK</b>	<b>HBLPP12GFBK</b>	<b>HBLPP15GFBK</b>	
	Gray	<b>HBLPP10GF</b>	<b>HBLPP12GF</b>	<b>HBLPP15GF</b>	
	Ivory	<b>HBLPP10GFI</b>	<b>HBLPP12GFI</b>	<b>HBLPP15GFI</b>	
	Office White	<b>HBLPP10GFW</b>	<b>HBLPP12GFW</b>	<b>HBLPP15GFW</b>	
	White	<b>HBLPP10GFW</b>	<b>HBLPP12GFW</b>	<b>HBLPP15GFW</b>	
Clear Anodized Aluminum	<b>HBLPP10GFAL</b>	<b>HBLPP12GFAL</b>	<b>HBLPP15GFAL</b>		
Blank pole; divider; (4) Style Line® device knockouts	Black	<b>HBLPPOBK</b>	<b>HBLPPO12BK</b>	<b>HBLPPO15BK</b>	
	Gray	<b>HBLPPOA</b>	<b>HBLPPO12A</b>	<b>HBLPPO15A</b>	
	Ivory	<b>HBLPPOAI</b>	<b>HBLPPO12AI</b>	<b>HBLPPO15AI</b>	
	Office White	<b>HBLPPOOW</b>	<b>HBLPPO12OW</b>	<b>HBLPPO15OW</b>	
	White	<b>HBLPPOW</b>	<b>HBLPPO12W</b>	<b>HBLPPO15W</b>	
Clear Anodized Aluminum	<b>HBLPPOAAL</b>	<b>HBLPPO12AAL</b>	<b>HBLPPO15AAL</b>		



### Accessories

Description	
Adjustable T-bar assembly for mounting poles in the middle of ceiling tile.	<b>ATB</b>
Replacement service pole trim kit (office white).	<b>PPTRIM1</b>







## Metal and Non-Metallic Raceway

Hubbell's complete line of **Metal** and **Non-Metallic Raceway** is optimal for delivering power and technology to the point of use in laboratories, classrooms, offices and more while offering maximum flexibility for changing needs. Raceway offers the ability to provide standard convenience receptacles and datacomm connections, as well as serve the power requirements of larger equipment. Receptacles or datacomm ports can also be easily added where needed.

### Features

- Metal and Non-Metallic Raceways are available in a single and multi-channel as well as PlugTrak and Portable PlugTrak
- Hubbell Handi-Screw® eliminates difficult to install long screws for easier installation
- Aluminum Raceway resists oxidation, corrosion and fading and are available in single, dual and three channel with a wide selection of fittings and boxes

### Single Channel Metal Raceway



#### Raceway

Description	Color	HBL500	HBL700	HBL750	HBL4750	Single Channel Base	5 ft. Cover	7.5 In. Precut Cover*
Base and Cover	Ivory	<b>HBL5005IV</b>	—	<b>HBL7505IV</b>	Ivory	<b>HBL4750B10IV</b>	<b>HBL4750CIV</b>	<b>HBL4750C075IV</b>
	Ivory	<b>HBL50010IV</b>	<b>HBL700IV</b>	<b>HBL75010IV</b>	Gray	<b>HBL4750B10GY</b>	<b>HBL4750CGY</b>	<b>HBL4750C075GY</b>
	White	<b>HBL50010W</b>	<b>HBL700W</b>	<b>HBL75010W</b>				

	A: .53" (13.46) B: .76" (19.30)	A: .67" (16.90) B: .76" (19.30)	A: .85" (21.59) B: .76" (19.30)		A: 4.75" (120.65) B: 1.75" (44.45)	*Available in pre-cut lengths of 7.5 in. to 31.5 in.
--	------------------------------------	------------------------------------	------------------------------------	--	---------------------------------------	--



#### Boxes (HBL500, HBL700 and HBL750 Series)

Color	Low Profile Switch/Recept.	Alarm Device Box	Round Extension Box	Outlet Box
Ivory	<b>HBL5748SIVA</b>	<b>HBL5752IVA</b>	<b>HBL5737IVA</b>	<b>HBL5733IVA</b>
White	<b>HBL5748SWA</b>	—	<b>HBL5737WA</b>	—
Red	—	<b>HBL5752RA</b>	—	—



#### 2-Gang Cover Plates (HBL4750 Series)

Color	(2) Duplex	(1) Duplex, (1) Style Line®	(1) Style Line®, (1) Blank	(1) Single Round (1) Blank
Ivory	<b>HBL4747BBIV</b>	<b>HBL4747BRIV</b>	<b>HBL4747RXIV</b>	<b>HBL4747AXIV</b>
Gray	<b>HBL4747BBGY</b>	<b>HBL4747BRGY</b>	<b>HBL4747RXGY</b>	<b>HBL4747AXGY</b>

### Non-Metallic Raceway



#### Raceway (Office White)

Single Channel PP1		Two Channel PB2		
Length	Base and Cover	Length	Base	Cover
5 ft.	<b>PP1BC5</b>	5 ft.	<b>PB2B5</b>	<b>PB2C5</b>
7 ft.	<b>PP1BC7</b>	10 ft.	<b>PB2B10</b>	<b>PB2C10</b>

	A: 0.77" (19.56) B: 0.84" (21.34)		A: .85" (21.59) B: .76" (19.30)
--	--------------------------------------	--	------------------------------------

### Aluminum Raceway



#### Raceway (Anodized Aluminum)

Channel	Base 10ft. Lengths	Cover 5ft. Lengths	Duplex Receptacle	Rectangular Style Line®
Single	<b>HBLALU3800B10</b>	<b>HBLALUC5</b>	<b>HBLALUDR</b>	<b>HBLALUG</b>
Two	<b>HBLALU4800B10</b>	<b>HBLALUC5</b>		

	A: 2.25" (57.15) B: 3.00" (76.20)		Single Receptacle
	A: 2.25" (57.15) B: 6.00" (152.40)		Blank



## Wire Basket Tray and Duct Systems

**Hubbell Wire Basket Systems** are designed to meet specific requirements. Pre-galvanized wire baskets are ideal for commercial and controlled interior environments while the stainless steel baskets are best suited for highly corrosive industrial applications such as food processing and marine.

**Hubbell Trench and Wall Duct Systems** are large capacity in-floor and in-wall management systems that enclose the wiring to X-Ray or MRI equipment. Ideal for retail facilities, open office workstations, fitness centers, casinos, medical facilities and libraries, the **Hubbell Under Floor Duct System** is an in-slab wire management product for delivering power, voice and data services. This system is uniquely designed with multiple compartments, allowing unlimited design options and cost savings in labor and materials from other single-compartment systems.

### Features

- Wire basket pre-galvanized finish is environmentally friendly
- High capacity design supports large wiring for single and multiple service requirements while open top design allows wire to be easily laid in duct.



### Wire Basket Trays



Flattened

.03125 sq. inch  
"Flat" Wire Design

### Flat Style Wire Basket Trays

Width x Length Inches (mm)	2" (51mm) Deep		6" (152mm) Deep	
	Pre-Galvanized	Black	Pre-Galvanized	Black
4" (102) x 118" (3000)	<b>HBT0204S</b>	<b>HBT0204SBK</b>	<b>HBT0604S</b>	<b>HBT0604SBK</b>
6" (152) x 118" (3000)	<b>HBT0206S</b>	<b>HBT0206SBK</b>	<b>HBT0606S</b>	<b>HBT0606SBK</b>
8" (203) x 118" (3000)	<b>HBT0208S</b>	<b>HBT0208SBK</b>	<b>HBT0608S</b>	<b>HBT0608SBK</b>
12" (305) x 118" (3000)	<b>HBT0212S</b>	<b>HBT0212SBK</b>	<b>HBT0612S</b>	<b>HBT0612SBK</b>
16" (406) x 118" (3000)	<b>HBT0216S</b>	<b>HBT0216SBK</b>	<b>HBT0616S</b>	<b>HBT0616SBK</b>
18" (457) x 118" (3000)	<b>HBT0218S</b>	<b>HBT0218SBK</b>	<b>HBT0618S</b>	<b>HBT0618SBK</b>
20" (508) x 118" (3000)	<b>HBT0220S</b>	<b>HBT0220SBK</b>	<b>HBT0620S</b>	<b>HBT0620SBK</b>

### Wall and Trench Duct



#### Wall Duct Products

Hubbell's Wall Duct System is a large capacity in-wall management system that encloses the wiring to X-Ray machines or MRI equipment. The HBL Wall Duct System is available in steel or aluminum or versions and may be surfaced or flush mounted. Vertical runs along the wall are typically flush mounted while ceiling applications are typically surfaced mounted.

#### Trench Duct Products

The Hubbell Trench system is an in-floor wire management system for high capacity wiring needs that require multiple circuit separation. Trench duct is commonly used as a feeder system for medical wall duct when installing radiology equipment such as X-Ray and MRI machines. The HBL Trench Duct series is available in single, double, three and four compartment types providing a method of separating multiple services.

#### Under Floor Duct Products

The Hubbell Underfloor Duct system is an in-slab wire management product for delivering power, voice and data services for applications that include retail facilities, open office workstations, fitness centers, casinos, medical facilities and libraries. Eight duct profiles are available to accommodate numerous in-slab wire management for power and communications.



## Ceiling Enclosures and Wall Enclosures and Boxes

**AV Wall Boxes** deliver high-density connectivity and power in the wall while the **Ceiling Enclosures** are designed to work with active AV devices to integrate AV distribution, data connections and power in one location, providing a direct connection to a projector or a display device. The **Hubbell Gangable AV Wall Boxes** are designed to be installed independently or ganged together to receive any number of devices, allowing them to accept any standard wallplate

### Features

- The Hubbell Gangable AV Wall Boxes are the ideal solution for in wall applications requiring AV, data and power
- The FPTV Box allows flat panel displays and interactive "smart" boards to sit flush against walls with no dangling cords
- The AV Ceiling Box is a flush mounted white enclosure providing a consistent look when mounted in the ceiling

### In the Wall Solutions



#### AV In-Wall Enclosure (FPTV)

Enclosure	Cover	Power Kits	
		Standard	Surge
2-Gang	<b>NSAV62M</b>	<b>NSAV6C</b>	<b>NSOKP</b> <b>NSOKPS</b>
4-Gang	<b>NSAV124M</b>	<b>NSAV12C</b>	



#### Large Capacity Wall Box with 2 Inch KOs

Description	Wall Box	Mud Rings (Height)				Low Voltage Partition
		1/2"	5/8"	3/4"	1"	
2-Gang 66.7 in. <sup>3</sup> capacity	<b>HBL260</b>	-	<b>HBL818</b>	<b>HBL840</b>	<b>HBL819</b>	<b>HBL981</b>
3-Gang 113.3 in. <sup>3</sup> capacity	<b>HBL263</b>	<b>HBL792</b>	<b>HBL793</b>	<b>HBL794</b>	-	<b>HBL981</b>



#### Wall Box

	Office White	Black
8"x11"x13"	<b>WBW10W</b>	<b>WBW1BK</b>



**HBL985** and **HBL986**  
with **HBL989**  
Low Voltage Partition

#### Two and Three Gang Gangable AV Wall Box with 2 Inch KOs

	Catalog Number	Low Voltage Partition
2-Gang 54 in. <sup>3</sup> capacity	<b>HBL985</b>	<b>HBL989</b>
3-Gang 79 in. <sup>3</sup> capacity	<b>HBL986</b>	

### In the Ceiling Solutions



#### Wireless Access Point Ceiling Box

Description	Cisco® Aironet® 1200 series	
	Universal WAP	
	<b>WBC1</b>	<b>WBC12</b>



#### AV Ceiling Enclosure

Description	Catalog Number
Flush mounted to ceiling 24"x12"x8" white enclosure (2) 20A Duplex and 2-gang back box	<b>AVCE1H</b>





## Work Surface Connectivity Boxes and Table Top Boxes

This family of furniture and **Work Surface Connectivity Boxes** installs into conference tables and workstations to bring power, voice, data, and multimedia directly to the point of use. In addition, they offer an aesthetic design with improved cable management. Now, users can plug in laptops, projectors and other equipment at the desktop level — no more crawling under the table or moving obstacles to get to the electrical outlet and network connectivity.

### Features

- Boxes are designed for easy installation and are available pre-wired or empty for field wiring.
- Convenient and attractive method for work surface power and data connections, these boxes are available in several finishes to match any decor.



### Table Top Boxes



#### Low Voltage Only

Description	Finish	Blank Opening	XLR Microphone Jack
For 2 inch diameter hole configurations.	Black Anod. Alum.	<b>TTBKSBK</b>	<b>TTBXLRBK</b>
	Clear Anod. Alum.	<b>TTBKSAAL</b>	<b>TTBXLRAL</b>
	Solid Brass	<b>TTBKSBR</b>	<b>TTBXLRRB</b>

#### Pre-Wired Dual-Service

Description	Finish	(1) 15-pin and (1) 15A Outlet	(2) 15A Outlets
For 3.5" diameter hole configurations, 9 ft. power supply cord.	Black Anod. Alum.	<b>TTBDS1BK</b>	<b>TTBDS2BK</b>
	Clear Anod. Alum.	<b>TTBDS1AL</b>	<b>TTBDS2AL</b>
	Solid Brass	<b>TTBDS1BR</b>	<b>TTBDS2BR</b>

### Furniture and Work Surface Connectivity Boxes



#### Flush Mount Boxes

Gang	Square Flush Mount Box with Cover		Rectangular Flush Mount with Cover		Recessed Mount
	Black Finish	Stainless Steel	Black Finish	Stainless Steel	
2-Gang	<b>HBLSHA2</b>	<b>HBLSHA2BSS</b>	<b>HBLPHA2</b>	<b>HBLPHA2BSS</b>	<b>HBLMIR2</b>
4-Gang	—	—	<b>HBLPHA4</b>	<b>HBLPHA4BSS</b>	<b>HBLMIR4</b>

#### Surface and Under Desk Mount

Gang	Surface Mount		Under the Desk Mount
	Black Finish	Black Finish	
2-Gang	<b>HBLCON2</b>	<b>HBLMAR2</b>	
3-Gang	<b>HBLCON3</b>	<b>HBLMAR3</b>	

### Pre-Wired Work Surface Boxes



#### 2x2 USB Work Surface Box

Finish	Catalog Number
Brushed Aluminum	<b>WSBUSB2X2ALU</b>
Black Powder Coat	<b>WSBUSB2X2BLK</b>

#### Lift-Up Style

Finish	Catalog Number
Black Finish	<b>WSBC21UBK</b>
Silver	<b>WSBC21USV</b>



# HUBBELL®

## Delivery Systems



### Delivery eTour

This interactive, virtual tour of a city takes visitors through various commercial settings. As users navigate their way through the virtual city, the eTour demonstrates where and how Hubbell Delivery Systems products can be deployed in the floor, through the floor, on the wall, on the surface and from floor to ceiling and demonstrates solutions in these spaces.

Visit [www.hubbell-wiring.com](http://www.hubbell-wiring.com) to take the tour.



Car Dealership



Show Room




Product Page



### Available Literature


Hubbell offers an extensive literature library for product support. Downloadable PDFs are available on line.



Hubbell Wiring Device-Kellems Catalog



Hubbell Premise Wiring Catalog



SystemOne Recessed Floor Boxes



SystemOne Recessed Fire-Rated Poke-Throughs

**HUBBELL®**  
Wiring Systems

[www.hubbell-wiring.com](http://www.hubbell-wiring.com)  
[www.hubbell-premise.com](http://www.hubbell-premise.com)



Hubbell Wiring Device-Kellems  
Hubbell Incorporated (Delaware)  
40 Waterview Drive, Shelton, CT 06484  
Phone (800) 288-6000 • FAX (800) 255-1031

Hubbell Premise Wiring  
Hubbell Incorporated (Delaware)  
23 Clara Drive • Mystic, CT 06355  
Phone (800) 626-0005 • FAX (860) 535-8328



Innovative Products Solutions  
for Delivering  
Power, Data and Audio Video