



PROGRESS LIGHTING
DESIGN+SERIES™

2021



*INTRODUCING STATEMENT-
MAKING PIECES FROM OUR
DESIGN SERIES COLLECTION.*

Our Design Series fixtures feature artistic influence, fashion forward elements and details to contribute to affordable luxury for the home.

The fixtures found throughout the Design Series become the statement, the art piece and the focal point – and contribute to an overall luxurious experience in the home. They don't blend in. They stand out.

 **PROGRESS**
LIGHTING

TABLE OF CONTENTS

4 Pictorial Index
20 Guest Designer: Jeffrey Alan Marks
48 Design Series™ Inspiration
64 Point Dume™ Collection



88 Fixture Collections



182 Pendants



204 Sconces



212 Bath Collections



250 Outdoor
288 Index

To explore more of the Design Series™ visit us online:



- @ProgressLtg
- @ProgressLtg
- @ProgressLtg
- Progress Lighting
- @ProgressLighting
- Progress-Lighting

POINT DUME™ COLLECTION

POINT DUME™ COLLECTION

CHANDELIERS AND PENDANTS

WANDERMERE
Brushed Brass p.65



MOONRISE
Antique Nickel p.72



ONSHORE
Brushed Nickel p.69



ONSHORE
Brushed Brass p.68



ROCKDANCE
Antique Nickel p.79



ROCKDANCE
Aged Brass p.79



ROCKDANCE
Brushed Nickel p.79



ROCKDANCE
Aged Brass p.79



SANDBAR
Brushed Brass p.70



SANDBAR
Brushed Brass p.71



SEQUIT POINT
Antique Nickel p.81



SEQUIT POINT
Brushed Brass p.80



SHEARWATER
White p.77



SHEARWATER
Antique Nickel p.77



SHEARWATER
Aged Brass p.76



SURFRIDER
Galvanized p.67



POINT DUME™ COLLECTION

PENDANTS

SURFRIDER
Malibue p.67



SURFRIDER
Galvanized p.67



SURFRIDER
Malibue p.66



TAPIA TRAIL
Brushed Nickel p.84



TAPIA TRAIL
Aged Brass p.85



WINDBLUFF
Brushed Brass p.86



YERBA
Silver Ridge p.74



YERBA
Silver Ridge p.75



CLOSE TO CEILING

ROCKDANCE
Antique Nickel p.79



ROCKDANCE
Aged Brass p.79



SANDBAR
Brushed Brass p.71



SEQUIT POINT
Antique Nickel p.81



SEQUIT POINT
Brushed Brass p.80



TAPIA TRAIL
Brushed Nickel p.84



TAPIA TRAIL
Aged Brass p.85



YERBA
Silver Ridge p.75



POINT DUME™ COLLECTION

SCONCES / WALL BRACKETS

LATIGO BAY
Brushed Nickel p.82




LATIGO BAY
Antique Bronze p.83



LOOKOUT
Brushed Nickel p.73



ONSHORE
Brushed Brass p.69



SHEARWATER
Antique Nickel p.77



SHEARWATER
Aged Brass p.77



SURFRIDER
Antique Bronze p.67



SURFRIDER
White p.67



SURFRIDER
Galvanized p.67



SANDBAR
Brushed Brass p.71



YERBA
Silver Ridge p.75



COLLECTIONS

ADAGIO
Black p.96



ADAGIO
Black p.97



ASSEMBLY HALL
Brushed Nickel p.177



ASSEMBLY HALL
Antique Bronze p.176



DEBUT
Brushed Nickel p.139



DEBUT
Graphite p.140



ELEVATE
Matte Black p.106



ELEVATE
Polished Chrome p.108



ASTRA
Brushed Nickel p.120




ASTRA
Antique Bronze p.121



BLAKELY
Graphite p.102



BLAKELY
Graphite p.103



ELEVATE
Brushed Bronze p.110



EVOKE
Antique Bronze p.152



EVOKE
Polished Nickel p.154



FONTAYNE
Brushed Nickel p.146



BLAKELY
Graphite p.105



BONITA
Satin Brass p.170



BONITA
Matte Black p.171



BONITA
Brushed Nickel p.173



FONTAYNE
Antique Bronze p.144



GLAYSE
Brushed Nickel p.114



GLAYSE
Antique Bronze p.116



GLIMMER
Antique Bronze p.165



BONITA
Polished Chrome p.172



CINQ
Brushed Nickel p.181



CINQ
Antique Bronze p.180




CUMBERLAND
Matte Black p.92



GLIMMER
Silver Ridge p.164



GLIMMER
Antique Bronze p.166



GLIMMER
Silver Ridge p.166



GRESHAM
Graphite p.132



COLLECTIONS

GRESHAM
Graphite p.134



HANGAR
Brushed Nickel p.126



HANGAR
Brushed Nickel p.127



HANGAR
Antique Bronze p.128



RAE
Brushed Bronze p.94



RATIO
Brushed Nickel p.99



RATIO
Antique Bronze p.98



REMIX
Graphite p.142



HANGAR
Antique Bronze p.129



ION
Polished Nickel p.123



ION
Brushed Bronze p.122



LOOKING GLASS
Antique Bronze p.136



SPATIAL
Black p.124



SPICEWOOD
Gilded Iron p.150



TORRES
Matte Black p.100



TORRES
Matte Black p.101



LOWERY
Textured Black p.90



MARCHÉ
Polished Nickel p.168



MARQUE
Graphite p.178



MOD
Polished Chrome p.112



TURNBURY
Galvanized Finish p.148



UNION SQUARE
Stainless Steel p.130



UNION SQUARE
Stainless Steel p.131



WESTFALL
Antique Bronze p.174



NOMA
Antique Bronze p.156



NOMA
Polished Nickel p.158



ORRIZO
Black p.113



PALACIO
Vintage Gold p.118



WESTFALL
Graphite p.175



WEST VILLAGE
Brushed Nickel p.162




WEST VILLAGE
Antique Bronze p.160



PENDANTS

ADAGIO
Black p.96



ASSEMBLY HALL
Brushed Nickel p.177



ASSEMBLY HALL
Brushed Nickel p.176



BLAKELY
Graphite p.103



GALLEY
Polished Nickel p.187



GLAYSE
Antique Bronze p.117



GLAYSE
Brushed Nickel p.115



GLIMMER
Antique Bronze p.166



BONITA
Brushed Nickel p.173



BONITA
Satin Brass p.171



BONITA
Matte Black p.171



BONITA
Polished Chrome p.173



GLIMMER
Silver Ridge p.166



GRESHAM
Graphite p.135



GRESHAM
Graphite p.135



LOOKING GLASS
Antique Bronze p.137



CARBON
Polished Nickel p.203



CARBON
Graphite p.202



CHRONICLE
Antique Bronze p.190



CINQ
Brushed Nickel p.181



LOWERY
Textured Black p.90



MALBEC
Brushed Nickel p.194



MALBEC
Antique Bronze p.195



MALBEC
Graphite p.195



CINQ
Antique Bronze p.181



CUMBERLAND
Matte Black p.93



ELEVATE
Matte Black p.107



ELEVATE
Polished Chrome p.109



MARCHÉ
Polished Nickel p.169



MARQUE
Graphite p.178



MAULDIN
Brushed Nickel p.184



MAULDIN
Matte Black p.185



ELEVATE
Brushed Bronze p.111



ELLYSON
Brushed Bronze p.200



ERA
Matte Black p.196



FINN
Matte Black p.191




MESH
Antique Bronze p.198



MODERNA
Brushed Nickel p.201



NOMA
Polished Nickel p.159



NOMA
Antique Bronze p.157



FINN
Metallic Silver p.191



FONTAYNE
Antique Bronze p.145



FONTAYNE
Brushed Nickel p.147



GALLEY
Antique Bronze p.186



PALACIO
Vintage Gold p.119



PALACIO
Vintage Gold p.119



RATIO
Brushed Nickel p.99



RATIO
Antique Bronze p.98



PENDANTS

<p><i>REMIX</i> Graphite p.142</p> 	<p><i>SPATIAL</i> Black p.125</p> 	<p><i>SPATIAL</i> Black p.124</p> 	<p><i>SPICEWOOD</i> Gilded Iron p.151</p> 
<p><i>STAUNTON</i> Brushed Nickel p.189</p> 	<p><i>STAUNTON</i> Antique Bronze p.189</p> 	<p><i>STAUNTON</i> Graphite p.189</p> 	<p><i>TORRES</i> Matte Black p.101</p> 
<p><i>TURNBURY</i> Galvanized Finish p.149</p> 	<p><i>WESTFALL</i> Antique Bronze p.175</p> 	<p><i>WESTFALL</i> Graphite p.175</p> 	<p><i>WEST VILLAGE</i> Antique Bronze p.161</p> 
<p><i>WEST VILLAGE</i> Brushed Nickel p.163</p> 	<p><i>ZIN</i> Brushed Nickel p.193</p> 	<p><i>ZIN</i> Antique Bronze p.193</p> 	<p><i>ZIN</i> Graphite p.192</p> 

SCONCES / WALL BRACKETS

<p><i>ADAGIO</i> Black p.97</p> 	<p><i>ASTRA</i> Brushed Nickel p.121</p> 	<p><i>ASTRA</i> Antique Bronze p.121</p> 	<p><i>AVANA</i> Brushed Nickel p.207</p> 	<p><i>AVANA</i> Polished Nickel p.207</p> 
<p><i>BLAKELY</i> Graphite p.105</p> 	<p><i>BONITA</i> Antique Bronze p.209</p> 	<p><i>BONITA</i> Satin Brass p.209</p> 	<p><i>BONITA</i> Matte Black p.209</p> 	<p><i>BONITA</i> Brushed Nickel p.208</p> 
<p><i>BONITA</i> Polished Chrome p.209</p> 	<p><i>CAHILL</i> Brushed Bronze p.229</p> 	<p><i>CORDIN</i> Brushed Nickel p.211</p> 	<p><i>CUMBERLAND</i> Matte Black p.93</p> 	<p><i>DEBUT</i> Brushed Nickel p.139</p> 
<p><i>DEBUT</i> Graphite p.141</p> 	<p><i>ELEVATE</i> Matte Black p.107</p> 	<p><i>ELEVATE</i> Polished Chrome p.109</p> 	<p><i>ELEVATE</i> Brushed Bronze p.111</p> 	<p><i>GLAYSE</i> Brushed Nickel p.115</p> 
<p><i>GLAYSE</i> Antique Bronze p.117</p> 	<p><i>GLIMMER</i> Antique Bronze p.167</p> 	<p><i>GLIMMER</i> Silver Ridge p.167</p> 	<p><i>GRESHAM</i> Graphite p.135</p> 	<p><i>HANGAR</i> Brushed Nickel p.127</p> 
<p><i>HANGAR</i> Antique Bronze p.129</p> 	<p><i>HOBBS</i> Brushed Nickel p.210</p> 	<p><i>HOBBS</i> Polished Chrome p.210</p> 	<p><i>HOBBS</i> Antique Bronze p.210</p> 	<p><i>LOOKING GLASS</i> Antique Bronze p.137</p> 

SCONCES / WALL BRACKETS

LOWERY Textured Black p.91 *MARCHÉ* Polished Nickel p.169 *METRO* Polished Chrome p.206 *METRO* Brushed Nickel p.206 *METRO* Antique Bronze p.206



MOD Polished Chrome p.112 *ORRIZO* Black p.113 *PALACIO* Vintage Gold p.119 *RAE* Brushed Bronze p.95 *TORRES* Matte Black p.101



UNION SQUARE Stainless Steel p.131 *WEST VILLAGE* Brushed Nickel p.163 *WEST VILLAGE* Antique Bronze p.161 *ZURA* Brushed Nickel p.248 *ZURA* Polished Chrome p.249



ZURA Matte Black p.249



BATH

CAHILL Brushed Bronze p.228 *DEBUT* Brushed Nickel p.231 *DEBUT* Graphite p.230 *ELEVATE* Matte Black p.218



ELEVATE Polished Chrome p.221 *ELEVATE* Brushed Bronze p.220 *FLIGHT* Brushed Nickel p.232 *FLIGHT* Polished Chrome p.233



GLANCE Polished Chrome p.236 *GLAYSE* Brushed Nickel p.214 *GLAYSE* Antique Bronze p.215 *GLIDE* Brushed Nickel p.238



GLIDE Polished Chrome p.240 *GLIDE* Oil Rubbed Bronze p.241 *LISBON* Matte Black p.227 *LISBON* Polished Nickel p.226



METRIC Brushed Nickel p.244 *METRIC* Polished Chrome p.245 *MOD* Polished Chrome p.222 *SPATIAL* Black p.224



BATH

UNION SQUARE
Stainless Steel p.216



VOLO LED
Brushed Nickel p.246



WANDER
Brushed Nickel p.242



WANDER
Polished Chrome p.243



WANDER
Venetian Bronze p.243



WEST VILLAGE
Brushed Nickel p.235



WEST VILLAGE
Antique Bronze p.234



ZURA
Brushed Nickel p.248



ZURA
Polished Chrome p.249



ZURA
Matte Black p.249



OUTDOOR

CADENCE
Oil Rubbed Bronze p.258



CADENCE
Textured Black p.260



CHATSWORTH
Textured Black p.252



CREIGHTON
Antique Bronze p.270



CREIGHTON
Textured Black p.271



CULLMAN
Antique Bronze p.286



GIBBES STREET
Antique Bronze p.264



GIBBES STREET
Textured Black p.266



JANSSEN
Oil Rubbed Bronze p.280



KIAWAH
Textured Black p.272



LEAWOOD LED
White p.275



LEAWOOD LED
Textured Black p.274



MAISON
Textured Black p.262



MORRISON
Antique Bronze p.254



MORRISON
Antique Pewter p.256



PATEWOOD
Black p.282



SANTEE
Antique Bronze p.268



SANTEE
Matte Black p.269



UNION SQUARE
Stainless Steel p.284



VERDAE
Antique Bronze p.278



VERDAE
Textured Black p.279



WHITACRE LED
Antique Bronze p.276






JEFFREY ALAN MARKS

PROGRESS LIGHTING
DESIGN+SERIES™

A fitting collaboration between dreamer and maker.



DREAMER

Jeffrey's purposeful and authentic spaces beg to be lived in rather than existing only to be stylish. Today this Elle Décor A-List designer's spirited aesthetic is realized beyond his fortunate clients through licensing partnerships and a broader audience can look forward to homes that are more genuine, more personal and more engaging.

JEFFREY ALAN MARKS



INSPIRED BY

POINT DUME





Photo by Lisa Romerein

“I believe that lighting has a higher purpose, to be at once illuminating and decorative, purposeful and beautiful. Lighting is the ultimate marriage of form and function and the most transformative element in a design project. The very nature of light itself is inspirational.”

JEFFREY ALAN MARKS



Jeffrey's Point Dume™ lighting collection celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences. At home in a range of lifestyles from coastal to urban, the Collection is inspired by one of his favorite places, Point Dume, California, with

exceptional combinations of materials woven throughout. Emulating both the raw strength and the captivating honesty of the landscape, Jeffrey intuitively elevates lighting to a more authentic art form as he marries craftsmanship and style with some of his favorite materials and memories.



MAKER

In the eclectic Point Dume™ Collection, the dreamer and the maker are united by the desire to provide an elevated level of home fashion to an enthusiastic design-savvy consumer. As the inaugural guest designer of Progress' Design Series brand, Jeffrey's design goals are in sync with the Design Series

philosophy — to offer sophisticated styling at an accessible price. Together they are on a journey to inspire individuals to update the favorite spaces in their homes through fixtures that highlight artistic influence, rich finishes and fashion-forward elements.

POINT DUME™ COLLECTION







Featuring Point Dume™ Surfrider

Photo by Lisa Romerein



Featuring Point Dume™ Shearwater / Photo by Lisa Romerein



Featuring Point Dume™ Wandermere



Featuring Point Dume™ Wandermere





Featuring Point Dume™ Onshore



Featuring Point Dume™ Windbluff and Point Dume™ Sandbar



Featuring Point Dume™ Rockdance / Photo by Lisa Romerein



Photo by Lisa Romerein

Featuring Point Dume™ Yerba






Featuring Point Dume™ Latigo Bay / Photo by Lisa Romerein



Photo by Lisa Romerein

Featuring Point Dume™ Surfrider



“Beautiful lighting can appeal to both one’s pragmatic nature and one’s artistic spirit. For me, there is no better reward than to create well-loved spaces where life can be enjoyed fully and lived beautifully.”

JEFFREY ALAN MARKS



GOOD DESIGN HAS NO LIMITS

Test interior design limits by taking the chandelier out of the dining room and into the living room. Placed over a sofa in a richly layered and beautifully realized living room décor, it makes an artistic silhouette that punctuates a room and adds life to a tonal palette. The Rae chandelier doubles as a work of art, with its blend of geometric shapes and a sculpted, handcrafted frame finished in a glowing golden finish.

PLAYING WITH ANGLES

Basic geometry is anything but boring when you add shapely influences to your home for a unique touch of style. This foyer sets the stage for the first steps into your home as it plays up the geometric trend to the hilt with abstract artwork, a clean-lined X base console table, and a dramatic lighting fixture. Your guests will do a double-take as they gaze up at Cumberland, a unique geometric pendant finished in matte black frames and accented with circular seed glass panes. Its artistic "X" and "O" tic-tac-toe pattern echoes the geometry of the hall table for a design scheme that's sure to draw compliments.



Featuring Cumberland



Featuring Chatsworth

FIRST IMPRESSIONS COUNT

It only takes seven seconds to make a first impression, so make it count with your front entryway. Here, classic architectural style gets a modern vibe with an unadorned column and the elongated shape of the Chatsworth lantern.

*CLASSIC +
MODERN PLAY
WELL TOGETHER*

Exaggerated color and playful silhouettes abound in this living room that is a unique juxtaposition of modern and traditional styling. Traditional highboy and side table furnishings meld with the contemporary use of two circular stools as a coffee table. The simply charming Maudlin pendant at either end of an emerald couch adds symmetry and balances the bright color. Maudlin's geometric frames and clear seeded glass panes play off the diamond-patterned rug and showcase a modern twist on age-old classics.





SHADES OF BLACK AND GRAY

Turn the shiplap trend on its head by installing it vertically on the wall and painting it an accent color. The black vanity placed against the gray wall adds a moody, comforting tone to a serene bathroom. A pair of Bonita wall sconces flank an oversized mirror, adding understated elegance to the vignette. Contemporary ladder shelving displays bath necessities against an adjoining wall for additional visual flair.

A rustic mountain home interior featuring a stone fireplace, leather sofa, and dining table. The room has a high ceiling with exposed beams and a large stone fireplace in the center. A brown leather sofa is positioned in front of a large window with sheer curtains. A wooden coffee table with a metal base sits in front of the sofa. To the right, a white armchair and a brown leather ottoman are visible. In the background, a dining table with a wooden top and metal legs is set with a bowl of fruit. A large chandelier hangs from the ceiling, and a framed picture is mounted on the stone fireplace mantel.

RUSTIC MOUNTAIN HOME

Set the mood with a display of substantial style, Gresham's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection to highlight rustic-inspired spaces. Morrison and Fontayne complete the lighting design with complementary forms.

LAYER LIGHTING WITH GEOMETRIC ACCENTS

Circular elements featured in the mirror and Debut chandelier work together to provide dramatic focal points to this living space. Additionally, the Squire outdoor wall lantern was incorporated in a clever way in this interior setting to create a rich layer of light to contribute to the room's décor.



Featuring Debut and Squire



Featuring Zura

SLEEK AND SOPHISTICATED

One of the most important things to remember when illuminating your bathroom is to provide shadow-free lighting at the mirror. This bath area benefits from a generous amount of natural light, while our sleek and sophisticated Zura sconces placed on either side of the bathroom mirror work to further reduce shadows on the side of the face.

*MARBLE, GLASS &
GOLD – OH MY!*

Everyone deserves a little bit of luxe in his or her home. Sleek design, nature-inspired elements and ornate details make a statement within this lavishly designed setting. Our Palacio fixtures pair a Vintage Gold finish with faux white marble accents that complement the sophisticated glass spheres found in the Ellyson pendants.



MODERN ARTISTIC APPEAL

Raise the bar on modern design to a new artistic ideal. Warm colors, organic wood and shimmering metals create a welcoming contrast to cool white walls and contemporary art. The Lowery pendant and wall sconce add dramatic appeal with their free-form rectangular shapes finished in alternating textured black iron and softly distressed gold leaf. The Penn pendant's clear glass sphere topped with lustrous gold offers a touch of glamour over a polished wooden chest. The mixed metal theme continues in the dining area, where the Adagio pendant strikes a sculptural note above the table.

POINT DUME™ COLLECTION



POINT DUME™ / WANDERMERE

With elegant out-stretched arms and the grace of a Calder mobile, the Wandermere chandelier is “modern symmetry in balance.” Available in Brushed Brass with curved metal shades, the Wandermere is an architectural presence for any space.

*FINISH*

● Brushed Brass - 160

EIGHT LIGHT CHANDELIER

P400192-160 Brushed Brass
with white
40" dia., 28-1/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

*For additional chain, reference
the January 2021 Product
Supplement - P8755*

POINT DUME™ / SURFRIDER

Rows of lapping wave-like metal are combined with beautifully braided cords, and suspension hooks for an ageless “industrial meets the modern minded” point of view. The inspired Surfrider pendant is offered in a Galvanized finish and a refreshing “Maliblu” finish. To round out the versatile group, the Surfrider collection also includes complementary sconces available in Galvanized, Antique Bronze or White.



P500200-162



P500199-141



P500199-162



P500200-141



P500200-162



P710064-030



P710064-020



P710064-141

FINISHES

- Antique Bronze - 020
- White - 030
- Galvanized - 141
- Maliblu - 162

ONE-LIGHT PENDANT

P500199-141 Galvanized with white
P500199-162 Maliblu with white
 13-7/8" dia., 12-3/8" ht.
 Overall ht. w/hooks & chain 96-1/2",
 wire 15'.
 One medium base lamp,
 75w max.

THREE-LIGHT PENDANT

P500200-141 Galvanized with white
P500200-162 Maliblu with white
 24-7/8" dia., 17-1/2" ht.
 Overall ht. w/hooks & chain 103-1/2",
 wire 15'.
 Three medium base lamps,
 each 75w max.

WALL SCONCE

P710064-020 Antique Bronze
P710064-030 White
P710064-141 Galvanized
 9" W., 11-1/8" ht.
 Extends 3-7/8". H/CTR 6".
 Two candelabra base lamps,
 each 60w max.



For additional chain, reference
 the January 2021 Product
 Supplement - P8755

POINT DUME™ / ONSHORE

Continuing Jeffrey's modern take on light and movement, the Onshore series combines some of his favorite materials and finishes. Offered as a White and Brushed Brass pendant, or a "Maliblu" and Brushed Nickel option, the Onshore group is a fresh and uplifting choice for casual living. The Onshore swing arm wall sconce in Brushed Brass has a three-tiered white enamel shade that complements this lifestyle.



P500194-160



P500194-009



P500194-160

FINISHES

- Brushed Nickel - 009
- Brushed Brass - 160

ONE LIGHT PENDANT

P500194-009 Brushed Nickel with white and Maliblu
P500194-160 Brushed Brass with white
 8" dia., 13" ht.
 Overall ht. w/stem 79", wire 10'.
 One medium base lamp,
 100w max.

WALL BRACKET

P710070-160 Brushed Brass with white
 8-7/8" dia., 1-3/4" ht..
 Extends 22-1/2". H/CTR 4".
 One medium base lamp,
 60w max.

*For additional chain, reference
 the January 2021 Product
 Supplement - P8755*



P710070-160

POINT DUME™ / SANDBAR

Ageless Brushed Brass is layered in modern tiers for the Sandbar ceiling fixture, sconce and pendant light. The addition of Jeffrey's tailormade leather details, brass hooks, milk glass and cables make for memorable, luxury lighting with infinite design applications.



P500198-160



P350141-160



P350141-160
shown as semi-flush



P710068-160



P500198-160

FINISH

● Brushed Brass - 160

SEMI-FLUSH CONVERTIBLE

P350141-160 Brushed Brass with milk glass Hanging and ceiling mount hardware included. 15-1/8" dia., 14-7/8" ht. Overall ht. w/stem 76", wire 10'. Three medium base lamps, each 100w max.

THREE LIGHT PENDANT

P500198-160 Brushed Brass with milk glass and beige leather 21-1/4" dia., 14-7/8" ht. Overall ht. w/hook & chain 93-1/2", wire 15'. Three medium base lamps, each 100w max.


WALL SCONCE

P710068-160 Brushed Brass with milk glass 8-7/8" W., 12" ht. Extends 4-1/2". H/CTR 6". One candelabra base lamp, 60w max.

For additional chain, reference the January 2021 Product Supplement - P8755

POINT DUME™ / MOONRISE

Quintessential JAM, Moonrise is an ethereal globe fashioned of Antique Nickel and marbled white glass. With a nod to its vintage ancestry, this simple style statement manages to defy time and live quite happily in the present. Jeffrey recommends the simplicity of Moonrise's round silhouette the perfect choice when the design calls for multiples.



FINISH

● Antique Nickel - 081

THREE LIGHT PENDANT

P500204-081 Antique Nickel
with marble glass
18-1/2" dia., 19-1/4" ht.
Overall ht. w/chain 94", wire 15'.
Three medium base lamps,
each 100w max.

*For additional chain, reference
the January 2021 Product
Supplement - P8755*

POINT DUME™ / LOOKOUT

The Lookout wall sconce is a modern classic that combines Brushed Nickel, clear seeded glass and handsome leather accents. Perfectly at home in so many locations and lifestyles, the Lookout sconce is ideal to use when multiples are a must. The Lookout wall sconce has the enduring sensibility that adds an uncomplicated elegance to any interior.



FINISH

● Brushed Nickel - 009

ONE LIGHT WALL BRACKET

P710069-009 Brushed Nickel
with brown leather
6" W., 12-7/8" ht.
Extends 7-3/8". H/CTR 7-3/4"
One medium base lamp,
60w max

POINT DUME™ / YERBA

The Yerba group marries a modernized Moroccan shape with Mid-Century geometric detail. Crafted of pierced metal in a Silver Ridge finish, the Yerba collection offers an inverted pendant, a dome shaped pendant, ceiling mounted fixture and wall sconce, each casting dramatic dappled light throughout a space.



P500197-134



P500201-134



P710067-134



P350140-134



P500197-134

FINISH

- Silver Ridge - 134

THREE LIGHT SEMI-FLUSH

P350140-134 Silver Ridge
17-3/8" dia., 12-3/8" ht.
Three candelabra base lamps,
each 60w max.

FOUR LIGHT PENDANT

P500197-134 Silver Ridge
21-5/8" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Four medium base lamps,
each 60w max.

ONE LIGHT PENDANT

P500201-134 Silver Ridge
12" dia., 8-1/4" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.

ONE LIGHT WALL SCONCE

P710067-134 Silver Ridge
8-1/4" W., 12-1/2" ht.
Extends 3-7/8". H/CTR 6-1/4".
One candelabra base lamp,
60w max.



For additional chain, reference
the January 2021 Product
Supplement - P8755

POINT DUME™ / SHEARWATER

The Shearwater hanging lanterns and wall sconces embody Jeffrey's love of easy coastal living. His lighter lantern and sconce option combine Antique Nickel with clear glass and a soft-beige stitched leather handle, while the more traditional version combines Aged Brass, clear glass, and a handsome brown stitched leather handle. For a more California look, Jeffrey offers a White or Antique Nickel lantern with clear glass and his signature Maliblu accent as a pop of color in the roof of the fixture.



P500196-161



P500196-030



P500196-081



P500196-161



P710066-081



P710066-161

FINISHES

- White - 030
- Antique Nickel - 081
- Aged Brass - 161

FOUR LIGHT PENDANT

P500196-030 White with Maliblu and Brown Leather
P500196-081 Antique Nickel with Maliblu and Beige Leather
P500196-161 Aged Brass and Brown Leather
 16-1/4" dia., 32" ht.
 Overall ht. w/chain 109", wire 15'.
 Four candelabra base lamps, each 60w max.

ONE LIGHT WALL SCONCE

P710066-081 Antique Nickel with Beige Leather
P710066-161 Aged Brass with Brown Leather
 8" W., 15-7/8" ht.
 Extends 3-7/8. H/CTR 7-7/8".
 One candelabra base lamp, 60w max.



For additional chain, reference the January 2021 Product Supplement - P8755

POINT DUME™ / ROCKDANCE

The Rockdance Lighting series is a graceful series fashioned from unique glass, hook elements, and handsome stitched leather strapping. With the signatures of a bespoke handbag or boot, the surprising design elements that punctuate this exciting group are certain to become design favorites for generations. Available in Brushed Nickel or Antique Nickel with clear seeded glass or Aged Brass with mercury glass.



P500195-009



P500195-009



P500195-161



P500202-081



P500202-161



P350143-081



P350143-161

FINISHES

- Brushed Nickel - 009
- Aged Brass - 161
- Antique Nickel - 081

FOUR LIGHT SEMI-FLUSH

P350143-081 Antique Nickel with seeded glass with beige leather
P350143-161 Aged Brass with mercury glass and brown leather
 14-3/8" dia., 10-1/4" ht.
 Four candelabra base lamps, each 60w max.

ONE LIGHT PENDANT

P500195-009 Brushed Nickel with seeded glass and beige leather
P500195-161 Aged Brass with mercury glass and brown leather
 15-3/4" dia., 10-1/8" ht.
 Overall ht. w/hooks & chain 85-1/2", wire 10'.
 One medium base lamp, 100w max.

ONE LIGHT PENDANT

P500202-081 Antique Nickel with beige leather and seeded glass
P500202-161 Aged Brass with brown leather and mercury glass
 9-1/2" dia., 17-1/2" ht.
 Overall ht. w/hooks & chain 92-1/2", wire 10'.
 One medium base lamp, 100w max.

For additional chain, reference the January 2021 Product Supplement - P8755

POINT DUME™ / SEQUIT POINT

The romance and architectural presence of a lighthouse is expressed in the Sequit Point group. In the same way strips of glass increased the effectiveness of lighthouse beacons, the modern Sequit Point series benefits from a similar ingenuity. Mercury glass sleeves stand in tandem with clear glass rods to provide a familiar glow for the convertible ceiling fixture/pendant. Available in Antique Nickel and Brushed Brass.



P350142-160



P350142-081



P350142-160



P350142-081
shown as semi-flush



P350142-160
shown as semi-flush

FINISHES

- Antique Nickel - 081
- Brushed Brass - 160

SEMI-FLUSH CONVERTIBLE

P350142-081 Antique Nickel with mercury glass
P350142-160 Brushed Brass with mercury glass
 Hanging and ceiling mount hardware included.
 14" dia., 9-5/8" ht.
 Overall ht. w/stem 78", wire 10'.
 Three candelabra base lamps, each 60w max.

For additional chain, reference the January 2021 Product Supplement - P8755

POINT DUME™ / LATIGO BAY

The timeless Latigo Bay wall sconce hugs the wall with a simple lined Mercury glass back and an articulated curved metal shade. Predicted to be a classic go-to for a variety of easy interior updates, this slim vertical sconce is available in Antique Bronze and Brushed Nickel.



P710065-009



P710065-009



P710065-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

WALL SCONCE

P710065-009 Brushed Nickel with mercury glass
P710065-020 Antique Bronze with mercury glass
 7" W., 11" ht.
 Extends 4". H/CTR 5-1/2".
 One medium base lamp, 60w max.



POINT DUME™ / TAPIA TRAIL

Jeffrey creates two distinctive looks when combining first Aged Brass and milk glass and then timeless Brushed Nickel and seeded glass. Both versions of the Tapia Trail fixture are defined by rivet details and remind us of their industrial origins — part Nautical, part Farmhouse, all American.



P350139-009



P350139-009



P350139-161



P350139-009
shown as semi-flush



P350139-161
shown as semi-flush

FINISHES

- Brushed Nickel - 009
- Aged Brass - 161

SEMI-FLUSH CONVERTIBLE

P350139-009 Brushed Nickel with seeded glass
P350139-161 Aged Brass with milk glass
 Hanging and ceiling mount hardware included.
 11-3/4" dia., 12-7/8" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 One medium base lamp, 100w max.

For additional chain, reference the January 2021 Product Supplement - P8755

POINT DUME™ / WINDBLUFF

With sophisticated effortlessness, the Windbluff pendant was inspired by breezy shoreline living and incorporates Brushed Brass and natural linen. This transitional pendant, perfect for both modern and traditional interiors, is suspended by decorative brass hooks and thoughtfully has a white diffuser to create that perfect glow.



FINISH

● Brushed Brass - 160

THREE LIGHT PENDANT

P500203-160 Brushed Brass
with linen shade
20" dia., 16-1/2" ht.
Overall ht. w/hook & chain 91-1/2",
wire 15'.
Three medium base lamps,
each 100w max.

*For additional chain, reference
the January 2021 Product
Supplement - P8755*


DESIGN+SERIES™
COLLECTIONS



COLLECTIONS

LOWERY NEW

The Lowery collection raises the bar on contemporary design to a new artistic ideal. Layered rectangular shields finished in textured black iron are interposed with distressed gold leaf panels against a black frame. Lowery casts a shimmering reflective light that highlights the beautiful contrast between light and dark while adding a touch of glamour.



P500330-031



P500331-031



P500330-031



P350203-031



P710100-031



P350203-031
shown as semi-flush

COLLECTIONS

FINISH

- Textured Black - 031

PAIR WITH

- Adagio
- Orrizo
- Rae

SEMI-FLUSH CONVERTIBLE

P350203-031 Textured Black Hanging and ceiling mount hardware included. 19" dia., 15-3/8" ht. Overall ht. w/stem 78-1/2", wire 10'. Three medium base lamps, each 60w max.

FIVE-LIGHT PENDANT

P500330-031 Textured Black 26" dia., 20" ht. Overall ht. w/stem 86", wire 15'. Five medium base lamps, each 60w max.

SIX-LIGHT PENDANT

P500331-031 Textured Black 31-3/4" dia., 23-3/4" ht. Overall ht. w/stem 90", wire 15'. Six medium base lamp, each 60w max.

ONE-LIGHT WALL SCONCE

P710100-031 Textured Black 5-3/8" W., 15-1/8" ht. Extends 3-5/8". H/CTR 7-1/2". One candelabra base lamp, 60w max.



CUMBERLAND

Experience the sense of shelter, warmth, and protection offered by the Modern Mountain glow of the Cumberland collection. Let wandering eyes hungry for a satisfying lighting experience satiate their appetites as their gaze feasts upon the artistic “X” and “O” tic-tac-toe pattern intricately weaved into Matte Black frames. Signature circular seeded glass panes foster a gazing window design on each fixture in the collection to give Cumberland that rustic, modern cabin vibe.



P500233-031



P500232-031



P500233-031



P350159-031



P710076-031

FINISH

- Matte Black - 031

PAIR WITH

Looking Glass
Foster

TWO-LIGHT FLUSH MOUNT

P350159-031 Matte Black
13" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500232-031 Matte Black
16-7/8" sq., 27-5/8" ht.
Overall ht. w/stem 94", wire 15'.
Eight candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT

P500233-031 Matte Black
16-1/8" sq., 17-1/8" ht.
Overall ht. w/stem 83", wire 15'.
Five candelabra base lamps,
each 60w max.


WALL SCONCE

P710076-031 Matte Black
5-1/8" W., 14-5/8" ht.
Extends 4". H/CTR 7-1/4".
One candelabra base lamp,
60w max.



RAE

Execute bold visions and design statements with the Rae Collection. A blend of geometric shapes and a sculpted, hand artisan frame with a golden finish bring this modern collection to life for an awe-inspiring lighting experience guaranteed to spark conversation amongst your gazing guests.



P400216-109



P400217-109



P710078-109



P350158-109



P350158-109
shown as semi-flush

COLLECTIONS

FINISH

● Brushed Bronze - 109

PAIR WITH

Palacio
Evoke

SEMI-FLUSH CONVERTIBLE

P350158-109 Brushed Bronze
18" dia., 8-1/2" ht.
Hanging and ceiling mount
hardware included.
Overall ht. w/chain 73-1/2", wire 10'.
3 candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400216-109 Brushed Bronze
26-7/8" dia., 14" ht.
Overall ht. w/chain 80", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400217-109 Brushed Bronze
30-1/2" dia., 21-5/8" ht.
Overall ht. w/chain 87-1/2", wire 15'.
Nine candelabra base lamps,
each 60w max.

WALL SCONCE

P710078-109 Brushed Bronze
5-1/2" W., 15" ht.
Extends 3-3/4". H/CTR 7-1/2".
Two candelabra base lamps,
each 60w max.



ADAGIO


An array of geometric patterns in Adagio is a nod to the musical description of a tender and melodic tone. The modern design features lights that are distributed around a circular band. Mixed metal elements, which are present in Brushed Silver and Brushed Gold accents, can complement monochromatic color palettes that are popular in homes today. Each fixture in the Adagio collection creates a focal point and is ideal for Luxe and Modern interiors.




P500174-031



P400170-031



P710057-031



P500173-031

COLLECTIONS

FINISH

● Matte Black - 031

PAIR WITH

Orrizo
Glaysé

SIX-LIGHT ISLAND

P400170-031 Matte Black
38" W., 16-3/8" ht., 7" d.
Overall ht. w/stem 82-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

MINI-PENDANT

P500173-031 Matte Black
12" dia., 14-5/8" ht.
Overall ht. w/stem 80", wire 10'.
One medium base lamp,
75w max.

SIX-LIGHT PENDANT

P500174-031 Matte Black
24" dia., 26" ht.
Overall ht. w/stem 87-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWO-LIGHT WALL SCONCE

P710057-031 Matte Black
11" W., 15-1/2" ht.
Extends 6". H/CTR 7-3/4".
Two G16.5 candelabra base lamps,
each 60w max.

RATIO

A sleek metal frame supports a low-slung shade to create Ratio's casual modern style. The frame's proportion to the white linen drum shade evokes a perfect ratio for lighting. All fixtures include a polished glass diffuser that offers an elegant appeal.



P5015-20



P3604-09
shown as
pendant



P3604-09
shown as semi-flush



P5015-09



P5021-09



P3604-20



P5021-20

COLLECTIONS

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH

- Metric
- Finn
- Glaysé

SEMI-FLUSH CONVERTIBLE

P3604-09 Brushed Nickel
P3604-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 16" dia., 11-1/2" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5015-09 Brushed Nickel
P5015-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 24" dia., 15-7/8" ht.
 Overall ht. w/stem 82", wire 10'.
 Four medium base lamps, each 75w max.

SIX-LIGHT PENDANT

P5021-09 Brushed Nickel
P5021-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 30" dia., 19-1/8" ht.
 Overall ht. w/stem 85", wire 10'.
 Six medium base lamps, each 75w max.

TORRES

Elevate your Modern Mountain home décor by incorporating ravishing rustic design in the heart of your home with the Torres Collection. Handcrafted spires reminiscent of rugged forest surroundings coalesce in cultivated masterpieces of rustic sophistication. Beautiful black, blunt edges crisscross in open-cage designs for an organic interpretation of the popular tic-tac-toe pattern.



P400213-031



P400215-031



P710077-031



P500248-031

COLLECTIONS

FINISH

- Textured Black - 031

PAIR WITH

Looking Glass
Spicewood

FOUR-LIGHT CHANDELIER

P400213-031 Textured Black
18" dia., 11-5/8" ht.
Overall ht. w/stem 77-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT ISLAND

P400215-031 Textured Black
40" W., 11-3/8" ht., 14" d.
Overall ht. w/stem 77-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500248-031 Textured Black
16" dia., 22" ht.
Overall ht. w/stem 88", wire 15'.
Four candelabra base lamps,
each 60w max.

WALL SCONCE

P710077-031 Textured Black
8" W., 22" ht.
Extends 3-7/8". H/CTR 11".
Two candelabra base lamps,
each 60w max.



BLAKELY

The Blakely collection has two unique and fashion-forward design styles. Choose between a rectangular frame or an open linear form. Both styles celebrate geometric interplay with clean, straight lines. Finished in Graphite with satin brass accents, the Blakely collection is ideal for Modern and Traditional interiors.



P500168-143



P350120-143



P350120-143
shown as semi-flush



P500168-143



P400086-143

COLLECTIONS

FINISH

● Graphite - 143

PAIR WITH

Rae
Rainey

SEMI-FLUSH CONVERTIBLE

P350120-143 Graphite
Hanging and ceiling mount hardware included.
17-1/4" W., 9-3/8" ht.
Overall ht. w/chain 74-1/2", wire 10'.
Two medium base lamps, each 60w max.

FOUR-LIGHT ISLAND

P400086-143 Graphite
40-7/8" W., 17-1/4" ht., 11" depth.
Overall ht. w/stem 82-1/2", wire 15'.
Four medium base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500168-143 Graphite
23-1/4" W., 25-3/4" ht.
Overall ht. w/stem 91-1/2", wire 15'.
Four medium base lamps, each 60w max.

BLAKELY

FINISHES

- Brushed Nickel - 009
- Polished Nickel - 104
- Brushed Bronze - 109
- Graphite - 143

TWO-LIGHT WALL BRACKET

P300214-143 Graphite
 8-1/4" W., 9-3/8" ht.
 Extends 4-7/8". H/CTR 5-5/8".
 Two candelabra base lamps,
 each 60w max.

TWO-LIGHT FLUSH MOUNT

P350121-009 Brushed Nickel
P350121-104 Polished Nickel
P350121-109 Brushed Bronze
 13-5/8" dia., 5-3/4" ht.
 Two medium base lamps,
 each 60w max.

FOUR-LIGHT CHANDELIER

P400179-143 Graphite
 20" W., 15-5/8" ht.
 Overall ht. w/stem 82", wire 15'.
 Four candelabra base lamps,
 each 60w max.

SIX-LIGHT CHANDELIER

P400113-143 Graphite
 28" W., 15-5/8" ht.
 Overall ht. w/stems 82", wire 15'.
 Six candelabra base lamps,
 each 60w max.

SIX-LIGHT ISLAND

P400114-143 Graphite
 40" W., 15-5/8" ht., 15" d.
 Overall ht. w/stems 82", wire 15'.
 Six candelabra base lamps,
 each 60w max.



ELEVATE

Achieve a sleek and modern look with Elevate. Etched glass white shades paired with a Matte Black, Brushed Bronze or Polished Chrome frame provide an elegant contrast for Modern interior design settings.

ALSO AVAILABLE IN
Bath, page 218



P400022-031



P500305-031 **N**



P400021-031



P400022-031



P350040-031



P500151-031



P400023-031

COLLECTIONS

FINISH

● Matte Black - 031

PAIR WITH

Penn
Ratio
Mod

THREE-LIGHT FLUSH MOUNT

P350040-031 Matte Black
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

THREE-LIGHT CHANDELIER

P400021-031 Matte Black
21-3/4" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-031 Matte Black
27-3/8" dia., 23" ht.
Overall ht. w/stem 89", wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-031 Matte Black
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89", wire 15'.
Seven medium base lamps,
each 100w max.

MINI-PENDANT

P500151-031 Matte Black
3-7/8" dia., 7" ht.
Overall ht. w/stem 73", wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT PENDANT

P500305-031 Matte Black
20" dia., 30" ht.
Overall ht. w/stem 99", wire 15'.
Four medium base lamps,
each 75w max.



P300020-031

N New Product

ELEVATE

FINISH

- Polished Chrome - 015

ONE-LIGHT WALL BRACKET

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-015 Polished Chrome
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

LED FLUSH MOUNT

P350105-015-30 Polished Chrome
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-015 Polished Chrome
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-015 Polished Chrome
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500151-015 Polished Chrome
3-7/8" dia., 7" ht.
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT PENDANT

P500305-015 Polished Chrome
20" dia., 30" ht.
Overall ht. w/stem 99"; wire 15'.
Four medium base lamps,
each 75w max.



P400022-015



P500305-015 **N**



P350040-015



P350105-015-30



P400021-015



P500151-015



P400022-015



P300020-015

N New Product



P400022-109



P500305-109 N



P350105-109-30



P500151-109



P350040-109



P400021-109



P400022-109



P300020-109

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT WALL BRACKET

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-109 Brushed Bronze
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

LED FLUSH MOUNT

P350105-109-30 Brushed Bronze
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 source lumens.



THREE-LIGHT CHANDELIER

P400021-109 Brushed Bronze
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-109 Brushed Bronze
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500151-109 Brushed Bronze
3-7/8" dia., 7" ht.
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.

FOUR-LIGHT PENDANT

P500305-109 Brushed Bronze
20" dia., 30" ht.
Overall ht. w/stem 99"; wire 15'.
Four medium base lamps,
each 75w max.

N New Product

MOD

Giving a nod to the space age with mid-century modern appeal, Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.



ALSO AVAILABLE IN

Bath, page 222



FINISH

● Polished Chrome - 15

PAIR WITH

Ion

WALL BRACKET

P2850-15 Polished Chrome
5-7/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-7/8".
One candelabra base lamp,
60w max.



P2850-15

SIX-LIGHT CHANDELIER

P4756-15 Polished Chrome
34" dia., 24-7/8" ht.
Overall ht. w/stem 91", wire 15'.
Six candelabra base lamps
each, 60w max.

ORRIZO

Suitable for sleek and sophisticated interiors, Orrizo presents an artful arrangement of clear glass and golden metal rods that adorn a Black band. Geometric and artisan design influences complement both Modern and Luxe settings. Common applications for these statement-making fixtures include dining rooms and bedrooms and foyers. Six-light chandelier may be staggered in a cluster or grouping for large entryway settings.



FINISH

● Matte Black - 031

PAIR WITH

Adagio

SIX-LIGHT CHANDELIER

P400176-031 Matte Black
24" dia., 19-3/8" ht.
Overall ht. w/stem 84", wire 15'.
Six candelabra base lamps,
each 60w max.



P710063-031

TWO-LIGHT WALL SCONCE

P710063-031 Matte Black
6-3/8" W., 23" ht.
Extends 5". H/CTR 10-1/2".
Two medium base lamps,
each 60w max.

GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN

Bath, page 214



P500095-009



P350090-009



P500073-009



P500074-009



P500095-009



P400116-009



P300105-009

COLLECTIONS

FINISH

● Brushed Nickel - 009

PAIR WITH

Ratio

WALL SCONCE

P300105-009 Brushed Nickel
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER

P400116-009 Brushed Nickel
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-009 Brushed Nickel
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-009 Brushed Nickel
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500095-009 Brushed Nickel
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.

GLAYSE

FINISH

- Antique Bronze - 020

WALL SCONCE

P300105-020 Antique Bronze
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-020 Antique Bronze
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.

**FIVE-LIGHT LINEAR
CHANDELIER**

P400116-020 Antique Bronze
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-020 Antique Bronze
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-020 Antique Bronze
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500095-020 Antique Bronze
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.



P500095-020



P350090-020



P500073-020



P500074-020



P500095-020



P400116-020



P300105-020

PALACIO

An intriguing fashion-forward lighting collection, Palacio pairs a Vintage Gold finish with faux white marble accents for a stunningly elegant design. White silk shades complement gold accents to create a statement-making style. Ideal for a variety of interiors.



P400098-078



P500108-078



P400098-078



P400099-078



P500105-078



P500106-078



P500107-078

COLLECTIONS

FINISH

● Vintage Gold - 078

PAIR WITH

Cahill
Rae

FIVE-LIGHT CHANDELIER

P400098-078 Vintage Gold
27" dia., 21-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Five medium base lamps,
each 75w max.

NINE-LIGHT CHANDELIER

P400099-078 Vintage Gold
36" dia., 25" ht.
Overall ht. w/chain 148", wire 15'.
Nine medium base lamps,
each 75w max.

FOUR-LIGHT FOYER

P500105-078 Vintage Gold
15" Sq., 26-1/2" ht.
Overall ht. w/chain 110", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500106-078 Vintage Gold
20" dia., 30-1/2" ht.
Overall ht. w/chain 113-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P500107-078 Vintage Gold
8" dia., 17" ht.
Overall ht. w/stem 83", wire 10'.
One medium base lamp, 75w max.

FOUR-LIGHT PENDANT

P500108-078 Vintage Gold
22" dia., 9-5/8" ht.
Overall ht. w/stem 73", wire 10'.
Four candelabra base lamps,
each 60w max.

WALL BRACKET

P710037-078 Vintage Gold
6" W., 17" ht.
Extends 7-1/2". H/CTR 9".
One medium base lamp, 75w max.



P710037-078

ASTRA

An iconic fixture, Astra features an organic, asymmetrical design. Ideal for dining room settings or entryways, these classic Mid-Century inspired pieces are so versatile they can be incorporated into a variety of interiors.



P400108-009



P710027-009



P710027-020



P400108-009



P400108-020



P400109-009



P400109-020

COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH

Hangar
Glaysé

SIX-LIGHT CHANDELIER

P400108-009 Brushed Nickel
P400108-020 Antique Bronze
22-5/8" dia., 10-1/2" ht.
Overall ht. w/stem 72", wire 15'.
Six medium base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P400109-009 Brushed Nickel
P400109-020 Antique Bronze
42-3/8" dia., 19-5/8" ht.
Overall ht. w/stem 77", wire 15'.
Eight medium base lamps,
each 60w max.


WALL BRACKET

P710027-009 Brushed Nickel
P710027-020 Antique Bronze
7-1/4" W., 17-3/4" ht.
Extends 3-7/8". H/CTR 7".
Two medium base lamps,
each 60w max.

*Fixture dimension does not
include lamps.*

ION

Featuring a Polished Nickel or Brushed Bronze finish, these Space-Age inspired chandeliers boast either twelve or sixteen lights, each extending to support a single candelabra base lamp. Additionally, Ion chandeliers pair with Progress Lighting's Elevate collection for stunning Mid-Century inspired interiors.



P400040-109



P400041-104



P400040-104



P400041-109



P400040-109

COLLECTIONS

FINISHES

- Polished Nickel - 104
- Brushed Bronze - 109

PAIR WITH

Orrizo
Glaysé

TWELVE-LIGHT CHANDELIER

P400040-104 Polished Nickel
P400040-109 Brushed Bronze
14-1/8" dia.,
Overall ht. w/stem 76"; wire 15'.
Twelve candelabra base lamps,
each 25w max.

SIXTEEN-LIGHT CHANDELIER

P400041-104 Polished Nickel
P400041-109 Brushed Bronze
24" dia.,
Overall ht. w/stem 79-1/2"; wire 15'.
Sixteen candelabra base lamps,
each 25w max.

Fixture dimension does not include lamps.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century Modern and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. Matte Black finish is highlighted by clear globe shades or open candles. Spatial pendants are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.



ALSO AVAILABLE IN

Bath, page 224



P500083-031



P500082-031



P500083-031



P400077-031



P500084-031

COLLECTIONS

FINISH

● Matte Black - 031

PAIR WITH

Remix
Finn

SEMI-FLUSH CONVERTIBLE

P400077-031 Matte Black
Hanging and ceiling mount hardware included.
19-5/8" dia., 14" ht.
Overall ht. w/chain 52", wire 10'.
Three candelabra base lamps, each 60w max.

MINI-PENDANT

P500082-031 Matte Black
12" dia., 11-1/4" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT

P500083-031 Matte Black
23-1/2" dia., 19" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500084-031 Matte Black
28" dia., 26" ht.
Overall ht. w/chain 101", wire 15'.
Six candelabra base lamps, each 60w max.

HANGAR

Fixtures in the Hangar collection are fun, light and airy pieces – perfect for both casual and modern homes. A sophisticated, statement-making frame occupies a large visual space. Modern wire basket forms are finished in Brushed Nickel with graphite accents or Antique Bronze and natural brass accents to complete the design.



P500117-009



P400105-009



P500117-009



P710043-009



P350102-009

COLLECTIONS

FINISH

- Brushed Nickel - 009

PAIR WITH

Astra

SEMI-FLUSH CONVERTIBLE

P350102-009 Brushed Nickel Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht. Overall ht. w/stem 78-1/2", wire 10'. Two medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400105-009 Brushed Nickel 30" dia., 19-3/4" ht.* Overall ht. w/stem 77", wire 15'. Five medium base lamps, each 60w max.

THREE-LIGHT PENDANT

P500117-009 Brushed Nickel Vintage Linen Shade. 24" dia., 24-1/4" ht. Overall ht. w/stem 90", wire 15'. Three medium base lamps, each 75w max.

WALL BRACKET

P710043-009 Brushed Nickel 5" W., 8-3/4" ht.* Extends 4-1/2". H/CTR 4". One medium base lamp, 60w max.

*Fixture dimension does not include lamps.

HANGAR

FINISH

- Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350102-020 Brushed Nickel
Hanging and ceiling mount hardware included. Vintage Linen Shade. 16" dia., 13-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Two medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400105-020 Antique Bronze
30" dia., 19-3/4" ht.*
Overall ht. w/stem 77", wire 15'.
Five medium base lamps, each 60w max.

THREE-LIGHT PENDANT

P500117-020 Antique Bronze
Vintage Linen Shade.
24" dia., 24-1/4" ht.
Overall ht. w/stem 90", wire 15'.
Three medium base lamps, each 75w max.

WALL BRACKET

P710043-020 Antique Bronze
5" W., 8-3/4" ht.*
Extends 4-1/2". H/CTR 4".
One medium base lamp, 60w max.

*Fixture dimension does not include lamps.



P500117-020



P400105-020



P500117-020



P710043-020



P350102-020

UNION SQUARE

Originally inspired by historical reproduction gas lanterns, Union Square now offers a four-light chandelier and five-light linear island fixture. The simple geometric form features a Stainless Steel frame that is paired with vintage-style light bulbs. Mechanical details such as exaggerated knobs provide character to the form.

ALSO AVAILABLE IN

Bath, page 216
Outdoor, page 284



P400112-135



P400112-135

FINISH
● Stainless Steel - 135

PAIR WITH
Remix
Turnbury

FOUR-LIGHT CHANDELIER
P400112-135 Stainless Steel
20" W., 9-3/4" ht.
Overall ht. w/stems 76-1/2", wire 15'.
Four medium base lamps,
each 60w max.

FIVE-LIGHT ISLAND
P400145-135 Stainless Steel
38" W., 9-3/4" ht., 8-1/2" d.
Overall ht. w/stems 76", wire 15'.
Five medium base lamps,
each 60w max.

ONE-LIGHT BRACKET
P710038-135 Stainless Steel
5-1/4" W., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.



P400145-135



P710038-135

GRESHAM

A display of substantial style, Gresham's frame was inspired by the elegance of traditional iron structures. Specific attention to forging details creates a distinctive collection for Transitional and Farmhouse interior spaces. Seeded glass shades and a Graphite finish pair together to complete the look.



P400164-143



P400164-143



P400165-143



P400166-143

FINISH

● Graphite - 143

PAIR WITH

Debut
Spicewood

SIX-LIGHT CHANDELIER

P400164-143 Graphite
28" dia., 22-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400165-143 Graphite
36" dia., 24-7/8" ht.
Overall ht. w/chain 99", wire 15'.
Nine candelabra base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400166-143 Graphite
47-1/8" dia., 40-3/8" ht.
Overall ht. w/chain 163", wire 15'.
Fifteen candelabra base lamps,
each 60w max.

GRESHAM

FINISH

- Graphite - 143

SEMI-FLUSH CONVERTIBLE

P350119-143 Graphite
Hanging and ceiling mount hardware included.
17-3/4" dia., 12" ht.
Overall ht. w/chain 50", wire 10'.
Three medium base lamps, each 60w max.

FOUR-LIGHT FOYER

P500164-143 Graphite
20" dia., 26-1/4" ht.
Overall ht. w/chain 100", wire 15'.
Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER

P500165-143 Graphite
24" dia., 41-3/8" ht.
Overall ht. w/chain 115-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

EIGHT-LIGHT LINEAR CHANDELIER

P400180-143 Graphite
38" W., 17-1/2" ht., 13-7/8" d.
Overall ht. w/chain 91-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.

ONE-LIGHT WALL BRACKET

P710055-143 Graphite
4-3/4" W., 15" ht.
Extends 5-3/4". H/CTR 10".
One candelabra base lamp, 60w max.



P500165-143



P350119-143



P350119-143
shown as semi-flush



P500164-143



P500165-143



P710055-143



P400180-143

LOOKING GLASS

Whether for a mountain cabin or an urban retreat, the rustic charm of the Looking Glass collection is an artful display of romantic vintage lighting. Inspired by a timber frame farmhouse, Looking Glass features iron elements that support clear seeded glass reflectors. Hints of brass accentuate the mechanical details to enhance a vintage feel.



P400002-020



P400002-020

FINISH
● Antique Bronze - 020

PAIR WITH
Torres
Cumberland

FOUR-LIGHT CHANDELIER
P400002-020 Antique Bronze
25-3/8" W., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Four medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER
P400003-020 Antique Bronze
19" W., 36-3/4" L., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Six medium base lamps,
each 60w max.

MINI-PENDANT
P500042-020 Antique Bronze
9" dia., 14 3/4" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

WALL SCONCE
P710002-020 Antique Bronze
9" W., 17-7/8" ht.
Extends 7-5/8". H/CTR 11-3/8".
One medium base lamp,
60w max.



P400003-020



P500042-020



P710002-020

DEBUT

Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.



ALSO AVAILABLE IN

Bath, page 230



P400015-009



P350036-009



P400015-009
shown with
P860003-001 shade



P400017-009
shown with
P860002-001 shade



P300008-009



P860002-001



P860003-001



P400016-009

COLLECTIONS

FINISH

● Brushed Nickel -009

PAIR WITH

Remix
Staunton

WALL BRACKET

P300008-009 Brushed Nickel
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-009 Brushed Nickel
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-009 Brushed Nickel
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-009 Brushed Nickel
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

DEBUT

FINISH

● Graphite - 143

WALL BRACKET

P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-143 Graphite
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-143 Graphite
28" dia., 27-1/2" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-143 Graphite
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-143 Graphite
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.



P350036-143
shown with
P860002-001 shade



P400015-143



P400017-143
shown with
P860003-001 shade



P300008-143

P400016-143



P860002-001



P860003-001

P400015-143

REMIX

Remix features industrial-inspired pendant options. A Graphite frame is comprised of straps that weave together to create an open cage design. Brushed Nickel accents on the inside add a touch of mixed metal accents.



P500012-143



P500012-143

FINISH

- Graphite - 143

PAIR WITH

Spicewood
West Village

FOUR-LIGHT PENDANT

P500012-143 Graphite
22" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Four medium base lamps,
each 60w max.

MINI-PENDANT

P500010-143 Graphite
10" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One medium base lamp,
60w max.

THREE-LIGHT PENDANT

P500011-143 Graphite
16" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Three medium base lamps,
each 60w max.



P500011-143



P500010-143

FONTAYNE

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations include Antique Bronze with faux oak accents or Brushed Nickel with weathered gray accents.



P500088-020



P500088-020



P500089-020



P400081-020

FINISH

- Antique Bronze - 020

PAIR WITH

- Galley
- Conestee
- Hansford

SIX-LIGHT CHANDELIER

P400081-020 Antique Bronze
22" dia., 24-3/4" ht.
Overall ht. w/stem 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-020 Antique Bronze
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-020 Antique Bronze
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

FONTAYNE

FINISH

- Brushed Nickel - 009

SIX-LIGHT CHANDELIER

P400081-009 Brushed Nickel

22" dia., 24-3/4" ht.

Overall ht. w/stem 111-1/2", wire 15'.

Six candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-009 Brushed Nickel

14" Sq., 25" ht.

Overall ht. w/chain 99", wire 15'.

Four candelabra base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500089-009 Brushed Nickel

20" Sq., 32" ht.

Overall ht. w/chain 107-1/2", wire 15'.

Six candelabra base lamps,
each 60w max.



P500088-009



P500088-009



P500089-009



P400081-009

TURNBURY

Coastal-inspired pieces are popular in a variety of today's home designs. Turnbury pendants feature a solid wood frame surround with hand-painted, galvanized metal fittings. The distressed pine frame finish is reminiscent of driftwood that has been weathered in the sun.



P4761-141



P5317-141
Shown with
P7825-01
vintage lamps



P4760-141



P4763-141

COLLECTIONS

FINISH

- Galvanized Finish - 141

PAIR WITH

- Fontayne
- Zin
- Union Square

FOUR-LIGHT CHANDELIER

P4760-141 Galvanized Finish
16" dia., 18-3/4" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4761-141 Galvanized Finish
26" dia., 28-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

EIGHT-LIGHT CHANDELIER

P4763-141 Galvanized Finish
Two tier
36" W., 39" ht.
Overall ht. w/chain 162", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P5317-141 Galvanized Finish
10" dia., 12-1/4" ht.
Overall ht. w/chain 87", wire 10'.
One medium base lamp,
100w max.

SPICEWOOD

The statement-making Spicewood pendants feature a rich, solid wood surround in a classic quatrefoil pattern. Wrought iron metal fittings in a Gilded Iron finish are paired with a distressed pine frame to complement rustic and reclaimed design styles.



P4766-71



P5318-71
shown with
P7825-01
vintage lamp



P4766-71



P4767-71

FINISH
● Gilded Iron - 71

PAIR WITH
Fontayne
Gresham
Malbec

FOUR-LIGHT CHANDELIER
P4766-71 Gilded Iron
22" dia., 24-1/2" ht.
Overall ht. w/chain 99-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER
P4767-71 Gilded Iron
30" dia., 32-1/2" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

MINI-PENDANT
P5318-71 Gilded Iron
10" dia., 11" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
100w max.

EVOKE

Evoke features an elliptical frame that gracefully supports a candelabra with clear glass shade. Mixed finishes highlight the unique shape and provide a hint of livable luxury to your home.



P400117-020



P400024-020



P400026-020



P400025-020



P400117-020

COLLECTIONS

FINISH

- Antique Bronze - 020

PAIR WITH

Noma
Marche

THREE-LIGHT CHANDELIER

P400024-020 Antique Bronze
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-020 Antique Bronze
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-020 Antique Bronze
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-020 Antique Bronze
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103", wire 15'.
Five candelabra base lamps,
each 60w max.

EVOKE

FINISH

● Polished Nickel - 104

THREE-LIGHT CHANDELIER

P400024-104 Polished Nickel
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-104 Polished Nickel
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-104 Polished Nickel
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-104 Polished Nickel
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103"; wire 15'.
Five candelabra base lamps,
each 60w max.



P400117-104



P400024-104



P400026-104



P400025-104



P400117-104

NOMA

Mixed finishes, such as Polished Nickel with silver ridge accents and Antique Bronze with champagne accents are highlighted in Noma. Soft angles and curving lines created from flat metal straps elegantly frame etched white glass shades.



P400012-020



P350034-020



P400011-020



P400014-020



P400013-020

COLLECTIONS

FINISH

- Antique Bronze - 020

PAIR WITH

Ratio
Evoke

SEMI-FLUSH CONVERTIBLE

P350034-020 Antique Bronze
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-020 Antique Bronze
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-020 Antique Bronze
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-020 Antique Bronze
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-020 Antique Bronze
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.

NOMA

FINISH

- Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350034-104 Polished Nickel
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-104 Polished Nickel
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-104 Polished Nickel
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-104 Polished Nickel
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-104 Polished Nickel
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.



P400012-104



P350034-104



P400011-104



P400014-104



P400013-104

WEST VILLAGE

A modern form with industrial-inspired accents are featured in West Village. Double prismatic glass shades provide a beautiful illumination effect. Visual interest continues with a three-spoke frame that holds each glass shade. Antique Bronze with antique brass accents or Brushed Nickel with chrome accents provide touches of mixed metal in all fixtures within the collection.



ALSO AVAILABLE IN

Bath, page 234



P400009-020



P400008-020



P500006-020



P400010-020



P300004-020



P350032-020



P350032-020

COLLECTIONS

FINISH

● Antique Bronze - 020

PAIR WITH

Union Square
Remix

WALL BRACKET

P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7" H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-020 Antique Bronze
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-020 Antique Bronze
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-020 Antique Bronze
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-020 Antique Bronze
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-020 Antique Bronze
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.

WEST VILLAGE

FINISH

● Brushed Nickel - 009

WALL BRACKET

P300004-009 Brushed Nickel
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-009 Brushed Nickel
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400009-009 Brushed Nickel
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-009 Brushed Nickel
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-009 Brushed Nickel
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



P400009-009



P400008-009



P500006-009



P400010-009



P300004-009



P350032-009



P350032-009

GLIMMER

Elements that sparkle create an instant statement within the home - Glimmer fits the definition of livable luxury. Prismatic glass pendants are supported by an architecturally styled frame in Silver Ridge or Antique Bronze finishes.



P5321-134



P2326-134



P2326-20



P5321-134



P5321-20



P5346-134



P5346-20

COLLECTIONS

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

PAIR WITH

Equinox
Anjoux

SEMI-FLUSH CONVERTIBLE

P2326-134 Silver Ridge
P2326-20 Antique Bronze
Hanging and ceiling mount hardware included.
16-1/4" dia., 19" ht.
Overall ht. w/chain 96-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT PENDANT

P5321-134 Silver Ridge
P5321-20 Antique Bronze
22-1/4" dia., 23-7/8" ht.
Overall ht. w/chain 99", wire 10'.
Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P5346-134 Silver Ridge
P5346-20 Antique Bronze
28" dia., 29-1/4" ht.
Overall ht. w/chain 104-1/2", wire 10'.
Six candelabra base lamps, each 60w max.

GLIMMER

FINISHES


- Antique Bronze - 20
- Silver Ridge - 134

FOUR-LIGHT LINEAR CHANDELIER

P400101-134 Silver Ridge
P400101-20 Antique Bronze
 33-7/8" W., 11-1/2" L. 11" ht.
 Overall ht. w/stem 76", wire 15'.
 Four medium base lamps,
 each 60w max.

MINI-PENDANT

P5320-20 Antique Bronze
P5320-134 Silver Ridge
 6" dia., 11-1/4" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 One medium base lamp,
 100w max.



P400101-134



P400101-020



P5320-134



P5320-20



P2325-134



P2325-20



P2325-134



P2325-20



P7198-134



P7198-20

GLIMMER

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P2325-20 Antique Bronze
P2325-134 Silver Ridge
 Hanging and ceiling mount
 hardware included.
 13-1/8" dia., 15-1/2" ht.
 Overall ht. w/chain 94", wire 10'.
 Three candelabra base lamps,
 each 60w max.

WALL SCONCE

P7198-134 Silver Ridge
P7198-20 Antique Bronze
 8" W., 10" ht.
 Extends 4-3/4". H/CTR 3-1/2".
 Two candelabra base lamps,
 each 60w max.

MARCHÉ

Marché is an eclectic arrangement of gleaming metal turnings, which recreates the vintage styles found in Parisian neighborhood markets. Polished Nickel elements are combined with a luxurious sheer silver organza shade and clear K9 glass elements. Coordinate with Nissé or Caress collections to create a truly distinctive addition to your home.



P400049-104



P400049-104



P500043-104



P710013-104



P350029-104

COLLECTIONS

FINISH

- Polished Nickel - 104

PAIR WITH

- Glimmer
- Glaysé

SEMI-FLUSH CONVERTIBLE

P350029-104 Polished Nickel Hanging and ceiling mount hardware included. 18" dia., 14" ht. Overall ht. w/chain 55", wire 10'. Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400049-104 Polished Nickel 28" dia., 25-1/8" ht. Overall ht. w/chain 100", wire 15'. Five candelabra base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500043-104 Polished Nickel 22" dia., 20" ht. Overall ht. w/chain 95", wire 15'. Four candelabra base lamps, each 60w max.

WALL BRACKET

P710013-104 Polished Nickel 6-7/8" W., 12-1/4" ht. Extends 10-1/2". H/CTR 6-5/8". One candelabra base lamp, 60w max.

BONITA

Inspired at its roots by an understated beauty and a breathtaking formal elegance, the Bonita collection makes a stunning addition to any luxurious living space. This gaze-grabbing modern collection grants a slight nod to antique candle-like fixtures with graceful, arrow drum shades held in place by light bases supported by elegantly curved arms. Bonita's signature elegant design is ideal for illuminating family meals at your dining table or around a kitchen island.

ALSO AVAILABLE IN

Sconces, page 208



P400227-012



P400227-012



P400227-031



P500285-012



P500285-031



P710018-012



P710019-012



P710018-031



P710019-031

COLLECTIONS

FINISHES

- Satin Brass - 012
- Matte Black - 031

PAIR WITH

Glimmer
Marche

SIX-LIGHT CHANDELIER

P400227-012 Satin Brass
P400227-031 Matte Black
30-1/2" dia., 24" ht.
Overall ht. w/stem 90", wire 15'.
Six candelabra base lamps,
each 40w max.

FOUR-LIGHT FOYER

P500285-012 Satin Brass
P500285-031 Matte Black
23" dia., 25-7/8" ht.
Overall ht. w/stem 92", wire 15'.
Four candelabra base lamps,
each 40w max.

WALL BRACKET

P710018-012 Satin Brass
P710018-031 Matte Black
4-1/2" W., 17-1/8" ht.
Extends 6-7/8". H/CTR 13-5/8".
One candelabra base lamp,
40w max.

WALL BRACKET

P710019-012 Satin Brass
P710019-031 Matte Black
13-5/8" W., 17-1/4" ht.
Extends 6-7/8". H/CTR 13-5/8".
Two candelabra base lamps,
each 40w max.

BONITA

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

SIX-LIGHT CHANDELIER

P400227-009 Brushed Nickel
P400227-015 Polished Chrome
 30-1/2" dia., 24" ht.
 Overall ht. w/stem 90", wire 15'.
 Six candelabra base lamps,
 each 40w max.

FOUR-LIGHT FOYER

P500285-009 Brushed Nickel
P500285-015 Polished Chrome
 23" dia., 25-7/8" ht.
 Overall ht. w/stem 92", wire 15'.
 Four candelabra base lamps,
 each 40w max.

WALL SCONCE

P710018-009 Brushed Nickel
P710018-015 Polished Chrome
P710018-020 Antique Bronze
 4-1/2" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL SCONCE

P710019-009 Brushed Nickel
P710019-015 Polished Chrome
P710019-020 Antique Bronze
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.



P400227-015



P400227-009



P500285-015



P500285-009



P710018-015

P710019-015



P710018-009

P710019-009



P710018-020

P710019-020

P400227-015

WESTFALL

Westfall is a combination of arching elements that create a dramatic soaring frame. A dual-tone finish highlights the distinctive form. Metal fittings add a touch of elegance and dimension to further enhance the classic architectural form.



P500040-143



P500038-020



P500038-143



P500039-020
Shown with
Antique Bronze
candle covers



P500039-143



P500040-020



P500040-143

COLLECTIONS

FINISHES

- Antique Bronze - 020
- Graphite - 143

PAIR WITH

Noma

FOUR-LIGHT FOYER

P500038-020 Antique Bronze
P500038-143 Graphite
10-1/8" sq., 19-5/8" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500039-020 Antique Bronze
P500039-143 Graphite
13-7/8" sq., 25-1/8" ht.
Overall ht. w/chain 100", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500040-020 Antique Bronze
P500040-143 Graphite
19-3/4" sq., 33-1/8" ht.
Overall ht. w/chain 156", wire 15'.
Eight candelabra base lamps,
each 60w max.

Note: Antique Bronze fixtures include Vintage Brass and Antique Bronze candle covers for additional customization.

ASSEMBLY HALL

Assembly Hall provides a formal and classic open caged pendant for a variety of traditional and transitional interiors. Available in two sizes, arching frames are great in scale and surround a candelabra with matching candles – Antique Bronze fixtures also include vintage brass candles for additional customization.



P500036-020



P500036-009



P500036-020
Shown with
Antique Bronze
candle covers



P500037-009



P500037-020

COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH

Noma

FOUR-LIGHT FOYER

P500036-009 Brushed Nickel
P500036-020 Antique Bronze
 15" sq., 26" ht.
 Overall ht. w/chain 100"; wire 15'.
 Four candelabra base lamps,
 each 60w max.

SIX-LIGHT FOYER

P500037-009 Brushed Nickel
P500037-020 Antique Bronze
 20" sq., 32-3/4" ht.
 Overall ht. w/chain 106-1/2"; wire 15'.
 Six candelabra base lamps,
 each 60w max.

Note: Antique Bronze fixtures include Vintage Brass and Antique Bronze candle covers for additional customization.

MARQUE

With clear seeded glass in the Graphite finish, this vintage pendant family can be used as a sleek substitute for chandeliers in a variety of living spaces, including foyers and hallways.



P3598-143



P3601-143



P5073-143



P3598-143

COLLECTIONS

FINISH

- Graphite - 143

PAIR WITH

Remix

ONE-LIGHT FOYER

P3598-143 Graphite
12" dia., 19-3/4" ht.
Overall ht. w/stem 86"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT FOYER

P3601-143 Graphite
18" dia., 28-3/4" ht.
Overall ht. w/stem 95"; wire 15'.
Three medium base lamps,
each 100w max.

MINI-PENDANT

P5073-143 Graphite
7-3/4" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/4"; wire 10'.
One medium base lamp,
100w max.

CINQ

Cinq finds inspiration from modern geometric designs and the beauty of contrasting elements. Five-sided bottom panels are outlined in an Antique Bronze finish with antique mirrored glass or Brushed Nickel finish with clear seeded glass lower panels, while the upper panels are comprised of clear glass..



P5322-20



P5322-20



P5322-09



P5319-20



P5319-09



P3868-20



P3868-09

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PAIR WITH
Hangar

ONE-LIGHT PENDANT

P5319-09 Brushed Nickel
P5319-20 Antique Bronze
 12" dia., 18-1/2" ht.
 Overall ht. w/stem 84-1/2", wire 10'
 One medium base lamp,
 100w max.

THREE-LIGHT PENDANT

P5322-09 Brushed Nickel
P5322-20 Antique Bronze
 19" dia., 25-7/8" ht.
 Overall ht. w/stem 92", wire 10'
 Three medium base lamps,
 each 100w max.

ONE-LIGHT FLUSH MOUNT


P3868-09 Brushed Nickel
P3868-20 Antique Bronze
 12" dia., 9-1/4" ht.
 One medium base lamp,
 100w max.



PENDANTS

MAULDIN

Enjoy the generous, antique glow of the simply charming Mauldin Collection. Geometric frames and clear seeded glass panes foster a soft, vintage demeanor and recall memories of raindrops clinging to windows during a summer evening thunderstorm.



P500221-009



P500221-031



P500221-009



P500222-031



P500222-009

PENDANTS

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ONE-LIGHT PENDANT

P500221-009 Brushed Nickel
P500221-031 Matte Black
 12" sq., 19-7/8" ht.
 Overall ht. w/chain 82", wire 10".
 One medium base lamp,
 100w max.

THREE-LIGHT PENDANT

P500222-009 Brushed Nickel
P500222-031 Matte Black
 17" sq., 27-1/4" ht.
 Overall ht. w/chain 89-1/2", wire 10".
 Three medium base lamps,
 each 60w max.

GALLEY

Galley is a simple modern form that complements both coastal décor and commercial style kitchens. The arched supporting frame features overscale metal turnings for an enhanced sense of architectural styling. The linen shades are comprised of rich, satin lining for the feel of a tailored fit and finish to complement the multi-light cluster.



P500047-020



P500046-020



P500046-104



P500047-020



P500047-104

PENDANTS

FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

TWO-LIGHT PENDANT

P500046-020 Antique Bronze
P500046-104 Polished Nickel
 15" dia., 18" ht.
 Overall ht. w/stem 84", wire 10'.
 Two medium base lamps,
 each 75w max.

THREE-LIGHT PENDANT

P500047-020 Antique Bronze
P500047-104 Polished Nickel
 21" dia., 24-1/2" ht.
 Overall ht. w/stem 90-1/2", wire 10'.
 Three medium base lamps,
 each 75w max.

STAUNTON

Inspired by the stacked modern elements of items found in Parisian boutiques, Staunton's chess piece silhouette offers a signature focal point. Available in three shapes and color variations – they can be grouped as a single style or mixed and matched to offer a more eclectic look. All pendants feature a vintage, woven cloth cord.



P5332-20



P5332-09



P5332-20



P5332-143



P5333-09



P5333-20



P5333-143



P5334-09



P5334-20



P5334-143

PENDANTS

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

ONE-LIGHT PENDANT

P5332-09 Brushed Nickel with clear glass

P5332-20 Antique Bronze with champagne glass

P5332-143 Graphite with smoked glass

12" dia., 11-1/4" ht.

Overall ht. w/cord 125-1/2"; cord 10'.

One medium base lamp, 75w max.

ONE-LIGHT PENDANT

P5333-09 Brushed Nickel with clear glass

P5333-20 Antique Bronze with champagne glass

P5333-143 Graphite with smoked glass

9" dia., 16-1/2" ht.

Overall ht. w/cord 124"; cord 10'.

One medium base lamp, 75w max.

ONE-LIGHT PENDANT

P5334-09 Brushed Nickel with clear glass

P5334-20 Antique Bronze with champagne glass

P5334-143 Graphite with smoked glass

8 1/2" dia., 12-3/4" ht.

Overall ht. w/cord 126-1/2"; cord 10'.

One medium base lamp, 75w max.

CHRONICLE

Chronicle pendants add visual interest and are ideal for commercial-style home kitchens or vintage dining areas. A metal accent ring adds a finishing touch on the glass globe. Clear seeded glass with an Antique Bronze frame.



P5311-20



P5309-20

FINISH

● Antique Bronze - 20

ONE-LIGHT MINI-PENDANT

P5309-20 Antique Bronze
8" dia., 9" ht.
Overall ht. w/stem 75"; wire 10'.
One medium base lamp,
100w max.


ONE-LIGHT PENDANT

P5311-20 Antique Bronze
12" dia., 13" ht.
Overall ht. w/stem 79"; wire 10'.
One medium base lamp,
100w max.

FINN

Finn takes a new perspective on an open cage design. The beautifully graphic frame wraps around an etched white glass shade creating a focal aperture for a single lamp. Available in Matte Black and Metallic Silver finishes.

PENDANTS



P5324-31



P5324-121

FINISHES

● Matte Black - 31
● Metallic Silver - 121

MINI-PENDANT

P5324-31 Matte Black
P5324-121 Metallic Silver
10" dia., 10-1/2" ht.
Overall ht. w/stem 76-1/2"; wire 10'.
One medium base lamp,
100w max.

ZIN

Inspired by a beautiful wine cask design, the Zin pendants are artfully formed from one large piece of glass. Create a customized look for Rustic Farmhouse and Modern Farmhouse to Urban Industrial settings by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual texture.



P500064-143



P500064-009



P500064-020

PENDANTS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT

P500064-009 Brushed Nickel with clear glass

P500064-020 Antique Bronze with light blue glass

P500064-143 Graphite with smoked glass

13" dia., 20-3/8" ht.

Overall ht. w/chain 95-1/2", wire 10'


One medium base lamp, 100w max.



P500064-143

MALBEC

Artisanal glass and high quality craftsmanship offers a signature focal point in the Malbec pendants. Create a customized look suitable for designs from Bohemian to Coastal by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual interest.



P500063-009



P500063-009



P500063-020



P500063-143

PENDANTS

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT

P500063-009 Brushed Nickel with clear glass

P500063-020 Antique Bronze with light blue glass

P500063-143 Graphite with smoked glass

11-3/4" dia., 14" ht.

Overall ht. w/chain 89", wire 10'

One medium base lamp, 100w max.

ERA

Achieve a vintage feel with Era's carefully crafted details and special eclectic accents. One light pendant or mini pendant options are available in Matte Black with gold leaf accents.



P500033-031



P500098-031



P500032-031



P500033-031

PENDANTS

FINISH

- Matte Black - 031

MINI-PENDANT

P500032-031 Matte Black
6-3/8" dia., 11-3/4" ht.
Overall ht. w/cord 78"; cord 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT

P500033-031 Matte Black
8-3/8" dia., 16-3/4" ht.
Overall ht. w/cord 82-1/2"; cord 10'.
One medium base lamp,
75w max.

ONE-LIGHT PENDANT

P500098-031 Matte Black
12-3/4" dia., 25" ht.
Overall ht. w/cord 91"; wire 10'.
One medium base lamp,
75w max.

MESH

Mesh pendants offer an interweaving open cage frame that can serve as a focal point in any lighting design.



P5337-20



P5337-20



P5338-20

PENDANTS

FINISH

- Antique Bronze - 20

MINI-PENDANT


P5337-20 Antique Bronze
8-1/2" dia., 8-3/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.

MINI-PENDANT

P5338-20 Antique Bronze
8-1/2" dia., 8-3/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp,
100w max.

ELLYSON

Clear prismatic glass creates a sophisticated, spherical globe in Ellyson. Influenced by mid century aesthetics, the glass is highlighted by simple accents finished in Polished Chrome or Brushed Bronze. From Mid-Century Modern to Luxe and Vintage Electric to Coastal, these pendants enhance a variety of design styles and can be displayed singularly or in groupings of two or more.



FINISHES

- Brushed Bronze - 109

ONE-LIGHT PENDANT

P500118-109 Brushed Bronze
18-3/8" dia., 24" ht.
Overall ht. w/stem 90", wire 10'.
One medium base lamp,
100w max.

MODERNA

Moderna's modern-inspired silhouette provides a signature focal point for a variety of interior spaces. Features clear outer glass with an inner etched white glass shade and a sleek linear frame.



FINISH

- Brushed Nickel - 009

LED MINI-PENDANT

P500000-009-30 Brushed Nickel
5-3/4" dia., 9-1/2" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One 9w LED module, 3000K,
90 CRI, 623 source lumens.



CARBON

Light spills out onto a streamlined shade in the Carbon pendant and mini- pendant. Etched white glass diffuser allows the light to illuminate the Graphite or Polished Nickel shade.



P500013-143



P500013-104



P500013-143

PENDANTS

FINISHES

- Polished Nickel - 104
- Graphite - 143

MINI-PENDANT

P500013-104 Polished Nickel
P500013-143 Graphite
11" dia., 8-1/4" ht.
Overall ht. w/stem 74-1/2"; wire 10'.
One medium base lamp,
100w max.



SCONCES

DESIGN+SERIES™

METRO

Metro delivers a clean, geometric form with a pleasing balance of angular metal fittings and a crisp linen shade. The stately fixture adds a modern accent with an elegant sense of architectural distinction.



P710016-015



P710016-009

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL BRACKET

P710016-009 Brushed Nickel
P710016-015 Polished Chrome
P710016-020 Antique Bronze
 5-1/2" W., 15-1/8" ht.
 Extends 7-1/4". H/CTR 10-1/2".
 One candelabra base lamp,
 60w max.



P710016-020

AVANA

Avana features a graceful tapered candle-arm with a crisp geometric linen shade. The faceted backplate provides a rich architectural detail that complements many fashionable vanity styles.



P710025-104



P710025-009

FINISHES

- Brushed Nickel - 009
- Polished Nickel - 104

WALL BRACKET

P710025-009 Brushed Nickel
P710025-104 Polished Nickel
 5-5/8" W., 16" ht.
 Extends 7-1/2". H/CTR 12-1/2".
 One candelabra base lamp,
 60w max.

BONITA

Bonita sconces have a traditional elegance to complement luxurious living with an understated beauty. Crisp metal fittings support a graceful frame and candle topped with a linen shade. Coordinate with Marché or Glimmer collections to add a variation of textures.

ALSO AVAILABLE IN

Collections, page 170



P710019-009



P710018-009



P710019-009



P710018-012



P710019-012



P710018-015



P710019-015



P710018-020



P710019-020



P710018-031



P710019-031

SCONCES

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Polished Chrome - 015
- Antique Bronze - 020
- Matte Black - 031

WALL BRACKET

P710018-009 Brushed Nickel
P710018-012 Satin Brass
P710018-015 Polished Chrome
P710018-020 Antique Bronze
P710018-031 Matte Black
 9" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 40w max.

WALL BRACKET

P710019-009 Brushed Nickel
P710019-012 Satin Brass
P710019-015 Polished Chrome
P710019-020 Antique Bronze
P710019-031 Matte Black
 13-5/8" W., 17-1/4" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 40w max.

HOBBS

Modern traditional design is the combination of crisp geometric forms in classic shapes and materials. Hobbs delivers on this concept with an elegant beveled glass diffuser framing a vintage lamp. The rectangular and circular fittings add a sense of classic craftsmanship for a timeless design.



P710017-009



P710017-015



P710017-020

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710017-009 Brushed Nickel
P710017-015 Polished Chrome
P710017-020 Antique Bronze
 6" W., 12" ht.
 Extends 4-7/8". H/CTR 6".
 One medium base lamp,
 60w max.

CORDIN

Featuring a striking combination of traditional and modern design, classic styling in the Cordin collection highlights a distinctive look for a variety of interiors. Elegant linear arms and a double-lined linen shade create a softer feel when combined with the vintage mechanical details and dual-tone frame. A Brushed Nickel finish with natural brass accents are incorporated in all fixtures in the Cordin family, including chandeliers, semi-flush, mini-pendant, island and swing arm options.



FINISH

- Brushed Nickel - 009

PAIR WITH

Hangar
 Bonn
 Hansford

WALL BRACKET

P710034-009 Brushed Nickel
 10" W., 17-1/2" ht.
 Extends 13-1/2". H/CTR 13-1/8".
 Arm pivots 120°
 One medium base lamp,
 75w max.



BATH

GLAYSE

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.

ALSO AVAILABLE IN
Collections, page 114



P300106-009



P300106-009



P300105-009



P300107-009



P300106-020



P300105-020



P300107-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300105-009 Brushed Nickel
P300105-020 Antique Bronze
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300106-009 Brushed Nickel
P300106-020 Antique Bronze
14-7/8" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300107-009 Brushed Nickel
P300107-020 Antique Bronze
22-3/4" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
Three medium base lamps,
each 60w max.

All fixtures mount up or down.

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open top and bottom on fixture provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Collections, page 130
Outdoor, page 284



P300135-135



P710038-135

FINISH

- Stainless Steel - 135

ONE-LIGHT BATH

P710038-135 Stainless Steel
5-1/4" sq., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300135-135 Stainless Steel
16" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Two medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300136-135 Stainless Steel
30" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Four medium base lamps,
each 60w max.



P300135-135



P300136-135

ELEVATE

Achieve a mid-century modern look with Elevate, which boasts glass shades and a frame inspired by modern styling. Brushed Bronze and Polished Chrome finish options also available.

ALSO AVAILABLE IN
Collections, page 106



P300021-031



P300021-031



P300020-031



P300022-031



P300023-031

FINISH

- Matte Black - 031

ONE-LIGHT BATH

P300020-031 Matte Black
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300021-031 Matte Black
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300022-031 Matte Black
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300023-031 Matte Black
34-1/2" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

ELEVATE

FINISH

● Brushed Bronze - 109

ONE-LIGHT BATH

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300020-109



P300021-109

TWO-LIGHT BATH

P300021-109 Brushed Bronze
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-109

THREE-LIGHT BATH

P300022-109 Brushed Bronze
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300023-109 Brushed Bronze
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.



P300023-109

All fixtures mount up or down.

ELEVATE

FINISH

● Polished Chrome - 015

ONE-LIGHT BATH

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.



P300021-015



P300020-015

TWO-LIGHT BATH

P300021-015 Polished Chrome
15-3/8" W., 7-1/2" ht.
Extends 6-1/8". H/CTR 5".
Two medium base lamps,
each 100w max.



P300022-015

THREE-LIGHT BATH

P300022-015 Polished Chrome
24-3/4" W., 7-1/2" ht.
Extends 8". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300023-015 Polished Chrome
34-1/2" W., 7-1/2" ht.
Extends 7-3/4". H/CTR 5".
Four medium base lamps,
each 100w max.



P300023-015

All fixtures mount up or down.

MOD

Giving a nod to the space age with mid-century modern appeal. Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.

ALSO AVAILABLE IN

Collections, page 112



P2854-15



P2854-15



P2850-15



P2856-15



P2857-15

FINISH

- Polished Chrome - 15

ONE-LIGHT BATH

P2850-15 Polished Chrome
5-7/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-7/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P2854-15 Polished Chrome
15" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P2856-15 Polished Chrome
24" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P2857-15 Polished Chrome
33" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Four candelabra base lamps,
each 60w max.

All fixtures mount up or down.

SPATIAL

Spatial showcases a modern form that complements Urban Industrial, Mid-Century and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. A Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.

ALSO AVAILABLE IN
Collections, page 124



P300113-031



P300113-031



P300112-031



P300114-031



P300115-031

FINISH

● Matte Black - 031

ONE-LIGHT BATH

P300112-031 Matte Black
5-3/8" W., 6-1/2" ht.
Extends 8". H/CTR 3-3/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300113-031 Matte Black
14-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300114-031 Matte Black
22" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three candelabra base lamps,
each 60w max.



FOUR-LIGHT BATH

P300115-031 Matte Black
31-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Four candelabra base lamps,
each 60w max.

All fixtures mount up or down.

LISBON

Enjoy high status with a bath and vanity collection full of femininity, sparkle and shine. Etched opal glass shades sit atop an elegant K9 glass rod, highlighted with a Polished Nickel or Matte Black finish. The highly polished design style complements both Modern and Luxe interiors and can be mounted up or down.



P300198-104



P300198-031

P300197-031



P300199-031



P300200-031



P300198-104

P300197-104



P300199-104



P300200-104

FINISHES

- Matte Black - 031
- Polished Nickel - 104

ONE-LIGHT BATH

P300197-031 Matte Black
P300197-104 Polished Nickel
 4-3/4" W., 14" ht.
 Extends 6". H/CTR 5-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300198-031 Matte Black
P300198-104 Polished Nickel
 14-1/2" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300199-031 Matte Black
P300199-104 Polished Nickel
 24" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300200-031 Matte Black
P300200-104 Polished Nickel
 33-1/2" W., 8" ht.
 Extends 6". H/CTR 5-5/8".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

CAHILL

A stylish Brushed Bronze finish frames brilliant clear beveled glass panels in the Cahill collection. Ideal for Luxe or Mid-Century Modern interiors, the visual interest provides a reinvention of the popular glass design.



P300109-109



P300109-109



P300108-109



P300110-109



P300111-109

FINISH

● Brushed Bronze - 109

ONE-LIGHT BATH

P300108-109 Brushed Bronze
4-1/2" W., 19-3/4" ht.
Extends 7-1/2".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300109-109 Brushed Bronze
16-3/4" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300110-109 Brushed Bronze
24" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300111-109 Brushed Bronze
30" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Four candelabra base lamps,
each 60w max.

All fixtures mount up or down.

DEBUT

Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.

ALSO AVAILABLE IN

Collections, page 138



P300009-143
Shown with
P860003-001 shade



P300009-143
shown with
P860003-001 shade



P300008-143



P300010-143
shown with
P860003-001 shade



P300011-143
shown with
P860002-001 shade



P300009-009
shown with
P860002-001 shade



P300008-009
shown with
P860003-001 shade



P300010-009
shown with
P860003-001 shade



P300011-009

BATH COLLECTIONS

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ONE-LIGHT BATH

P300008-009 Brushed Nickel
P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300009-009 Brushed Nickel
P300009-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 5-3/4". H/CTR 5-5/8".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300010-009 Brushed Nickel
P300010-143 Graphite
23-3/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300011-009 Brushed Nickel
P300011-143 Graphite
30-1/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Four medium base lamps,
each 60w max.

P860002-001
Etched glass shade.

P860003-001
Seeded glass shade.

All fixtures mount up or down.



P860002-001



P860003-001

FLIGHT

The Flight bath and vanity collection features a variety of industrial modern elements, including a linear frame and circular wall plate. The geometric and linear design is complemented by Brushed Nickel and Polished Chrome finish options.



P300001-009



P300001-009



P300000-009



P300002-009



P300003-009



P300001-015



P300000-015



P300002-015



P300003-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300000-009 Brushed Nickel
P300000-015 Polished Chrome
 6-1/8" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300001-009 Brushed Nickel
P300001-015 Polished Chrome
 15-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300002-009 Brushed Nickel
P300002-015 Polished Chrome
 26-1/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300003-009 Brushed Nickel
P300003-015 Polished Chrome
 36-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

WEST VILLAGE

Visual interest continues with a three-spoke design that holds each glass shade. Brushed Nickel with chrome accents or Antique Bronze with antique brass accents provide touches of mixed metal in all fixtures within the collection.

ALSO AVAILABLE IN
Collections, page 160



P300005-020



P300005-009

P300004-009



P300006-009



P300007-009



P300005-020

P300004-020



P300006-020



P300007-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300004-009 Brushed Nickel
P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300005-009 Brushed Nickel
P300005-020 Antique Bronze
14-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300006-009 Brushed Nickel
P300006-020 Antique Bronze
23-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300007-009 Brushed Nickel
P300007-020 Antique Bronze
32-1/4" W., 8-1/8" ht.
Extends 7". H/CTR 6".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

GLANCE

A sophisticated bath and vanity collection. Glance's stout frame and etched linen glass shades complement a variety of contemporary design schemes. Available in a Polished Chrome for the one- through four-light fixtures.



P300017-015



P300017-015



P300016-015



P300018-015



P300019-015

FINISHES

- Polished Chrome - 015

ONE-LIGHT BATH

P300016-015 Polished Chrome
5-3/8" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3-5/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300017-015 Polished Chrome
14-1/2" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3-5/8".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300018-015 Polished Chrome
24" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3-5/8".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300019-015 Polished Chrome
33-3/8" W., 7-1/4" ht.
Extends 7-1/4". H/CTR 3-5/8".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

GLIDE

Let Glide's nautical-inspired bath and vanity collection bring elegance and a spa-like atmosphere into the home. Available in Brushed Nickel, Polished Chrome or Rubbed Bronze, the oval-shaped opal glass sits upon a pedestal while offering a traditional or formal style. One-through four-light vanity options.



P300013-009



P300013-009



P300012-009



P300014-009



P300015-009

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH
P300012-009 Brushed Nickel
 4-1/2" W., 8" ht.
 Extends 6". H/CTR 4".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH
P300013-009 Brushed Nickel
 16" W., 7-3/4" ht.
 Extends 6-7/8". H/CTR 4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH
P300014-009 Brushed Nickel
 24" W., 7-3/4" ht.
 Extends 6-7/8". H/CTR 4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH
P300015-009 Brushed Nickel
 34" W., 7-3/4" ht.
 Extends 6-3/4". H/CTR 4".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

GLIDE

FINISH

- Polished Chrome - 015

ONE-LIGHT BATH

P300012-015 Polished Chrome
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-015



P300013-015

TWO-LIGHT BATH

P300013-015 Polished Chrome
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300014-015 Polished Chrome
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-015

FOUR-LIGHT BATH

P300015-015 Polished Chrome
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-015

All fixtures mount up or down.

GLIDE

FINISH

- Rubbed Bronze - 139

ONE-LIGHT BATH

P300012-139 Rubbed Bronze
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-139



P300013-139

TWO-LIGHT BATH

P300013-139 Rubbed Bronze
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300014-139 Rubbed Bronze
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-139

FOUR-LIGHT BATH

P300015-139 Rubbed Bronze
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-139

All fixtures mount up or down.

WANDER

A Victorian-inspired bath and vanity collection, Wander wall brackets offer a clean and classic look. Etched glass shades are paired with a Polished Chrome, Brushed Nickel or Venetian Bronze finish to offer versatile styling for any home.



P300025-009



P300025-009



P300024-009



P300025-009
Mount Down



P300024-015



P300025-074



P300024-074



P300026-074



P300027-074

FINISH

- Brushed Nickel - 009
- Polished Chrome - 015
- Venetian Bronze - 074

ONE-LIGHT BATH

P300024-009 Brushed Nickel
P300024-015 Polished Chrome
P300024-074 Venetian Bronze
 4-3/4" W., 8-7/8" ht.
 Extends 7". H/CTR 5-3/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300025-009 Brushed Nickel
P300025-074 Venetian Bronze
 16" W., 8-1/4" ht.
 Extends 7". H/CTR 5".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300026-074 Venetian Bronze
 24-1/2" W., 8-1/4" ht.
 Extends 7". H/CTR 5".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300027-074 Venetian Bronze
 34" W., 8-1/4" ht.
 Extends 7". H/CTR 5".
 Four medium base lamps,
 each 100w max.

All fixtures mount up or down.

METRIC

A simple, etched opal glass shade nestles inside a die-cast frame that is finished in either Polished Chrome or Brushed Nickel – providing light above and below the fixture.



P2194-09



P2194-09



P2193-09



P2195-09



P2196-09



P2194-15



P2193-15



P2195-15



P2196-15

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15

ONE-LIGHT BATH

P2193-09 Brushed Nickel
P2193-15 Polished Chrome
 4-5/8" W., 8" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P2194-09 Brushed Nickel
P2194-15 Polished Chrome
 13" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Two medium base lamps
 each, 100w max.

THREE-LIGHT BATH

P2195-09 Brushed Nickel
P2195-15 Polished Chrome
 22-1/8" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Three medium base lamps
 each, 100w max.

FOUR-LIGHT BATH

P2196-09 Brushed Nickel
P2196-15 Polished Chrome
 31-1/4" W., 6-1/2" ht.
 Extends 5-1/4". H/CTR 4-1/8".
 Four medium base lamps
 each, 100w max.

All fixtures mount up or down.

VOLO LED

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.



P300063-009-30



P300063-009-30

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH

P300063-009-30 Brushed Nickel
 10" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 One 9w LED module, 3000K,
 90 CRI, 624 source lumens.

THREE-LIGHT BATH

P300065-009-30 Brushed Nickel
 24" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 Three 9w LED modules, 3000K,
 90 CRI, 624 source lumens per module.

All fixtures can be installed vertically or horizontally.

All fixtures:



P300065-009-30

ZURA

Zura features triangular, etched opal glass that provides geometric elements to add modern flair. This contemporary fixture is available in a Brushed Nickel, Polished Chrome, or Matte Black finish.



P300061-009



P300061-009



P300061-015



P300061-031



P300062-009



P300062-015



P300062-031



P300062-015
shown horizontally



P300062-031
shown horizontally

ZURA

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Matte Black - 031

ONE-LIGHT BATH

P300061-009 Brushed Nickel
P300061-015 Polished Chrome
P300061-031 Matte Black
 4-1/2" W., 13-3/4" ht.
 Extends 7". H/CTR 9-7/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300062-009 Brushed Nickel
P300062-015 Polished Chrome
P300062-031 Matte Black
 Can be installed vertically
 or horizontally.
 4-1/2" W., 21" ht.
 Extends 7". H/CTR 10-1/2".
 Two medium base lamps,
 each 100w max.



OUTDOOR

DESIGN+SERIES™

CHATSWORTH

Imagine sleepy, vintage streets and old-world architecture with the Chatsworth Collection. Elongated lantern silhouettes boast antique charm as brass tone accents highlight vintage character and inspiration.



P550067-031



P560182-031

P560183-031

P560184-031

P550067-031

P540067-031

OUTDOOR

FINISH
● Textured Black - 031

HANGING LANTERN
P550067-031 Textured Black
9" sq., 23-7/8" ht.
Overall ht. w/chain 99", wire 10".
Two candelabra base lamps,
each 60w max.

POST LANTERN
P540067-031 Textured Black
9" sq., 23-1/2" ht.
Fits 3" post (order separately).
Two candelabra base lamps,
each 60w max.

SMALL WALL LANTERN
P560182-031 Textured Black
7-1/2" W., 14-1/4" ht.
Extends 8-1/2". H/CTR 11-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P560183-031 Textured Black
9" W., 22" ht.
Extends 10". H/CTR 18-7/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN
P560184-031 Textured Black
11" W., 28" ht.
Extends 12". H/CTR 25-5/8".
Three candelabra base lamps,
each 60w max.

MORRISON

Morrison blends delicate geometric patterns with lasting durability in a modern form. Intricate die cast aluminum construction is paired with clear glass and an Antique Bronze or Antique Pewter finish. A tall and stately design accommodates expansive modern and traditional architecture settings that require larger scale outdoor fixtures. Available in hanging, post and wall lantern options.



P560116-020



P560116-020



P560117-020



P560118-020



P550041-020



P540016-020

OUTDOOR

FINISH

● Antique Bronze - 020

POST LANTERN

P540016-020 Antique Bronze
9" dia., 26-1/2" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550041-020 Antique Bronze
7-1/2" dia., 22" ht.
Overall ht. w/chain 95"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560116-020 Antique Bronze
6-1/8" W., 17-1/4" ht.
Extends 7-5/8". H/CTR 14-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560117-020 Antique Bronze
7-1/2" W., 21-3/8" ht.
Extends 9-1/4". H/CTR 18-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560118-020 Antique Bronze
9" W., 25-1/2" ht.
Extends 11-1/8". H/CTR 21-5/8".
One medium base lamp,
100w max.



P560116-103



P560116-103



P560117-103



P560118-103



P550041-103



P540016-103

FINISH

- Antique Pewter- 103

POST LANTERN

P540016-103 Antique Pewter
9" dia., 26-1/2" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550041-103 Antique Pewter
7-1/2" dia., 22" ht.
Overall ht. w/chain 95"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560116-103 Antique Pewter
6-1/8" W., 17-1/4" ht.
Extends 7-5/8". H/CTR 14-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560117-103 Antique Pewter
7-1/2" W., 21-3/8" ht.
Extends 9-1/4". H/CTR 18-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560118-103 Antique Pewter
9" W., 25-1/2" ht.
Extends 11-1/8". H/CTR 21-5/8".
One medium base lamp,
100w max.

CADENCE

The Cadence collection showcases classic lantern styling. Clear water glass panels surround traditional lighting clusters. A curved, Mediterranean-influenced frame is finished in Textured Black and Oil rubbed Bronze.



P6542-108



P6080-108



P6639-108



P6640-108



P6542-108



P6638-108



P6442-108

OUTDOOR

FINISH

● Oil Rubbed Bronze - 108

SMALL WALL-LANTERN

P6080-108 Oil Rubbed Bronze
6" W., 16-1/4" ht.
Extends 7-1/4". H/CTR 7-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6638-108 Oil Rubbed Bronze
8" W., 21-1/4" ht.
Extends 9-3/8". H/CTR 9-7/8".
Two candelabra base lamps,
each 60w max.

POST LANTERN

P6442-108 Oil Rubbed Bronze
10" sq., 22-5/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P6542-108 Oil Rubbed Bronze
10" sq., 24" ht.
Overall ht. w/chain 99-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P6639-108 Oil Rubbed Bronze
10" W., 26-5/8" ht.
Extends 11-1/2". H/CTR 9-5/8".
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN

P6640-108 Oil Rubbed Bronze
12-1/4" W., 32" ht.
Extends 13-3/4". H/CTR 11-5/8".
Four candelabra base lamps,
each 60w max.

CADENCE

FINISH

- Textured Black - 31

SMALL WALL LANTERN

P6626-31CD Textured Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One candelabra base lamp,
60w max.



P6626-31CD



P6627-31MD

MEDIUM WALL LANTERN

P6627-31MD Textured Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6628-31MD Textured Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One medium base lamp,
100w max.



P6629-31MD



P6628-31MD

EXTRA LARGE WALL LANTERN

P6629-31MD Textured Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One medium base lamp,
100w max.



P6627-31MD

MAISON

Maison offers French country styling for a variety of home settings. Classic and formal clear water seeded glass in a die-cast aluminum frame.



P6637-31MD



P6634-31CD



P6635-31CD



P6636-31MD



P6637-31MD

OUTDOOR

FINISH

- Textured Black - 31

SMALL WALL LANTERN

P6634-31CD Textured Black
5-3/4" W., 13-5/8" ht.
Extends 6-1/8". H/CTR 9-1/8".
One candelabra base lamp,
60w max.

MEDIUM WALL LANTERN

P6635-31CD Textured Black
7-1/4" W., 16-7/8" ht.
Extends 7-5/8". H/CTR 11-3/4".
One candelabra base lamp,
60w max.

LARGE WALL LANTERN


P6636-31MD Textured Black
8-1/2" W., 18-3/4" ht.
Extends 8-7/8". H/CTR 13-3/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN

P6637-31MD Textured Black
10-1/2" W., 23-3/4" ht.
Extends 11-1/4". H/CTR 16-3/8".
One medium base lamp,
100w max.

GIBBES STREET

Elongated frames capture the romantic charm of vintage gas lanterns. Inspired by a stroll down a Charlestonian street bearing the same name, the Gibbes Street outdoor lantern collection features clear beveled glass and a classic Black or Antique Bronze finish. Wall, post, and hanging lanterns complete the family.



P550004-020



P560021-020



P560022-020



P560023-020



P550004-020



P540004-020

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540004-020 Antique Bronze
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550004-020 Antique Bronze
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560022-020 Antique Bronze
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-020 Antique Bronze
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

GIBBES STREET



P550009-031



P560021-031



P560022-031



P560023-031



P550004-031



P540004-031

FINISH

- Textured Black - 031

POST LANTERN

P540004-031 Textured Black
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P560021-031 Textured Black
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-031 Textured Black
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560022-031 Textured Black
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-031 Textured Black
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

SANTEE

A classic colonial wall lantern with contemporary touches describes Santee. Featuring a geometric frame and graphic handle, the wider beveled glass offers more refraction – and visual interest – than typical lantern designs. Choose from a Matte Black frame with stainless steel candle or an Antique Bronze frame with painted brass candle.



P560003-020



P560002-020



P560002-031



P560003-020



P560003-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Matte Black - 031

SMALL WALL LANTERN

P560002-020 Antique Bronze
P560002-031 Matte Black
 8" W., 15-1/4" ht.
 Extends 5-3/4". H/CTR 8-3/4".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560003-020 Antique Bronze
P560003-031 Matte Black
 9-1/2" W., 19-5/8" ht.
 Extends 6-1/2". H/CTR 11-3/8".
 Three candelabra base lamps,
 each 60w max.

CREIGHTON

Creighton features clear water glass with Antique Bronze or Textured Black finish options. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.



P550009-020



P560031-031



P560031-020



P560032-031



P560032-020



P560033-031



P560033-020



P540009-031



P540009-020



P550009-020



P550009-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540009-020 Antique Bronze
P540009-031 Textured Black
 10-1/2" dia., 21-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P550009-020 Antique Bronze
P550009-031 Textured Black
 10-1/2" dia., 21-5/8" ht.
 Overall ht. w/chain 96-1/2"; wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL-LANTERN

P560031-020 Antique Bronze
P560031-031 Textured Black
 6" W., 11-1/2" ht.
 Extends 7-1/4". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560032-020 Antique Bronze
P560032-031 Textured Black
 8-3/8" W., 15-3/4" ht.
 Extends 9-3/8". H/CTR 3".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560033-020 Antique Bronze
P560033-031 Textured Black
 10-1/2" W., 19-1/4" ht.
 Extends 11-1/8". H/CTR 3".
 One medium base lamp,
 100w max.

KIAWAH

Seeded glass panels and traditional detailing combine to create a soft and updated lantern design. Hinged door for easy relamping is available for post, hanging and medium and large wall lanterns.



P550001-031



P560010-031



P560011-031



P540001-031



P550001-031



P560012-031

OUTDOOR

FINISH

- Textured Black - 031

POST LANTERN

P540001-031 Textured Black
9-1/2" sq., 20-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550001-031 Textured Black
9-1/2" sq., 19-5/8" ht.
Overall ht. w/chain 94-1/2"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560010-031 Textured Black
5-5/8" W., 12-7/8" ht.
Extends 6-3/8". H/CTR 5-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560011-031 Textured Black
7-1/2" W., 21-7/8" ht.
Extends 8-3/8". H/CTR 8-1/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560012-031 Textured Black
9-1/2" W., 27-1/4" ht.
Extends 10-1/4". H/CTR 10".
Three candelabra base lamps,
each 60w max.

LEAWOOD LED


Leawood LED provides delicate scrollwork with dramatic shadow patterns in a modern form. Intricate die cast aluminum construction is available in classic Black or White finish options. A taller design accommodates the larger scale commonly seen in today's modern and traditional architecture. Available in hanging, post and wall lanterns.



P560105-031-30



P550037-030-30



P550037-031-30



P560104-030-30



P560104-031-30



P560105-030-30



P560105-031-30



P540037-030-30



P540037-031-30

OUTDOOR

FINISHES

- Textured White - 030
- Textured Black - 031

POST LANTERN

P540037-030-30 White
P540037-031-30 Textured Black
 10" dia., 18-7/8" ht.
 Fits 3" post (order separately).
 One 17w LED module, 3000K, 90CRI, 1276 source lumens.

HANGING LANTERN

P550037-030-30 White
P550037-031-30 Textured Black
 10" dia., 19-3/8" ht.
 Overall ht. w/chain 93-1/2", wire 10'.
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

SMALL WALL LANTERN

P560104-030-30 White
P560104-031-30 Textured Black
 8" dia., 13-5/8" ht.
 Extends 9-12". H/CTR 4-5/8".
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

MEDIUM WALL LANTERN

P560105-030-30 White
P560105-031-30 Textured Black
 10" dia., 17" ht.
 Extends 11-3/4". H/CTR 5-3/4".
 One 9w LED module, 3000K, 90CRI, 624 source lumens.

All fixtures:



WHITACRE LED

Inspired by traditional lantern styles, Whitacre incorporates handsome details. Clear seeded glass surrounds an etched opal glass candle diffuser. An Antique Bronze finish complements a variety of exteriors, including Transitional, Traditional and Farmhouse designs.



P560069-020-30



P560068-020-30



P560069-020-30

OUTDOOR

FINISH

● Antique Bronze - 020

SMALL WALL LANTERN

P560068-020-30 Antique Bronze
7-7/8" W., 14-3/8" ht.
Extends 8". H/CTR 3-5/8".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

MEDIUM WALL LANTERN

P560069-020-30 Antique Bronze
10" W., 18" ht.
Extends 10". H/CTR 4".
One 9w LED module, 3000K,
90 CRI, 624 source lumens.

All fixtures:



VERDAE

Classic and formal clear seeded glass complements a Textured Black or Antique Bronze finish. Open bottom or hinged door provide easy access for cleaning and relamping.



P560016-020



P560014-020



P560014-031



P560015-020



P560015-031



P560016-020



P560016-031



P560017-020



P560017-031

OUTDOOR

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540002-020 Antique Bronze
P540002-031 Textured Black
 10-3/8" dia., 22-5/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.



P540002-031

SMALL WALL-LANTERN

P560014-020 Antique Bronze
P560014-031 Textured Black
 6-1/4" W., 13-1/4" ht.
 Extends 8-5/8". H/CTR 5-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560015-020 Antique Bronze
P560015-031 Textured Black
 8-1/4" W., 17-3/4" ht.
 Extends 11-3/8". H/CTR 10-1/8".
 One medium base lamp,
 100w max.



P540002-020

LARGE WALL-LANTERN

P560016-020 Antique Bronze
P560016-031 Textured Black
 10-3/8" W., 21-3/4" ht.
 Extends 13-5/8". H/CTR 10".
 Three candelabra base lamps,
 each 60w max.

EXTRA-LARGE WALL-LANTERN

P560017-020 Antique Bronze
P560017-031 Textured Black
 10-3/8" W., 30-1/2" ht.
 Extends 13-1/4". H/CTR 14-3/4".
 Three candelabra base lamps,
 each 60w max.

JANSSEN

Create a home fully of modern elegance with the Janssen Collection. Sleek, elongated frames with rectangular forms hold gorgeous etched glass diffuser in an architectural design intended to add a contemporary glow while commanding visual interest.



P550044-108



P560122-108



P560123-108



P550044-108



P540017-108

OUTDOOR

FINISH

- Oil Rubbed Bronze - 108

POST LANTERN

P540017-108 Oil Rubbed Bronze
7-1/2" dia., 20-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550044-108 Oil Rubbed Bronze
7-1/2" dia., 21" ht.
Overall ht. w/chain 96", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560122-108 Oil Rubbed Bronze
7-1/2" W., 12-1/2" ht.
Extends 8-1/4". H/CTR 3-1/2".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560123-108 Oil Rubbed Bronze
7-1/2" W., 19" ht.
Extends 8-1/4". H/CTR 5".
One medium base lamp,
100w max.

PATEWOOD

Patewood lanterns have a modern shadowbox housing in a sleek Black finish constructed from durable stainless steel. The pillar candle style diffusers provide crisp illumination for a pleasing complement to your home's exterior.



P550024-031



P550024-031



P560041-031



P560039-031



P560040-031



P540013-031

OUTDOOR

FINISH

- Black - 031

POST LANTERN

P540013-031 Black
Fits 3" post (order separately).
7" W., 19-3/8" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550024-031 Black
7 W., 18" ht.
Overall ht. w/stem 84, wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560039-031 Black
4-1/2" W., 12" ht.
Extends 5-3/8". H/CTR 8-5/8".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P560040-031 Black
5-11/16" W., 14-1/2" ht.
Extends 6-1/2". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560041-031 Black
7" W., 17-3/8" ht.
Extends 7-3/4". H/CTR 11-7/8".
One medium base lamp,
100w max.

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Collections, page 130
Bath, page 216



P560005-135



P560004-135



P560005-135



P560006-135



P550018-135



P550007-135



P540046-135

OUTDOOR

FINISH

● Stainless Steel - 135

FLUSH MOUNT

P550007-135 Stainless Steel
12-3/8" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL-LANTERN

P560004-135 Stainless Steel
6-1/2" W., 15-7/8" ht.
Extends 5-1/2". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560005-135 Stainless Steel
7-7/8" W., 19-3/8" ht.
Extends 6-1/2". H/CTR 7-3/4".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560006-135 Stainless Steel
9-3/4" W., 23-5/8" ht.
Extends 8". H/CTR 9-5/8".
One medium base lamp,
100w max.

HANGING LANTERN

P550018-135 Stainless Steel
7" sq., 27-3/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
100w max.

POST LANTERN

P540046-135 Stainless Steel
7" L., 9-3/4" W., 26" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.



N New Product

CULLMAN

Cullman outdoor lanterns deliver dramatic scale with Craftsman appeal. Bold and linear details in an Antique Bronze finish highlight clear seeded glass. Ideal for spacious Modern architecture settings. Available in post, hanging and wall lantern options.



P560125-020



P560124-020



P560125-020



P560126-020



P550045-020



P540018-020

OUTDOOR

FINISH

- Antique Bronze - 020

POST LANTERN

P540018-020 Antique Bronze
11" sq., 22-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550045-020 Antique Bronze
11" sq., 19-5/8" ht.
Overall ht. w/chain 94", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560124-020 Antique Bronze
7" W., 16-5/8" ht.
Extends 8-3/8". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560125-020 Antique Bronze
9" W., 16" ht.
Extends 10-3/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560126-020 Antique Bronze
11" W., 19-1/4" ht.
Extends 12-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

PRODUCT INDEX

P2000

P2193..... 245
 P2194..... 245
 P2195..... 245
 P2196..... 245
 P2325..... 167
 P2326..... 165
 P2850..... 112, 223
 P2854..... 223
 P2856..... 223
 P2857..... 223

P3000

P300000..... 233
 P300001..... 233
 P300002..... 233
 P300003..... 233
 P300004..... 161, 163, 235
 P300005..... 235
 P300006..... 235
 P300007..... 235
 P300008..... 139, 141, 231
 P300009..... 231
 P300010..... 231
 P300011..... 231
 P300012..... 239, 240, 241
 P300013..... 239, 240, 241
 P300014..... 239, 240, 241
 P300015..... 239, 240, 241
 P300016..... 237
 P300017..... 237
 P300018..... 237
 P300019..... 237
 P300020..... 107, 109, 111,
 219, 220, 221
 P300021..... 219, 220, 221
 P300022..... 219, 220, 221
 P300023..... 219, 220, 221
 P300024..... 243
 P300025..... 243
 P300026..... 243
 P300027..... 243
 P300061..... 249
 P300062..... 249
 P300063..... 247
 P300065..... 247
 P300105..... 115, 117, 215
 P300106..... 215
 P300107..... 215
 P300108..... 229
 P300109..... 229
 P300110..... 229
 P300111..... 229
 P300112..... 225
 P300113..... 225
 P300114..... 225
 P300115..... 225

P300135..... 217
 P300136..... 217
 P300197..... 227
 P300198..... 227
 P300199..... 227
 P300200..... 227
 P300214..... 105
 P350029..... 169
 P350032..... 161, 163
 P350034..... 157, 159
 P350036..... 139, 141
 P350040..... 107, 109, 111
 P350090..... 115, 117
 P350102..... 127, 129
 P350105..... 109, 111
 P350119..... 135
 P350120..... 103
 P350121..... 105
 P350139..... 85
 P350140..... 75
 P350141..... 71
 P350142..... 81
 P350143..... 79
 P350158..... 95
 P350159..... 93
 P350203..... 91
 P3598..... 179
 P3601..... 179
 P3604..... 99
 P3868..... 181

P4000

P400002..... 137
 P400003..... 137
 P400008..... 161, 163
 P400009..... 161, 163
 P400010..... 161, 163
 P400011..... 157, 159
 P400012..... 157, 159
 P400013..... 157, 159
 P400014..... 157, 159
 P400015..... 139, 141
 P400016..... 139, 141
 P400017..... 139, 141
 P400021..... 107, 109, 111
 P400022..... 107, 109, 111
 P400023..... 107, 109, 111
 P400024..... 153, 155
 P400025..... 153, 155
 P400026..... 153, 155
 P400040..... 123
 P400041..... 123
 P400049..... 169
 P400077..... 125
 P400081..... 145, 147
 P400086..... 103
 P400098..... 119
 P400099..... 119
 P400101..... 166
 P400105..... 127, 129
 P400108..... 121
 P400109..... 121

P4000 (cont'd)

P400112..... 131
 P400113..... 105
 P400114..... 105
 P400116..... 115, 117
 P400117..... 153, 155
 P400145..... 131
 P400164..... 133
 P400165..... 133
 P400166..... 133
 P400170..... 97
 P400176..... 113
 P400179..... 105
 P400180..... 135
 P400192..... 65
 P400213..... 101
 P400215..... 101
 P400216..... 95
 P400217..... 95
 P400227..... 171, 173
 P4756..... 112
 P4760..... 149
 P4761..... 149
 P4763..... 149
 P4766..... 151
 P4767..... 151

P5000

P500000..... 201
 P500006..... 161, 163
 P500010..... 143
 P500011..... 143
 P500012..... 143
 P500013..... 203
 P500032..... 197
 P500033..... 197
 P500036..... 177
 P500037..... 177
 P500038..... 175
 P500039..... 175
 P500040..... 175
 P500042..... 137
 P500043..... 169
 P500046..... 187
 P500047..... 187
 P500063..... 195
 P500064..... 193
 P500073..... 115, 117
 P500074..... 115, 117
 P500082..... 125
 P500083..... 125
 P500084..... 125
 P500088..... 145, 147
 P500089..... 145, 147
 P500095..... 115, 117
 P500098..... 197
 P500105..... 119
 P500106..... 119
 P500107..... 119
 P500108..... 119
 P500117..... 127, 129
 P500118..... 200
 P500151..... 107, 109, 111
 P500164..... 135
 P500165..... 135
 P500168..... 103
 P500173..... 97
 P500174..... 97
 P500194..... 69
 P500195..... 79
 P500196..... 77
 P500197..... 75

P500198..... 71
 P500199..... 67
 P500200..... 67
 P500201..... 75
 P500202..... 79
 P500203..... 86
 P500204..... 72
 P500221..... 185
 P500222..... 185
 P500232..... 93
 P500233..... 93
 P500248..... 101
 P500285..... 171, 173
 P500305..... 107, 109, 111
 P500330..... 91
 P500331..... 91
 P5015..... 99
 P5021..... 99
 P5073..... 179
 P5309..... 190
 P5311..... 190
 P5317..... 149
 P5318..... 151
 P5319..... 181
 P5320..... 166
 P5321..... 165
 P5322..... 181
 P5324..... 191
 P5332..... 189
 P5333..... 189
 P5334..... 189
 P5337..... 199
 P5338..... 199
 P5346..... 165
 P540001..... 273
 P540002..... 279
 P540004..... 265, 267
 P540009..... 271
 P540013..... 283
 P540016..... 255, 257
 P540017..... 281
 P540018..... 287
 P540037..... 275
 P540046..... 285

P540067..... 253
 P550001..... 273
 P550004..... 265, 267
 P550007..... 285
 P550009..... 271
 P550018..... 285
 P550024..... 283
 P550037..... 275
 P550041..... 255, 257
 P550044..... 281
 P550045..... 287
 P550067..... 253
 P560002..... 269
 P560003..... 269
 P560004..... 285
 P560005..... 285
 P560006..... 285
 P560010..... 273
 P560011..... 273
 P560012..... 273
 P560014..... 279
 P560015..... 279
 P560016..... 279
 P560017..... 279
 P560021..... 265, 267
 P560022..... 265, 267
 P560023..... 265, 267
 P560031..... 271
 P560032..... 271
 P560033..... 271
 P560039..... 283
 P560040..... 283
 P560041..... 283
 P560068..... 277
 P560069..... 277
 P560104..... 275
 P560105..... 275
 P560116..... 255, 257
 P560117..... 255, 257
 P560118..... 255, 257
 P560122..... 281
 P560123..... 281
 P560124..... 287
 P560125..... 287

PRODUCT INDEX

P5000 <i>(cont'd)</i>	P6000	P7000	P8000
P560126 287	P6080 259	P710002 137	P860002..... 139, 141, 231
P560182 253	P6442 259	P710013..... 169	P860003..... 139, 141, 231
P560183 253	P6542 259	P710016..... 206	
P560184 253	P6626 261	P710017..... 210	
	P6627 261	P710018..... 171, 173, 209	
	P6628 261	P710019..... 171, 173, 209	
	P6629 261	P710025 207	
	P6634 263	P710027 121	
	P6635 263	P710034 211	
	P6636 263	P710037 119	
	P6637 263	P710038 217, 131	
	P6638 259	P710043 127, 129	
	P6639 259	P710055 135	
	P6640 259	P710057 97	
		P710063 113	
		P710064 67	
		P710065 83	
		P710066 77	
		P710067 75	
		P710068 71	
		P710069 73	
		P710070 69	
		P710076 93	
		P710077 101	
		P710078 95	
		P710100..... 91	
		P7198..... 167	

ICON KEY



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energyc.ca.gov



Complies with the "Americans with Disabilities Act"



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseperable SSL luminaires that are installed outdoors



Products with this icon are Dark Sky friendly by minimizing glare, reducing light trespass and skyglow.

EQUIP EDUCATE EXCITE

These three words define the mission of Progress Lighting. Flip through our catalog, and you'll quickly see how we equip you with the education to make all your exciting design dreams come true. Whether you're browsing our catalog or visiting our website, Progress is at your service to help you envision where and how to use our products.

To explore more of the Design Series™ visit us online:



progresslighting.com/designseries

EXPERIENCE PROGRESS

Learn how lighting can totally transform a space. Experience Progress features beautiful room images from our builder partners, design firms, social media fans and influencers bringing the Progress Lighting story to life. By working together, we're furthering a vision of providing whole home solutions to those who are seeking inspiration.

Visit progresslighting.com/experienceprogress

LET'S GET SOCIAL

Explore our blog for even more design inspiration, product integration and trend guidance to make your home into a haven of livable luxury.

See progresslighting.com/blog

- @ProgressLtg
- @ProgressLtg
- @ProgressLtg
- Progress Lighting
- @ProgressLighting
- Progress-Lighting

#ProgressLighting
#DesignSeries

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2021
All rights reserved.
International copyright secured.



701 Millennium Blvd
Greenville, SC 29607



COMPLETE YOUR DESIGN

with eye-catching accessories.

Enhance the style of your Design Series fixture with a selection from our lighting accessories. Add a new canopy to complement the design and personalize the fixture to fit your décor. Create your own look by mounting several pendants on a multi-pendant canopy, or swap out shades for a different style or color. Order extra stem rod or chains to extend the hanging length of the fixture. *THE CHOICE IS YOURS!*

PENDANT CANOPIES, STEM KITS, CHAINS, SHADES + MORE!



For more lighting accessory design tips: www.progresslighting.com/accessories



