PROGRESS LIGHTING

JEFFREY ALAN MARKS

Recognized as one of today's most influential American designers, Jeffrey's work is infused with the same lighthearted, good-natured disposition as the Southern California talent himself. With a thoughtful and tailored sensibility, his designs are always an effortless blend of timelessness and casual livability, devoid of trend or artifice. From Nantucket Beach houses to San Francisco town houses, Jeffrey's work resonates.

progress lighting DESIGN**+SERIES**





A fitting collaboration between dreamer and maker.












DREAMER

Jeffrey's purposeful and authentic spaces beg to be lived in rather than existing only to be stylish. Today this Elle Décor A-List designer's spirited aesthetic is realized beyond his fortunate clients through licensing partnerships and a broader audience can look forward to homes that are more genuine, more personal and more engaging.



4 | PROGRESS LIGHTING


Photo by Steven Lippman



POINT DUME







"I believe that lighting has a higher purpose, to be at once illuminating and decorative, purposeful and beautiful. Lighting is the ultimate marriage of form and function and the most transformative element in a design project. The very nature of light itself is inspirational."

JEFFREY ALAN MARKS

Jeffrey's Point Dume™ lighting collection celebrates a curated mix of yesterday and today, distilling both industrial and artisanal influences. At home in a range of lifestyles from coastal to urban, the Collection is inspired by two of his favorite places, Point Dume, California, and East Hampton, New York, with exceptional combinations of materials woven throughout. Emulating both the raw strength and the captivating honesty of the landscape, Jeffrey intuitively elevates lighting to a more authentic art form as he marries craftsmanship and style with some of his favorite materials and memories.



MAKER

In the eclectic Point Dume™ Collection, the dreamer and the maker are united by the desire to provide an elevated level of home fashion to an enthusiastic design-savvy consumer. As the inaugural guest designer of Progress' Design Series brand, Jeffrey's design goals are in sync with the Design Series

philosophy — to offer sophisticated styling at an accessible price. Together they are on a journey to inspire individuals to update favorite spaces in their homes through interior and exterior fixtures that highlight artistic influence, rich finishes and fashionforward elements.

10 | PROGRESS LIGHTING -

Shadmore

With the Shadmore Pendant, Jeffrey embraces bold architectural influences to create a minimalistic design that effectively blurs the lines between indoor and outdoor living. Airy interconnected geometric cubes form a spacious frame giving the light a modern personality. An elegant, marbleized acrylic shade creates a striking focal point while delivering an inviting, warm glow.



OUTDOOR HANGING LANTERN P550118-141 Galvanized



OUTDOOR HANGING LANTERN P550118-31M Matte Black





Edgecliff

The Edgecliff Pendant celebrates the austere simplicity and functionality of America's architecturally distinct corrugated metal-clad buildings. Crisp, sharp lines form a frame of iconic metal curves, making a sculptural gesture to its traditional inspiration. Silver mesh patterned glass on each end of the frame provides a luxurious touch to the rustic design. Jeffrey recommends using exposed filament style bulbs in the open-bottom frame to further the authentic Farmhouse style of the light.



OUTDOOR HANGING LANTERN P550119-108 Oil Rubbed Bronze



OUTDOOR HANGING LANTERN P550119-192 Shelter White



OUTDOOR HANGING LANTERN

P550119-141 Galvanized

Seamoor


For Seamoor, Jeffrey created a sophisticated adaptation of the utilitarian metal roofs found on farm buildings throughout the countryside. A square frame supports a wavy roof inspired by traditional corrugated rooflines. The rectangular handle is reminiscent of handles on old barn lanterns, but its oversized scale adds a contemporary element. Clear glass panels surround a classic silver reflector on the back panel, enhancing the glow cast from an elegant double candle holder. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



WALL LANTERN P560297-108 Oil Rubbed Bronze



WALL LANTERN P560297-141 Galvanized







OUTDOOR HANGING LANTERN P550117-141 Galvanized



OUTDOOR HANGING LANTERN P550117-108 Oil Rubbed Bronze

Hook Pond

Evoking thoughts of Jeffrey's East Coast summer home, the Hook Pond Collection features a steeply pitched, barn-inspired roof crowned with a distinctive loop finial. A clean, modern frame holds glass panels printed with a unique silver mesh pattern reminiscent of a traditional screened-in porch. Light is comfortably diffused from the white opal glass orb held within the generously scaled frame. The versatile collection is constructed of engineered composite polymers. Hook Pond wall lanterns are made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.





OUTDOOR HANGING LANTERN P550117-192 Shelter White







Ze



LANTERN P560305-141 Galvanized



LL.

SMALL WALL LANTERN P560305-192 Shelter White



LARGE WALL LANTERN P560306-108

P560306-108 Oil Rubbed Bronze



LARGE WALL LANTERN P560306-141 Galvanized



LARGE WALL LANTERN P560306-192 Shelter White



Dunemere

Homes from coast to coast will appreciate how the Dunemere Wall Lantern embodies Jeffrey's love of casual, relaxed outdoor living. Vintage barn details of symmetrical gables and a slanted corrugated roof form a peaked canopy over modern ribbed lamp holders and clear glass panels. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



MEDIUM WALL

LANTERN

P560303-141

Galvanized



MEDIUM WALL LANTERN P560303-192 Shelter White



MEDIUM WALL LANTERN P560303-31M Matte Black









SMALL WALL LANTERN P560302-192 Shelter White



LARGE WALL LANTERN P560304-141 Galvanized



LANTERN P560304-192 Shelter White





SMALL WALL LANTERN P560302-31M Matte Black



LARGE WALL LANTERN

P560304-31M Matte Black



SMALL WALL LANTERN

P560300-141-27 Galvanized



SMALL WALL

P560300-192-27 Shelter White



MEDIUM WALL LANTERN P560299-141-27 Galvanized



MEDIUM WALL LANTERN P560299-192-27 Shelter White



SMALL WALL LANTERN P560300-31M-27 Matte Black



MEDIUM WALL LANTERN P560299-31M-27 Matte Black

Wakecrest LED

The Wakecrest LED Wall Sconce is a contemporary take on rustic luxury. Jeffrey translated the corrugated rooflines of classic barns into a softly waved sconce frame, paying homage to the Americana aesthetic. A crisp, sharp edge defines the modern roof peak and complements the vintage character of the fixture's design. Made with DURASHIELD, a durable material specially designed and tested to resist harsh environmental conditions.



"This collection of exterior lighting represents the true meaning of home – inviting spaces filled with warmth, comfort and beauty. Through these designs, I strive to capture the magic that is East Hampton, New York, a spot that is very sentimental to me and my family. The unobstructed landscape dominates, with beautiful green pastures surrounding tranquil ponds on the ocean's edge."

JEFFREY ALAN MARKS

This outdoor lighting extension of the Point Dume[™] Collection expresses the relaxed attitude of shingled homes on the East Coast shoreline married with the elegant style of Hampton estates. Jeffrey turns to a familiar mix of finishes, such as galvanized and aged metals alongside a new palette of crisp white and artistic glass, evoking a bygone era of craftsmanship and glamour that epitomizes Hampton retreats. These designs blur the lines between indoor and outdoor living, creating a welcoming and luxurious atmosphere for homes from coast to coast.







CHANDELIER

P400192-160 Brushed Brass

Wandermere

With elegant out-stretched arms and the grace of a Calder mobile, the Wandermere chandelier is "modern symmetry in balance." Available in Brushed Brass with curved metal shades, the Wandermere is an architectural presence for any space.

Surfrider

Rows of lapping wave-like metal are combined with beautifully braided cords, and suspension hooks for an ageless "industrial meets the modern minded" point of view. The inspired Surfrider pendant is offered in a Galvanized finish and a refreshing "Maliblue" finish. To round out the versatile group, the Surfrider collection also includes complementary sconces available in Galvanized, Antique Bronze or White.



LARGE PENDANT

P500200-162 Maliblue



LARGE PENDANT

P500200-141 Galvanized







PENDANT P500199-141 Galvanized



PENDANT P500199-162 Maliblue



WALL SCONCE

P710064-030 White



WALL SCONCE P710064-020 Antique Bronze



WALL SCONCE P710064-141 Galvanized







PENDANT P500194-160 Brushed Brass





WALL BRACKET P710070-160 Brushed Brass

Onshore

Continuing Jeffrey's modern take on light and movement, the Onshore series combines some of his favorite materials and finishes. Offered as a White and Brushed Brass pendant, or a "Maliblue" and Brushed Nickel option, the Onshore group is a fresh and uplifting choice for casual living. The Onshore swing arm wall sconce in Brushed Brass has a three-tiered white enamel shade that complements this lifestyle.





Sandbar

Ageless Brushed Brass is layered in modern tiers for the Sandbar ceiling fixture, sconce and pendant light. The addition of Jeffrey's tailormade leather details, brass hooks, milk glass and cables make for memorable, luxury lighting with infinite design applications.



SEMI-FLUSH CONVERTIBLE

P350141-160 Brushed Brass



SEMI-FLUSH CONVERTIBLE P350141-160 Brushed Brass



PENDANT P500198-160 Brushed Brass



WALL SCONCE

P710068-160 Brushed Brass



WALL BRACKET

P710069-009 Brushed Nickel

Lookout

The Lookout wall sconce is a modern classic that combines Brushed Nickel, clear seeded glass and handsome leather accents. Perfectly at home in so many locations and lifestyles, the Lookout sconce is ideal to use when multiples are a must. The Lookout wall sconce has the enduring sensibility that adds an uncomplicated elegance to any interior.



"For me the true meaning of home is being surrounded with natural physical beauty and well-crafted objects that feel both polished and personal."

JEFFREY ALAN MARKS





LARGE PENDANT P500197-134 Silver Ridge

Yerba

The Yerba group marries a modernized Moroccan shape with Mid Century geometric detail. Crafted of pierced metal in a Silver Ridge finish, the Yerba collection offers an inverted pendant, a dome shaped pendant, ceiling mounted fixture and wall sconce, each casting dramatic dappled light throughout a space.







P500197-134 Silver Ridge



SEMI-FLUSH P350140-134 Silver Ridge



PENDANT P500201-134

Silver Ridge



WALL SCONCE P710067-134 Silver Ridge

Shearwater

The Shearwater hanging lanterns and wall sconces embody Jeffrey's love of easy coastal living. His lighter lantern and sconce option combine Antique Nickel with clear glass and a soft-beige stitched leather handle, while the more traditional version of Shearwater combines Aged Brass, clear glass, and a handsome brown stitched leather handle. For a more California look, Jeffrey offers a white lantern with clear glass and his signature Maliblue accent as a pop of color in the roof of the fixture.



WALL SCONCE P710066-161 Aged Brass



WALL SCONCE P710066-081 Antique Nickel







LARGE PENDANT

P500196-030 White



LARGE PENDANT P500196-161 Aged Brass



LARGE PENDANT P500196-081 Antique Nickel



PENDANT P500195-009 Brushed Nickel



PENDANT P500195-161 Aged Brass

Rockdance

The Rockdance Lighting series is a graceful series fashioned from unique glass, hook elements, and handsome stitched leather strapping. With the signatures of a bespoke handbag or boot, the surprising design elements that punctuate this exciting group are certain to become design favorites for generations. Available in Brushed Nickel or Antique Nickel with clear seeded glass or Aged Brass with mercury glass.







PENDANT P500202-081 Antique Nickel



SEMI-FLUSH P350143-081 Antique Nickel



PENDANT P500202-161 Aged Brass



SEMI-FLUSH P350143-161 Aged Brass



SEMI-FLUSH CONVERTIBLE P350139-009

Brushed Nickel



SEMI-FLUSH CONVERTIBLE P350139-009 Brushed Nickel



PENDANT P500204-081 Antique Nickel

Moonrise

Quintessential JAM, Moonrise is an ethereal globe fashioned of Antique Nickel and marbled white glass. With a nod to its vintage ancestry, this simple style statement manages to defy time and live quite happily in the present. Jeffrey recommends the simplicity of Moonrise's round silhouette the perfect choice when the design calls for multiples.

Tapia Trail

Jeffrey creates two distinctive looks when combining first Aged Brass and milk glass and then timeless Brushed Nickel and seeded glass. Both versions of the Tapia Trail fixture are defined by rivet details and remind us of their industrial origins — part Nautical, part Farmhouse, all American.



SEMI-FLUSH CONVERTIBLE

P350139-161 Aged Brass



SEMI-FLUSH CONVERTIBLE P350139-161

Aged Brass





PENDANT P500203-160 Brushed Brass

Windbluff

With sophisticated effortlessness, the Windbluff pendant was inspired by breezy shoreline living and incorporates Brushed Brass and natural linen. This transitional pendant, perfect for both modern and traditional interiors, is suspended by decorative brass hooks and thoughtfully has a white diffuser to create that perfect glow.

Sequit Point

The romance and architectural presence of a lighthouse is expressed in the Sequit Point group. In the same way strips of glass increased the effectiveness of lighthouse beacons, the modern Sequit Point series benefits from a similar ingenuity. Mercury glass sleeves stand in tandem with clear glass rods to provide a familiar glow for the convertible ceiling fixture/ pendant. Available in Antique Nickel and Brushed Brass.



SEMI-FLUSH CONVERTIBLE P350142-081 Antique Nickel



SEMI-FLUSH CONVERTIBLE P350142-160 Brushed Brass



SEMI-FLUSH CONVERTIBLE P350142-081 Antique Nickel



SEMI-FLUSH CONVERTIBLE P350142-160 Brushed Brass







WALL SCONCE P710065-020 Antique Bronze

Latigo Bay

The timeless Latigo Bay wall sconce hugs the wall with a simple lined Mercury glass back and an articulated curved metal shade. Predicted to be a classic go-to for a variety of easy interior updates, this slim vertical sconce is available in Antique Bronze and Brushed Nickel.



WALL SCONCE P710065-009 Brushed Nickel

OUTDOOR



SHADMORE Outdoor Hanging Lantern P550118-31M Matte Black with marbleized acrylic shade

26" sq., 31-1/4" ht. Overall ht. w/stem 97-1/2", wire 10'. One medium base lamp. 100w max.



EDGECLIFF Outdoor Hanging Lantern P550119-141 Galvanized with silver mesh patterned glass

33-1/8" W., 22-3/4 L., 14-1/2" ht. Overall ht. w/stem 92", wire 10'. Three medium base lamps, 100w max.



SHADMORE Outdoor Hanging Lantern P550118-141 Galvanized with marbleized acrylic shade

26" sq., 31-1/4" ht. Overall ht. w/stem 97-1/2", wire 10'. One medium base lamp. 100w max.



EDGECLIFF Outdoor Hanging Lantern P550119-192 Shelter White with silver mesh patterned glass

33-1/8" W., 22-3/4 L., 14-1/2" ht. Overall ht. w/stem 92", wire 10'. Three medium base lamps, 100w max.



+

EDGECLIFF Outdoor Hanging Lantern P550119-108 Oil Rubbed Bronze with silver mesh patterned glass

33-1/8" W., 22-3/4 L., 14-1/2" ht. Overall ht. w/stem 92", wire 10'. Three medium base lamps, 100w max.









HOOK POND Outdoor Hanging Lantern P550117-108 Oil Rubbed Bronze with silver mesh patterned glass

16-1/8" sq., 26-7/8" ht. Overall ht. w/stem 101", wire 15'. One medium base lamp, 60w max.

HOOK POND Outdoor Hanging Lantern P550117-141 Galvanized with silver mesh patterned glass

16-1/8" sq., 26-7/8" ht. Overall ht. w/stem 101", wire 15'. One medium base lamp. 60w max.



HOOK POND Small Wall Lantern P560305-108 Oil Rubbed Bronze with silver mesh patterned glass

6-1/4" W., 16-1/2" ht. Extends 5-1/4". H/CTR 11". One medium base lamp, 60w max.



HOOK POND Large Wall Lantern P560306-108 Oil Rubbed Bronze with silver mesh patterned glass

8-1/2" W., 22-3/8" ht. Extends 7-1/8". H/CTR 15-1/8". One medium base lamp, 60w max.





HOOK POND Large Wall Lantern P560306-141 Galvanized with silver mesh patterned glass

8-1/2" W., 22-3/8" ht. Extends 7-1/8". H/CTR 15-1/8". One medium base lamp, 60w max.



SEAMOOR Wall Lantern P560297-108 Oil Rubbed Bronze

11" W., 12-5/8" ht. Extends 6". H/CTR 7-1/2". Two candelabra base lamps, 60w max.



SEAMOOR Wall Lantern P560297-141 Galvanized

11" W., 12-5/8" ht. Extends 6". H/CTR 7-1/2". Two candelabra base lamps, 60w max.

POINT DUME[™] COLLECTION



HOOK POND Outdoor Hanging Lantern P550117-192 Shelter White with silver mesh patterned glass

16-1/8" sq., 26-7/8" ht. Overall ht. w/stem 101", wire 15'. One medium base lamp. 60w max.



HOOK POND Small Wall Lantern P560305-192 Shelter White with silver mesh patterned glass

6-1/4" W., 16-1/2" ht. Extends 5-1/4". H/CTR 11". One medium base lamp, 60w max.



HOOK POND Large Wall Lantern P560306-192 Shelter White with silver mesh patterned glass

8-1/2" W., 22-3/8" ht. Extends 7-1/8". H/CTR 15-1/8". One medium base lamp, 60w max.

OUTDOOR -



DUNEMERE Small Wall Lantern P560302-141 Galvanized

6-5/8" W., 10-1/2" ht. Extends 5-7/8". H/CTR 7-5/8". One medium base lamp, 60w max.



DUNEMERE Medium Wall Lantern P560303-141 Galvanized

6-5/8" W., 14" ht. Extends 5-7/8". H/CTR 9-1/4". One medium base lamp, 60w max.



DUNEMERE Large Wall Lantern P560304-141 Galvanized

8" W., 16" ht. Extends 7-1/8". H/CTR 10-1/8". One medium base lamp, 60w max.



DUNEMERE Small Wall Lantern P560302-192 Shelter White

6-5/8" W., 10-1/2" ht. Extends 5-7/8". H/CTR 7-5/8". One medium base lamp, 60w max.



DUNEMERE Medium Wall Lantern P560303-192 Shelter White

6-5/8" W., 14" ht. Extends 5-7/8". H/CTR 9-1/4". One medium base lamp, 60w max.



DUNEMERE Large Wall Lantern P560304-192 Shelter White

8" W., 16" ht. Extends 7-1/8". H/CTR 10-1/8". One medium base lamp, 60w max.



+

DUNEMERE Small Wall Lantern P560302-31M Matte Black

6-5/8" W., 10-1/2" ht. Extends 5-7/8". H/CTR 7-5/8". One medium base lamp, 60w max.



DUNEMERE Medium Wall Lantern P560303-31M Matte Black

6-5/8" W., 14" ht. Extends 5-7/8". H/CTR 9-1/4". One medium base lamp, 60w max.



DUNEMERE Large Wall Lantern P560304-31M Matte Black

8" W., 16" ht. Extends 7-1/8". H/CTR 10-1/8". One medium base lamp, 60w max.



WAKECREST LED Medium Wall Lantern P560299-141-27 Galvanized

9" W., 6-5/8" ht. Extends 3-7/8". H/CTR 4-1/2". 8w integrated LED, 2700K, 90 CRI, 388 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.



9" W., 6-5/8" ht. Extends 3-7/8". H/CTR 4-1/2". 8w integrated LED, 2700K, 90 CRI, 464 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.



WAKECREST LED Small Wall Lantern P560300-141-27 Galvanized

6-1/2" W., 6-5/8" ht. Extends 3-7/8". H/CTR 3-3/4". 6w integrated LED, 2700K, 90 CRI, 248 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.



WAKECREST LED Small Wall Lantern P560300-192-27 Shelter White

6-1/2" W., 6-5/8" ht. Extends 3-7/8". H/CTR 3-3/4". 6w integrated LED, 2700K, 90 CRI, 281 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.



+

POINT DUME[™] COLLECTION





WAKECREST LED Medium Wall Lantern P560299-192-27 Shelter White

WAKECREST LED Medium Wall Lantern P560299-31M-27 Matte Black

9" W., 6-5/8" ht. Extends 3-7/8". H/CTR 4-1/2". 8w integrated LED, 2700K, 90 CRI, 298 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.



WAKECREST LED Small Wall Lantern P560300-31M-27 Matte Black

6-1/2" W., 6-5/8" ht. Extends 3-7/8". H/CTR 3-3/4". 6w integrated LED, 2700K, 90 CRI, 217 delivered lumens. T24 for outdoor application only. ADA. Dark Sky friendly.

CHANDELIERS AND PENDANTS



WANDERMERE Chandelier P400192-160 Brushed Brass with white

40" dia., 28-1/4" ht. Overall ht. w/chain 103-1/2", wire 15'. Eight candelabra base lamps, each 60w max.

SANDBAR Pendant

21-1/4" dia., 14-7/8" ht.

each 100w max.

milk glass

P500198-160 Brushed Brass with

Overall ht. w/chain 93-1/2", wire 15'.

milk glass and beige leather

Three medium base lamps,



SURFRIDER Large Pendant P500200-162 Maliblue with white

24-7/8" dia., 17-1/2" ht. Overall ht. w/chain 103-1/2", wire 15'. Three medium base lamps, each 75w max.



SURFRIDER Pendant P500199-162 Maliblue with white 13-7/8" dia., 12-3/8" ht. Overall ht. w/chain 96-1/2", wire 15'. One medium base lamp, 75w max.



ONSHORE Pendant P500194-009 Brushed Nickel with white and Maliblue

8" dia., 13" ht. Overall ht. w/stem 79", wire 10'. One medium base lamp, 100w max.



SURFRIDER Large Pendant P500200-141 Galvanized with white

24-7/8" dia., 17-1/2" ht. Overall ht. w/chain 103-1/2", wire 15'. Three medium base lamps, each 75w max.



SURFRIDER Pendant P500199-141 Galvanized with white 13-7/8" dia., 12-3/8" ht. Overall ht. w/chain 96-1/2", wire 15'. One medium base lamp, 75w max.



ONSHORE Pendant P500194-160 Brushed Brass with white 8" dia., 13" ht. Overall ht. w/stem 79", wire 10'. One medium base lamp,

100w max.

PENDANTS



SHEARWATER Large Pendant P500196-161 Aged Brass and brown leather

16-1/4" dia., 32" ht. Overall ht. w/chain 109", wire 15'. Four candelabra base lamps, each 60w max.



SHEARWATER Large Pendant P500196-081 Antique Nickel with Maliblue and beige leather

16-1/4" dia., 32" ht. Overall ht. w/chain 109", wire 15'. Four candelabra base lamps, each 60w max.



YERBA Large Pendant P500197-134 Silver Ridge 21-5/8" dia., 24" ht. Overall ht. w/stem 90", wire 15'. Four medium base lamps,

each 60w max.

WINDBLUFF Pendant

Three medium base lamps,

linen shade

20" dia., 16-1/2" ht.

each 100w max.

P500203-160 Brushed Brass with

Overall ht. w/chain 91-1/2", wire 15'.



YERBA Pendant P500201-134 Silver Ridge

12" dia., 8-1/4" ht. Overall ht. w/stem 74-1/2", wire 10'. One medium base lamp, 100w max.



MOONRISE Pendant P500204-081 Antique Nickel with marble glass

18-1/2" dia., 19-1/4" ht. Overall ht. w/chain 94", wire 15'. Three medium base lamps, each 100w max.

SANDBAR Semi-Flush Convertible

P350141-160 Brushed Brass with

Hanging and ceiling mount

Three medium base lamps,

Overall ht. w/stem 76", wire 10'.

hardware included.

each 100w max.

15 1/8" dia., 14 7/8" ht.

POINT DUME[™] COLLECTION







SHEARWATER Large Pendant P500196-030 White with Maliblue and brown leather

16-1/4" dia., 32" ht. Overall ht. w/chain 109", wire 15'. Four candelabra base lamps, each 60w max.



TAPIA TRAIL Semi-Flush Convertible P350139-009 Brushed Nickel with seeded glass

Hanging and ceiling mount hardware included. 11-3/4" dia., 12-7/8" ht. Overall ht. w/stem 77-1/2", wire 12'. One medium base lamp, 100w max.



TAPIA TRAIL Semi-Flush Convertible P350139-161 Aged Brass with milk glass

Hanging and ceiling mount hardware included. 11-3/4" dia., 12-7/8" ht. Overall ht. w/stem 77-1/2", wire 12'. One medium base lamp, 100w max.

PENDANTS



ROCKDANCE Pendant P500202-081 Antique Nickel with beige leather and seeded glass 9-1/2" dia., 17-1/2" ht. Overall ht. w/chain 92-1/2", wire 10'.

One medium base lamp, 100w max.



ROCKDANCE Pendant P500195-009 Brushed Nickel with seeded glass and beige leather

15-3/4" dia., 10-1/8" ht. Overall ht. w/chain 85-1/2", wire 10'. One medium base lamp, 100w max.



ROCKDANCE Pendant P500195-161 Aged Brass with mercury glass and brown leather 15-3/4" dia., 10-1/8" ht. Overall ht. w/chain 85-1/2", wire 10'. One medium base lamp, 100w max.

CLOSE TO CEILING



YERBA Close to Ceiling P350140-134 Silver Ridge 17-3/8" dia., 12-3/8" ht. Three candelabra base lamps, each 60w max.

SEQUIT POINT Semi-Flush Convertible

P350142-160 Brushed Brass with

Hanging and ceiling mount

Overall ht. w/stem 78", wire 10'.

Three candelabra base lamps,

TAPIA TRAIL Semi-Flush Convertible

P350139-161 Aged Brass with

Overall ht. w/stem 77-1/2", wire 12'.

Hanging and ceiling mount

hardware included.

11-3/4" dia., 12-7/8" ht.

One medium base lamp,

mercury glass

hardware included.

14" dia., 9-5/8" ht.

each 60w max.

milk glass

100w max.



ROCKDANCE Close to Ceiling P350143-081 Antique Nickel with seeded glass with beige leather 14-3/8" dia., 10-1/4" ht. Four candelabra base lamps, each 60w max.



SEQUIT POINT Semi-Flush Convertible P350142-081 Antique Nickel with mercury glass

Hanging and ceiling mount hardware included. 14" dia., 9-5/8"" ht. Overall ht. w/stem 78", wire 10'. Three candelabra base lamps, each 60w max.



TAPIA TRAIL Semi-Flush Convertible P350139-009 Brushed Nickel with seeded glass

Hanging and ceiling mount hardware included. 11-3/4" dia., 12-7/8" ht. Overall ht. w/stem 77-1/2", wire 12'. One medium base lamp. 100w max.



ROCKDANCE Pendant P500202-161 Aged Brass with brown leather and mercury glass

9-1/2" dia., 17-1/2" ht. Overall ht. w/chain 92-1/2", wire 10'. One medium base lamp, 100w max.



SEQUIT POINT Semi-Flush Convertible P350142-160 Brushed Brass with mercury glass

Hanging and ceiling mount hardware included. 14" dia., 9-5/8" ht. Overall ht. w/stem 78", wire 10'. Three candelabra base lamps, each 60w max.



SEQUIT POINT Semi-Flush Convertible P350142-081 Antique Nickel with mercury glass

Hanging and ceiling mount hardware included. 14" dia., 9-5/8" ht. Overall ht. w/stem 78", wire 10'. Three candelabra base lamps, each 60w max.



POINT DUME[™] COLLECTION



ROCKDANCE Close to Ceiling P350143-161 Aged Brass with mercury glass and brown leather

14-3/8" dia., 10-1/4" ht. Four candelabra base lamps, each 60w max.





SANDBAR Semi-Flush Convertible P350141-160 Brushed Brass with milk glass

Hanging and ceiling mount hardware included. 15-1/8" dia.. 14-7/8" ht. Overall ht. w/stem 76", wire 10'. Three medium base lamps, each 100w max.

WALL BRACKETS AND SCONCES

WALL BRACKETS AND SCONCES



ONSHORE Wall Bracket P710070-160 Brushed Brass with white 8-7/8" dia., 8-3/8" ht.. Extends 22-1/2". H/CTR 4". One medium base lamp, 60w max.



YERBA Wall Sconce P710067-134 Silver Ridge 8-1/4" W., 12-1/2" ht.

Extends 3-7/8". H/CTR 6-1/4". One candelabra base lamp, 60w max. ADA



SURFRIDER Wall Sconce P710064-141 Galvanized

9" W., 11-1/8" ht. Extends 3-7/8". H/CTR 6". Two candelabra base lamps, each 60w max. ADA



SANDBAR Wall Sconce P710068-160 Brushed Brass with milk glass 8-7/8" W., 12" ht. Extends 4-1/2". H/CTR 6". One candelabra base lamp, 60w max.



SHEARWATER Wall Sconce P710066-081 Antique Nickel with beige leather

8" W., 15-7/8" ht. Extends 3-7/8. H/CTR 7-7/8". One candelabra base lamp, 60w max. ADA



SURFRIDER Wall Sconce P710064-020 Antique Bronze

9" W., 11-1/8" ht. Extends 3-7/8". H/CTR 6". Two candelabra base lamps, each 60w max. ADA



+

LOOKOUT Wall Sconce P710069-009 Brushed Nickel with brown leather 6" W., 12-7/8" ht. Extends 7-3/8". H/CTR 7-3/4" One medium base lamp, 60w max.



SHEARWATER Wall Sconce P710066-161 Aged Brass with brown leather 8" W., 15-7/8" ht. Extends 3-7/8. H/CTR 7-7/8".

One candelabra base lamp, 60w max. ADA



SURFRIDER Wall Sconce P710064-030 White

9" W., 11-1/8" ht. Extends 3-7/8". H/CTR 6". Two candelabra base lamps, each 60w max. ADA

+



LATIGO BAY Wall Sconce P710065-020 Antique Bronze with mercury glass 7" W., 11" ht. Extends 4". H/CTR 5-1/2". One medium base lamp, 60w max. ADA



LATIGO BAY Wall Sconce P710065-009 Brushed Nickel with mercury glass 7" W., 11" ht. Extends 4". H/CTR 5-1/2". One medium base lamp, 60w max. ADA

ACCESSORY -



ACCESSORY CHAIN P8755-31M Matte Black

ACCESSORY CHAIN P8755-108 Oil Rubbed Bronze

POINT DUME[™] COLLECTION

ACCESSORY CHAIN P8755-141 Galvanized



ACCESSORY CHAIN P8755-192 Shelter White

— DESIGN**+SERIES**™ | 75

"Beautiful lighting can appeal to both one's pragmatic nature and one's artistic spirit. For me, there is no better reward than to create well-loved spaces where life can be enjoyed fully and lived beautifully."

JEFFREY ALAN MARKS



ALAN

progresslighting.com/**jeffreyalanmark**s