



**PRODUCT
SUPPLEMENT**
JANUARY 2021



See
Yourself
Here.

Lighting helps tell a story, whether it's setting the mood or enjoying a special moment. These occasions are meaningful, expressive, and shared with those we care about most. Let Progress Lighting be your guide in illuminating these spaces into special places.

Be Inspired

-  @ProgressLtg
-  @ProgressLtg
-  @ProgressLighting
-  @ProgressLtg
-  Progress Lighting
-  Progress-Lighting



Table of Contents

Light up your life by finding the perfect fixtures that express your personal style, inside and out.

[Pictorial Index](#) 4

[DESIGN+SERIES™](#) 14

[Collections](#) 14

[Outdoor](#) 110



[Collections](#) 20



[Ceiling Fans](#) 72



[Pendants](#) 68



[Close-To-Ceiling](#) 92



[Bath Collections](#) 97



[Recessed Downlighting](#) 124



[Surface Mount Downlighting](#) 126



[Outdoor](#) 111



[Undercabinet](#) 127



[Index](#) 128

Collections

BRIARWOOD Galvanized p.40 **BRIARWOOD** Textured Black p.43 **ELEVATE** Brushed Bronze p.17 **ELEVATE** Polished Chrome p.17 **ELEVATE** Matte Black p.16



GEODESIC LED Matte Black p.30 **HEDGEROW** Brushed Nickel p.48 **HEDGEROW** Distressed Brass p.50 **KELLWYN** Brushed Nickel p.60 **KELLWYN** Matte Black p.63



KYLO LED Brushed Nickel p.27 **KYLO LED** Matte Black p.24 **LAVELLE** Matte Black p.52 **LEYDEN** Brushed Nickel p.56 **LEYDEN** Matte Black p.59




LOCKHART Matte Black p.44 **LOWERY** Textured Black p.14 **MARIPOSA** Antique Gold p.32 **MARIPOSA** Gilded Silver p.35 **MERRY** Brushed Nickel p.64




MERRY Matte Black p.66 **MILL BEAM** Brushed Nickel p.46 **PIVOT LED** Matte Black p.20 **PIVOT LED** Satin White p.21 **PLANCK LED** Brushed Nickel p.30



QUADRANT LED Matte Black p.28 **SPOKE LED** Brushed Nickel p.22 **SPOKE LED** Matte Black p.23 **STOCKBRACE** Matte Black p.38 **THORPE** Brushed Nickel p.37



THORPE Satin Brass p.36 **VININGS** Brushed Nickel p.54



Pendants

ATWELL Brushed Bronze p.70 **ATWELL** Brushed Nickel p.70 **ATWELL** Matte Black p.70 **BRIARWOOD** Galvanized p.41 **BRIARWOOD** Textured Black p.43



HEDGEROW Brushed Nickel p.49 **HEDGEROW** Distressed Brass p.51 **HINTON** Brushed Nickel p.68 **HINTON** Brushed Nickel p.68 **HINTON** Matte Black p.68



Pendants

| | | | | |
|---------------------------------------|---------------------------------------|---|--|--|
| HINTON Matte Black p.68 | HINTON Polished Nickel p.68 | HINTON Polished Nickel p.68 | HINTON Vintage Brass p.68 | HINTON Vintage Brass p.68 |
| KELLWYN Brushed Nickel p.61 | KELLWYN Matte Black p.63 | KYLO LED Brushed Nickel p.27 | KYLO LED Brushed Nickel p.27 | KYLO LED Matte Black p.25 |
| KYLO LED Matte Black p.25 | LAVELLE Matte Black p.53 | LEYDEN Brushed Nickel p.57 | LEYDEN Matte Black p.59 | MILL BEAM Brushed Nickel p.47 |
| RUSHTON Brushed Nickel p.69 | RUSHTON Graphite p.69 | SPOKE LED Brushed Nickel p.23 | SPOKE LED Matte Black p.23 | TERRAZZO Distressed Brass p.69 |
| TERRAZZO Graphite p.69 | TREMONT Matte Black p.119 | TREMONT Stainless Steel p.119 | | |

Indoor Ceiling Fans

| | | | | |
|---------------------------------------|---|--|--------------------------------------|---|
| ALLERON Flat Black p.82 | ALLERON Antique Nickel p.83 | BRADEN Brushed Nickel p.90 | BRADEN Matte Black p.90 | BRADEN Matte White p.90 |
| CLARET Brushed Nickel p.87 | CLARET Matte Black p.87 | CLARET Oil Rubbed Bronze p.86 | EDWIDGE Matte Black p.79 | EDWIDGE Matte White p.79 |
| EDWIDGE Painted Nickel p.78 | GLENFALLS Brushed Nickel p.85 | GLENFALLS Matte Black p.85 | GLENFALLS Matte White p.84 | KAYSVILLE Antique Nickel p.80 |
| KAYSVILLE Graphite p.81 | MIDVALE Blistered Iron p.89 | MIDVALE Galvanized Finish p.88 | MIDVALE Matte White p.89 | RYNE Koa Woodgrain p.75 |
| RYNE Matte Black p.74 | RYNE Matte White p.75 | VERNAL Koa Woodgrain p.72 | VERNAL Matte Black p.73 | VERNAL Painted Nickel p.73 |

Indoor Ceiling Fans

WILLACY
Matte Black p.77



WILLACY
Painted Nickel p.76



Outdoor Ceiling Fans

ALLERON
Flat Black p.82



ALLERON
Antique Nickel p.83



EDWIDGE
Matte Black p.79



EDWIDGE
Matte White p.79



EDWIDGE
Painted Nickel p.78



KAYSVILLE
Antique Nickel p.80



KAYSVILLE
Graphite p.81



MIDVALE
Blistered Iron p.89



MIDVALE
Galvanized Finish p.88



MIDVALE
Matte White p.89



RYNE
Koa Woodgrain p.75



RYNE
Matte Black p.74



RYNE
Matte White p.75



VERNAL
Koa Woodgrain p.72



VERNAL
Matte Black p.73



VERNAL
Painted Nickel p.73



WILLACY
Matte Black p.77



WILLACY
Painted Nickel p.76



Sconces/Wall Brackets

AIKEN
Brushed Nickel p.102



AIKEN
Vintage Brass p.103



ASHFORD
Brushed Nickel p.108



ASHFORD
Polished Chrome p.108



AXLE
Antique Bronze p.107



AXLE
Brushed Nickel p.107



CLARION
Brushed Nickel p.101



CLARION
Matte Black p.101



CLARION
Polished Chrome p.101



CLARION
Satin Brass p.101



CONWAY
Brushed Nickel p.104



CONWAY
Matte Black p.105



CURVED LED
Opal White p.92



LOWERY
Textured Black p.15



MERRY
Brushed Nickel p.109



MERRY
Matte Black p.109



MILL BEAM
Brushed Nickel p.100
























QUADRANT
Matte Black p.29




























STOCKBRACE
Matte Black p.39



Bath Collections

| | | | | |
|--|---|---|--|---|
| AIKEN Brushed Nickel p.102 | AIKEN Vintage Brass p.103 | ASHFORD Brushed Nickel p.108 | ASHFORD Polished Chrome p.108 | AXLE Antique Bronze p.107 |
|  |  |  |  |  |
| AXLE Brushed Nickel p.107 | CLARION Brushed Nickel p.101 | CLARION Matte Black p.101 | CLARION Polished Chrome p.101 | CLARION Satin Brass p.101 |
|  |  |  |  |  |
| CONWAY Brushed Nickel p.104 | CONWAY Matte Black p.105 | EVERLUME VANITY Brushed Nickel p.97 | EVERLUME VANITY Satin White p.97 | GRID LED Matte Black p.99 |
|  |  |  |  |  |
| GRID LED Silver Ridge p.99 | MERRY Brushed Nickel p.109 | MERRY Matte Black p.109 | MILL BEAM Brushed Nickel p.100 | PEARL LED Matte Black p.98 |
|  |  |  |  |  |
| PEARL LED Satin Brass p.98 | | | | |
|  | | | | |

Outdoor

| | | | | |
|---|---|---|---|---|
| BARLOWE Antique Bronze p.120 | BARLOWE Stainless Steel p.120 | CORD MOUNT ALUMINUM CYLINDERS Antique Bronze p.123 | CORD MOUNT ALUMINUM CYLINDERS Black p.123 | CORD MOUNT ALUMINUM CYLINDERS White p.123 |
|  |  |  |  |  |
| CORD MOUNT ALUMINUM CYLINDERS LED Antique Bronze p.123 | CORD MOUNT ALUMINUM CYLINDERS LED Black p.123 | EXTON Textured Black p.118 | GABLES Antique Bronze p.120 | MANTEO Cottage White p.113 |
|  |  |  |  |  |
| NAVARRE Matte Black p.111 | PAWLEY Galvanized Finish p.112 | PAWLEY Matte Black p.112 | PHOTOCELL ALUMINUM CYLINDERS LED Antique Bronze p.122 | PHOTOCELL ALUMINUM CYLINDERS LED Black p.122 |
|  |  |  |  |  |
| STATURE Oil Rubbed Bronze p.114 | STATURE Textured Black p.114 | TREMONT Matte Black p.119 | TREMONT Stainless Steel p.119 | UNION SQUARE Stainless Steel p.110 |
|  |  |  |  |  |
| WAKEFORD Antique Copper p.115 | WATCH HILL Textured Black p.117 | WILLIAMSTON Antique Bronze p.116 | WILLIAMSTON Antique Pewter p.116 | Z-2020 LED Satin White p.121 |
|  |  |  |  |  |

Outdoor

Z-2020 LED
Textured Black p.121



Z-2025 LED
Satin White p.121




Z-2025 LED
Textured Black p.121



LOWERY

The Lowery collection raises the bar on contemporary design to a new artistic ideal. Layered rectangular shields finished in textured black iron are interposed with distressed gold leaf panels against a black frame. Lowery casts a shimmering reflective light that highlights the beautiful contrast between light and dark while adding a touch of glamour.



P500330-031



P500331-031



P500330-031



P350203-031



P710100-031



P350203-031
shown as semi-flush

FINISH

● Textured Black - 031

PAIR WITH

Adagio
Orrizo
Rae

SEMI-FLUSH CONVERTIBLE

P350203-031 Textured Black
Hanging and ceiling mount
hardware included.
19" dia., 15-3/8" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Three medium base lamps,
each 60w max.

FIVE-LIGHT PENDANT

P500330-031 Textured Black
26" dia., 20" ht.
Overall ht. w/stem 86", wire 15'.
Five medium base lamps,
each 60w max.

SIX-LIGHT PENDANT

P500331-031 Textured Black
31-3/4" dia., 23-3/4" ht.
Overall ht. w/stem 90", wire 15'.
Six medium base lamp,
each 60w max.

ONE-LIGHT WALL SCONCE

P710100-031 Textured Black
5-3/8" W., 15-1/8" ht.
Extends 3-5/8". H/CTR 7-1/2".
One candelabra base lamp,
60w max.



ELEVATE

Achieve a sleek and modern look with the Elevate Collection. Etched white glass cylindrical shades are captured within an angular frame adding a clean panache to contemporary interiors.



P500305-031



P500305-015



P500305-109

COLLECTIONS

FINISHES

- Polished Chrome - 015
- Matte Black - 031
- Brushed Bronze - 109

PAIR WITH

Ratio
Mod

FOUR-LIGHT PENDANT

P500305-015 Polished Chrome

P500305-031 Matte Black

P500305-109 Brushed Bronze
20" dia., 30" ht.

Overall ht. w/stem 99", wire 15".
Four medium base lamps,
each 75w max.



 **PROGRESS**
LIGHTING™

ILLUMINATE THE MOMENTS

Whether you're looking for the latest and greatest trends or some tried-and-true pieces, you'll find the just-right lighting choices to illuminate the special moments in your life.

Pivot LED

FINISHES

- Satin White - 028
- Matte Black - 031


P400260-031-30

Pivot LED has a bold architectural form that captures the imagination with its possibilities for design. Angled arms rotate around a central axis and can be adjusted to complement a room's décor. Lustrous LED lightbars within the arms create a softly glowing ambient light. An integrated downlight shines from the bottom of the center column to illuminate tasks on the surface below.


Bold Architectural Form

Angled Arms

Downlight



P400260-028-30



P400260-031-30



Pivot LED

SIX-LIGHT LED CHANDELIER WITH DOWNLIGHT

P400260-028-30 Satin White

P400260-031-30 Matte Black

28-1/4" dia., 8-3/4" ht.

Overall ht. w/stem 62-1/2", wire 10'

23.4w integrated LED, 3000K,

90CRI, 1062 delivered lumens.

JAB

Spoke LED

FINISHES

- Brushed Nickel - 009
- Matte Black - 031


P400255-009-30

Modern minimalism meets the future of industrial style in the Spoke LED pendant collection. A slim disk of integrated LEDs casts an ethereal glow that creates a multi-directional wash of even light. Sleek rods anchor the luminous circles for a retro yet contemporary vibe that complements Modern spaces.

Sleek Rods

Modern Minimalist Style

Luminous Circles



P400255-009-30

FOUR-LIGHT LED CHANDELIER

P400255-009-30 Brushed Nickel

P400255-031-30 Matte Black

25-1/2" dia., 27-1/8" ht.

Overall ht. w/stem 57-1/2", wire 10'.

20w integrated LED, 3000K,

90CRI, 2096 delivered lumens.

JAB

LED PENDANT

P500318-009-30 Brushed Nickel

P500318-031-30 Matte Black


17-3/4" dia., 6-1/2" ht.

Overall ht. w/stem 122-3/8", wire 10'.

20w integrated LED, 3000K,

90CRI, 1762 delivered lumens.

JAB



P400255-031-30



P500318-031-30



P500318-009-30


Kylo LED

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

P400263-031-30

Sleek metal bars capped with solid tubes of seamless light provide a futuristic effect to Kylo LED chandeliers. Stainless steel cables attach the LED light bars to a central stem, creating an asymmetrical form that adds drama to a room's design. Kylo LED pendants are available as single or multi-light option, the LED light bars are suspended on sleek stainless steel cables that can be individually adjusted for a customized appearance to suit your personal taste.



Kylo LED

FOUR-LIGHT LED CHANDELIER

P400262-031-30 Matte Black
30" dia., 21-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
17w integrated LED, 3000K,
90CRI, 981 delivered lumens.

JAB

SIX-LIGHT LED CHANDELIER

P400263-031-30 Matte Black
40" dia., 22-3/4" ht.
Overall ht. w/stem 80", wire 10'.
23w integrated LED, 3000K,
90CRI, 1471 delivered lumens.

JAB

LED PENDANT

P500321-031-30 Matte Black
4-3/4" dia., 13" ht.
Overall ht. w/cord 132-5/8", wire 10'.
6.5w integrated LED, 3000K,
90CRI, 420 delivered lumens.

JAB

SIX-LIGHT LED PENDANT

P500322-031-30 Matte Black
11-3/4" dia., 13" ht.
Overall ht. w/cord 132-5/8", wire 10'.
23.2w integrated LED, 3000K,
90CRI, 1790 delivered lumens.

JAB



P500322-031-30

P500321-031-30



Featuring Kylo, Willacy and Clarion

A Focus on Form

Lighting takes center stage against a dark neutral backdrop in this modern space. The Willacy ceiling fan swirls ribbon-like blades around a gleaming center hub, making a striking focal point. Over the sofa, the Kylo LED multi-light pendant presents a contemporary splash of minimalist style as it cascades downwards in an arrangement of seamless light. Abstract wall art lends pops of blue and is flanked by a pair of clean-lined Clarion wall sconces on the feature wall. In the dining area, the Kylo chandelier adds drama with sleek metal bars capped with solid tubes of light that hang in a stunning asymmetrical form.

Kylo LED



P400263-009-30

FOUR-LIGHT LED CHANDELIER
P400262-009-30 Brushed Nickel
 30" dia., 21-1/4" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 17w integrated LED, 3000K,
 90CRI, 981 delivered lumens.



P400262-009-30

SIX-LIGHT LED CHANDELIER
P400263-009-30 Brushed Nickel
 40" dia., 22-3/4" ht.
 Overall ht. w/stem 80", wire 10'.
 23w integrated LED, 3000K,
 90CRI, 1471 delivered lumens.



P500321-009-30

LED PENDANT
P500321-009-30 Brushed Nickel
 4-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 6.5w integrated LED, 3000K,
 90CRI, 420 delivered lumens.



SIX-LIGHT LED PENDANT
P500322-009-30 Brushed Nickel
 11-3/4" dia., 13" ht.
 Overall ht. w/cord 132-5/8", wire 10'.
 23.2w integrated LED, 3000K,
 90CRI, 1790 delivered lumens.



P500322-009-30

Quadrant LED

FINISH
● Matte Black - 031



P400264-031-30

With its precise arrangement of light, Quadrant LED defines space with a minimalistic approach. Metal struts tipped with integrated LED lights are arranged in a modern geometric design, giving the layered frame an impression of substance while creating airy illumination in a space.

Modern Geometric Design

Airy Illumination

Layered Frame



P400264-031-30



P710103-031-30



P710103-031-30
shown ceiling mounted



P350209-031-30

Quadrant LED

FOUR-LIGHT FLUSH MOUNT
P350209-031-30 Matte Black
Ceiling or wall mount.
20" dia., 4" ht.
24w integrated LED, 3000K,
90CRI, 1261 delivered lumens.

JAB

SIX-LIGHT LED CHANDELIER
P400264-031-30 Matte Black
26-1/8" dia., 26-1/8" ht.
Overall ht. w/stem 71-1/16", wire 10'.
24w integrated LED, 3000K,
90CRI, 1346 delivered lumens.

JAB

TWO-LIGHT LED WALL SCONCE
P710103-031-30 Matte Black
Ceiling or wall mount. Can be
installed vertically or horizontally.
8" W., 24" ht.
Extends 3-5/16". H/CTR 12".
13w integrated LED, 3000K,
90CRI, 686 delivered lumens.

JAB ADA

Geodesic LED

Geodesic radiates a magical beauty from a uniform, continuous disc of light that glows through an airy structural frame. Diffused edge-lit LED dispenses even illumination through the open diamond-patterned frame while a simple cable suspension adds to the clean style. Geodesic takes contemporary spaces to a new level.

FINISH

● Matte Black - 031

LED PENDANT

P500319-031-30 Matte Black
17-7/8" dia., 9-1/4" ht.
Overall ht. w/cord 100-3/4", wire 8'.
28w integrated LED, 3000K,
90CRI, 2067 delivered lumens.

LED PENDANT

P500320-031-30 Matte Black
27-1/8" dia., 12-5/16" ht.
Overall ht. w/cord 103-3/4", wire 8'.
38w integrated LED, 3000K,
90CRI, 3373 delivered lumens.



P500320-031-30



P500319-031-30

All fixtures:

JAB

Planck LED

A trio of clean light bars suspended from a sleek single rod defines the Planck LED chandelier. Slices of light complement a room with modern style and provide a punch of illumination for both intimate and open spaces.

FINISH

● Brushed Nickel - 009

THREE-LIGHT LED CHANDELIER

P400257-009-30 Brushed Nickel
26-1/2" dia., 3-1/16" ht.
Overall ht. w/stem 60-3/8", wire 10'.
30w integrated LED, 3000K,
90CRI, 2245 delivered lumens.



P400257-009-30



Mariposa

P500416-168


FINISHES

- Antique Gold - 168
- Gilded Silver - 176

PAIR WITH

- Spicewood
- Gresham

Take a naturalistic approach to modern room design with Mariposa. Slender branches bloom outward from the central stem, bearing delicate leaves finished in bright and luxurious tones. Mariposa's organic feel is balanced by the minimalist lines of its multi-directional light arrangement, bringing a fresh touch to a range of settings seeking a global flair.



Mariposa

SEMI-FLUSH CONVERTIBLE

P350210-168 Antique Gold
Hanging and ceiling mount hardware included.
20" dia., 8-3/8" ht.
Overall ht. w/stem 33-1/2", wire 36".
Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500415-168 Antique Gold
28" dia., 20" ht.
Overall ht. w/stem 75", wire 15'.
Six candelabra base lamps, each 60w max.

EIGHT-LIGHT PENDANT

P500416-168 Antique Gold
36" dia., 25" ht.
Overall ht. w/stem 77-1/2", wire 15'.
Eight candelabra base lamps, each 60w max.



Antique Gold finish detail



Featuring Mariposa and Clarion

Naturally Inspired Design

Take a naturalistic approach to modern room design with organic décor. Soothing blue-sky walls and a clean white color palette create a calming backdrop that is punctuated by the stunning Mariposa chandelier. Mariposa's organic feel is balanced by the minimalist lines of its multi-directional light arrangement, making a striking focal point. The clear glass shades of the Clarion pendants offer a simple form and functionality that complements the serene setting.

Mariposa



P500416-176

SEMI-FLUSH CONVERTIBLE
P350210-176 Gilded Silver
 Hanging and ceiling mount hardware included.
 20" dia., 8-3/8" ht.
 Overall ht. w/stem 33-1/2", wire 36".
 Five candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT
P500415-176 Gilded Silver
 28" dia., 20" ht.
 Overall ht. w/stem 75", wire 15'.
 Six candelabra base lamps, each 60w max.

EIGHT-LIGHT PENDANT
P500416-176 Gilded Silver
 36" dia., 25" ht.
 Overall ht. w/stem 77-1/2", wire 15'.
 Eight candelabra base lamps, each 60w max.



Gilded Silver finish detail



P500415-176



P350210-176
 shown as semi-flush

Thorpe

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012

PAIR WITH

- Atwell
- Clarion

P400270-012

A softer, playful ambiance is brought to mid-century design with Thorpe, whose starburst form is reinvented by a rustic twist on the space-age style. Angular lines make a clean and striking silhouette. The Brushed Nickel finish features a faux Barnwood finish while the Satin Brass finish is complimented by a faux Hickory wood finish.



Thorpe

FIVE-LIGHT CHANDELIER

P400270-009 Brushed Nickel
P400270-012 Satin Brass
 27-5/8" dia., 23-7/8" ht.
 Overall ht. w/stem 80-1/2", wire 15'.
 Five medium base lamps,
 each 60w max.

Stockbrace

FINISH
● Matte Black - 031

PAIR WITH
Briarwood
Lockhart

P400243-031

Inspired by traditional post-and-beam construction, Stockbrace presents a structured sense of visual transparency with its minimalist design. A metal frame features strut-like arms descending to a loop that supports clear glass shades. Clean lines, an open design and architectural details make Stockbrace a perfect complement to casual, modern and rustic interiors.

Minimalist Design

Architectural Details

Clean Glass Shades



P400243-031

Stockbrace

THREE-LIGHT FLUSH MOUNT
P350181-031 Matte Black
12-1/2" dia., 10" ht.
Three medium base lamp,
each 60w max.

THREE-LIGHT CHANDELIER
P400235-031 Matte Black
16" dia., 18" ht.
Overall ht. w/stem 84", wire 15'.
Three medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400243-031 Matte Black
24" dia., 22-1/2" ht.
Overall ht. w/stem 88-1/2", wire 15'.
Five medium base lamps,
each 60w max.

WALL BRACKET
P710097-031 Matte Black
4-3/4" W., 13-1/2" ht.
Extends 5-1/2". H/CTR 9-1/2".
One medium base lamp, 60w max.



P400235-031



P710097-031



P350181-031

Briarwood

FINISHES

- Textured Black - 031
- Galvanized - 141

PAIR WITH

- Durrell
- Hemsworth

P400048-141

*Vintage Farmhouse
Detailing*

The Briarwood Collection brings vintage farmhouse detailing into the present day with a classic cross-brace pattern highlighting an airy, open-frame design. Hand-painted faux wood accentuates Briarwood's simple geometric form. The Textured Black finish is paired with a faux Cerused Black Oak while the Galvanized finish features a Bleached Oak. Briarwood adds the perfect touch of country character to Farmhouse and Rustic interiors.

Geometric Form



Cross-brace Pattern



P400048-141

Briarwood

ONE-LIGHT FLUSH MOUNT

P350022-141 Galvanized
9-1/2" sq., 7-5/8" ht.
One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT

P350039-141 Galvanized
12" sq., 6" ht.
Two medium base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER

P400048-141 Galvanized
38" L., 10" W., 9" ht.
Overall ht. w/stem 54", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500041-141 Galvanized
10" sq., 9" ht.
Overall ht. w/stem 54", wire 10'.
One medium base lamp, 100w max.



P500041-141



P350039-141



P350022-141



Featuring Briarwood

Classic, Cozy and Refined

A classic white color palette is grounded by warm touches of wood and black, bringing in a softer, earthy edge. The Briarwood linear chandelier has a classic cross-brace pattern highlighting an airy, open-frame design accentuated with faux-painted wood, adding a refined touch of country character.

Briarwood



P400048-031

ONE-LIGHT FLUSH MOUNT
P350022-031 Textured Black
 9-1/2" sq., 7-5/8" ht.
 One medium base lamp, 60w max.

TWO-LIGHT FLUSH MOUNT
P350039-031 Textured Black
 12" sq., 6" ht.
 Two medium base lamps, each 60w max.

FIVE-LIGHT LINEAR CHANDELIER
P400048-031 Textured Black
 38" L., 10" W., 9" ht.
 Overall ht. w/stem 54", wire 15'.
 Five medium base lamps, each 100w max.

MINI-PENDANT
P500041-031 Textured Black
 10" sq., 9" ht.
 Overall ht. w/stem 54", wire 10'.
 One medium base lamp, 100w max.



P500041-031



P350039-031



P350022-031

Lockhart

P500279-031

FINISH

● Matte Black - 031

PAIR WITH

Hemsworth
Rushton

Bold in scale with an industrial vibe, Lockhart mixes a central band, finished in a hand-painted Aged Oak faux wood with curved metal arms, enclosing a candle cluster that casts a soft, warm illumination. Its open form fills a room with substance without weight, a look that is ideal in homes seeking an update to popular trends.



Lockhart

P500279-031



FOUR-LIGHT PENDANT
P500278-031 Matte Black
19-3/4" dia., 20-5/8" ht.
Overall ht. w/chain 96", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT PENDANT
P500279-031 Matte Black
25-1/2" dia., 26-7/8" ht.
Overall ht. w/chain 102", wire 15'.
Five candelabra base lamps,
each 60w max.

P500278-031



Mill Beam

FINISH


● Brushed Nickel - 009

PAIR WITH

Hemsworth
Bonn

The beautiful contrasts of gleaming and rustic finishes are epitomized in Mill Beam, a linear form in a painted Gray Concrete faux finish that gives an unexpected artisanal edginess. Its slab silhouette showcases an industrial-inspired design and creates a perfect base for recessed sockets that allow decorative bulbs to take center stage in casting an eye-catching glow.

P400269-009



P710099-009

Mill Beam

SIX-LIGHT LINEAR CHANDELIER

P400269-009 Brushed Nickel
48" L., 2-3/8" W., 2-3/4" ht.
Overall ht. w/stem 54", wire 10'.
Six medium base lamps,
each 60w max.

TWO-LIGHT CONVERTIBLE MINI-PENDANT

P500328-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
2-3/8" sq., 10-1/2" ht.
Overall ht. w/stem 54", wire 10'.
Two medium base lamps,
each 60w max.

WALL BRACKET

P710099-009 Brushed Nickel
Install facing up or down.
4-3/4" W., 7-1/8" ht.
Extends 4-3/8". H/CTR 3-5/8".
One medium base lamp, 60w max.

Hedgerow

FINISHES

- Brushed Nickel - 009
- Distressed Brass - 175

PAIR WITH


- Terrazzo
- Rushton

P400253-009

Hedgerow has a softly textured, artistic faux wood finish frame that elevates the look from a typical Farmhouse fixture to one of urban sophistication. The Brushed Nickel finish features a hand-painted faux Gray Washed Oak frame while the Distressed Brass finish has a faux Aged Oak frame. Hedgerow showcases a classic windowpane design to complement the traditional form and offers an overall lighter look and feel.

*Elevated
Farmhouse Style*

*Artistic Faux
Wood*



Windowpane Design



P400254-009


Hedgerow

ONE-LIGHT FLUSH MOUNT
P350197-009 Brushed Nickel
 10-3/8" sq., 8" ht.
 One medium base lamp, 60w max.

FOUR-LIGHT CHANDELIER
P400253-009 Brushed Nickel
 21-3/8" sq., 12-7/8" ht.
 Overall ht. w/stem 101-1/2", wire 15'.
 Four candelabra base lamps,
 each 60w max.

FIVE-LIGHT LINEAR CHANDELIER
P400254-009 Brushed Nickel
 40" L., 11-3/8" W., 11" ht.
 Overall ht. w/stem 100-1/2", wire 15'.
 Five candelabra base lamps,
 each 60w max.

MINI-PENDANT
P500317-009 Brushed Nickel
 10-3/8" sq., 19-3/8" ht.
 Overall ht. w/stem 94-1/2", wire 10'.
 One medium base lamp, 60w max.



P400253-009



P500317-009



P350197-009

P400253-175



Distressed Brass

Artistic Form



Softly Textured

P400254-173



Hedgerow

ONE-LIGHT FLUSH MOUNT
P350197-175 Distressed Brass
10-3/8" sq., 8" ht.
One medium base lamp, 60w max.

FOUR-LIGHT CHANDELIER
P400253-175 Distressed Brass
21-3/8" sq., 12-7/8" ht.
Overall ht. w/stem 101-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

FIVE-LIGHT LINEAR CHANDELIER
P400254-175 Distressed Brass
40" L., 11-3/8" W., 11" ht.
Overall ht. w/stem 100-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

MINI-PENDANT
P500317-175 Distressed Brass
10-3/8" sq., 19-3/8" ht.
Overall ht. w/stem 94-1/2", wire 10'.
One medium base lamp, 60w max.

P400253-173



P500317-173



P350197-173



Lavelle

FINISH
● Matte Black - 031

PAIR WITH
Kempsey
Caisson

Artistry and texture combine in the Lavelle pendant collection for the ultimate in global design. A softly curved, black frame complements the airy open weave of the earthy, mocha colored rattan shade. Lavelle is the perfect accent for a carefree, relaxed lifestyle that embraces the natural world.

Softly Curved Frame

Rattan Shade

Global Design

P500308-031



P500308-031

Lavelle

SEMI-FLUSH CONVERTIBLE

P350183-031 Matte Black
Hanging and ceiling mount hardware included.
15-5/8" dia., 14-3/8" ht.
Overall ht. w/chain 72", wire 10'.
Three medium base lamps, each 60w max.

MINI-PENDANT

P500307-031 Matte Black
8" dia., 12-5/8" ht.
Overall ht. w/chain 72", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT PENDANT

P500308-031 Matte Black
20-1/2" dia., 13-3/8" ht.
Overall ht. w/chain 72", wire 15'.
Four medium base lamps, each 60w max.



P350183-031



P350183-031
shown as semi-flush



P500307-031

Vinings

FINISH
● Brushed Nickel - 009

PAIR WITH
Austelle
Winslett

P400267-009

Add a touch of casual charm with Vinings, whose graceful scrolling form creates a peaceful harmony between old and new. Vining's chic frame is ornamented with hand-painted Gray Washed Oak faux wood finish beads for a sweet play on comfortable elegance that elevates Farmhouse décor to new levels

Graceful Scrolling Form

Casual Charm

Natural Wood Finish Beads



P400267-009

Vinings

THREE-LIGHT SEMI-FLUSH
P350211-009 Brushed Nickel
14" dia., 9-3/4" ht.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER
P400267-009 Brushed Nickel
22" dia., 21-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER
P500296-009 Brushed Nickel
15-3/4" dia., 19-1/2" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Three candelabra base lamps,
each 60w max.



P500296-009



P350211-009

Leyden

FINISHES


- Brushed Nickel - 009
- Matte Black - 031

PAIR WITH

- Winslett
- Hemsworth

P400202-031

The Leyden Collection complements Farmhouse-inspired interiors with its casual style and subtle hints of industrial-inspired design. Gentle curves soften the classic appearance of Leyden's clean lines, providing a simple, graceful look and offering plenty of light from its open design.



Leyden

FIVE-LIGHT CHANDELIER

P400202-009 Brushed Nickel
22-3/8" dia., 20" ht.
Overall ht. w/chain 95", wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400228-009 Brushed Nickel
28" dia., 27" ht.
Overall ht. w/chain 102", wire 15'.
Nine candelabra base lamps,
each 60w max.

FOUR-LIGHT FOYER

P500302-009 Brushed Nickel
15" dia., 23" ht.
Overall ht. w/chain 98", wire 15'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT FOYER

P500303-009 Brushed Nickel
18" dia., 33" ht.
Overall ht. w/chain 108", wire 15'.
Eight candelabra base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500316-009 Brushed Nickel
13" dia., 13" ht.
Overall ht. w/chain 88", wire 10'.
One medium base lamp, 60w max.





Featuring Leyden

An Elegant Take on Farmhouse Style

Elevate Farmhouse style with subtle hints of industrial design. A classic wooden table is surrounded by eclectic seating that has accents of metal and curving lines. The Leyden chandelier complements this look with gentle curves that soften its traditional form, providing an elegant, graceful look and offering plenty of light from its open design.

Leyden



P400228-031



P500303-031



P400202-031



P500302-031



P500316-031

- FIVE-LIGHT CHANDELIER**
P400202-031 Matte Black
 22-3/8" dia., 20" ht.
 Overall ht. w/chain 95", wire 15'.
 Five candelabra base lamps,
 each 60w max.
- NINE-LIGHT CHANDELIER**
P400228-031 Matte Black
 28" dia., 27" ht.
 Overall ht. w/chain 102", wire 15'.
 Nine candelabra base lamps,
 each 60w max.
- FOUR-LIGHT FOYER**
P500302-031 Matte Black
 15" dia., 23" ht.
 Overall ht. w/chain 98", wire 15'.
 Four candelabra base lamps,
 each 60w max.
- EIGHT-LIGHT FOYER**
P500303-031 Matte Black
 18" dia., 33" ht.
 Overall ht. w/chain 108", wire 15'.
 Eight candelabra base lamps,
 each 60w max.
- ONE-LIGHT PENDANT**
P500316-031 Matte Black
 13" dia., 13" ht.
 Overall ht. w/chain 88", wire 10'.
 One medium base lamp, 60w max.

Kellwyn

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

PAIR WITH

- Riley
- Replay

P400251-009

Balancing the best of modern and traditional, the Kellwyn Collection has a classic frame interpreted in a slender form. Kellwyn can add a clean finish to a New Traditional space or act as a relaxing counterpoint to a Modern interior. Clear glass shades complement the sleek design while adding a touch of luxury.

Slender Form

Clear Glass Shades

Classic Frame



P400250-009
shown as semi-flush

Kellwyn

THREE-LIGHT CONVERTIBLE CHANDELIER

P400250-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 12-5/8" ht.
Overall ht. w/chain 74-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400251-009 Brushed Nickel
23" dia., 24-3/8" ht.
Overall ht. w/chain 75-1/2", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400252-009 Brushed Nickel
28" dia., 34-1/4" ht.
Overall ht. w/chain 109-1/2", wire 15'.
Nine candelabra base lamps, each 60w max.

MINI-PENDANT

P500314-009 Brushed Nickel
5" dia., 8-7/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT FOYER

P500315-009 Brushed Nickel
18" dia., 31-3/4" ht.
Overall ht. w/chain 106-1/2", wire 15'.
Four candelabra base lamps, each 60w max.



Featuring Kellwyn and Stature

A Perfect Blend of New and Old

Balance the best of modern and traditional with a crisp white color scheme and elegant furnishings with simple lines. Place a minimalist chandelier like Kellwyn, whose classic frame is re-interpreted in a slender form over the dining table. The Stature wall lantern adds a bold touch with clear glass doors accented by an unexpected detail of cross-hatched brass accents that provides signature style.

Kellwyn



P400252-031



P500315-031

THREE-LIGHT CONVERTIBLE CHANDELIER

P400250-031 Matte Black
Hanging and ceiling mount hardware included.
16" dia., 12-5/8" ht.
Overall ht. w/chain 74-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400251-031 Matte Black
23" dia., 24-3/8" ht.
Overall ht. w/chain 75-1/2", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400252-031 Matte Black
28" dia., 34-1/4" ht.
Overall ht. w/chain 109-1/2", wire 15'.
Nine candelabra base lamps, each 60w max.

MINI-PENDANT

P500314-031 Matte Black
5" dia., 8-7/8" ht.
Overall ht. w/stem 74-1/2", wire 10'.
One medium base lamp, 60w max.

FOUR-LIGHT FOYER

P500315-031 Matte Black
18" dia., 31-3/4" ht.
Overall ht. w/chain 106-1/2", wire 15'.
Four candelabra base lamps, each 60w max.



P400251-031



P400250-031



P500314-031



P400250-031
shown as semi-flush

Merry

P400276-009

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

Bath

PAIR WITH

Tobin

The Merry Collection brings a joyful aura to any room, with its modern vibe and clean-lined tubular frame accentuated with etched glass shades. Its generous scale and contemporary design make Merry ideal for today's open-concept Modern and Transitional spaces.

Modern Vibe

Etched Glass

Tubular Frame



P400276-009

Merry

THREE-LIGHT CHANDELIER

P400274-009 Brushed Nickel
18" dia., 16-3/8" ht.
Overall ht. w/chain 67-1/2", wire 10'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400275-009 Brushed Nickel
22-1/8" dia., 14-3/4" ht.
Overall ht. w/chain 66", wire 10'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400276-009 Brushed Nickel
28" dia., 24" ht.
Overall ht. w/chain 75", wire 10'.
Nine medium base lamps,
each 100w max.

ONE-LIGHT FOYER

P500333-009 Brushed Nickel
15" dia., 23" ht.
Overall ht. w/chain 74", wire 10'.
One medium base lamp, 100w max.



P400275-009



P500333-009



P400274-009

P400276-031



Matte Black Finish

Contemporary Design

Clean-lined Frame

P400276-031



P400275-031



P400274-031



P500333-031



Merry

THREE-LIGHT CHANDELIER

P400274-031 Matte Black
18" dia., 16-3/8" ht.
Overall ht. w/chain 67-1/2", wire 10'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400275-031 Matte Black
22-1/8" dia., 14-3/4" ht.
Overall ht. w/chain 66", wire 10'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400276-031 Matte Black
28" dia., 24" ht.
Overall ht. w/chain 75", wire 10'.
Nine medium base lamps,
each 100w max.

ONE-LIGHT FOYER

P500333-031 Matte Black
15" dia., 23" ht.
Overall ht. w/chain 74", wire 10'.
One medium base lamp, 100w max.

Hinton

Simplicity defined is the hallmark of the Hinton Collection. Hinton's metal fittings offer an industrial demeanor, complemented by a clear seeded glass shade or opaque metal shade that provides effective task lighting wherever focused illumination is called upon.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Polished Nickel - 104
- Vintage Brass - 163

PAIR WITH

Winslett
Saluda

ALSO IN

Close-To-Ceiling
Sconces
See www.progresslighting.com for more details.

PENDANT WITH GLASS SHADE

P500324-009 Brushed Nickel
P500324-031 Matte Black
P500324-104 Polished Nickel
P500324-163 Vintage Brass
12" dia., 12-1/2" ht.
Overall ht. w/stem 78-1/2", wire 10'.
One medium base lamp, 100w max.

PENDANT WITH METAL SHADE

P500325-009 Brushed Nickel
P500325-031 Matte Black
P500325-104 Polished Nickel
P500325-163 Vintage Brass
12-1/4" dia., 12-1/2" ht.
Overall ht. w/stem 78-1/2", wire 10'.
One medium base lamp, 100w max.



Terrazzo

Terrazzo features a polished, Gray or Sandstone concrete composite shade, flecked with warm earthy hues offering a sophisticated contrast to its natural interior and clean metal stem suspension. The Terrazzo pendant expresses an artistic sensibility that is ideal for eclectic settings.

FINISHES

- Graphite - 143
- Distressed Brass - 175

PAIR WITH

Hedgerow
Bonn

ONE-LIGHT PENDANT

P500313-143 Graphite
P500313-175 Distressed Brass
10" dia., 9-3/8" ht.
Overall ht. w/stem 66-1/2", wire 10'.
One medium base lamp, 75w max.



Rushton

The Rushton collection features exposed bulbs that glow elegantly from within clear glass. Mechanical-inspired fittings complete the industrial theme to make a bold statement in your home.

FINISHES

- Brushed Nickel - 009
- Graphite - 143

PAIR WITH

Hemsworth
Lockhart

TWO-LIGHT FLUSH MOUNT

P350205-009 Brushed Nickel
P350205-143 Graphite
12" dia., 6-7/8" ht.
Two medium base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500329-009 Brushed Nickel
P500329-143 Graphite
8-1/2" dia., 16-7/8" ht.
Overall ht. w/stem 82-1/2", wire 10'.
One medium base lamp, 100w max.

Atwell

Extraordinary on the first impression, but always at peace with whatever setting it calls home, Atwell blends crisp architectural detailing with circular glass for statement-making lighting design. A clear globe adds a soft contrast to the clean metal cap creating a remarkable and enduring design.

FINISHES

- Brushed Nickel - 009
- Matte Black - 031
- Brushed Bronze - 109

ALSO IN

Pendants
See www.progresslighting.com for more details.

MINI-PENDANT


P500309-009 Brushed Nickel
P500309-031 Matte Black
P500309-109 Brushed Bronze
 8" dia., 8-1/2" ht.
 Overall ht. w/stem 128-1/2", wire 10'.
 One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500310-009 Brushed Nickel
P500310-031 Matte Black
P500310-109 Brushed Bronze
 10" dia., 10-1/2" ht.
 Overall ht. w/cord 130-1/2", wire 10'.
 One medium base lamp, 60w max.

ONE-LIGHT PENDANT

P500311-009 Brushed Nickel
P500311-031 Matte Black
P500311-109 Brushed Bronze
 11-7/8" dia., 12-3/4" ht.
 Overall ht. w/cord 132-1/2", wire 10'.
 One medium base lamp, 60w max.



Accessories

Stem Kits

Contains (2) 6" and (1) 12" stem.

- P8602-31M** Matte Black
- P8602-163** Vintage Brass
- P8602-168** Antique Bronze
- P8602-175** Distressed Brass
- P8602-176** Gilded Silver

9-Gauge Square Chain

- 4' feet of 9 gauge, square profile chain for Jeffrey Alan Marks Point Dume™ Collection fixtures. Permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight - 50 lbs.

- P8755-09** Brushed Nickel
- P8755-30** Gloss White
- P8755-81** Antique Nickel
- P8755-134** Silver Ridge
- P8755-141** Galvanized
- P8755-160** Aged Brass
- P8755-161** Distressed Brass

9-Gauge Chain

- 4' feet of 9 gauge chain permits installation of large chain-hung fixtures on high ceilings.
- Maximum fixture weight - 50 lbs.

- P8758-31M** Matte Black
- P8758-175** Distressed Brass

Vernal

P250059-179-30
shown with Koa Woodgrain blades

FINISHES

- Matte Black - 031
- Painted Nickel - 152
- Koa Woodgrain - 179

Vernal refreshes a room's decor with elegant curves and an expansive 60-inch, five-blade span for the ultimate in design-savvy comfort. Vernal includes Wi-Fi smart control: once installed, Vernal can be controlled by a voice assistant, tablet or smart phone. Finished in Koa Woodgrain, Matte Black or Painted Nickel, Vernal is designed to complement New Traditional and Transitional interiors.

Integrated Smart Control

Elegant Curves

Dimmable LED Light

Vernal

P250059-031-30 Matte Black




Matte Black

P250059-152-30 Painted Nickel



Painted Nickel

P250059-179-30 Koa Woodgrain



Koa Woodgrain



P250059-031-30
shown with Matte Black blades



P250059-152-30
shown with Painted Nickel blades



P250059-179-30
shown with Koa Woodgrain blades
with Architectural Bronze accents

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 6,810 cubic feet per minute |
| Electricity Use | 34 watts (excludes lights) |
| DOE Weighted CFM/W | 242 CFM/W |

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Wi-Fi enabled
- Remote control with batteries is included

SIZE

60" dia., 14-1/4" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1600 lumens, dimmable.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Ryne

P250060-031-30
shown with Matte Black blades



Aerodynamic Design

Modern Appeal

Dimmable LED Light

FINISHES

- Matte White - 028
- Matte Black - 031
- Koa Woodgrain - 179

The 52-inch Ryne fan is modern in appeal, with beautifully flowing blades that join in the middle to create a minimalistic housing. Ryne is smart control adaptable with the P2673 Wi-Fi Module: once installed, Ryne can be controlled by a voice assistant, tablet or smart phone. Ryne's aerodynamic design and Koa Woodgrain, Matte White or Matte Black finish perfectly suits New Traditional and Transitional interiors.

Ryne

P250060-028-30 Matte White



P250060-031-30 Matte Black



P250060-179-30 Koa Woodgrain



P250060-028-30
shown with Matte White blades



P250060-031-30
shown with Matte Black blades



P250060-179-30
shown with Koa Woodgrain blades
with Architectural Bronze accents



P2673-01

DC FAN WI-FI MODULE P2673-01

Add the Wi-Fi module to your Ryne ceiling fan for control at your fingertips. You can easily control your fan with a hand-held remote; or a smart phone, tablet, voice assistant (Amazon Alexa and Google Home) via the Smart By Bond app.

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 5,802 cubic feet per minute |
| Electricity Use | 33 watts (excludes lights) |
| DOE Weighted CFM/W | 204 CFM/W |



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included
- Add a P2673-01 Wi-Fi module to convert to a smart fan

SIZE

52" dia., 13-1/2" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1600 lumens, dimmable.



Willacy

P250063-152
shown with Painted Nickel blades

FINISHES


- Matte Black - 031
- Painted Nickel - 152

Willacy is striking in design, inspired by flowing ribbons that swirl around a gleaming center hub to create a gentle breeze. Willacy includes Wi-Fi smart control: once installed, the fan can be controlled by a voice assistant, tablet or smart phone. Willacy features all weather hand finished ABS blades making it ideal for indoor or outdoor use.

Striking Design

Ribbon-Like Blades

For Indoor & Outdoor Use



P250063-031
shown with Matte Black blades



P250063-152
shown with Painted Nickel blades

Willacy

P250063-031 Matte Black



Matte Black

P250063-152 Painted Nickel



Painted Nickel

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 4,544 cubic feet per minute |
| Electricity Use | 14 watts (excludes lights) |
| DOE Weighted CFM/W | 318 CFM/W |

FEATURES

- Limited Lifetime Warranty
- DC Motor
- ABS blades
- Wi-Fi enabled
- Remote control with batteries is included

SIZE

48" dia., 14-1/2" ht.
12" lead wires.



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

Edwidge

FINISHES

- Matte White - 028
- Matte Black - 031
- Painted Nickel - 152

P250062-152-30
shown with Painted Nickel blades

Edwidge cleverly houses the motor within the trio of fan blades providing a sleek, modern look. All-weather ABS fan blades and a non-metallic housing and canopy offer rust-proof, contemporary style to indoor and covered outdoor settings.

Modern Design

For Indoor & Outdoor Use

Dimmable LED Light

Edwidge

P250062-028-30 Matte White



P250062-031-30 Matte Black



P250062-152-30 Painted Nickel



P250062-028-30
shown with Matte White blades



P250062-031-30
shown with Matte Black blades



P250062-152-30
shown with Painted Nickel blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 5,874 cubic feet per minute |
| Electricity Use | 20 watts (excludes lights) |
| DOE Weighted CFM/W | 328 CFM/W |



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- Opal shatterproof shade
- Remote control with batteries is included

SIZE

52" dia., 13-9/16" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 lumens, dimmable.



Kaysville

P250003-081-30
shown with Chestnut blades

FINISHES

- Antique Nickel - 081
- Graphite - 143

Beautiful long bent blades appear to be held only by a simple metal band in Kaysville, offering a modern industrial style. Kaysville pairs the beauty of the blades with a strong, all-weather ABS material to prevent warping.



Modern Style

Simple Metal Band

Dimmable LED Light

Kaysville

P250003-081-30 Antique Nickel



Chestnut

P250003-143-30 Graphite



Gray Weathered Wood



P250003-081-30
shown with Chestnut blades



P250003-143-30
shown with Gray Weathered Wood blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 9,650 cubic feet per minute |
| Electricity Use | 31 watts (excludes lights) |
| DOE Weighted CFM/W | 361 CFM/W |



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White Opal glass shade
- Remote control with batteries is included

SIZE

56" dia., 17-1/4" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2100 lumens, dimmable.



Alleron

P250009-182-30
shown with Antique Black blades

FINISHES

- Antique Nickel - 081
- Flat Black - 182

Reminiscent of aviation days gone by, Alleron takes its styling cues from a set of airplane propeller blades. The hand-finished ABS blades paired with a sleek metal ceiling canopy and light kit add a modern industrial flair to indoor and covered outdoor settings.



Modern Industrial Flair

Propeller Inspired Blades

Dimmable LED Light

Alleron

P250009-081-30 Antique Nickel

 Gray Weathered Wood

P250009-182-30 Flat Black

 Antique Black



P250009-081-30
shown with Gray Weathered Wood blades



P250009-182-30
shown with Antique Black blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 7,801 cubic feet per minute |
| Electricity Use | 20 watts (excludes lights) |
| DOE Weighted CFM/W | 423 CFM/W |



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC Motor
- ABS blades
- White opal glass shade
- Remote control with batteries is included

SIZE

56" dia., 16" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2100 lumens, dimmable.



Glenfalls

P250021-028-30
shown with Matte White blades and Black Chrome accents

FINISHES

- Brushed Nickel - 009
- Matte White- 028
- Matte Black - 031

Glenfalls highlights its beautiful simulated wood fan blades with bright metallic accents on the blade arms and tips to create a timeless yet modern design. Glenfalls is ideal for cooling large living areas in sophisticated style.



Timeless Design

Metallic Accents

Dimmable LED Light



P250021-009-30
shown with Chestnut blades
and Brushed Nickel accents



P250021-028-30
shown with Matte White blades
and Black Chrome accents



P250021-031-30
shown with Matte Black blades
and Brushed Nickel accents

Glenfalls

P250021-009-30 Brushed Nickel



Chestnut

P250021-028-30 Matte White



Matte White

P250021-031-30 Matte Black



Matte Black

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 6,393 cubic feet per minute |
| Electricity Use | 85 watts (excludes lights) |
| DOE Weighted CFM/W | 84 CFM/W |

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-031 Wifi Remote

SIZE

56" dia., 14-7/8" ht.
80" lead wires.

LAMP

24w LED Module, 3000K,
90 CRI, 2100 lumens, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light



Claret

P250007-108-30
shown with Antique Wood blades

FINISHES


- Brushed Nickel - 009
- Matte Black - 031
- Oil Rubbed Bronze - 108

Claret gracefully blends old and new with an eye-catching fluted motor housing paired with long blade arms. With its unique take on a classic design, Claret will make a statement in a variety of interiors.




Claret


P250007-009-30 Brushed Nickel



P250007-031-30 Matte Black



P250007-108-30 Oil Rubbed Bronze



P250007-009-30
shown with Matte Black blades



P250007-031-30
shown with Distressed Ebony blades



P250007-108-30
shown with Chestnut blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 5,553 cubic feet per minute |
| Electricity Use | 61 watts (excludes lights) |
| DOE Weighted CFM/W | 106 CFM/W |

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-031 Wifi Remote

SIZE

54" dia., 15-1/8" ht.
80" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 lumens, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light



Midvale

FINISHES

- Matte White- 028
- Blistered Iron - 171
- Galvanized - 141

P250011-141-WB
shown with Galvanized Finish blades

Midvale offers a nostalgic appeal, with vintage-style LED bulbs inside a clear seeded glass shade, a rustic cage frame, and a banded metal ceiling canopy to complete the charming look.



Vintage Style

Nostalgic Appeal

Clear Seeded Glass



P250011-028-WB
shown with Matte White blades



P250011-141-WB
shown with Galvanized Finish blades



P250011-171-WB
shown with Blistered iron blades

Midvale

P250011-028-WB Matte White



P250011-141-WB Galvanized Finish



P250011-171-WB Blistered Iron



ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 7,627 cubic feet per minute |
| Electricity Use | 84 watts (excludes lights) |
| DOE Weighted CFM/W | 98 CFM/W |

FEATURES

- Limited Lifetime Warranty
- Dual Mount (flat or sloped ceiling-20°)
- AC Motor
- ABS blades
- Clear seeded glass shade
- Remote control with batteries is included
- Remote control may be replaced with the P2667-31 Wifi Remote

SIZE

56" dia., 20-3/8" ht.
80" lead wires.

LAMP

Two LED medium base vintage lamps, 2700K, 80 CRI, 7w max each, included, dimmable.



Remote Control Included
Three-speed fan operation
Full-range dimming for light





44" Braden

The Braden 44 inch, three-blade, hugger-style ceiling fan features clean lines and a classic, sleek design that is ideal for Modern and Contemporary interiors. With its simple and elegant look and Brushed Nickel, Matte Black or Matte White finish, Braden complements most décor schemes.



FINISHES

- Brushed Nickel - 009
- Matte White - 028
- Matte Black - 031



P250058-009-30 Brushed Nickel

-  American Walnut
-  Silver

P250058-028-30 Matte White

-  Natural Cherry
-  White

P250058-031-30 Matte Black

-  Distressed Ebony
-  Matte Black



P250058-009-30
shown with American Walnut blades



P250058-028-30
shown with Natural Cherry blades



P250058-031-30
shown with Distressed Ebony blades

ENERGY INFORMATION AT HIGH SPEED

| | |
|---------------------------|-----------------------------|
| Airflow | 3,212 cubic feet per minute |
| Electricity Use | 45 watts (excludes lights) |
| DOE Weighted CFM/W | 78 CFM/W |



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light

FEATURES

- Limited lifetime warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- Frosted shatterproof shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2667-31 Wi-Fi remote control

SIZE

44" dia., 9-7/8" ht.
12" lead wires.

LAMP

18w LED Module, 3000K,
90 CRI, 1400 lumens, dimmable.



Featuring Braden and Clarion

Sweet Dreaming

Muted colors and a light, airy feeling offer a dreamy look to this bedroom. The Braden hugger fan lends a contemporary touch while keeping the room comfortable and welcoming. A feature wall of lightly distressed wood paneling is accented by a pair of Clarion wall sconces, whose clear glass shade and clean styling embrace minimalist modernity and functional task lighting.

Curve LED

Curve LED is simply designed with an arching acrylic shade accented by two finials that add visual interest. Curve LED brings a touch of contemporary style to interior spaces.

LED WALL SCONCE

P710102-060-30 Opal White
Includes Architectural Bronze, Brushed Nickel and Matte Black finials.
8" dia., 8" ht.
Extends 3-5/8", H/CTR 4".
10w Integrated LED, 3000K, 90 CRI, 744 delivered lumens.



P710102-060-30
shown with Matte Black finials

Perimeter

Inspired by geometric simplicity, Perimeter has a rectangular frame composed of clean, straight lines. Perimeter has a fashion-forward appeal that works across a variety of room styles.

TWO-LIGHT FLUSH MOUNT

P350200-009 Brushed Nickel
P350200-012 Satin Brass
P350200-031 Matte Black
12" sq., 4-1/2" ht.
Two medium base lamps,
each 60w max.



P350200-009



P350200-012



P350200-031



P350198-009



P350199-009



P350198-031



P350199-031



P350198-104



P350199-104



P350198-163



P350199-163
Shown tilted

Hinton

Simplicity defined is the hallmark of the Hinton Collection. Hinton's stylized metal fittings offer an industrial demeanor, complemented by a choice of clear seeded glass shade or opaque metal shade that provides effective task lighting wherever focused illumination is called upon.

ALSO IN

Pendants
Sconces
See www.progresslighting.com for more details.

SEMI-FLUSH WITH GLASS SHADE

P350198-009 Brushed Nickel
P350198-031 Matte Black
P350198-104 Polished Nickel
P350198-163 Vintage Brass
8" dia., 10" ht.
One medium base lamp, 60w max.

SEMI-FLUSH WITH METAL SHADE

P350199-009 Brushed Nickel
P350199-031 Matte Black
P350199-104 Polished Nickel
P350199-163 Vintage Brass
8-1/4" dia., 10" ht.
One medium base lamp, 60w max.

Medal

The Medal flush mount takes a cue from classic warehouse work lights with an open metal cage to create authentic industrial appeal. Knurled detailing on lamp holders adds visual interest to the automotive inspired styling.

TWO-LIGHT FLUSH MOUNT

P350195-143 Graphite

P350195-164 Coastal Blue w/ Brushed Nickel Accents

14-1/2" dia., 7-7/8" ht.
Two medium base lamps, each 60w max.



P350195-143



P350195-164

Gulliver


Circular bands create an open design for the Gulliver flush mount ceiling light. Gulliver features an embossed wood-grain texture with a hand-painted faux finish effect that complements Farmhouse and Coastal home decor.

TWO-LIGHT FLUSH MOUNT

P350169-141 Galvanized Finish

P350169-143 Graphite

14-3/8" dia., 6-1/2" ht.
Two medium base lamps, each 60w max.



P350169-141



P350169-143



Everlume™ Linear Panel LED

The Everlume™ Linear Panel LED is a modern take on a classic rectangular wrap frame. Its clean low-profile design has a frosted polycarbonate diffuser lit by LEDs along the perimeter of the fixture. Light is diffused through a light guide, providing even illumination without dark spots, shadow or glare. Hardware and fasteners are not visible after installation, providing a clean appearance. The fixture can be mounted to off-centered junction boxes making aligning multiple fixtures on center easy. This product is a great addition to laundry rooms, kitchens, walk in closets, garages and basements.

24" LED LINEAR PANEL
P810032-028-30 Satin White
 23-3/4" L., 11-15/16" W., 1-1/4" ht.
 21w integrated LED, 3000K, 90CRI, 1587 lumens.

48" LED LINEAR PANEL
P810033-028-30 Satin White
 47-3/4" L., 11-15/16" W., 1-1/4" ht.
 43w integrated LED, 3000K, 90CRI, 3181 lumens.



P810032-028-30



P810033-028-30

- LED FEATURES**
- Flicker-free dimming with many Triac and ELV dimmers.
 - 120v input voltage.
 - 50,000 hour life.



All fixtures:



P300304-009-CS



P300304-028-CS



P300305-009-CS



P300305-028-CS



P300306-009-CS



P300306-028-CS

Shown wall mounted



3000K
Soft White



4000K
Cool White

Everlume™ Vanity LED

The Everlume™ Vanity LED has a clean rectangular frame and a frosted polycarbonate diffuser lit by LEDs along the perimeter of the fixture. Light is diffused through a light guide, providing even illumination without dark spots, shadows or glare. Two color temperatures can be selected, soft white or cool white. This versatile fixture can be wall or ceiling mounted in a variety of residential and commercial settings.

FINISHES

- Brushed Nickel - 009
- Satin White - 028

16" LINEAR BATH
P300304-009-CS Brushed Nickel
P300304-028-CS Satin White
 16" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 17w Integrated LED, 3000K, 4000K, 90 CRI, 1386 delivered lumens.

24" LINEAR BATH
P300305-009-CS Brushed Nickel
P300305-028-CS Satin White
 24" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 26w Integrated LED, 3000K, 4000K, 90 CRI, 2182 delivered lumens.

32" LINEAR BATH
P300306-009-CS Brushed Nickel
P300306-028-CS Satin White
 32" W., 5" ht.
 Extends 1-3/8", H/CTR 2-1/2".
 32w Integrated LED, 3000K, 4000K, 90 CRI, 2808 delivered lumens.

- LED FEATURES**
- Damp location listed.
 - Flicker-free dimming with many Triac and ELV dimmers.
 - 120v input voltage.
 - 50,000 hour life.



All fixtures can be installed horizontally or vertically.

All fixtures:



Pearl LED


FINISHES

- Satin Brass - 012
- Matte Black - 031

P300311-012-30

Pearl LED combines elements of simple geometry, adding together circles and rectangles to equal an elegant streamlined design. Light is multiplied from a reflective polished chrome backplate, giving extra dimension and dazzle.

Geometric Form



Streamlined Design

Polished Chrome Backplate

TWO-LIGHT LED BATH

P300311-012-30 Satin Brass
P300311-031-30 Matte Black
 12" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/4".
 13w integrated LED, 3000K,
 90CRI, 812 delivered lumens.



P300312-012-30




P300311-012-30

THREE-LIGHT LED BATH

P300312-012-30 Satin Brass
P300312-031-30 Matte Black
 18" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/2".
 19.5w integrated LED, 3000K,
 90CRI, 1292 delivered lumens.



P300313-012-30



P300311-031-30

FOUR-LIGHT LED BATH

P300313-012-30 Satin Brass
P300313-031-30 Matte Black
 23-7/8" L., 5" ht.
 Extends 5-1/2". H/CTR 2-1/2".
 24w integrated LED, 3000K,
 90CRI, 1692 delivered lumens.



P300312-031-30



P300313-031-30

All fixtures can be installed horizontally or vertically.

All fixtures:



Grid LED

FINISHES

- Matte Black - 031
- Silver Ridge - 134

P300331-031-30

Grid LED pairs sleek geometric frame with a linear acrylic, etched linen shade to provide a dramatic look and soft illumination.

Geometric Frame



Etched Linen Shade

Dramatic Look



P300333-031-30



P300331-031-30

14" LINEAR LED BATH

P300331-031-30 Matte Black
P300331-134-30 Silver Ridge
 14" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 14w integrated LED, 3000K,
 90CRI, 569 delivered lumens.



P300332-031-30



P300331-134-30

22" LINEAR LED BATH

P300332-031-30 Matte Black
P300332-134-30 Silver Ridge
 22" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 22w integrated LED, 3000K,
 90CRI, 1033 delivered lumens.



P300332-134-30



P300333-134-30

30" LINEAR LED BATH

P300333-031-30 Matte Black
P300333-134-30 Silver Ridge
 30" W., 4-3/4" ht.
 Extends 3-1/8". H/CTR 2-3/8".
 32w integrated LED, 3000K,
 90CRI, 1639 delivered lumens.

All fixtures can be installed horizontally or vertically.

All fixtures:




Mill Beam

FINISHES

- Brushed Nickel - 009

P300319-009

The beautiful contrasts of gleaming and rustic finishes are epitomized in Mill Beam, a linear form in a painted concrete finish that gives an unexpected artisanal edginess. Its slab frame creates a perfect base for recessed sockets that allow decorative bulbs to take center stage in casting an eye-catching glow.




THREE-LIGHT BATH

P300319-009 Brushed Nickel
24" W., 4-3/4" ht.
Extends 4-1/2". H/CTR 2-3/8".
Three medium base lamps,
each 60w max.

WALL BRACKET

P710099-009 Brushed Nickel
4-3/4" W., 7-1/8" ht.
Extends 4-3/8". H/CTR 3-5/8".
One medium base lamp, 60w max.

*Fixture can be installed
horizontally or vertically.*



P300319-009



P710099-009



P710099-009
shown facing up



P300319-009
shown vertical

Clarion

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Satin Brass - 012
- Matte Black - 031

P300300-031

Clarion embraces a minimalist simplicity of style. A clear, tubular glass shade is secured by a sleek cylindrical base for a precision look that is ideal for modern settings.



P300300-009



P300300-012



P300300-015



P300300-031



P300299-009



P300299-012



P300299-015



P300299-031

ONE-LIGHT BATH

P300299-009 Brushed Nickel
P300299-012 Satin Brass
P300299-015 Polished Chrome
P300299-031 Matte Black
5" W., 12-5/8" ht.
Extends 4-1/4". H/CTR 2-1/2".
One medium base lamp, 60w max.

TWO-LIGHT BATH

P300300-009 Brushed Nickel
P300300-012 Satin Brass
P300300-015 Polished Chrome
P300300-031 Matte Black
20-3/8" W., 5" ht.
Extends 4". H/CTR 2-1/2".
Two medium base lamps,
each 60w max.

*P300300 can be installed
horizontally or vertically.*

Aiken

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163

P300322-009

Delightful details pair with clear glass creating the charm of the Aiken Collection. Vintage-style caps top globes reminiscent of an apothecary bottle that has been repurposed for a new life as a light fixture.

*Delightful
Details*



*Vintage-Style
Caps*

Clear Glass Shades

ONE-LIGHT BATH

P300320-009 Brushed Nickel
4-1/2" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
One medium base lamp, 60w max.



P300320-009

TWO-LIGHT BATH

P300321-009 Brushed Nickel
14-5/8" W., 9" ht.
Extends 7". H/CTR 4-1/4".
Two medium base lamps, each 60w max.



P300323-009

THREE-LIGHT BATH

P300322-009 Brushed Nickel
23-3/8" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
Three medium base lamps, each 60w max.



P300321-009



P300322-009

FOUR-LIGHT BATH

P300323-009 Brushed Nickel
32-1/4" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
Four medium base lamps, each 60w max.

All fixtures mount up or down.

Aiken

ONE-LIGHT BATH

P300320-163 Vintage Brass
4-1/2" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
One medium base lamp, 60w max.



P300321-163



P300320-163

TWO-LIGHT BATH

P300321-163 Vintage Brass
14-5/8" W., 9" ht.
Extends 7". H/CTR 4-1/4".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH

P300322-163 Vintage Brass
23-3/8" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
Three medium base lamps, each 60w max.



P300322-163

FOUR-LIGHT BATH

P300323-163 Vintage Brass
32-1/4" W., 9-7/8" ht.
Extends 7". H/CTR 4-1/4".
Four medium base lamps, each 60w max.

All fixtures mount up or down.



P300323-163

Conway

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

P300296-009

Conway creates a relaxing haven with styling that gives a nod to seaside charm. A bell-shaped frame has a nautical air that pairs seeded glass with a hand painted wood-style accent.

Seaside Charm

Faux Wood Accents



Seeded Glass Shades

ONE-LIGHT BATH

P300295-009 Brushed Nickel
6" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
One medium base lamp,
60w max.



P300295-009

TWO-LIGHT BATH

P300296-009 Brushed Nickel
15" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Two medium base lamps,
each 60w max.



P300296-009

THREE-LIGHT BATH

P300297-009 Brushed Nickel
24" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Three medium base lamps,
each 60w max.



P300297-009

FOUR-LIGHT BATH

P300298-009 Brushed Nickel
33" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Four medium base lamps,
each 60w max.



P300298-009

Conway

ONE-LIGHT BATH

P300295-031 Matte Black
6" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
One medium base lamp,
60w max.



P300295-031

TWO-LIGHT BATH

P300296-031 Matte Black
15" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Two medium base lamps,
each 60w max.



P300296-031

THREE-LIGHT BATH

P300297-031 Matte Black
24" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Three medium base lamps,
each 60w max.



P300297-031

FOUR-LIGHT BATH

P300298-031 Matte Black
33" W., 8-1/4" ht.
Extends 7". H/CTR 3-3/4".
Four medium base lamps,
each 60w max.



P300298-031



Retro, Yet Modern Vibes

Mix old and new for a charming effect in the bath. Pair a rustic wooden vanity with chic gold finishes and a contemporary vessel sink to balance interesting texture with sleek styling. The Axle vanity light completes the look with retro details like vintage-style gooseneck arms and gleaming decorative sockets holding clear glass globes that add a modern edge to the design.

Axle

Axle mixes old and new to charming effect. Industrial elements are seen in the working gooseneck arm that provides tilt adjustment for vintage style sockets. Axle provides the perfect platform to showcase bulbs that stray from the ordinary for a truly distinctive splash of style.

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300189-009 Brushed Nickel
P300189-020 Antique Bronze
 6-1/8" W., 6-3/4" ht.
 Extends 6". H/CTR 3-3/4".
 One medium base lamp,
 60w max.

TWO-LIGHT BATH

P300190-009 Brushed Nickel
P300190-020 Antique Bronze
 16" W., 6-3/4" ht.
 Extends 6". H/CTR 3-3/4".
 Two medium base lamps,
 each 60w max.

THREE-LIGHT BATH

P300191-009 Brushed Nickel
P300191-020 Antique Bronze
 24" W., 6-3/4" ht.
 Extends 6". H/CTR 3-3/4".
 Three medium base lamps,
 each 60w max.

All fixtures mount up or down.



P300189-009



P300190-009



P300191-009



P300189-020



P300190-020



P300191-020

Ashford

Ashford provides nostalgic charm with crisp details like knurled sockets and vintage-style opal glass shades. This handsome pairing combined with a classic metallic finish is a skillful blending of old and new.

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300314-009 Brushed Nickel

P300314-015 Polished Chrome

5-3/8" W., 10" ht.

Extends 8". H/CTR 5".

One medium base lamp, 100w max.

TWO-LIGHT BATH

P300315-009 Brushed Nickel

P300315-015 Polished Chrome

14-1/2" W., 10" ht.

Extends 8". H/CTR 5".

Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P300316-009 Brushed Nickel

P300316-015 Polished Chrome

24" W., 10" ht.

Extends 8". H/CTR 5".

Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P300317-009 Brushed Nickel

P300317-015 Polished Chrome

33-1/2" W., 10" ht.

Extends 8". H/CTR 5".

Four medium base lamps, each 100w max.

All fixtures mount up or down.



P300314-009



P300317-009



P300316-009



P300315-009



P300314-015



P300317-015



P300316-015



P300315-015



P300327-009



P300330-009



P300328-009



P300329-009



P300330-031



P300327-031



P300329-031



P300328-031

Merry

The Merry Collection brings a joyful aura to any room, with its modern vibe and clean-lined tubular frame accentuated with etched glass shades.

FINISH

- Brushed Nickel - 009
- Matte Black - 031

ONE-LIGHT BATH

P300327-009 Brushed Nickel

P300327-031 Matte Black

4-3/8" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 4-7/8".

One medium base lamp, 100w max.

TWO-LIGHT BATH

P300328-009 Brushed Nickel

P300328-031 Matte Black

12" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 4-7/8".

Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P300329-009 Brushed Nickel

P300329-031 Matte Black

24" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 4-7/8".

Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P300330-009 Brushed Nickel

P300330-031 Matte Black

30" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 4-7/8".

Four medium base lamps, each 100w max.

All fixtures mount up or down.

UNION SQUARE

Gas lanterns of yesteryear inspire the charming design of Union Square. Mechanical details of exaggerated knobs and a handle at the top provides character and visual appeal.



P540046-135

FINISH

● Stainless Steel - 135

POST LANTERN

P540046-135 Stainless Steel
7" L., 9-3/4" W., 26" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

Navarre

FINISH

● Matte Black - 031

P550089-031

The Navarre pendant defines indoor-outdoor gathering spaces with statement-making style. Several rectangular cubes nest within each other, forming a breezy contemporary angular silhouette. Shimmering seeded glass panels cast a pleasing glow that is punctuated by its dramatic Matte Black frame. Navarre will shine as the focal point of covered outdoor dining and entertaining areas. Listed for damp location installation.

*Dramatic
Frame*



Seeded Glass

Statement-making Style

ONE-LIGHT OUTDOOR PENDANT

P550089-031 Matte Black
10" SQ., 28-5/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
60w max.




Pawley

FINISHES

- Matte Black - 031
- Galvanized-141

Pawley has an airy basketweave design offering an organic global feel and coastal warmth. The synthetic rattan frame has a graceful, lattice-like design and a lovely, hand-applied finish that gives charm and depth. The frame's woven structure comfortably diffuses the glow from the etched glass shade at its center. Pawley's natural aesthetic is ideal for indoor-outdoor entertaining in Coastal, Rustic and Transitional settings. Listed for damp location installation.



Synthetic Rattan

Woven Structure

Etched Glass Shade

ONE-LIGHT OUTDOOR PENDANT
P550083-031 Matte Black
P550083-141 Galvanized
 12" dia., 16" ht.
 Overall ht. w/stem 82", wire 10'.
 One medium base lamp,
 100w max.



Manteo

FINISH

- Cottage White - 151

P550084-151

Manteo features a dense woven design that infuses outdoor spaces with a rugged style. Its double-shade design filters warm, subtle light downwards to add a glowing ambiance to covered outdoor patios, porches, and dining areas. Constructed of natural-looking synthetic rattan, Manteo adds a unique, warm touch to Coastal and Transitional settings. Listed for damp location installation.



Synthetic Rattan

Rugged Style

Glowing Ambiance

ONE-LIGHT OUTDOOR PENDANT
P550084-151 Cottage White
 12" dia., 16-5/8" ht.
 Overall ht. w/stem 82-1/2", wire 10'.
 One medium base lamp,
 100w max.



Stature

FINISHES

- Textured Black - 031
- Oil Rubbed Bronze - 108

P560268-108



Hinged Door

Elevate your home's curb appeal with Stature, where a traditional, gaslight look is modernized with clean lines and minimal detailing. Clear glass doors allow for bright illumination and feature a recessed hinged door that adds to the lantern's sleek style and ease of maintenance. Brass-toned accents with crosshatch pattern offer signature historical detailing.

Gaslight Look

Brass-toned Accents



P560267-031



P560267-108



P560268-031



P560268-108



P560269-031



P560269-108

SMALL WALL LANTERN

P560267-031 Textured Black
P560267-108 Oil Rubbed Bronze
 6" W., 11-1/2" ht.
 Extends 5-3/8". H/CTR 5-3/4".
 One candelabra base lamp,
 60w max.

MEDIUM WALL LANTERN

P560268-031 Textured Black
P560268-108 Oil Rubbed Bronze
 8" W., 16" ht.
 Extends 5-7/8". H/CTR 8".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560269-031 Textured Black
P560269-108 Oil Rubbed Bronze
 9" W., 21" ht.
 Extends 5-7/8". H/CTR 10-1/2".
 Two candelabra base lamps,
 each 60w max.

Wakeford

FINISH

- Antique Copper - 169

P560262-169

Modern Sophistication



Water Glass

Cross Brace Design

Elements of painted Antique Copper, water glass and crown molding trim give Wakeford a nostalgic look with modern sophistication. A cross brace design contrasts against the textured glass panes to offer a vintage look that fits well with both rustic and traditional exteriors.



P560261-169



P560262-169

SMALL WALL LANTERN

P560261-169 Antique Copper
 8" W., 17-7/8" ht.
 Extends 5-3/4". H/CTR 9-1/4".
 One medium base lamp,
 60w max.

MEDIUM WALL LANTERN

P560262-169 Antique Copper
 10" W., 21-1/2" ht.
 Extends 6-3/4". H/CTR 11-1/4".
 One medium base lamp,
 60w max.

Williamston

FINISHES

- Antique Bronze - 020
- Antique Pewter - 103

P560265-103



Curved Handle

Classic Appeal

Williamston brings the timeless details expected from an outdoor lantern into a fresh silhouette. The lantern's frame features a two-over-two grille design reminiscent of a traditional casement window frame. A curved handle accentuates the tiers of the fixture's square top for classic appeal.

Timeless Details



P560264-020



P560264-103



P560265-020



P560265-103



P560266-020



P560266-103



P540095-020



P540095-103

POST LANTERN

P540095-020 Antique Bronze
P540095-103 Antique Pewter
 7" sq., 20-1/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P560264-020 Antique Bronze
P560264-103 Antique Pewter
 5" W., 12" ht.
 Extends 6". H/CTR 2-3/4".
 One medium base lamp,
 60w max.

MEDIUM WAL LANTERN

P560265-020 Antique Bronze
P560265-103 Antique Pewter
 6" W., 14-1/4" ht.
 Extends 7". H/CTR 3-1/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P560266-020 Antique Bronze
P560266-103 Antique Pewter
 7" W., 18" ht.
 Extends 8-1/8". H/CTR 4-1/8".
 One medium base lamp,
 100w max.

Watch Hill

FINISH

- Textured Black - 031

P550292-031



Timeless Style

Elongated Design

Seeded Glass

Watch Hill features an elongated design, highlighted by slender arms curving gracefully around a seeded glass shade. With design elements inspired by Victorian-era gaslight fittings, Watch Hill has a timeless style that complements a variety of home styles.



P560255-031



P550292-031



P560256-031



P560257-031



P540292-031

SMALL WALL LANTERN

P560255-031 Textured Black
 6-1/8" W., 12-3/4" ht.
 Extends 7-3/8". H/CTR 4-1/2".
 One medium base lamp,
 60w max.

MEDIUM WALL LANTERN

P560256-031 Textured Black
 7-1/2" W., 17" ht.
 Extends 8-3/4". H/CTR 4-1/4".
 One medium base lamp,
 60w max.

LARGE WALL LANTERN

P560257-031 Textured Black
 8-1/2" W., 19-3/8" ht.
 Extends 10-1/4". H/CTR 4-1/4".
 One medium base lamp,
 60w max.

POST LANTERN

P540292-031 Textured Black
 8-1/8" dia., 18-1/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp,
 60w max.

HANGING LANTERN

P550292-031 Textured Black
 7-1/2" dia., 15-3/8" ht.
 Overall ht. w/stem 80-1/2",
 wire 10'.
 One medium base lamp,
 60w max.

Exton

FINISH

- Textured Black - 031

P550097-031

Peaked Roof



Geometric Forms

Architectural influences blend harmoniously in Exton, resulting in a modern design that works in both urban and suburban landscapes. Clean lines and geometric forms interact in its textured black frame, culminating in an iconic peaked roof. Exton brings bold design and visual unity to contemporary elevations.



P550097-031

P560273-031

Architectural Influences

POST LANTERN

P540097-031 Textured Black
11-1/8" dia., 17-1/8" ht.
Fits 3" post (sold separately).
One medium base lamp,
100w max.

MED WALL LANTERN

P560273-031 Textured Black
9-1/8" W., 12" ht.
Extends 9-3/8". H/CTR 9".
One medium base lamp,
100w max.

HANGING LANTERN

P550097-031 Textured Black
11-1/8" dia., 16" ht.
Overall ht. w/stem 91",
wire 10'.
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560274-031 Textured Black
11-1/8" W., 15-1/2" ht.
Extends 11-1/4". H/CTR 12-1/2".
One medium base lamp,
100w max.



P560274-031

P540097-031

Tremont

FINISHES

- Matte Black - 031
- Stainless Steel - 135

P550093-031

Industrial Detail



Mechanical Fittings

The cool factor reigns with the Tremont collection of outdoor lighting. Mechanical stainless-steel fittings offer industrial detail to the design. A seeded glass shade gives a rustic look that's tailor-made for modern home exteriors.



P550094-031

P550094-135

Seeded Glass Shade

OUTDOOR MINI-PENDANT

P550093-031 Matte Black
P550093-135 Stainless Steel
9" dia., 8" ht.
Overall ht. w/chain 77", wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT SEMI-FLUSH

P550094-031 Matte Black
P550094-135 Stainless Steel
9" dia., 10" ht.
One medium base lamp,
60w max.

WALL LANTERN

P560263-031 Matte Black
P560263-135 Stainless Steel
9" W., 11" ht.
Extends 10". H/CTR 4-1/2".
One medium base lamp,
60w max.



P550093-031

P550093-135

P560263-031

P560263-135

Barlowe

Transform your home into a warm and cozy dream with the friendly farmhouse-style of this small wall lantern. A rustic cross brace design decorates the charming lantern silhouette. Clear seeded glass panes add an extra pop of rustic personality.

FINISHES

- Antique Bronze - 020
- Stainless Steel - 135

FLUSH MOUNT

P550069-020 Antique Bronze
P550069-135 Stainless Steel
 11" L, 11-1/2" W., 5-1/2" ht.
 Two medium base lamps, each 60w max.



P550069-020



P550069-135

Gables

The Gables features arch detailing around a clear glass shade and encloses a single light source. Gables is constructed from DURASHIELD, an engineered polymer developed to withstand a broad range of environmental conditions.

FINISH

- Antique Bronze - 020

POST LANTERN

P540033-020 Antique Bronze
 7-1/2" dia., 16-3/4" ht.
 Fits 3" post (sold separately).
 One medium base lamp, 75w max.

HANGING LANTERN

P550050-020 Antique Bronze
 7-1/2" dia., 14-1/8" ht.
 Overall ht. w/chain 89", wire 10'.
 One medium base lamp, 75w max.



P550050-020



P540033-020



P560260-028-30



P560260-031-30



P560260-031-30
shown lit



P560259-028-30



P560259-031-30



P560259-031-30
shown lit

Z-2020 LED

Function follows form in Z-2020. Unlit, it functions as a sleek piece of wall art; turn it on, and its LED light presents an otherworldly glow that is strikingly reminiscent of a total eclipse. Light is cast around the edges of the form, creating a dramatic dark center.

FINISHES

- Satin White - 028
- Textured Black - 031

OUTDOOR WALL SCONCE

P560260-028-30 Satin White
P560260-031-30 Textured Black
 6-1/4" dia., 2-1/4" ht.
 One 9w LED module, 3000K, 90CRI, 623 source lumens.



Z-2025 LED

Function follows form in Z-2025. Unlit, it functions as a sleek piece of wall art; turn it on, and its LED light presents an otherworldly glow that is strikingly reminiscent of a total eclipse. Light is cast around the edges of the form, creating a dramatic dark center.

FINISHES

- Satin White - 028
- Textured Black - 031

OUTDOOR WALL SCONCE

P560259-028-30 Satin White
P560259-031-30 Textured Black
 6-1/4" sq., 2-1/4" ht.
 One 9w LED module, 3000K, 90CRI, 623 source lumens.



Photocell Aluminum Cylinders LED

Add security, energy efficiency and style to exteriors with this sleek cylinder. Its contemporary design offers a modern accent. Energy efficiency from the integrated LEDs is enhanced by the integrated photocell, which automatically turns the fixture on at dusk and off at dawn – no programming required.

5" Aluminum Cylinders LED

| PRODUCT NO. | FINISH | DESCRIPTION | SIZE | LAMP(S) |
|--|-------------------------|---|-------------------|--|
| P550101-020-30 P550101-031-30 | Antique Bronze Black | Down cylinder with photocell. | 5" W., 7-1/4" ht. | 1 18.6w integrated LED, 3000K, 90CRI, 511 delivered lumens |
| P550102-020-30 P550102-031-30 | Antique Bronze Black | Up/down cylinder with photocell. Lens cover included. | 5" W., 14" ht. | 1 36.9w integrated LED, 3000K, 90CRI, 819 delivered lumens |

All fixtures:



6" Aluminum Cylinders LED

| PRODUCT NO. | FINISH | DESCRIPTION | SIZE | LAMP(S) |
|--|-------------------------|---|----------------|---|
| P550103-020-30 P550103-031-30 | Antique Bronze Black | Down cylinder with photocell. | 6" W., 12" ht. | 1 32.5w integrated LED, 3000K, 90CRI, 953 delivered lumens |
| P550104-020-30 P550104-031-30 | Antique Bronze Black | Up/down cylinder with photocell. Lens cover included. | 6" W., 18" ht. | 1 65.2w integrated LED, 3000K, 90CRI, 1582 delivered lumens |

All fixtures:



Cord Mount Aluminum Cylinders

A clean and modern design allow this sleek cord hung pendant cylinder to compliment a variety of areas and settings. A field cuttable cord provides flexibility in application, making it suitable for a large range of ceiling heights.

Aluminum Cylinders

| PRODUCT NO. | FINISH | DESCRIPTION | SIZE | LAMP(S) |
|--|----------------------------------|-------------------------|---|-----------------------------|
| P500355-020 P500355-030 P500355-031 | Antique Bronze White Black | 5" cord mount cylinder. | 5" dia., 9-13/16" ht. Overall ht. w/ cord 130-9/16"; wire 10' | 1 75w PAR-30 or 75w BR-30 |
| P500356-020 P500356-030 P500356-031 | Antique Bronze White Black | 6" cord mount cylinder. | 6" dia., 12" ht. Overall ht. w/ cord 132-13/16"; wire 10' | 1 250w PAR-38 or 150w BR-40 |

All fixtures:



Aluminum Cylinders LED

| PRODUCT NO. | FINISH | DESCRIPTION | SIZE | LAMP(S) |
|--|-------------------------|-----------------------------|---|--|
| P550099-020-30 P550099-031-30 | Antique Bronze Black | 5" LED cord mount cylinder. | 5" dia., 9-13/16" ht. Overall ht. w/ cord 130-9/16"; wire 10' | 1 18.6w integrated LED, 3000K, 90CRI, 468 delivered lumens |
| P550100-020-30 P550100-031-30 | Antique Bronze Black | 6" LED cord mount cylinder. | 6" dia., 12" ht. Overall ht. w/ cord 132-13/16"; wire 10' | 1 32.4w integrated LED, 3000K, 90CRI, 930 delivered lumens |

All fixtures:



Aluminum Cylinder Accessories

| PRODUCT NO. | FINISH | DESCRIPTION |
|--------------------|--------|---------------------------------------|
| P860058-030 | White | 150" cord replacement kit for P50355, |
| P860058-031 | Black | P500356, P550099 and P550100. |



P860058-031



P860058-030

6" Recessed LED

LED Shallow Housings

For complete fixture, order housing with trim.



New Construction Air-Tight IC & Non-IC with LED Quick Connect



Remodel Air-Tight IC & Non-IC with LED Quick Connect

P871-LED-001
Ceiling opening: 6-3/8" dia.
Plaster frame: 6-5/8" x 9-3/8"
Recessed depth: 5-1/2"
Pryouts: 1/2"

P1871-LED-001
Ceiling opening: 6-3/4" dia.
Recessed depth: 5-5/8"
Pryouts: 1/2"



LED Quick Connector

IC & Non-IC Trims

P800002-028-30 Satin White
7-3/8" dia., 2-3/16" ht.
8w integrated LED,
3000K, 90CRI, 759 lumens.



P800002-028-30

P800019-028-CS Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



P800019-028-CS

P800018-028-CS Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



P800018-028-CS



P800018-028-CS
shown adjusted



Intrinsic Recessed LED

Elevate any room's design with the Intrinsic Recessed LED collection, offered in smooth or baffle trim design options. The simple, classic design and adjustable mounting options of these light fixtures provide easy installation in a variety of 5-inch and 6-inch recessed housings. The trims are preset to work with 6-inch recessed housings out of the box and are provided with an E26 medium base socket adaptor

Smooth

A smooth polycarbonate trim ring houses an integrated LED light ready to emit general ambient lighting. The non-metallic construction is a dead front design that will not corrode. Torsion spring mounting provides easy installation into most 5-inch and 6-inch recessed housings.

P800002-028-30 Satin White
7-3/8" dia., 2-3/16" ht.
8w integrated LED,
3000K, 90CRI, 759 lumens.



P800002-028-30



COMPATIBLE RECESSED HOUSINGS
P851-ICAT P871-LED-001
P1851-ICAT P1871-LED-001
P1841-ICAT

Eyeball

The smooth metal trim provides an elevated look. The adjustable light source can be aimed allowing the trim to be used as a standard downlight, accent light, wall wash or sloped ceiling light. This unique design allows the adjustable light source to remain hidden within the trim, allowing for the cleanest appearance. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy. The 5-CCT selectable LED light engine offers flexibility in application, allowing for the choice of 5 different color temperatures: warm, soft, bright, cool or daylight.

P800018-028-CS Satin White
7-3/4" dia., 3-15/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 750 lumens (at 3000K).



P800018-028-CS



COMPATIBLE RECESSED HOUSINGS
P851-ICAT P87-AT P86-TG, P821-FBFC
P1851-ICAT P87-ATQC P186-TG P871-LED-001
P1841-ICAT P187-TG P821-FB P1871-LED-001




P800019-028-CS Satin White
7-3/8" dia., 3-7/16" ht.
8w integrated LED,
2700K, 3000K, 3500K, 4000K, 5000K,
90CRI, 771 lumens (at 3000K).



P800019-028-CS



COMPATIBLE RECESSED HOUSINGS
P851-ICAT P87-AT P86-TG, P1871-LED-001
P1851-ICAT P87-ATQC P186-TG
P1841-ICAT P187-TG P871-LED-001



6" Eyeball Trim

For insulated or non-insulated ceilings. 7-3/4" outside diameter, except where indicated.

P800020-028 Satin White
Rotates 358, tilts 30 max.
IC & Non-IC:
75w PAR30, 65w BR30



P800020-028

**COMPATIBLE
RECESSED HOUSINGS**
P87-AT
P87-ATQC
P187-TG
P821-FBFC
P821-FB

Intrinsic Surface Mount Eyeball LED

The Intrinsic Surface Mount Eyeball LED represents the ultimate in design flexibility and ease of installation. Installation to a standard height junction box is made easy with the intuitive snap spring design. Suitable for residential and commercial needs, its clean profile elegantly accents the ceiling while the light can be adjusted to offer standard downlight, accent light, wall washer or sloped ceiling light. An integrated ceiling pitch indicator makes adjusting the light to match the ceiling pitch easy.

P810029-020-030 Antique Bronze
P810029-028-030 Satin White
7-1/4" dia., 1-1/2" ht.
15.8w integrated LED, 3000K,
90CRI, 1000 lumens.



P810029-020-030



P810029-028-030

All fixtures:



P810029-020-30
shown adjusted

LED FEATURES

- Damp location listed.
- 120v input voltage.
- 60 Lumens per watt.
- Flicker-free dimming with many Triac and ELV dimmers.
- 50,000 hour life.

Linear Undercabinet LED

The Hide-a-Lite Linear Undercabinet LED has an elegant design combined with energy efficient LED light, providing the ideal solution for residential and light commercial applications. The clean design of its aluminum housing features a lens that optimizes light distribution, ensuring for proper illumination of the workspace below. The 5-CCT selectable LED light engine offers flexibility in application, allowing the choice of 5 different color temperatures: Warm, Soft, Bright, Cool, Daylight, allowing for the best lighting color to fulfill the design intent of the space. An access plate and quick connect wire connectors make installation easy. Fixture is direct wired. Two armored cable fittings are also included, an on-off switch on the front allows for easy task light illumination.



P700024-028-CS



P700025-028-CS



P700026-028-CS



P700027-028-CS



P700028-028-CS



CCT selector switch



Access plate



Quick connectors

**9" LED UNDERCABINET
P700024-028-CS** White
9" L., 3-1/4" W., 1-1/8" ht.
One 4w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 228 delivered
lumens (at 3000K).

**12" LED UNDERCABINET
P700025-028-CS** White
11-1/2" L., 3-1/4" W., 1-1/8" ht.
One 4.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 299 delivered
lumens (at 3000K).

**18" LED UNDERCABINET
P700026-028-CS** White
17-1/2" L., 3-1/4" W., 1-1/8" ht.
One 6.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 457 delivered
lumens (at 3000K).


**24" LED UNDERCABINET
P700027-028-CS** White
23-1/2" L., 3-1/4" W., 1-1/8" ht.
One 8.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 608 delivered
lumens (at 3000K).

**36" LED UNDERCABINET
P700028-028-CS** White
35-1/2" L., 3-1/4" W., 1-1/8" ht.
One 11.5w integrated LED,
2700K, 3000K, 3500K, 4000K,
5000K, 90CRI, 859 delivered
lumens (at 3000K).

All fixtures:



| | |
|-----------------------------|-------|
| 5 CCT SELECTABLE | 2700K |
| | 3000K |
| | 3500K |
| | 4000K |
| | 5000K |



Product Index

P1000

P1871 124

P2000

P25000381
 P25000787
 P25000983
 P25001189
 P25002185
 P25005890
 P25005973
 P25006075
 P25006279
 P25006377
 P267375

P3000

P300189 107
 P300190 107
 P300191 107
 P300295104, 105
 P300296104, 105
 P300297104, 105
 P300298104, 105
 P300299101
 P300300101
 P30030497
 P30030597
 P30030697
 P30031198
 P30031298
 P30031398
 P300314108
 P300315108
 P300316108
 P300317108
 P300319100
 P300320102, 103
 P300321102, 103
 P300322102, 103
 P300323102, 103
 P300327109
 P300328109
 P300329109
 P300330109
 P30033199
 P30033299
 P30033399

P350022 41, 43
 P350039 41, 43
 P35016994
 P35018139
 P35018353
 P35019594
 P35019749, 51
 P35019893
 P35019993
 P35020092
 P35020315
 P35020569
 P35020929
 P35021033, 35
 P35021155

P4000

P400048 41, 43
 P40020257, 59
 P40022857, 59
 P40023539
 P40024339
 P40025061, 63
 P40025161, 63
 P40025261, 63
 P40025349, 51
 P40025449, 51
 P40025523
 P40025730
 P40026021
 P40026225, 27
 P40026325, 27
 P40026429
 P40026755
 P40026947
 P40027037
 P40027465, 67
 P40027565, 67
 P40027665, 67

P5000

P50004141, 43
 P50027845
 P50027945
 P50029655
 P50030257, 59
 P50030357, 59
 P50030517
 P50030753
 P50030853
 P50030970
 P50031070
 P50031170
 P50031369
 P50031461, 63
 P50031561, 63
 P50031657, 59
 P50031749, 51
 P50031823
 P50031930
 P50032030
 P50032125, 27
 P50032225, 27
 P50032468
 P50032568
 P50032847
 P50032969
 P50033015
 P50033115
 P50033365, 67
 P500355123
 P500356123
 P50041533,35
 P50041633,35
 P540033120
 P540046110
 P540095116
 P540097118
 P540292117
 P550050120
 P550069120
 P550083112
 P550084113
 P550089111
 P550093119
 P550094119
 P550097118
 P550099123
 P550100123
 P550101122

P550102122
 P550103122
 P550104122
 P550292117
 P560255117
 P560256117
 P560257117
 P560259121
 P560260121
 P560261115
 P560262115
 P560263119
 P560264116
 P560265116
 P560266116
 P560267114
 P560268114
 P560269114
 P560273118
 P560274118

P7000

P700024127
 P700025127
 P700026127
 P700027127
 P700028127
 P71009739
 P71009947, 100
 P71010015
 P71010292
 P71010329

P8000

P800002124, 125
 P800018124, 125
 P800019124, 125
 P800020126
 P810029126
 P81003296
 P81003396
 P860058123
 P860271
 P871124
 P875571
 P875871

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

www.progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

www.progresslighting.com/where-to-buy

Icon Guide



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



Please note indoor only (dry location) fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor ceiling fans are perfectly acceptable to use in interior spaces.



If you are selecting a ceiling fan for a space that is outdoors and under a roof, i.e. any covered porches; you should select either a damp rated or wet listed fan. Damp location fans may also be used indoors.



If the fan comes directly into contact with water, you’ll need to ensure that the ceiling fan has a “wet” listing. Ceiling fans designed for damp or wet locations feature elements, such as moisture-resistant motors and all weather blades. Wet location fans may also be used indoors.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.enegy.ca.gov



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as “solid” have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2020
 All rights reserved.
 International copyright secured.



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Products with this icon are Dark-Sky Friendly: they are certified by the International Dark-Sky Association to minimize glare while reducing light trespass and skyglow (they don’t pollute the night sky.)



Fixtures that support compliance when used in outdoor lighting applications



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCAN.



Complies with “American with Disabilities Act”



Products with this icon have a feature that allows for selectable CCT (correlated color temperature)



Products with this icon are compatible with our AC Motor P2667-31 or DC motor P2673-01 Wi-Fi control. Easily control your fan with your smart phone, tablet, voice controls or a hand-held remote. Uses Smart by Bond technology to control: on/off or speed function of the fan and full range dimming of the light kit.



Products include integrated Wi-Fi control. Easily control your fan with your smart phone, tablet, voice controls or a hand-held remote. Uses Smart by Bond technology to control: on/off or speed function of the fan and full range dimming of the light kit.



See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

www.progresslighting.com

