



**PRODUCT
SUPPLEMENT
SUMMER 2022**

**PROGRESS
LIGHTING™**

Table of Contents

Pictorial Index 2

DESIGN+SERIES™ 6



Collections 10



Pendants 14



Bath Collections 18



Light up your life by finding the perfect fixtures that express your personal style, inside and out.

Ceiling Fans

26



Outdoor

32



Step Lights

35



Recessed Lighting

36



Index

40

DESIGN SERIES INDEX



ASTRA
Matte Black p.6



ASTRA
Satin Brass p.7



ASTRA
Matte Black p.7



ASTRA
Satin Brass p.7



ASTRA
Antique Bronze p.9



ASTRA
Brushed Nickel p.9



See the 2022 Design Series Catalog or progresslighting.com for additional products.

ASTRA
Matte Black p.9



ASTRA
Satin Brass p.9



ASTRA
Matte Black p.9



ASTRA
Satin Brass p.9



Collections

GALLOWAY
Brushed Nickel p.13



GALLOWAY
Matte Black p.11



GALLOWAY
Brushed Nickel p.13



GALLOWAY
Matte Black p.10



GALLOWAY
Brushed Nickel p.12



GALLOWAY
Matte Black p.11



GALLOWAY
Brushed Nickel p.13



GALLOWAY
Matte Black p.11



GALLOWAY
Brushed Nickel p.13



GALLOWAY
Matte Black p.11



GALLOWAY
Brushed Nickel p.13



GALLOWAY
Matte Black p.11



SINGLETON
Brushed Nickel p.14



SINGLETON
Matte Black p.14



SINGLETON
Vintage Brass p.14



SINGLETON
Brushed Nickel p.15



SINGLETON
Matte Black p.15



SINGLETON
Vintage Brass p.15



SINGLETON
Brushed Nickel p.15



SINGLETON
Matte Black p.15



SINGLETON
Vintage Brass p.15



Bath Collections

CLEAR GLASS

Brushed Nickel p.22



CLEAR GLASS

Matte Black p.22



GOODWIN

Brushed Nickel p.20



GOODWIN

Matte Black p.20



GOODWIN

Polished Chrome p.20



SINGLETON

Brushed Nickel p.18



SINGLETON

Matte Black p.18



SINGLETON

Vintage Brass p.18



Outdoor

PEMBROKE

Matte Black p.34



PEMBROKE

Matte Black p.34



SWANSEA

Matte Black p.33



SWANSEA

Matte Black p.33




SWANSEA

Matte Black p.33



Indoor Ceiling Fans



BRADEN
Matte Black p.31



BRADEN
Matte White p.31



BYARS
Brushed Nickel p.28



BYARS
Matte Black p.29



GILLEN
Blistered Iron p.27



GILLEN
Matte Black p.27



See the 2022 Ceiling Fan Catalog or progresslighting.com for additional products.

GILLEN
Vintage Brass p.26



TREVINA V
Matte Black p.30



TREVINA V
Painted Nickel p.30



TREVINA V
Matte White p.30



Outdoor Ceiling Fans

GILLEN
Blistered Iron p.27



GILLEN
Matte Black p.27



GILLEN
Vintage Brass p.26



ASTRA

The Astra ceiling light features a space-age-inspired design perfect for modern and mid-century décor. The generous scale is ideal for bringing illumination to bedrooms, hallways and family rooms.



P400109-31M



FINISHES
● Matte Black - 31M
● Satin Brass - 012

SIX-LIGHT CHANDELIER

P400108-31M Matte Black
P400108-012 Satin Brass
22-5/8" dia., 10-1/2" ht.
Overall ht. w/chain 72", wire 15'.
Six medium base lamps,
each 60w max.



EIGHT-LIGHT CHANDELIER

P400109-31M Matte Black
P400109-012 Satin Brass
42-3/8" dia., 19-5/8" ht.
Overall ht. w/chain 77", wire 15'.
Eight medium base lamps,
each 60w max.

*Fixture dimension does not
include lamps.*





Featuring Astra

Sleek, Bold Style

Use dark walls to accentuate the white floor and earth tones in the room. Make a statement with the space-age-inspired Astra chandelier, whose luxurious Satin Brass finish contrasts beautifully against the dark color palette. Add dining chairs with a round silhouette to soften the linear lines that are prevalent throughout the room's décor elements.



P350225-31M



P350225-012



P350225-009



P350225-020



P710027-31M



P710027-012

FINISHES

- Matte Black - 31M
- Satin Brass - 012

THREE-LIGHT SEMI-FLUSH

P350225-31M Matte Black
P350225-012 Satin Brass
P350225-009 Brushed Nickel
P350225-020 Antique Bronze
 18" dia., 5-1/8" ht.
 Three medium base lamps,
 each 60w max.

TWO-LIGHT WALL BRACKET

P710027-31M Matte Black
P710027-012 Satin Brass
 7-1/4" W., 17-3/4" ht.
 Extends 3-7/8". H/CTR 7".
 Two medium base lamps,
 each 60w max.

Fixture dimension does not include lamps.

Galloway

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

P400301-31M

Clean, modern lines combine with rustic elements in the Galloway Collection. A lightly distressed finish highlights an angular frame with lights that glow brightly within the stately form to illuminate spaces in casual style.



Stately Form

Angular Frame

Lightly Distressed Finish

Galloway



P400302-31M

TWO-LIGHT FLUSH MOUNT

P350224-31M Matte Black
15" dia., 5-1/2" ht.
Two medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400301-31M Matte Black
28" dia., 19-1/4" ht.
Overall ht. w/chain 94", wire 10'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400302-31M Matte Black
30" dia., 28-1/4" ht.
Overall ht. w/chain 103", wire 15'.
Six candelabra base lamps,
each 60w max.

FOUR-LIGHT SMALL FOYER

P500377-31M Matte Black
14-1/4" dia., 18-3/8" ht.
Overall ht. w/chain 94", wire 10'.
Four candelabra base lamps,
each 60w max.



P500378-31M



P500377-31M

FOUR-LIGHT MEDIUM FOYER

P500378-31M Matte Black
24" dia., 30-7/8" ht.
Overall ht. w/chain 106-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

ONE-LIGHT WALL BRACKET

P710109-31M Matte Black
5-1/2" W., 18-1/8" ht.
Extends 4-1/2". H/CTR 9-1/16".
One candelabra base lamp, 60w max.




P350224-31M



P710109-31M

Clean, Modern Lines

Rustic Elements



Casual Style

Galloway



TWO-LIGHT FLUSH MOUNT

P350224-009 Brushed Nickel
15" dia., 5-1/2" ht.
Two medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400301-009 Brushed Nickel
28" dia., 19-1/4" ht.
Overall ht. w/chain 94", wire 10'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400302-009 Brushed Nickel
30" dia., 28-1/4" ht.
Overall ht. w/chain 103", wire 15'.
Six candelabra base lamps,
each 60w max.

FOUR-LIGHT SMALL FOYER

P500377-009 Brushed Nickel
14-1/4" dia., 18-3/8" ht.
Overall ht. w/chain 94", wire 10'.
Four candelabra base lamps,
each 60w max.

FOUR-LIGHT MEDIUM FOYER

P500378-009 Brushed Nickel
24" dia., 30-7/8" ht.
Overall ht. w/chain 106-1/2", wire 15'.
Four candelabra base lamps,
each 60w max.

ONE-LIGHT WALL BRACKET

P710109-009 Brushed Nickel
5-1/2" W., 18-1/8" ht.
Extends 4-1/2". H/CTR 9-1/16".
One candelabra base lamp, 60w max.



Singleton

The Singleton Collection pays homage to industrial styling with oversized warehouse shades fabricated from clear glass. Vintage-inspired metal fittings create a timeless design.

FINISHES

- Brushed Nickel - 009
- Vintage Brass - 163
- Matte Black - 31M

ONE-LIGHT MEDIUM PENDANT

P500381-009 Brushed Nickel

P500381-163 Vintage Brass

P500381-31M Matte Black

14" dia., 8-1/2" ht.

Overall ht. w/stem 65", wire 10'.

One medium base lamp,

60w max.

P500381-009



P500381-163



P500381-31M



Singleton



P350226-009



P350227-009

ONE-LIGHT SMALL SEMI-FLUSH

P350226-009 Brushed Nickel

P350226-163 Vintage Brass

P350226-31M Matte Black

7-5/8" dia., 7" ht.

One medium base lamp,

60w max.

ONE-LIGHT MEDIUM SEMI-FLUSH

P350227-009 Brushed Nickel

P350227-163 Vintage Brass

P350227-31M Matte Black

14" dia., 8-1/2" ht.

One medium base lamp,

60w max.



P350226-163



P350227-163



P350226-31M



P350227-31M



2

1

3



White combined with a rich, deep blue adds rich contrast to the bath, especially when accented by touches of gold.

1

Use pops of gold in the lighting, plumbing and furniture to warm the color scheme.

2

Create a timeless feeling with vanity lighting from the Singleton Collection, whose vintage-inspired metal fittings coordinate beautifully with retro-style plumbing fixtures.

3

Add the ideal amount of illumination over the tub with the Singleton ceiling light, featuring an oversized, clear glass warehouse shade.

Singleton

FINISHES

● Brushed Nickel - 009

● Vintage Brass - 163

● Matte Black - 31M

P300396-009

The Singleton Collection pays homage to industrial styling with oversized warehouse shades fabricated from clear glass. Vintage-inspired metal fittings create a timeless design.



Oversized Warehouse Shades

ONE-LIGHT BATH

P300395-009 Brushed Nickel

P300395-163 Vintage Brass

P300395-31M Matte Black

7-5/8" W., 8" ht.

Extends 9". H/CTR 4-1/8".

One medium base lamp,

60w max.



P300395-009



P300396-009

TWO-LIGHT BATH

P300396-009 Brushed Nickel

P300396-163 Vintage Brass

P300396-31M Matte Black

17" W., 8" ht.

Extends 9". H/CTR 5-5/8".

Two medium base lamps,

each 60w max.



P300395-163



P300396-163

All fixtures mount up or down.



P300395-31M



P300396-31M

Singleton



P300397-009



P300397-163



P300397-31M



P300398-009



P300398-163



P300398-31M

THREE-LIGHT BATH

P300397-009 Brushed Nickel

P300397-163 Vintage Brass

P300397-31M Matte Black

26-1/2" W., 8" ht.

Extends 9". H/CTR 5-5/8".

Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300398-009 Brushed Nickel

P300398-163 Vintage Brass

P300398-31M Matte Black

36" W., 8" ht.

Extends 9". H/CTR 5-5/8".

Four medium base lamps, each 60w max.

All fixtures mount up or down.

Goodwin

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Matte Black - 31M

P300389-009

The Goodwin vanity light has a clean design that seamlessly blends with today's décor. Crisp lines highlight the modern profile of the rectangular backplate that supports columns of clear glass shades for bright illumination in the bath.



Modern Profile

Crisp Lines

ONE-LIGHT BATH

P300386-009 Brushed Nickel
P300386-015 Polished Chrome
P300386-31M Matte Black
 4-1/2" W., 8-3/8" ht.
 Extends 5". H/CTR 4-3/4".
 One medium base lamp,
 60w max.



P300386-009



P300387-009

TWO-LIGHT BATH

P300387-009 Brushed Nickel
P300387-015 Polished Chrome
P300387-31M Matte Black
 12-7/8" W., 8-1/4" ht.
 Extends 5". H/CTR 5-7/8".
 Two medium base lamps,
 each 60w max.



P300386-015



P300387-015

All fixtures mount up or down.



P300386-31M



P300387-31M

Goodwin



P300388-009



P300388-015



P300388-31M



P300389-009



P300389-015



P300389-31M

THREE-LIGHT BATH

P300388-009 Brushed Nickel

P300388-015 Polished Chrome

P300388-31M Matte Black

21" W., 8-1/4" ht.

Extends 5". H/CTR 5-7/8".

Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300389-009 Brushed Nickel

P300389-015 Polished Chrome

P300389-31M Matte Black

29-1/4" W., 8-1/4" ht.

Extends 5". H/CTR 5-7/8".

Four medium base lamps, each 60w max.

All fixtures mount up or down.

Clear Glass

FINISHES

● Brushed Nickel - 009

● Matte Black - 31M

P300392-31M

The Clear Glass vanity light features an updated transitional design complemented by flared shades that offer classic appeal. An extended backplate with scalloped edges provides generous coverage for easy installation.

Flared Shades



*Updated
Transitional
Design*

TWO-LIGHT BATH

P300390-009 Brushed Nickel

P300390-31M Matte Black

18" W., 8-3/8" ht.

Extends 8". H/CTR 4-7/8".

Two medium base lamps,
each 60w max.



P300390-009



P300391-009

THREE-LIGHT BATH

P300391-009 Brushed Nickel

P300391-31M Matte Black

24" W., 8-3/8" ht.

Extends 8". H/CTR 4-7/8".

Three medium base lamps,
each 60w max.



P300390-31M



P300391-31M

All fixtures mount up or down.

Clear Glass



P300392-009



P300392-31M



P300393-009



P300393-31M



P300394-009



P300394-31M

FOUR-LIGHT BATH

P300392-009 Brushed Nickel

P300392-31M Matte Black

30" W., 8-3/8" ht.

Extends 8". H/CTR 4-7/8".

Four medium base lamps,
each 60w max.

FIVE-LIGHT BATH

P300393-009 Brushed Nickel

P300393-31M Matte Black

36" W., 8-3/8" ht.

Extends 8". H/CTR 4-7/8".

Five medium base lamps,
each 60w max.

SIX-LIGHT BATH

P300394-009 Brushed Nickel

P300394-31M Matte Black

48" W., 8-3/8" ht.

Extends 8". H/CTR 4-7/8".

Six medium base lamps,
each 60w max.

All fixtures mount up or down.

Soft colors, touchable textures and vintage décor bring a nostalgic air and cozy feel to the bedroom.

1

Hang botanical prints to create a classic vignette on the wall above the bed.

2

Showcase retro styling lighting for instant impact. The Gillen ceiling fan in Vintage Brass features an aged metal patina and clear glass globe shade. The swing-arm Hinton wall sconce adds focused light next to the bed.

3

Use crushed velvet bedding in dusty pink and peach tones for a soft, romantic touch.





2

3

Gillen

FINISHES

- Vintage Brass - 163
- Blistered Iron - 171
- Matte Black - 31M

P250075-163-WB
shown with Chestnut blades

Retro Styling

Retro styling brings a nostalgic look to the Gillen 56-in Ceiling Fan. A small motor housing allows its vintage design to take center stage, showcasing an aged metal patina finish and clear glass globe shade. A DC motor controlled by a 6-speed full-function remote with full range dimming compatibility circulates the air as desired. Add charm and warmth with 1 – 7 watt, vintage-style LED Bulb (included).

*Aged Metal
Patina Finish*

*Vintage-Style
LED Bulbs*

Gillen



P250075-163-WB
shown with Chestnut blades

P250075-163-WB Vintage Brass



Chestnut



P250075-171-WB
shown with Grey Weathered Wood blades

P250075-171-WB Blistered Iron



Grey Weathered Wood



P250075-31M-WB
shown with Rustic Charcoal blades

P250075-31M-WB Matte Black



Rustic Charcoal

ENERGY INFORMATION AT HIGH SPEED

Airflow	6500 cubic feet per minute
Electricity Use	35 watts (excludes lights)
DOE Weighted CFM/W	198 CFM/W

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Damp rated
- Full Function Remote control
- Plywood blades
- Clear glass lens
- Remote control with battery included

SIZE

56" dia., 21-5/8" ht.
80" lead wires.

LAMP

7w LED Lamp, 2700K, 90 CRI,
600 source lumens, dimmable



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control



Byars

FINISHES

- Brushed Nickel - 009
- Matte Black - 31M

P250061-009-30
shown with American Walnut blades

Deep functionality meets modern transitional styling in the Byars 54-in. Ceiling Fan. A clean-lined motor housing featuring a DC motor descends from the down rod, holding five reversible plywood blades with softly squared edges for optimal airflow. Byars offers both soft uplight and even downlight illumination with Dual-Lens combination integrated LED light sources that can be controlled individually with the 6 speed, full-function remote control with full range dimming.

*Soft Uplight
Illumination*

*Modern
Transitional
Styling*

Full Range Dimming

Byars

P250061-009-30 Brushed Nickel



Chestnut

American Walnut

P250061-31M-30 Matte Black



Matte Black

Antique Black



P250061-009-30
shown with Chestnut blades



P250061-31M-30
shown with Antique Black blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	6,477 cubic feet per minute
Electricity Use	30 watts (excludes lights)
DOE Weighted CFM/W	250 CFM/W



Full Function Remote Control Included
Six-speed fan operation
Full-range dimming for light
Reverse direction control

FEATURES

- Limited Lifetime Warranty
- DC Motor
- Reversible Plywood blades
- Full Function Remote control
- Up and Down light
- Double Lens shades

SIZE

54" dia., 16" ht.
80" lead wires.

LAMP

Downlight - 18w LED Module,
3000K, 90 CRI,
1400 source lumens, dimmable
Uplight - 12W LED module,
3000K, 90 CRI, 1100 source
lumens, dimmable



Trevina V Energy Star




Trevina V features updated modern styling, an Energy Star rating and efficient LED lamping to create cool, cost-saving breezes inside your home. Three reversible plywood blades and a white opal glass shade add to the elegant and straightforward design of the motor housing. Individual pull chains operate both the fan and the light.

FINISHES

- Matte White - 028
- Painted Nickel - 152
- Matte Black - 31M


P250076-028-WB Matte White



Matte White

Natural Cherry


P250076-152-WB Painted Nickel



Silver

Matte Black

P250076-31M-WB Matte Black



Matte Black

Distressed Ebony



P250076-028-WB
shown with Natural Cherry blades



P250076-152-WB
shown with Silver blades



P250076-31M-WB
shown with Distressed Ebony blades

ENERGY INFORMATION AT HIGH SPEED

Airflow	4,364 cubic feet per minute
Electricity Use	43 watts (excludes lights)
DOE Weighted CFM/W	116 CFM/W

FEATURES

- Limited Lifetime Warranty
- AC Motor
- White opal glass shade
- Add a P2663-01 Remote or P2630-30 Wall control
- Add the P2667-31 WiFi remote

SIZE

52" dia., 16-1/2" ht.
80" lead wires.

LAMP

Two 9w LED Lamps, 3000K, 90 CRI, 800 source lumens, dimmable.



Braden

This Braden 56 inch, three-blade, hugger-style ceiling fan features clean lines and a design that complements modern interiors. A white opal shade contains an integrated 18W LED module, offering both form and function with energy and cost-savings benefits.



P2588-028-30K
shown with Natural Cherry blades




P2588-31M-30K
shown with Distressed Ebony blades


FINISHES

- Matte White - 028
- Matte Black - 31M

P2588-028-30K Matte White



P2588-31M-30K Matte Black



ENERGY INFORMATION AT HIGH SPEED

Airflow	4,263 cubic feet per minute
Electricity Use	55 watts (excludes lights)
DOE Weighted CFM/W	85 CFM/W

FEATURES

- Limited Lifetime Warranty
- Hugger low profile mounting
- AC Motor
- Reversible plywood blades
- White opal glass shade
- Full function remote control with batteries is included
- Remote control may be replaced with P2631-30 wall control
- Add the P2667-31 WiFi remote

SIZE

56" dia., 9-7/8" ht.
10" lead wires.

LAMP

18w LED Module, 3000K, 90 CRI, 1400 source lumens, dimmable.



Full Function Remote Control Included
Three-speed fan operation
Full-range dimming for light
Reverse direction control



AirPro Edgelit LED Light Kit

The AirPro Edgelit 7" universal light kit provides dimmable LED light through a glare-free, bright, and evenly illuminated surface. A very slim profile offers a discreet, subtle design and easy, universal installation ideal for many fan models.



P260002-028-30



P260002-152-30



P260002-31M-30

AIRPRO® EDGELIT LED LIGHT KIT

- P260002-028-30** Matte White
 - P260002-152-30** Painted Nickel
 - P260002-31M-30** Matte Black
- 7-7/16" dia., 1" ht.
14w LED Module, 3000K, 90 CRI, 940 delivered lumens, dimmable.



FINISHES

- Matte White - 028
- Painted Nickel - 152
- Matte Black - 31M



Featuring Gillen and Swansea

The Outdoor Living is Easy

A neutral palette creates a relaxing space for outdoor entertaining. Stoic gray and white stone, warm wood tones and crisp white trim define the room's layout. The Swansea Island chandelier anchors the bar area with clear glass shades and an airy frame distinguished by strong geometric lines finished in modern black. The Gillen ceiling fan takes center stage over the seating area, with a vintage design showcased by a classic black finish and clear glass globe shade.

Swansea

FINISH

- Matte Black - 31M

The Swansea outdoor collection is distinguished by strong geometric lines finished in modern black to create an open, minimalist frame. Crisp, clear glass shades surround elegant lights that cast beautiful illumination in outdoor covered areas.



FOUR-LIGHT OUTDOOR CHANDELIER

P550128-31M Matte Black

18" sq., 17-1/4" ht.

Overall ht. w/chain 92-1/2", wire 15'

Four candelabra base lamps, each 60w max.



FOUR-LIGHT OUTDOOR ISLAND CHANDELIER

P550129-31M Matte Black

36" L., 10-7/8" W., 11" ht.

Overall ht. w/chain 77", wire 15'

Four candelabra base lamps, each 60w max.



FIVE-LIGHT OUTDOOR CHANDELIER

P550130-31M Matte Black

24" dia., 23" ht.

Overall ht. w/chain 98-1/2", wire 15'

Five candelabra base lamps, each 60w max.



Pembroke

FINISHES

- Matte Black - 31M

Classic meets casual in the Pembroke outdoor collection. A densely woven, weather-resistant handcrafted gallery surrounds seeded glass to provide softly diffused lighting with a warm and inviting glow.



ONE-LIGHT OUTDOOR PENDANT

P550126-31M Matte Black

14" W., 18-1/2" ht.

Overall ht. w/chain 94", wire 10'.

One medium base lamp,

60w max.



THREE-LIGHT OUTDOOR CHANDELIER

P550127-31M Matte Black

20" W., 21-1/2" ht.

Overall ht. w/chain 97", wire 15'.

Three candelabra base lamps,
each 60w max.



Indoor/Outdoor Step & Wall Lights **LED**

The LED Step/Wall Light will complement many interior and exterior architectural styles, whether residential or commercial. A horizontal and a vertical exterior face plate are provided to accommodate either a horizontally or vertically oriented installation. The step light features an integrated 120V AC light engine, eliminating the need for an additional LED driver. The light engine is enclosed in a gasketed lens, allowing it to meet the rigorous demands of wet location use. Its dimmable LED light source offers optimized, energy-efficient light output, 3000K, 90CRI. Use these lights to clearly illuminate stairs, walls, and walkways, resulting in performance, cost and safety benefits. It is cCSAus wet location rated for use in areas with direct water contact.

FEATURES

- Includes both horizontal and vertical faceplates
- Integral power supply module in a compact package
- Consumes less than 5w of power per fixture
- Enclosed in a gasketed lens
- cCSAus listed for wet locations
- Warm white 3000K dimmable LEDs
- 90 CRI

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Satin White - 028
- Black - 031

LOUVERED

P660004-009-30 Brushed Nickel
P660004-020-30 Antique Bronze
P660004-028-30 Satin White
P660004-031-30 Black
 Mounts horizontal and vertical.
 3-1/8" W., 4-7/8" ht.
 Wet location listed.
 4.5w LED included.



P660004-009-30



P660004-020-30



P660004-028-30



P660004-031-30

HOODED

P660005-009-30 Brushed Nickel
P660005-020-30 Antique Bronze
P660005-028-30 Satin White
P660005-031-30 Black
 Mounts horizontal and vertical.
 3" W., 4-7/8" ht.
 Wet location listed.
 4.5w LED included.



P660005-009-30



P660005-020-30



P660005-028-30



P660005-031-30

6" Recessed



New Construction Air-Tight IC and Non-IC with E26 socket

P806N-N-MD-ICAT

Ceiling Opening: 6" dia.
Plaster Frame: 9-13/32" X 6-5/8"
Pryouts: 7/8"



Remodel Air-Tight IC and Non-IC with E26 socket

P806N-R-MD-ICAT

Ceiling Opening: 6" dia.
Plaster Frame: Not applicable
Pryouts: 7/8"

HOUSING SPECIFICATIONS

- Standard height for 2x8 ceilings
- IC Rated for Insulation Contact
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from 1/2" to 1 1/4"
- Compatible with A19, PAR30, R30, BR30, PAR38 & BR40 lamps
- Provided with push in wire connectors
- Hanger bar max span 24"

IC Trims and Non-IC Trims



BAFFLE

P806000-020 Antique Bronze
7-1/4" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



BAFFLE

P806000-028 Satin White
7-1/4" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



BAFFLE

P806000-031 Black
7-1/4" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



OPEN

P806001-028 Satin White
7-5/16" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



OPEN

P806001-031 Black
7-5/16" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



SPLAY BAFFLE

P806002-028 Satin White
8" dia., 5-3/16" ht.
Lamp: PAR38, 90w max.



OPEN WET LOCATION

P806003-028 Satin White
7-5/16" dia., 4-7/8" ht.
Lamp: PAR38, 90w max.



LENSED SHOWER

P806004-028 Satin White
8-1/4" dia., 1-1/4" ht.
Lamp: A19, 40w max.



DROP LENSED SHOWER

P806005-028 Satin White
7-1/2" dia., 2-1/2" ht.
Lamp: A19, 40w max.



EYEBALL

P800020-028 Satin White
7-3/4" dia., 4" ht.
Lamp: A19, 8w max.



LED IC Trims



SMOOTH LED

P800002-028-30
Satin White
7-1/2" dia., 2-1/2" ht.
Lamp: One LED,
8w max.



EYEBALL LED

P800018-028-CS
Satin White
7-3/4" dia., 3-15/16" ht.
Lamp: One LED,
8w max.



BAFFLE LED

P800019-028-CS
Satin White
7-3/8" dia., 3-7/16" ht.
Lamp: One LED,
8w max.




HIGH LUMEN LED

P800021-028-30
Satin White
7-7/16" dia., 3-3/8" ht.
Lamp: One LED,
13w max.



6" Shallow Recessed



New Construction Air-Tight IC and Non-IC with E26 socket

P806S-N-MD-ICAT

Ceiling Opening: 6" dia.
Plaster Frame: 9-13/32" X 6-5/8"
Pryouts: 7/8"



Remodel Air-Tight IC and Non-IC with E26 socket

P806S-R-MD-ICAT

Ceiling Opening: 6" dia.
Plaster Frame: Not applicable
Pryouts: 7/8"

HOUSING SPECIFICATIONS

- Shallow height for 2x6 ceilings
- IC Rated for Insulation Contact
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from 1/2" to 1 1/4"
- Compatible with A19, PAR30, & R30 lamps
- Provided with push in wire connectors
- Hanger bar max span 24"

IC Trims and Non-IC Trims



BAFFLE
P806006-028 Satin White
7-5/16" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



BAFFLE
P806006-031 Black
7-5/16" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



OPEN
P806007-028 Satin White
7-5/16" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



LENSED SHOWER
P806004-028 Satin White
8-1/4" dia., 1-1/4" ht.
Lamp: A19, 40w max.



DROP LENS SHOWER
P806005-028 Satin White
7-1/2" dia., 2-1/2" ht.
Lamp: A19, 40w max.



EYEBALL
P800020-028 Satin White
7-3/4" dia., 4" ht.
Lamp: A19, 8w max.



LED IC Trims



SMOOTH LED
P800002-028-30
Satin White
7-1/2" dia., 2-1/2" ht.
Lamp: One LED,
8w max.



EYEBALL LED
P800018-028-CS
Satin White
7-3/4" dia., 3-15/16" ht.
Lamp: One LED,
8w max.



BAFFLE LED
P800019-028-CS
Satin White
7-3/8" dia., 3-7/16" ht.
Lamp: One LED,
8w max.



HIGH LUMEN LED
P800021-028-30
Satin White
7-7/16" dia., 3-3/8" ht.
Lamp: One LED,
13w max.



6" Sloped Recessed



New Construction Air-Tight IC and Non-IC with E26 socket

P806A-N-MD-ICAT

Ceiling Opening: 6" dia.
Plaster Frame: 13-13/32" X 10-5/16"
Pryouts: 7/8"



New Construction Air-Tight Non-IC with E26 socket

P806A-N-MD-AT

Ceiling Opening: 6" dia.
Plaster Frame: 13-13/32" X 10-5/16"
Pryouts: 7/8"



Remodel Air-Tight Non-IC with E26 socket

P806A-R-MD-AT

Ceiling Opening: 6" dia.
Plaster Frame: Not applicable
Pryouts: 7/8"

HOUSING SPECIFICATIONS

- Angled for slope ceiling installation
- Lamp socket adjusts to accommodate 2/12 to 7/12 ceiling pitches
- Insulation Contact & Non-IC contact options
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from 1/2" to 1 1/4"
- Compatible with PAR30, & R30 lamps
- Provided with push in wire connectors
- Hanger bar max span 24"

IC Trims and Non-IC Trims



BAFFLE

P806008-020 Antique Bronze
8-1/8" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



BAFFLE

P806008-028 Satin White
8-1/8" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



BAFFLE

P806008-031 Black
8-1/8" dia., 3-3/4" ht.
Lamp: PAR30S, 50w max.



4" Recessed



New Construction Air-Tight IC and Non-IC with E26 socket

P804N-N-MD-ICAT

Ceiling Opening: 4" dia.
Plaster Frame: 8-11/16" X 5-5/8"
Pryouts: 7/8"



New Construction Air-Tight Non-IC with E26 socket

P804N-N-MD-AT

Ceiling Opening: 4" dia.
Plaster Frame: 8-1/2" X 6"
Pryouts: 7/8"



Remodel Air-Tight Non-IC with E26 socket

P804N-R-MD-AT

Ceiling Opening: 4" dia.
Plaster Frame: Not applicable
Pryouts: 7/8"

HOUSING SPECIFICATIONS

- Suitable for 2x6 & 2x8 ceilings
- Insulation Contact & Non-IC contact options
- Airtight per ASTM E283 requirements
- Installs to ceiling thickness from 1/2" to 1 1/4"
- Compatible with A19, PAR20, & R20 lamps
- Provided with push in wire connectors
- Hanger bar max span 24"

IC Trims and Non-IC Trims



BAFFLE
P804000-020 Antique Bronze
5" dia., 2-3/16" ht.
Lamp: PAR20, 50w max.



BAFFLE
P804000-028 Satin White
5" dia., 2-3/16" ht.
Lamp: PAR20, 50w max.



BAFFLE
P804000-031 Black
5" dia., 2-3/16" ht.
Lamp: PAR20, 50w max.



EYEBALL LED
P800022-028-CS
Satin White
5-3/4" dia., 3-1/4" ht.
Lamp: One LED,
8w max.



OPEN
P804001-028
Satin White
5" dia., 3-7/16" ht.
Lamp: PAR20, 50w max.



OPEN WET LOCATION
P804002-028
Satin White
5" dia., 3-7/16" ht.
Lamp: PAR20, 50w max.



EYEBALL TRIM
P804003-028
Satin White
5" dia., 2-13/16" ht.
Lamp: PAR20, 50w max.



WALL WASH
P804004-028
Satin White
5" dia., 3" ht.
Lamp: PAR20, 35w max.



Product Index

P2000

P250061.....	28, 29
P250075.....	26, 27
P250076.....	30
P2588.....	31
P260002.....	31

P3000

P300386.....	20
P300387.....	20
P300388.....	21
P300389.....	21
P300390.....	22
P300391.....	22
P300392.....	23
P300393.....	23
P300394.....	23
P300395.....	18
P300396.....	18
P300397.....	19
P300398.....	19
P350224.....	11, 13
P350225.....	9
P350226.....	15
P350227.....	15

P4000

P400108.....	7
P400109.....	7
P400301.....	11, 13
P400302.....	11, 13

P5000

P500377.....	11, 13
P500378.....	11, 13
P500381.....	14
P550126.....	34
P550127.....	34
P550128.....	33
P550129.....	33
P550130.....	33

P6000

P660004.....	35
P660005.....	35

P7000

P710027.....	9
P710109.....	11, 13

P8000

P800002.....	36, 37
P800018.....	36, 37
P800019.....	36, 37
P800020.....	36, 37
P800021.....	36, 37
P800022.....	39
P804000.....	39
P804001.....	39
P804002.....	39
P804003.....	39
P804004.....	39
P804N-N-MD-AT.....	39
P804N-N-MD-ICAT.....	39
P804N-R-MD-AT.....	39
P806000.....	36
P806001.....	36
P806002.....	36
P806003.....	36
P806004.....	36, 37
P806005.....	36, 37
P806006.....	37
P806007.....	37
P806008.....	38
P806A-N-MD-AT.....	38
P806A-N-MD-ICAT.....	38
P806A-R-MD-AT.....	38
P806N-N-MD-ICAT.....	36
P806N-R-MD-ICAT.....	36
P806S-N-MD-ICAT.....	37
P806S-R-MD-ICAT.....	37

Icon Guide



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to energystar.gov for specific product qualifications and list of certified products.



Please note indoor only (dry location) products should only be used indoors. Even if an outdoor area or screened-in porch is covered, the fixture can be affected when exposed to humidity. You can, however, “bring the outdoors inside” – as using outdoor products are perfectly acceptable to use in interior spaces.



Damp Location products and fixtures can be used in covered spaces outdoors or indoors.



If the product will have direct contact with water, you'll need to ensure that the product has a “wet” listing. Products rated for damp or wet locations are designed with features specifically for this type of environment. Wet location products may also be used indoors.



This icon indicates products that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energy.ca.gov

DC MOTOR

DC motor ceiling fans feature high torque for increased air movement, whisper quiet operation, and greater energy efficiency than AC motors.



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at www.appliances.energy.ca.gov.



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors



Products with this icon have a feature that allows for selectable CCT (correlated color temperature)



The products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCAN.



Products with this icon are WiFi compatible and may be controlled with WiFi when one of the following controls is added;

- AC Motor fans can add the P2667-31 WiFi remote control
- DC Motor fans that are WiFi compatible can add the P2673-01 WiFi module.

With the addition of one of the above controls, you may easily control your ceiling fan or light with your smart phone, tablet, voice controls, or hand held remote. Use the Smart by Bond technology to control on/off function of the fan and the light kit along with full range dimming and fan speed control.

Warranty

For more details regarding product warranty coverage, please consult a qualified Progress Lighting distributor or visit:

www.progresslighting.com/warranty

Where to buy

To purchase Progress Lighting products from one of our authorized dealers visit:

www.progresslighting.com/where-to-buy

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as “solid” have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2022
All rights reserved.
International copyright secured.



See Yourself Here

Every home and every family has a story that's all their own. In this issue, we introduce you to the many ways Progress Lighting can bring that story to life.



PROGRESS LIGHTING

701 Millennium Boulevard
Greenville, SC 29607

www.progresslighting.com

