

# PRODUCT SUPPLEMENT JUNE 2019

 **PROGRESS**  
LIGHTING™



# Table of Contents

2	PICTORIAL INDEX		
5	WHAT'S YOUR STYLE?		
16	FIXTURE COLLECTIONS	29	CLOSE-TO-CEILING
		30	SCONCES



31	BATH COLLECTIONS	44	OUTDOOR
		46	CEILING FANS



52	UTILITY
56	INDEX


















# FIXTURE COLLECTIONS

<b>DRUM SHADE</b> Black p.28	<b>FOSTER</b> Gilded Iron p.24	<b>KEMPSEY</b> Antique Bronze p.22	<b>KEMPSEY</b> Brushed Nickel p.20
			
<b>MAST</b> Antique Bronze p.26	<b>MAST</b> Brushed Nickel p.27	<b>REPLAY</b> Black p.28	<b>REPLAY</b> Brushed Nickel p.28
			
<b>REPLAY</b> Polished Nickel p.28	<b>SENECA</b> Black p.16	<b>SENECA</b> Polished Nickel p.18	
			
















# CLOSE-TO-CEILING

<b>ARCHIE</b> Vintage Brass p.29	<b>ETCHED GLASS</b> Black p.29	<b>ETCHED GLASS</b> Brushed Nickel p.29	<b>FOSTER</b> Gilded Iron p.25	<b>MAST</b> Antique Bronze p.27
				
<b>MAST</b> Brushed Nickel p.27	<b>SIGNAL</b> Graphite p.29	<b>SIGNAL</b> Polished Chrome p.29		
				

# SCONCES / WALL BRACKETS

<b>ADLEY</b> Black p.33	<b>ADLEY</b> Brushed Nickel p.32	<b>ADLEY</b> Polished Nickel p.33	<b>ADLEY</b> Satin Brass p.32	<b>ARCHIE</b> Vintage Brass p.31
				
<b>CLASSIC</b> Black p.42	<b>CLASSIC</b> Brushed Nickel p.42	<b>INSPIRE LED</b> Summer Linen p.30	<b>INSPIRE LED</b> Off White Linen p.30	<b>KEMPSEY</b> Antique Bronze p.23
				
<b>KEMPSEY</b> Brushed Nickel p.21	<b>LINEN GLASS SCONCE</b> Black p.30	<b>LINEN GLASS SCONCE</b> Brushed Nickel p.30	<b>RUSHTON</b> Brushed Nickel p.34	<b>RUSHTON</b> Graphite p.34
				
<b>SIGNAL</b> Graphite p.41	<b>SIGNAL</b> Polished Chrome p.40			
				





# BATH COLLECTIONS

<b>ADLEY</b> Black p.33	<b>ADLEY</b> Brushed Nickel p.32	<b>ADLEY</b> Polished Nickel p.33	<b>ADLEY</b> Satin Brass p.32	<b>ARCHIE</b> Vintage Brass p.31
				
<b>BRIARWOOD</b> Antique Bronze p.38	<b>BRIARWOOD</b> Graphite p.38	<b>CLASSIC</b> Black p.42	<b>CLASSIC</b> Brushed Nickel p.42	<b>MAST</b> Antique Bronze p.36
				
<b>MAST</b> Brushed Nickel p.36	<b>RUSHTON</b> Brushed Nickel p.34	<b>RUSHTON</b> Graphite p.34	<b>SIGNAL</b> Graphite p.41	<b>SIGNAL</b> Polished Chrome p.40
				

# OUTDOOR

<b>ENGLEWOOD</b> Antique Bronze p.45	<b>ENGLEWOOD</b> Antique Pewter p.45	<b>ENGLEWOOD</b> Black p.45	<b>GREENE RIDGE</b> Architectural Bronze p.44	<b>GREENE RIDGE</b> Black p.44
				

# CEILING FANS

<b>GAZE</b> Black p.46	<b>GULLIVER</b> Galvanized p.50	<b>GULLIVER</b> Graphite p.51	<b>VAST</b> Black p.48
			

# What's Your Style?



DISCOVER  
STATEMENT-MAKING  
LIGHTING FOR EVERY  
BUDGET & STYLE.

One of today’s most popular design trends encourages individuals to create unique lighting designs by mixing and matching their favorite fixtures within the same space. There is no need to feel limited by fixtures or finishes in one particular collection!





Featuring Mast Mini-Pendants and Gulliver Ceiling Fan.

## REACH YOUR BLISS

Express style, relaxation, and tranquility using a tonal, minimal color palette in the bedroom. Neutral shades establish a calm and serene sentiment while textures and fabrics add layers of luxury to the mix for a modern-meets-farmhouse approach to inviting comfort. The Mast pendant placed bedside and the Gulliver fan overhead complement the subtly alluring, Zen look and ambiance.



## BOLD, BEAUTIFUL BATH

Whether dark or bright, a bold pop of color is trending in bath design. Pair a dark vanity and mirror with a white palette and bright natural light for a classic, sophisticated look. The industrial-styled Rushton bath sconces illuminate the face while adding a vintage charm that creates a polished balance with the clean décor.

*Featuring Rushton Bath.*



*Featuring Briarwood Bath.*


## ROOM WITH A VIEW

Placing a bath vanity between two windows lets an abundance of natural light stream into the bathroom, and the Briarwood bath bar adds light at face level, right where it's needed. Briarwood's richly painted finish and metal detailing coordinates with the plumbing fixtures, while contrasting nicely with the room's white color scheme.



## SWING ARM SCONCE

The Kempsey sconce features a swivel arm that provides customization to the direction of light once the fixture is mounted. Swivel the arm to be straight, left, right or anything in-between. This feature makes the Kempsey Sconce the perfect bedside companion.



*Featuring Kempsey Sconces and Fleurette Chandelier.*

## TRANSITIONAL WITH A TWIST

Masculine and feminine touches balance comfortably in this Transitional bedroom. A neutral color palette is punctuated by interestingly textured pillows and pops of dark brown to add depth. The unexpected addition of the whimsical Fleurette chandelier contrasts nicely with the streamlined Kempsey wall brackets and the clean lines of the furniture.

*Editor's Note:*  
View details on the Fleurette Chandelier online at [progresslighting.com](http://progresslighting.com).





Featuring Gaze Ceiling Fan, Tobin Chandelier and Gresham Sconces.

## COOL, CLASSIC AND COMFORTABLE

Modern Farmhouse design embraces tradition but is firmly planted in the present. With a nod to vintage touches of a weathered fireplace mantel, exposed beams, and an airy palette grounded by dark-toned furniture and accessories in a variety of textures, this open concept space modernizes a traditional approach. Our clean-lined Tobin chandelier and Gresham wall sconces accent the inviting ambiance with a touch of classic iron detailing while the Gaze ceiling fan offers a modern look and functionality as a refreshing update to Farmhouse style.

*Editor's Note:*

View details on the Tobin Chandelier and Gresham Sconces online at [progresslighting.com](https://progresslighting.com).



## AN INDUSTRIAL EDGE

With a simple but edgy vibe that takes its cue from industrial origins, this bedroom offers a warm backdrop of texture and interest against the clean ironwork designs of the lighting. Two low-hanging Foster pendants over the nightstands and the Sanford ceiling fan overhead play with the notions of substance and form, while organic elements of wood, layered textiles and a soothing color scheme celebrate the signature look of the Industrial setting.

*Editor's Note:*

View details on the Sanford Ceiling Fan online at [progresslighting.com](http://progresslighting.com).



Featuring Foster Mini-Pendants and Sanford Ceiling Fan.



# SENECA



P400115-031



Sophisticated simplicity is personified in the Seneca collection. Within its open cage design candelabra lights seem to float in midair, brought down to earth only by its simple base, offering a clean and modern look to any space.

## FINISHES

- Black - 031
- Polished Nickel - 104



P400115-031



P500121-031


**FIVE-LIGHT CHANDELIER**  
**P400115-031** Black  
 25-1/2" dia., 15-7/8" ht.,  
 Overall ht. w/stem 81-1/2"; wire 180".  
 Five candelabra base lamps,  
 each 60w max.

**SIX-LIGHT ISLAND**  
**P400175-031** Black  
 38-1/4" W., 14-1/8" ht.,  
 Overall ht. w/stem 80-1/2"; wire 180".  
 Six candelabra base lamps,  
 each 60w max.

**NINE-LIGHT CHANDELIER**  
**P400187-031** Black  
 30" dia., 20-7/8" ht.,  
 Overall ht. w/stem 86-1/2"; wire 180".  
 Nine candelabra base lamps,  
 each 60w max.

**FOUR-LIGHT FOYER**  
**P500121-031** Black  
 15" dia., 17-1/4" ht.,  
 Overall ht. w/stem 83-1/2"; wire 180".  
 Four candelabra base lamps,  
 each 60w max.

**EIGHT-LIGHT FOYER**  
**P500122-031** Black  
 19-5/8" dia., 32" ht.,  
 Overall ht. w/stem 98"; wire 180".  
 Eight candelabra base lamps,  
 each 60w max.



P400175-031



P400187-031



P500122-031





P400115-104

# SENECA

## FIVE-LIGHT CHANDELIER

**P400115-104** Polished Nickel  
25-1/2" dia., 15-7/8" ht.,  
Overall ht. w/stem 81-1/2"; wire 180".  
Five candelabra base lamps,  
each 60w max.

## SIX-LIGHT ISLAND

**P400175-104** Polished Nickel  
38-1/4" W., 14-1/8" ht.,  
Overall ht. w/stem 80-1/2"; wire 180".  
Six candelabra base lamps,  
each 60w max.

## NINE-LIGHT CHANDELIER

**P400187-104** Polished Nickel  
30" dia., 20-7/8" ht.,  
Overall ht. w/stem 86-1/2"; wire 180".  
Nine candelabra base lamps,  
each 60w max.

## FOUR-LIGHT FOYER

**P500121-104** Polished Nickel  
15" dia., 17-1/4" ht.,  
Overall ht. w/stem 83-1/2"; wire 180".  
Four candelabra base lamps,  
each 60w max.

## EIGHT-LIGHT FOYER


**P500122-104** Polished Nickel  
19-5/8" dia., 32" ht.,  
Overall ht. w/stem 98"; wire 180".  
Eight candelabra base lamps,  
each 60w max.



P400115-104



P500121-104



P400175-104



P400187-104



P500122-104



# KEMPSEY



P350110-009



For Farmhouse styling with a twist, look no further than Kempsey, whose inside-out design showcases stylish charm. A sturdy metal frame on the outside captures the textured linen shade within its arms, so that the structure becomes part of the design. The shade has an inner transparent backing, so its beautiful texture is visible from inside out. A wall bracket featuring a multi-directional arm holding the shade completes the collection.

## FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020



P350110-009



P350110-009  
Shown as  
semi-flush



P500138-009



P500138-009

## THREE-LIGHT SEMI-FLUSH CONVERTIBLE

**P350110-009** Brushed Nickel  
Hanging and ceiling mount hardware included  
21-3/4" dia., 11" ht.,  
Overall ht. w/stem 76"; wire 120".  
Three medium base lamps,  
each 60w max.

## ONE-LIGHT PENDANT

**P500138-009** Brushed Nickel  
11-3/4" dia., 9" ht.,  
Overall ht. w/stem 76"; wire 120".  
One medium base lamp,  
75w max.

## THREE-LIGHT PENDANT

**P500139-009** Brushed Nickel  
17-3/4" dia., 21-3/8" ht.,  
Overall ht. w/stem 87-1/2"; wire 120".  
Three medium base lamps,  
each 60w max.

## ONE-LIGHT WALL BRACKET

**P710045-009** Brushed Nickel  
12" dia., 19-3/4" ht.,  
Extends 23-5/8".  
One medium base lamp, 75w max.  
On/off rotary switch on backplate.



P710045-009





P350110-020

# KEMPSEY

**THREE-LIGHT SEMI-FLUSH CONVERTIBLE**  
**P350110-020** Antique Bronze  
Hanging and ceiling mount hardware included  
21-3/4" dia., 11" ht.,  
Overall ht. w/stem 76"; wire 120".  
Three medium base lamps, each 60w max.

**ONE-LIGHT PENDANT**  
**P500138-020** Antique Bronze  
11-3/4" dia., 9" ht.,  
Overall ht. w/stem 76"; wire 120".  
One medium base lamp, 75w max.

**THREE-LIGHT PENDANT**  
**P500139-020** Antique Bronze  
17-3/4" dia., 21-3/8" ht.,  
Overall ht. w/stem 87-1/2"; wire 120".  
Three medium base lamps, each 60w max.

**ONE-LIGHT WALL BRACKET**  
**P710045-020** Antique Bronze  
12" dia., 19-3/4" ht.,  
Extends 23-5/8".  
One medium base lamp, 75w max.  
On/off rotary switch on backplate.



P350110-020



P350110-020  
Shown as  
semi-flush



P500139-020



P500138-020



P710045-020

# FOSTER



P400153-071



Clean ironwork inspired by antique trains defines the look of Foster. Substance and form are the watchwords of this family, with a simple design of bent metal arms enclosing exposed bulbs held by an ornamental socket cover. Foster's squared lines and mixed metal elements are ideal for Industrial and Rustic settings.

**FINISH**  
● Gilded Iron - 071



P350116-071



P400153-071

**TWO-LIGHT FLUSH MOUNT**  
**P350116-071** Gilded Iron  
16" dia., 6" ht.,  
Two medium base lamps,  
each 60w max.

**FIVE-LIGHT CHANDELIER**  
**P400153-071** Gilded Iron  
25" dia., 14" ht.,  
Overall ht. w/stem 80-1/2"; wire 180".  
Five medium base lamps,  
each 60w max.

**SIX-LIGHT CHANDELIER**  
**P400154-071** Gilded Iron  
30" dia., 14" ht.,  
Overall ht. w/stem 81"; wire 180".  
Six medium base lamps,  
each 60w max.

**ONE-LIGHT MINI-PENDANT**  
**P500155-071** Gilded Iron  
11-1/4" dia., 10-3/4" ht.,  
Overall ht. w/stem 77"; wire 120".  
One medium base lamp,  
60w max.

*Fixtures shown with  
V6.5ST19DLED922/JA8 vintage lamps.*



P500155-071



P400154-071





Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to the linear pendant and mini-pendant. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

**FINISHES**

- Brushed Nickel - 009
- Antique Bronze - 020

**ALSO AVAILABLE IN**

Bath and Vanity, page 36 and Wall Sconce at [progresslighting.com](http://progresslighting.com)



[PROGRESSLIGHTING.COM](http://PROGRESSLIGHTING.COM)



**TWO-LIGHT FLUSH MOUNT**  
**P350144-009** Brushed Nickel  
**P350144-020** Antique Bronze  
 13" dia., 5-1/4" ht.,  
 Two medium base lamps,  
 each 60w max.

**FOUR-LIGHT ISLAND**  
**P400190-009** Brushed Nickel  
**P400190-020** Antique Bronze  
 38" W., 14-3/4" ht.,  
 Overall ht. w/stem 80-1/2"; wire 180".  
 Four medium base lamps,  
 each 100w max.

**ONE-LIGHT MINI-PENDANT**  
**P500192-009** Brushed Nickel  
**P500192-020** Antique Bronze  
 6-1/4" dia., 14" ht.,  
 Overall ht. w/stem 80"; wire 120".  
 One medium base base lamp,  
 100w max.



P350144-009



P350144-020



P500192-009



P500192-020

[PROGRESSLIGHTING.COM](http://PROGRESSLIGHTING.COM)


# REPLAY

Smooth forms, linear details and a pleasingly elegant frame enhance a simplified modern look in the Replay pendant. A rectangular silhouette extending below the etched glass shade makes a strong and simple vertical statement.

- FINISHES**
- Brushed Nickel - 009
  - Black - 031
  - Polished Nickel - 104

**ALSO AVAILABLE**  
Complete collection at  
[progresslighting.com](http://progresslighting.com)

**FOUR-LIGHT FOYER PENDANT**  
**P500206-009** Brushed Nickel  
**P500206-031** Black  
**P500206-104** Polished Nickel  
18" dia., 31-3/4" ht.,  
Overall ht. w/chain 106"; wire 180".  
Four medium base lamps,  
each 100w max.



# DRUM SHADE

A perennially popular look, the simple lines of the Drum Shade pendant are refreshed with a Harvest Linen shade, giving a rustic, country casual feel to this classic fixture. The shade has an inner transparent backing, so its beautiful texture is visible from inside out.

- FINISH**
- Black - 031

**FIVE-LIGHT PENDANT CHANDELIER**  
**P400193-031** Black  
21-5/8" dia., 21-1/8" ht.,  
Overall ht. w/chain 65-1/2"; wire 120".  
Five candelabra base lamps,  
each 60w max.



# ARCHIE

The Archie Collection brings a vintage, industrial flair to interior settings. The collection's distinctive double prismatic glass adds visual interest as its crisscross pattern comes to life when illuminated. The unusual, finely crafted strap and knob detail add authentic industrial style. Fixtures are offered in a Vintage Brass finish and provide an updated design to this quintessential collection.

- FINISH**
- Vintage Brass - 163

**TWO-LIGHT SEMI FLUSH CONVERTIBLE**  
**P2334-163** Vintage Brass  
Hanging and ceiling mount  
hardware included  
12-3/8" dia., 11-3/8" ht.,  
Overall ht. w/chain 48-1/2"; wire 120".  
Two medium base lamps,  
each 100w max.

**ALSO AVAILABLE IN**  
Bath and Vanity, page 31  
Complete collection at  
[progresslighting.com](http://progresslighting.com)

**TWO-LIGHT FLUSH MOUNT**  
**P3740-163** Vintage Brass  
12 3/8" dia., 6 1/4" ht.,  
Two medium base lamps,  
each 75w max.



P2334-163  
Shown as  
semi-flush



P350145-015



P350145-143

- FINISHES**
- Polished Chrome - 015
  - Graphite - 143

**ALSO AVAILABLE IN**  
Bath and Vanity, page 40

**ONE-LIGHT FLUSH MOUNT**  
**P350145-015** Polished Chrome  
**P350145-143** Graphite  
5-1/8" dia., 7-5/8" ht.,  
One medium base lamp,  
60w max.

# ETCHED GLASS

Some spaces call for a clean and straightforward close-to-ceiling fixture, and the Etched Glass flush mount easily fills that need. Unhindered by unnecessary detail, the fixture glows through a simple etched glass bowl clasped by a crown molding-inspired, wide metal band in Matte Black or Brushed Nickel.

- FINISHES**
- Brushed Nickel - 009
  - Black - 031

**ONE-LIGHT FLUSH MOUNT**  
**P350146-009** Brushed Nickel  
**P350146-031** Black  
11-1/2" dia., 3-3/4" ht.,  
One medium base lamp,  
60w max.

**TWO-LIGHT FLUSH MOUNT**  
**P350147-009** Brushed Nickel  
**P350147-031** Black  
14" dia., 4-5/8" ht.,  
Two medium base lamps,  
each 60w max.



P350146-009



P350146-031



P350147-009  
PROGRESSLIGHTING.COM



P350147-031



# INSPIRE LED

Harkening back to a simpler time, the Inspire Collection freshens traditional forms with its clean lines. Now debuting with an integrated LED light source, the wall sconce softly shines through a textured Summer Linen Shade or a creamy Off-White Linen Shade

- FINISHES**
- Summer Linen - 030
  - Off White Linen - 159

**ALSO AVAILABLE**

Complete collection at [progresslighting.com](http://progresslighting.com)

**LED WALL SCONCE**  
**P710071-030-30** Summer Linen  
**P710071-159-30** Off White Linen  
6-1/4" W., 9" ht.,  
Extends 3-1/8".  
One 9w LED module, 3000K,  
90CRI, 624 source lumens.  
ADA



P710071-030-30



P710071-159-30

# LINEN GLASS SCONCE

With a squared-off, architectural form complemented by etched linen glass, the Linen Glass Sconce is simple, modern and ideal for use in any Transitional setting.

- FINISHES**
- Brushed Nickel - 009
  - Black - 031

**ONE-LIGHT WALL SCONCE**  
**P710072-009** Brushed Nickel  
**P710072-031** Black  
6" W., 12" ht.,  
Extends 4".  
One medium base lamp,  
75w max.  
ADA



P710072-009



P710072-031

# ARCHIE



P2992-163

The Archie Collection brings a vintage, industrial flair to interior settings. The collection's distinctive double prismatic glass adds visual interest as its crisscross pattern comes to life when illuminated. The unusual, finely crafted strap and knob detail add authentic industrial style. Vanity fixtures are offered in a Vintage Brass finish and provide an updated design to this quintessential collection.

**ONE-LIGHT BATH**  
**P2989-163** Vintage Brass  
5 3/4" W., 8 1/4" ht.,  
Extends 7". H/CTR 5-1/4".  
One medium base lamp,  
100w max.

**TWO-LIGHT BATH**  
**P2991-163** Vintage Brass  
17 W., 8 3/4" ht.,  
Extends 7". H/CTR 5-1/4".  
Two medium base lamps,  
each 100w max.

**THREE-LIGHT BATH**  
**P2992-163** Vintage Brass  
26 1/4" W., 8 3/4" ht.,  
Extends 7". H/CTR 5-1/4".  
Three medium base lamps,  
each 100w max.

**FOUR-LIGHT BATH**  
**P2997-163** Vintage Brass  
35 1/2" W., 8 3/4" ht.,  
Extends 7". H/CTR 5-1/4".  
Four medium base lamps,  
each 100w max.

**FINISH**

- Vintage Brass - 163

**ALSO AVAILABLE IN**  
Close-to-Ceiling, page 29  
Complete collection at [progresslighting.com](http://progresslighting.com)

*Fixtures mount up or down.*



P2991-163



P2992-163



P2989-163



P2997-163

# ADLEY



Fundamentally modern but with a traditional twist, Adley combines a clear glass shade with a curved rectangular back plate. This sophisticated bath light is offered as a one, two, three or four-light fixture in a choice of four finishes. Adley is a universal choice for New Traditional and Transitional settings.

FINISHES

- Brushed Nickel - 009
- Satin Brass - 012
- Black - 031
- Polished Nickel - 104

**ONE-LIGHT BATH**  
**P300154-009** Brushed Nickel  
**P300154-012** Satin Brass  
4-1/2" W., 7-3/4" ht.,  
Extends 6". H/CTR 5-3/8".  
One medium base lamp,  
60w max.

**TWO-LIGHT BATH**  
**P300155-009** Brushed Nickel  
**P300155-012** Satin Brass  
13-7/8" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Two medium base lamps,  
each 60w max.

**THREE-LIGHT BATH**  
**P300156-009** Brushed Nickel  
**P300156-012** Satin Brass  
23" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Three medium base lamps,  
each 60w max.

**FOUR-LIGHT BATH**  
**P300157-009** Brushed Nickel  
**P300157-012** Satin Brass  
32" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Four medium base lamps,  
each 60w max.



P300154-009



P300155-009



P300156-009



P300157-009



P300154-012



P300155-012



P300156-012



P300157-012



P300154-031



P300155-031



P300156-031



P300157-031



P300154-104



P300155-104



P300156-104



P300157-104

**ONE-LIGHT BATH**  
**P300154-031** Black  
**P300154-104** Polished Nickel  
4-1/2" W., 7-3/4" ht.,  
Extends 6". H/CTR 5-3/8".  
One medium base lamp,  
60w max.

**TWO-LIGHT BATH**  
**P300155-031** Black  
**P300155-104** Polished Nickel  
13-7/8" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Two medium base lamps,  
each 60w max.

**THREE-LIGHT BATH**  
**P300156-031** Black  
**P300156-104** Polished Nickel  
23" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Three medium base lamps,  
each 60w max.

**FOUR-LIGHT BATH**  
**P300157-031** Black  
**P300157-104** Polished Nickel  
32" W., 7-5/8" ht.,  
Extends 6". H/CTR 5-3/8".  
Four medium base lamps,  
each 60w max.

*Fixtures mount up or down.*





# RUSHTON

P300229-143

Celebrate the past with the industrial-styled Rushton vanity. Mechanical details like a pulley wheel complete with a faux cord holding a clear glass shade, an antique style socket, and an exposed bulb (not included) add vintage charm. The mixed metal fixture is offered in either Brushed Nickel accented with a Black tube arm, or Graphite with an Antique Brass tube arm, for a look that preserves a sense of history.

**ONE-LIGHT BATH**  
**P300226-009** Brushed Nickel  
**P300226-143** Graphite  
5" W., 9-1/2" ht.,  
Extends 6". H/CTR 6-1/2".  
One medium base lamp,  
60w max.



P300226-009



P300226-143

**TWO-LIGHT BATH**  
**P300227-009** Brushed Nickel  
**P300227-143** Graphite  
16" W., 9-1/2" ht.,  
Extends 6". H/CTR 7".  
Two medium base lamps,  
each 60w max.



P300227-009



P300227-143

- FINISHES**
- Brushed Nickel - 009
  - Graphite - 143



P300228-009

**THREE-LIGHT BATH**  
**P300228-009** Brushed Nickel  
**P300228-143** Graphite  
24" W., 9-1/2" ht.,  
Extends 6". H/CTR 7".  
Three medium base lamps,  
each 60w max.



P300228-143

**FOUR-LIGHT BATH**  
**P300229-009** Brushed Nickel  
**P300229-143** Graphite  
32" W., 9-1/2" ht.,  
Extends 6". H/CTR 7".  
Four medium base lamps,  
each 60w max.

*Fixtures shown with  
V6.5ST19DLED922/JA8 vintage lamps.*



P300229-009



P300229-143

# MAST



P300217-009

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to these vanity fixtures. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

**TWO-LIGHT BATH**  
**P300216-009** Brushed Nickel  
**P300216-020** Antique Bronze  
13-7/8" W., 7-5/8" ht.,  
Extends 6-1/4". H/CTR 5-1/4".  
Two medium base lamps,  
each 100w max.



P300216-009



P300216-020

**FINISHES**

- Brushed Nickel - 009
- Antique Bronze - 020

**ALSO AVAILABLE IN**

Fixture Collections, page 26  
and Wall Sconce at  
[progresslighting.com](http://progresslighting.com)



P300217-009



P300217-020

**THREE-LIGHT BATH**  
**P300217-009** Brushed Nickel  
**P300217-020** Antique Bronze  
24" W., 7-3/4" ht.,  
Extends 6-1/4". H/CTR 5-1/4".  
Three medium base lamps,  
each 100w max.

**FOUR-LIGHT BATH**  
**P300218-009** Brushed Nickel  
**P300218-020** Antique Bronze  
33-7/8" W., 7-3/4" ht.,  
Extends 6-1/4". H/CTR 5-1/4".  
Four medium base lamps,  
each 100w max.

*Fixtures mount up or down.*



P300218-009



P300218-020



# BRIARWOOD



P300231-143

The classic, X-brace pattern inspired by farmhouse or barn doors is re-imagined in the Briarwood two, three, and four-light wall sconce offerings. The simple geometric shape, a hallmark of the Briarwood collection, is mounted on the faux-painted wood back plate, with a clear glass shade completing the look.

**TWO-LIGHT BATH**  
**P300230-020** Antique Bronze  
**P300230-143** Graphite  
14-3/4" W., 8-1/4" ht.,  
Extends 6-1/2". H/CTR 5-7/8".  
Two medium base lamps,  
each 60w max.



P300230-020



P300230-143

**FINISHES**  
● Antique Bronze - 020  
● Graphite - 143  
  
**ALSO AVAILABLE**  
Complete collection at  
[progresslighting.com](http://progresslighting.com)



P300231-020



P300231-143

**THREE-LIGHT BATH**  
**P300231-020** Antique Bronze  
**P300231-143** Graphite  
24-3/4" W., 8-1/4" ht.,  
Extends 6-1/2". H/CTR 5-7/8".  
Three medium base lamps,  
each 60w max.

**FOUR-LIGHT BATH**  
**P300232-020** Antique Bronze  
**P300232-143** Graphite  
34-3/4" W., 8-1/4" ht.,  
Extends 6-1/2". H/CTR 5-7/8".  
Four medium base lamps,  
each 60w max.

*Fixtures mount up or down.*

*Fixtures shown with  
V6.5ST19DLED922/JA8 vintage lamps.*



P300232-020



P300232-143

# SIGNAL



Signal has an industrial origin, yet its clean lines beckon a modern sensibility. Clear blown glass shades deliver a lighter touch, balancing the substantial look of the metal angular arm and round backplate. With its emphasis on simplicity and function, Signal is ideal for many residential settings.

**FINISHES**

- Polished Chrome - 015
- Graphite - 143

**ALSO AVAILABLE IN**

Close-to-Ceiling, page 29

**ONE-LIGHT BATH**  
**P300174-015** Polished Chrome  
5-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
One medium base lamp,  
60w max.

**TWO-LIGHT BATH**  
**P300175-015** Polished Chrome  
13-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Two medium base lamps,  
each 60w max.

**THREE-LIGHT BATH**  
**P300176-015** Polished Chrome  
23-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Three medium base lamps,  
each 60w max.

**FOUR-LIGHT BATH**  
**P300177-015** Polished Chrome  
33-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Four medium base lamps,  
each 60w max.



P300174-015



P300175-015



P300176-015



P300177-015



P300174-143



P300175-143



P300176-143



P300177-143

**ONE-LIGHT BATH**  
**P300174-143** Graphite  
5-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
One medium base lamp,  
60w max.

**TWO-LIGHT BATH**  
**P300175-143** Graphite  
13-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Two medium base lamps,  
each 60w max.

**THREE-LIGHT BATH**  
**P300176-143** Graphite  
23-1/8" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Three medium base lamps,  
each 60w max.

**FOUR-LIGHT BATH**  
**P300177-143** Graphite  
33-1/2" W., 9-1/8" ht.,  
Extends 5-3/8". H/CTR 2-5/8".  
Four medium base lamps,  
each 60w max.

*Fixtures mount up or down.*

*Fixtures shown with  
F8.5A19D927/JA8 vintage lamps.*



# CLASSIC



Traditional details and graceful lines add modern elegance to any interior. Classic vanities feature etched glass shades and is offered in Matte Black or Brushed Nickel finish.

**FINISHES**

- Brushed Nickel - 009
- Black - 031

**ALSO AVAILABLE**

Complete collection at [progresslighting.com](http://progresslighting.com)

**ONE-LIGHT BATH**  
**P300233-009** Brushed Nickel  
**P300233-031** Black  
5" W., 8" ht.,  
Extends 7". H/CTR 3".  
One medium base lamp,  
100w max.

**TWO-LIGHT BATH**  
**P300234-009** Brushed Nickel  
**P300234-031** Black  
13" W., 7-7/8" ht.,  
Extends 7". H/CTR 3".  
Two medium base lamps,  
each 100w max.

**THREE-LIGHT BATH**  
**P300235-009** Brushed Nickel  
**P300235-031** Black  
24" W., 7-7/8" ht.,  
Extends 7". H/CTR 3".  
Three medium base lamps,  
each 100w max.



P300233-009



P300233-031



P300234-009



P300234-031



P300235-009



P300235-031



P300236-009



P300236-031



P300237-009



P300237-031



P300238-009



P300238-031

**FOUR-LIGHT BATH**  
**P300236-009** Brushed Nickel  
**P300236-031** Black  
30" W., 7-7/8" ht.,  
Extends 7". H/CTR 3".  
Four medium base lamps,  
each 100w max.

**FIVE-LIGHT BATH**  
**P300237-009** Brushed Nickel  
**P300237-031** Black  
36" W., 7-7/8" ht.,  
Extends 7". H/CTR 3".  
Five medium base lamps,  
each 100w max.

**SIX-LIGHT BATH**  
**P300238-009** Brushed Nickel  
**P300238-031** Black  
48" W., 7-7/8" ht.,  
Extends 7". H/CTR 3".  
Six medium base lamps,  
each 100w max.

*Fixtures mount up or down.*

# GREENE RIDGE



With its uncomplicated lines and tailored look, Greene Ridge unites simplicity and artistry in a tribute to its Craftsman-style inspiration. A strong, boxy shape tops a clear glass shade in keeping with the utilitarian design and lack of curves that define the Arts and Crafts look.

- FINISHES**
- Black - 031
  - Architectural Bronze - 129

**ONE-LIGHT HANGING LANTERN**  
**P550033-031** Black  
**P550033-129** Architectural Bronze  
6-3/4" sq., 14" ht.,  
Overall ht. w/chain 88-1/2"; wire 120".  
One medium base lamp,  
100w max.

**ONE-LIGHT SMALL WALL LANTERN**  
**P560099-031** Black  
**P560099-129** Architectural Bronze  
5-1/4" W., 11-5/8" ht.,  
Extends 6-3/4". H/CTR 8".  
One medium base lamp,  
100w max.

**ONE-LIGHT MED WALL LANTERN**  
**P560100-031** Black  
**P560100-129** Architectural Bronze  
6-3/4" W., 14-1/4" ht.,  
Extends 8-1/4". H/CTR 10-3/4".  
One medium base lamp,  
100w max.

*Fixtures shown with  
V6.5ST19DLED922/JA8 vintage lamps.*



P560099-031



P560099-129



P560100-031



P560100-129



P550033-031



P550033-129

# ENGLEWOOD



Inspired by the warmth and beauty of hammered copper home accents, Englewood's design displays elements of rustic craftsmanship. Available in Antique Bronze, Black or Antique Pewter, the inside of the shade features a metallic finish, offering higher illumination reflection. Antique Bronze and Black finishes feature a copper inside shade, while the Antique Pewter finish is paired with a metallic silver inner shade. The post top fixture adds the finishing touch to outdoor settings, giving eye-catching appeal to Farmhouse and Rustic homes, and is Dark Sky compliant.

- FINISHES**
- Antique Bronze - 020
  - Black - 031
  - Antique Pewter - 103

**ALSO AVAILABLE**  
Complete collection at  
[progresslighting.com](http://progresslighting.com)

**ONE-LIGHT POST LANTERN**  
**P540032-020** Antique Bronze  
**P540032-031** Black  
**P540032-103** Antique Pewter  
16" W., 13-1/2" ht.  
Extends 12".  
One medium base lamp,  
100w max.  
Fits 3" post (sold separately).



P540032-020



P540032-031



P540032-103



# GAZE



P2554-3130K shown with Distressed Ebony blades

Three-blade 60" Gaze ceiling fan features an LED light source, offering both form and function with energy and cost-savings benefits. An opal white shade contains an 18W dimmable, 3000K LED module. Gaze features a dual mount system and includes a three-speed remote control with full range dimming.

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- Reversible plywood blades
- White shatterproof lens
- Remote control with batteries is included
- Remote may be replaced with P2630-30 or P2630-95 wall control

**SIZE**


60" dia., 13-1/8" ht.  
80" lead wires

**FINISH**

- Black - 31

**P2554-3130K**

Matte Black



Matte Black



Distressed Ebony

**ALSO AVAILABLE**

Complete Fan Collection at  
[progresslighting.com](http://progresslighting.com)



P2554-0930K



P2554-1530K



P2554-2030K

**ENERGY INFORMATION AT HIGH SPEED**

<b>AIRFLOW:</b>	5,902 cubic feet per minute
<b>ELECTRICITY USE:</b>	75 watts (excludes lights)
<b>AIRFLOW EFFICIENCY:</b>	79 cubic feet per minute per watt

**LAMPING INFORMATION**

18w LED Module, 3000K, 90 CRI,  
1400 lumens, dimmable.



Shown with Matte Black blades.



Shown with Distressed Ebony blades.



Fan



Light



Dry

Indoor only



Three-Speed Remote Included  
Full-range dimming for light  
Three-speed fan operation

# VAST



P2550-3130K shown with Matte Black blades

Beautiful and expansive in design, the 72" Vast ceiling fan is ideal for use in large areas and outdoor covered areas for maximum cooling. A white opal shade complements a variety of finish options, including Brushed Nickel with Chrome accents, Antique Bronze, White with Chrome accents or Matte Black. Vast features a dual mount system and comes with a full function remote control.

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-20°)
- DC motor
- Aluminum blades
- White opal glass
- Remote control with batteries is included

**SIZE**

72" dia., 16-3/4" ht.  
80" lead wires

**FINISH**

- Black - 31

**P2550-3130K**  
*Matte Black shown  
and Matte Black blades*



*Matte Black*



**ALSO AVAILABLE**

Complete Fan Collection at  
[progresslighting.com](http://progresslighting.com)



P2550-0930K



P2550-2030K



P2550-3030K

**ENERGY INFORMATION AT HIGH SPEED**

<b>AIRFLOW:</b>	7,982 cubic feet per minute
<b>ELECTRICITY USE:</b>	28 watts (excludes lights)
<b>AIRFLOW EFFICIENCY:</b>	285 cubic feet per minute per watt

**LAMPING INFORMATION**

18w LED Module, 3000K, 90 CRI,  
1400 lumens, dimmable.



Full Function Remote Control Included  
*Full-range dimming for light*  
*Six-speed fan operation*  
*Reverse direction control*



Fan



Light



Damp

Indoor/Outdoor



# GULLIVER



P250012-141-22 shown with Antique White Wood

Three circular bands wrap together to create an open design for Gulliver. Fan blades enclosed within a stylish cage design gives the rustic charm of a pendant combined with the functionality of a ceiling fan. Dual toned frame color combinations of Galvanized with antique white accents or Graphite with weathered gray accents. A hand painted wood grained texture complements Rustic and Modern Farmhouse home decor, as well as Urban Industrial and Coastal interior settings.

**FEATURES**

- Limited lifetime warranty
- Dual Mount (flat or sloped ceiling-18.5°)
- AC motor
- Remote control with batteries is included

**SIZE**

23" dia., 18-1/8" ht.  
80" lead wires

**FINISHES**

- Galvanized -141
- Graphite - 143

**P250012-141-22**

Galvanized



Antique White Wood

**P250012-143-22**

Graphite



Gray Wood

ENERGY INFORMATION AT HIGH SPEED

<b>AIRFLOW:</b>	1,297 cubic feet per minute
<b>ELECTRICITY USE:</b>	39 watts (excludes lights)
<b>AIRFLOW EFFICIENCY:</b>	33 cubic feet per minute per watt

LAMPING INFORMATION

Three LED medium base vintage lamps, 2200K, 80 CRI, 5.5w max each, included. (dimnable)



Three-Speed Remote Included  
Full-range dimming for light  
Three-speed fan operation



Canada



Fan



Damp  
Indoor/Outdoor

# LED EDGELIT FLUSH MOUNT



Edgelit technology creates a large glare free and evenly illuminated surface for a variety of applications for both residential and commercial applications. Offering a low profile design, LED Edgelit Flush Mount is available in 7" in a White finish. Additional sizes available; 11", 14" and 18". The integrated driver does not recess into junction box, allowing for easy installation into 4" octagonal, 4" round PVC and 4-1/2" ceiling pan junction boxes. LED Edgelit Flush Mount is wet location listed and offers a 50,000-hour LED life.

**FINISH**  
○ White - 030

**ALSO AVAILABLE**  
Complete collection at  
progresslighting.com



P810015-030-30

**LED EDGELIT FLUSH MOUNT**  
**P810015-030-30** White  
7" dia., 1-1/8" ht.  
One 15w LED, 3000K,  
90CRI, 1000 lumens.



# EDGELIT RECESSED ACCESSORIES

Progress lighting has released two new accessories for the Edgelit Recessed fixtures. P860040-028 - 18" extender cable allows for the junction box to be remote and mounted further away from the fixture. P860044 - rough in accessory allows for Edge Lit recessed fixtures to be used in new construction installations. This accessory ensures a mounting location after the dry wall is installed and can be used when building codes require that the luminaire is supported from the building structure

**18" CABLE W/ TERMINALS**  
**P860040-028** Satin White  
18" L., 1/2" dia.




P860040-028



P860044-001

**EDGELIT RECESSED ROUGH IN ACCESSORY**  
**P860044-001** Unfinished  
20" W., 9" ht.,



# 5" SHALLOW CEILING RECESSED HOUSINGS

## 5" MEDIUM BASE REMODEL HOUSING

For complete fixture, order housing with trim.

Remodel Air-Tight IC



**P1841-ICAT**  
Ceiling opening: 5-1/2"  
Recessed depth: 5-3/8"  
Pryouts: 1/2"

**P1841-ICAT REMODEL WITH E26 SOCKET, IC RATED, AIR-TIGHT HOUSING**

- Rated for direct contact with insulated ceiling
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2"
- Meets ASTM-E283 air flow requirements
- Use with compatible items only



## TRIM FOR P1841-ICAT

6-1/2" outside diameter.. Can also be used with P851-ICAT



**SHALLOW STEP BAFFLE**  
Damp location listed.  
**P8475-28** Satin White  
Lamp: PAR30/R30, 50w max.  
Compatible with **P851-ICAT** and **P1841-ICAT**.

## 5" LED REMODEL HOUSING

For complete fixture, order housing with trim.

Remodel Air-Tight IC



**P1841-LED**  
Ceiling opening: 5-1/2"  
Recessed depth: 5-3/8"  
Pryouts: 1/2"

**P1841-LED REMODEL, IC RATED, AIR-TIGHT HOUSING**

- Rated for direct contact with insulated ceiling
- Adjustable housing to accommodate ceiling thickness 1/2" to 1-1/2"
- Meets ASTM-E283 air flow requirements
- Use with compatible LED items only. Visit progresslighting.com.



# 5" RECESSED TRIMS

6-1/2" outside diameter. Compatible with P851-ICAT housing.



**OPEN**  
With gasket.  
Damp location listed.  
**P8268-21** Clear Alzak  
Lamp: PAR30/R30, 50w max.  
Compatible with **P851-ICAT**.



**OPEN**  
With gasket  
Damp Location Listed  
**P8268-28** Satin White  
Lamp: PAR30/R30, 50w max.  
Compatible with **P851-ICAT**.



**STEP BAFFLE**  
Damp location listed.  
**P868-31** Black  
Lamp: PAR30/R30, 50w max.  
Compatible with **P851-ICAT**.



**P851-ICAT**  
*New Construction, IC rated, Air-tight Housing.* Complete collection at progresslighting.com.



# LED TAPE UNDERCABINET SYSTEM

LED Tape provides lighting to enhance aesthetics, while also aiding in tasks around the home. Common applications for LED Tape include; undercabinet lighting in kitchens to add illumination to work surfaces, highlighting back splashes in kitchens or bathroom areas and adding toe kick lighting at the bases of cabinets for dramatic and functional lighting.



## FOLLOW FOUR SIMPLE STEPS:

### 1. CHOOSE A TAPE LENGTH



12", 60" and 240" lengths to meet different sized projects and features an adhesive backing for easy application to desired surfaces.




Flexible tape can be cut every 4 inches (cut ends can be reconnected, allowing for full use of LED tape).



Tape is fully enclosed in silicone to allow for use in damp location. 24 VDC tape pairs with 24 VDC power supplies.

PRODUCT NO.	COLOR TEMP.	SIZE	
<b>P700008-000-27</b> <b>P700008-000-30</b>	2700K 3000K	12" L., 3/8" W., 1/8" ht.	
<b>P700009-000-27</b> <b>P700009-000-30</b>	2700K 3000K	60" L., 3/8" W., 1/8" ht.	
<b>P700010-000-27</b> <b>P700010-000-30</b>	2700K 3000K	240" L., 3/8" W., 1/8" ht.	

- LED FEATURES**
- 90CRI, 50,000 hr. life
  - 300 lumens per foot and consumes 4.2 watts per foot (71 lumens/w)
  - Field cuttable at every 4" to end of run.
  - cETLus listed damp location
  - 5 year warranty



P700008-000-27



P700009-000-27  
P700010-000-27

### 2. SELECT TRANSFORMER

Progress Lighting offers multiple power supplies to meet various project sizes. Power supplies can be dimmed, flicker-free, on Forward Phase (TRIAC) and Reverse Phase (ELV) dimmers down to 10% output.

PRODUCT NO.	FINISH	SIZE	WATT	MAX LENGTH OF TAPE
<b>P700020-031</b>	Black	8-3/16" L., 2" W., 1-3/4" HT	25w	60" Tape
<b>P700021-031</b>	Black	8-3/16" L., 2" W., 1-3/4" HT.	40w	120" Tape
<b>P700023-031</b>	Black	9-3/16" L., 3-3/8" W., 1-15/16" HT.	80w	240" Tape

- PRODUCT FEATURES**
- Maximum operating temperature -20° C to +40° C
  - Enclosure provided
  - Wire nuts and additional hardware included



P700020-000  
P700021-000  
P700023-000

### 3. ADDITIONAL SYSTEM CONNECTORS

Various connectors allow for customized layouts. Use linking connectors to join runs of tape. Use the L Connector for 90° bends and use the Y Connector to split one run of tape into two.



Connectors feature piercing conductors for secure connection.



Y, L and multi-linking connectors allow for flexibility in design.



Connectors provided with snap-fit covers for intuitive installation.

**2" CONNECTOR CORD**  
**P700011-000** Black  
Connect tape sections (P700008, P700009, P700010)  
2" L., 5/8" W., 1/4" ht.



**12" CONNECTOR CORD**  
**P700012-000** Black  
Connect tape sections (P700008, P700009, P700010)  
12" L., 5/8" W., 1/4" ht.



**18" CONNECTOR CORD**  
**P700013-000** Black  
Connect tape sections (P700008, P700009, P700010)  
18" L., 5/8" W., 1/4" ht.



**36" CONNECTOR CORD**  
**P700014-000** Black  
Connect tape sections (P700008, P700009, P700010)  
36" L., 5/8" W., 1/4" ht.



**72" CONNECTOR CORD**  
**P700015-000** Black  
Connect tape sections (P700008, P700009, P700010)  
72" L., 5/8" W., 1/4" ht.



**L CONNECTOR**  
**P700016-000** Black  
90° connector for connecting sections of tape (P700008, P700009, P700010) on corners.  
2-1/16" L., 2-1/16" W., 1/6" ht.



**Y CONNECTOR**  
**P700017-000** Black  
Three-way Y connector for connecting sections of tape (P700008, P700009, P700010)  
3-3/16" L., 3-3/16" W., 1/4" ht.



**OUTPUT POWER CONNECTOR**  
**P700022-000** Black  
60" L., 5/8" W., 1/4" ht.



### 4. MOUNTING CLIPS/END CLIPS

Select end caps or add mounting clips to finish the installation.

**P700018-000**  
Pack of 10 clips/screws for straight runs for added support (2 clips per foot recommended)  
1-1/8" L., 1/4" W., 1/8" ht.




**P700019-000**  
End caps to terminate run of LED tape. For use when tape has been cut at end of run. Sold in sets of 10.  
1/2" L., 1/2" W., 1/4" ht.



# CEILING FAN ACCESSORY DOWNRODS

3/4" diameter; approximately 1" outside diameter.

	CEILING HT.	9'-10'	10'-11'	11'-12'	12'-14'	13'-15'	14'-16'	15'-17'
	DOWNROD L.	12"	18"	24"	36"	48"	60"	72"
○	Matte White	P2603-28	P2604-28	P2605-28	P2606-28	P2607-28	-	-
●	Matte Black	P2603-31	P2604-31	P2605-31	P2606-31	P2607-31	-	-



## PRODUCT INDEX

### P1000

P1841-ICAT	53
P1841-LED	53

### P200000

P2334-163	29
P2603-28	56
P2603-31	56
P2604-28	56
P2604-31	56
P2605-28	56
P2605-31	56
P2606-28	56
P2606-31	56
P2607-28	56
P2607-31	56
P250012-141-22	50
P250012-143-22	51
P2550-3130K	48
P2554-3130K	46
P2989-163	31
P2991-163	31
P2992-163	31
P2997-163	31

### P300000

P300154-009	32
P300154-012	32
P300154-031	33
P300154-104	33
P300155-009	32
P300155-012	32
P300155-031	33
P300155-104	33
P300156-009	32
P300156-012	32
P300156-031	33
P300156-104	33
P300157-009	32
P300157-012	32
P300157-031	33
P300157-104	33
P300174-015	40
P300174-143	41
P300175-015	40
P300175-143	41

P300176-015	40
P300176-143	41
P300177-015	40
P300177-143	41
P300216-009	36
P300216-020	36
P300217-009	36
P300217-020	37
P300218-009	37
P300218-020	37
P300226-009	34
P300226-143	34
P300227-009	34
P300227-143	34
P300228-009	35
P300228-143	35
P300229-009	35
P300229-143	34
P300230-020	38
P300230-143	38
P300231-020	39
P300231-143	38
P300232-020	39
P300232-143	39
P300233-009	42
P300233-031	42
P300234-009	42
P300234-031	42
P300235-009	42
P300235-031	42
P300236-009	43
P300236-031	43
P300237-009	43
P300237-031	43
P300238-009	43
P300238-031	43
P350110-009	20
P350110-020	22
P350116-071	25
P350144-009	27
P350144-020	27
P350145-015	29
P350145-143	29
P350146-009	29
P350146-031	29
P350147-009	29
P350147-031	29
P3740-163	29

### P400000

P400115-031	16
P400115-104	18
P400153-071	24
P400154-071	25
P400175-031	17
P400175-104	19
P400187-031	17
P400187-104	19
P400190-009	27
P400190-020	26
P400193-031	28

### P500000

P500121-031	17
P500121-104	19
P500122-031	17
P500122-104	19
P500138-009	21
P500138-020	23
P500139-009	21
P500139-020	23
P500155-071	25
P500192-009	27
P500192-020	27
P500206-009	28
P500206-031	28
P500206-104	28
P540032-020	45
P540032-031	45
P540032-103	45
P550033-031	44
P550033-129	44
P560099-031	44
P560099-129	44
P560100-031	44
P560100-129	44

### P700000

P700008-000-27	54
P700008-000-30	54
P700009-000-27	54
P700009-000-30	54
P700010-000-27	54
P700010-000-30	54
P700011-000	55
P700012-000	55
P700013-000	55
P700014-000	55
P700015-000	55
P700016-000	55
P700017-000	55
P700018-000	55
P700019-000	55
P700020-031	54
P700021-031	54
P700022-000	55
P700023-031	54
P710045-009	21
P710045-020	23
P710071-030-30	30
P710071-159-30	30
P710072-009	30
P710072-031	30

### P800000

P810015-030-30	52
P8268-21	53
P8268-28	53
P8475-28	53
P860040-028	52
P860044-001	52
P868-31	53



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to [www.energystar.gov](http://www.energystar.gov) for specific product qualifications and list of certified products.



This marking indicates fixtures that have an **integrated LED** or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to [cacertappliances.enegy.ca.gov](http://cacertappliances.enegy.ca.gov)



Products comply with the California Appliance Efficiency Regulations. Certified products are listed on the appliance efficiency database found at [www.appliances.energy.ca.gov](http://www.appliances.energy.ca.gov).



**Dry location, indoor only** fans should only be used indoors. Even if an outdoor area or screened-in porch is covered, the motor and the blades can be affected when exposed to humidity.



**Damp location, indoor/outdoor** fans may be used indoors or outdoors under covered porches and should not be subjected to water spray or rain.



The ceiling fan products with this logo have passed the cUL requirements and are available for sale in Canada. These products include the additional safety features needed to comply with the regulations in Canada. Items with the icon are listed with NRCan.

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted. Bulbs (lamps) not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.





**PROGRESS LIGHTING**

701 Millennium Boulevard  
Greenville, South Carolina  
29607

[progresslighting.com](http://progresslighting.com)

