



B080603CHQR

by Wiegmann
Catalog ID: B080603CHQR

N12 JIC Continuous Hinge Quick Release 8X6X3 Carbon Steel - Gray

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided for mounting optional panels securely. External quick release latches secure cover. Standard continuous hinged secures cover. Grounding provisions provided.

Product Details

General

| | |
|---------------|---|
| Application | Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door with quick-release latching provide convenient access. Designed to provide protection from dust, dirt, oil, and water. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Hinged Cover |
| Finish Type | Textured |
| Latches Type | Quick-Release Latches |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Type | Wall Mount |
| Type | Enclosure |
| UPC | 786725331758 |

Dimensions

| | |
|--------------|--------|
| Actual Depth | 3.5 in |
| Depth | 4 in |
| Height | 8 in |
| Weight | 5.7 lb |
| Width | 6 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |