

by Wiegmann Catalog ID: BN4121005

N4 JIC Lift-Off Cover 12X10X5 Carbon Steel - Gray

Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams
ground smooth, less knockouts or holes. Closed cell oil resistant neoprene gasket. External mounting
plates, top and bottom of enclosure. Weldnuts are provided to secure optional panel. Stainless steel
screws and clamps on four sides of cover to assure water tight seal. Grounding provisions provided.
Optional back panels and terminal kits must be ordered separately.

Product Details

General

Application	Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection where equipment is hosed down, very wet, or in outdoor applications.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Lift Off
Finish Type	Textured
Latches Type	Clamps
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	External Mounting Plates
Mounting Type	Wall Mount
Туре	Enclosure
UPC	786725377404

Dimensions

Cubic Capacity	1440 cu.in
Depth	12 in
Height	12 in
Weight	12 lb
Width	10 in

Certifications and Compliance

Certified Listed	CSA IEC UL
Nema Rating	4
UL Listed	Yes