



HS225NK

by Wiegmann
Catalog ID: HS225NK

N1 Hinged Wireway - No Knockouts 2X2X60 Carbon Steel - Gray

- Bodies and covers are fabricated from 16 gauge steel. HS Series combination hinge/screw cover design offers easy access to open top for "lay-in" of wireway. Screws do not need to be removed to open top.

Product Details

General

Application	Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.
Color	Gray
Cover Type	Hinged Cover
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Polyester Powder
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Wireway
UPC	786725608959

Dimensions

Actual Height	2.500 in
Actual Width	2.500 in
Depth	60 in
Height	3 in
Weight	11.5 lb
Width	3 in

Certifications and Compliance

Certified Listed	• UL • CSA
Nema Rating	1
UL Listed	Yes