



L080890G

by Wiegmann
Catalog ID: L080890G

N1 90 Degree Elbow (Hinged-Cover/Screw-Cover Wireway) 8X8 Carbon Steel - Galvanized

- Galvanized 90 degrees elbow fitting.

Product Details

General

Accessory Type	Elbow
Application	For use with HS and S Series wireway.
Cover Type	Hinged/Screw Cover
Finish Type	Galvanized
Fitting Type	90 Degree Elbow
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Type	Fitting
UPC	786725852758

Dimensions

Actual Length	12.000 in
Depth	12 in
Height	9 in
Weight	8 lb
Width	12 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • CSA
Nema Rating	1
UL Listed	Yes