



## LJWL902A

by Wiegmann  
Catalog ID: LJWL902A

N1 Lay-In 90 Degree Elbow Top 2.5X2.5 Carbon Steel - Gray

- Carbon steel 90 degrees elbow top-opening fitting.  
Tamper Resistant- Self Grounding, Less Ears

## Product Details

### General

Accessory Type	Elbow
Application	Residential Receptacles
Color	Ivory Gray
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Finish Type	Polyester Powder
Fitting Type	90 Degree Top
Item Type	Traditional Duplex
Knockouts	No
Listings	UL, CSA
Material	Thermoplastic/Composite Carbon Steel
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Performance	<ul style="list-style-type: none"> <li>• Environmental - Operating temperature - -20°C to 60°C</li> <li>• Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only</li> </ul>
Type	Fitting
UPC	883778301315

### Dimensions

Actual Depth	7.125 in
Actual Height	7.500 in
Actual Length	7.125 in

Actual Width	4.250 in
Depth	7 in
Display Size	Standard Sized Product
Height	8 in
Width	4 in

#### Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

#### Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

#### Certifications and Compliance

Nema Rating	5-15R 1
UL Listed	Yes