



N412302412CGP

by Wiegmann
Catalog ID: N412302412CGP

N412 Single Door Ultimate with Gland Plate 30X24X12 Carbon Steel - Gray

Product Details

General

Application	For use where dirt, dust, oil, water and other contaminants are present. Typical applications include municipal infrastructure, water treatment plants and other industrial or commercial facilities.
Color	Gray
Material	Carbon Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	Ultimate
UPC	786725890736

Dimensions

Cubic Capacity	8640 cu.in
Depth	12 in
Height	30 in
Weight	64 lb
Width	24 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	NEMA 4