



N412603812CD

by Wiegmann
Catalog ID: N412603812CD

N412 Single Door Flanged Disconnect Ultimate 60X38X12 Carbon Steel - Gray

Product Details

General

Application	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers, available with or without Wiegmann-supplied defeater door handle and handle hardware.
Color	Gray
Construction	Continuously Welded Seams
Finish Type	Polyester Powder
Latches Type	3-Point
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725862795

Dimensions

Cubic Capacity	27360 cu.in
Depth	12 in
Height	60 in
Weight	220 lb
Width	38 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • CSA • IEC • UL
------------------	--

Nema Rating	4
UL Listed	Yes