



PBSS2A

by Wiegmann
Catalog ID: PBSS2A

N4X 30.5 MM 2 Pushbutton Enclosure 5.75X3.2X2.8 316 Stainless Steel

- Bodies and doors fabricated from 14 gauge 316 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

| | |
|----------------------------|---|
| Application | Designed to hold all standard brands of pushbuttons, switches, and pilot lights. Provide protection from dust, dirt, oil, and water. PBSS Series designed for areas where serious corrosion problems exist. |
| Construction | Continuously Welded Seams |
| Cover Type | Pushbutton |
| Knockouts | No |
| Listings | UL, CSA |
| Material | 316 Stainless Steel |
| Mounting Type | Wall Mount |
| Number of Holes | 2 |
| Pushbutton Number of Holes | 2 |
| Pushbutton Size | 30.5 MM |
| Series | PBSS-A |
| Type | Enclosure |
| UPC | 786725845620 |

Dimensions

| | |
|---------------|----------|
| Actual Depth | 2.81 in |
| Actual Height | 5.750 in |
| Actual Width | 3.250 in |
| Depth | 3 in |

| | |
|--------|------|
| Height | 6 in |
| Weight | 2 lb |
| Width | 3 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | 4X |
| UL Listed | Yes |