



PBXD1SS

by Wiegmann
Catalog ID: PBXD1SS

N4X 30.5 MM 1 Deep Pushbutton Enclosure 4X4X4.8 304 Stainless Steel

- Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously welded seams ground smooth. Closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Captivated cover screws thread into sealed wells. Standard "4-way" pushbutton holes accept all brands of oil-tight push buttons, switches, and pilot lights. Grounding provisions provided.

Product Details

General

Application	Designed to hold 30.5mm oil-tight pushbuttons, switches, and pilot lights. Provide protection against dirt, dust, oil, and water. Extra deep design accommodates additional contact blocks for pushbuttons.
Construction	Continuously Welded Seams
Cover Type	Pushbutton
Knockouts	No
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Holes	1
Pushbutton Number of Holes	1
Pushbutton Size	30.5 MM
Series	PBXD-SS
Type	Enclosure
UPC	786725845682

Dimensions

Actual Depth	4.810 in
Actual Length	4.81 in
Depth	5 in
Height	4 in

Weight	2.45 lb
Width	4 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes